

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: METALUX

Report Number: P387915

Luminaire Tested: **22CZ2-39-SQR-UNV-L935-CD1-SDWPD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P387915
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-542-6)
Test Lab: INNOVATIONS CENTER(G3)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 22CZ2-39-SQR-UNV-L935-CD1-SDWPD1-U
Description: 2x2 CRUZE LED TROFFER WITH 3500K, 90 LEDS, AND SQUARE LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3123.8 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.31 / 1.37
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct


Input Watts (W): 34.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P387915

CATALOG NUMBER: 22CZ2-39-SQR-UNV-L935-CD1-SDWPD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P387915

CATALOG NUMBER: 22CZ2-39-SQR-UNV-L935-CD1-SDWPD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	99	95	106	101	97	94	97	94	91	93	91	88	90	87	85	83
2	99	90	83	77	96	88	82	76	85	79	75	81	77	73	78	75	71	69
3	90	79	71	64	87	77	70	63	74	68	62	72	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	64	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	43
6	70	56	47	41	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2936	2936	2936
5°	2916	2944	2960
10°	2889	2941	2974
15°	2842	2929	2982
20°	2781	2908	2989
25°	2703	2879	2985
30°	2612	2843	2981
35°	2518	2801	2990
40°	2412	2766	3000
45°	2296	2731	3024
50°	2197	2706	3048
55°	2080	2685	3096
60°	1971	2673	3128
65°	1841	2653	3153
70°	1692	2613	3196
75°	1526	2543	3083
80°	1309	2252	2320
85°	1053	1328	1053



TEST NUMBER: P387915

CATALOG NUMBER: 22CZ2-39-SQR-UNV-L935-CD1-SDWPD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.5	3.3
10°-20°	295.8	9.5
20°-30°	444.2	14.2
30°-40°	529.8	17.0
40°-50°	547.8	17.5
50°-60°	503.6	16.1
60°-70°	400.9	12.8
70°-80°	244.9	7.8
80°-90°	53.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	843.5	27.0
0°-40°	1373.3	44.0
0°-60°	2424.7	77.6
0°-90°	3123.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3123.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1091	1091	1091	1091	1091	
5°	1079	1082	1090	1094	1096	102
15°	1020	1032	1051	1066	1070	287
25°	910	933	970	996	1005	419
35°	766	799	852	897	910	478
45°	603	646	718	775	795	467
55°	443	492	572	638	660	397
65°	289	338	417	474	495	286
75°	147	190	245	288	296	156
85°	34	42	43	37	34	39
90°	0	0	0	0	0	



TEST NUMBER: P387915

CATALOG NUMBER: 22CZ2-39-SQR-UNV-L935-CD1-SDWPD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1085.3	1086.8	1091.2	1094.2	1094.2
5°	1079.4	1082.3	1089.7	1094.2	1095.7
7.5°	1070.5	1074.9	1085.3	1091.2	1092.7
10°	1057.1	1063.0	1076.4	1085.3	1088.3
12.5°	1040.8	1049.7	1066.0	1077.9	1080.8
15°	1020.1	1031.9	1051.2	1066.0	1070.5
17.5°	996.3	1011.2	1034.9	1052.7	1058.6
20°	971.1	986.0	1015.6	1036.4	1043.8
22.5°	941.5	960.7	994.8	1018.6	1024.5
25°	910.3	932.6	969.6	996.3	1005.2
27.5°	876.2	902.9	943.0	975.6	983.0
30°	840.7	868.8	914.8	950.4	959.3
32.5°	803.6	836.2	885.1	925.2	937.0
35°	766.5	799.1	852.5	897.0	910.3
37.5°	723.5	762.1	821.4	867.3	883.6
40°	686.5	723.5	787.3	837.7	854.0
42.5°	644.9	685.0	751.7	806.6	825.8
45°	603.4	646.4	717.6	775.4	794.7
47.5°	564.9	607.9	682.0	742.8	762.1
50°	524.9	569.3	646.4	708.7	728.0
52.5°	481.9	530.8	610.8	673.1	695.4
55°	443.3	492.2	572.3	637.5	659.8
57.5°	403.3	453.7	536.7	599.0	619.7
60°	366.2	415.1	496.7	557.5	581.2
62.5°	326.2	376.6	456.7	516.0	538.2
65°	289.1	338.0	416.6	474.4	495.2
67.5°	252.0	301.0	375.1	430.0	453.7
70°	215.0	263.9	332.1	385.5	406.2
72.5°	182.4	225.4	290.6	339.5	358.8
75°	146.8	189.8	244.6	287.6	296.5
77.5°	114.2	152.7	198.7	217.9	220.9
80°	84.5	114.2	145.3	149.7	149.7
82.5°	56.3	78.6	90.4	91.9	90.4
85°	34.1	41.5	43.0	37.1	34.1
87.5°	11.9	11.9	7.4	4.4	1.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)