

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: METALUX

Report Number: P295050

Luminaire Tested: **24CZ2-50-HRP-UNV-L950-CD1-U**

Issue Date: 12/2/2019

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P295050  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)  
Test Lab: INNOVATIONS CENTER(G3)  
Issue Date: 12/2/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: 24CZ2-50-HRP-UNV-L950-CD1-U  
Description: 2'x4' TROFFER LED MODULE, HIGH EFFICIENCY ROUND PERF. LENS  
Light Source: (84) 5000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3532.5 lumens  
Efficiency: N/A  
Efficacy: 72.7 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 48.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P295050  
CATALOG NUMBER: 24CZ2-50-HRP-UNV-L950-CD1-U

### Luminous Intensity Polar Plot





TEST NUMBER: P295050

CATALOG NUMBER: 24CZ2-50-HRP-UNV-L950-CD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1542	1542	1542
5°	1544	1538	1544
10°	1540	1538	1548
15°	1531	1535	1549
20°	1520	1531	1552
25°	1502	1524	1554
30°	1484	1519	1560
35°	1460	1511	1562
40°	1434	1501	1577
45°	1401	1500	1601
50°	1356	1498	1644
55°	1308	1509	1703
60°	1234	1532	1779
65°	1139	1568	1879
70°	995	1623	2001
75°	807	1707	2068
80°	596	1673	1673
85°	457	1233	1392



TEST NUMBER: P295050

CATALOG NUMBER: 24CZ2-50-HRP-UNV-L950-CD1-U

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.6	3.1
10°-20°	311.8	8.8
20°-30°	474.6	13.4
30°-40°	576.3	16.3
40°-50°	608.9	17.2
50°-60°	574.6	16.3
60°-70°	477.7	13.5
70°-80°	314.3	8.9
80°-90°	85.7	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	895.0	25.3
0°-40°	1471.3	41.7
0°-60°	2654.7	75.2
0°-90°	3532.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3532.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1146	1146	1146	1146	1146	
5°	1143	1143	1139	1143	1143	109
15°	1099	1100	1102	1112	1112	310
25°	1012	1017	1026	1044	1047	467
35°	889	899	920	944	951	556
45°	736	751	788	827	842	567
55°	558	581	643	704	726	497
65°	358	399	492	565	590	354
75°	155	226	328	389	398	167
85°	30	65	80	89	90	36
90°	0	0	0	0	0	



TEST NUMBER: P295050

CATALOG NUMBER: 24CZ2-50-HRP-UNV-L950-CD1-U

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1146.1	1146.1	1146.1	1146.1	1146.1
2.5°	1147.6	1146.1	1140.2	1146.1	1146.1
5°	1143.1	1143.1	1138.7	1143.1	1143.1
7.5°	1135.7	1135.7	1132.8	1138.7	1138.7
10°	1126.9	1126.9	1125.4	1132.8	1132.8
12.5°	1113.6	1115.0	1113.6	1122.4	1122.4
15°	1098.8	1100.3	1101.7	1112.1	1112.1
17.5°	1079.6	1082.5	1085.5	1097.3	1098.8
20°	1061.8	1063.3	1069.2	1082.5	1084.0
22.5°	1038.1	1042.6	1050.0	1063.3	1067.7
25°	1011.5	1017.4	1026.3	1044.1	1047.0
27.5°	986.4	990.8	1002.7	1021.9	1027.8
30°	955.3	962.7	977.5	996.7	1004.1
32.5°	925.8	933.1	950.9	971.6	977.5
35°	888.8	899.1	919.8	943.5	950.9
37.5°	853.3	863.6	888.8	915.4	924.3
40°	816.3	828.1	854.8	885.8	897.7
42.5°	776.4	792.7	822.2	856.2	869.6
45°	736.5	751.2	788.2	826.7	841.5
47.5°	693.6	711.3	751.2	797.1	814.8
50°	647.7	669.9	715.8	766.0	785.3
52.5°	601.9	627.0	678.8	735.0	755.7
55°	557.5	581.2	643.3	703.9	726.1
57.5°	508.7	538.3	606.3	671.4	693.6
60°	458.4	491.0	569.4	637.4	661.0
62.5°	408.2	445.1	533.9	601.9	627.0
65°	357.9	399.3	492.5	564.9	590.1
67.5°	309.1	354.9	454.0	526.5	551.6
70°	252.9	310.6	412.6	483.6	508.7
72.5°	201.1	267.7	372.7	439.2	461.4
75°	155.3	226.3	328.3	388.9	397.8
77.5°	113.9	184.9	282.5	303.2	304.6
80°	76.9	147.9	215.9	213.0	215.9
82.5°	50.3	110.9	136.1	152.3	153.8
85°	29.6	65.1	79.9	88.7	90.2
87.5°	14.8	22.2	28.1	29.6	32.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)