

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P274777

Luminaire Tested: **24CZ2-30HE-RDP-UNV-L940-CD1-U**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P274777  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: 24CZ2-30HE-RDP-UNV-L940-CD1-U  
Description: 2'x4' TROFFER LED MODULE,SMOOTH LENS WITH INSERT, 90CRI  
Light Source: (168) 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: Sample No.   Condition   Description

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1731.0 lumens  
Efficiency: N/A  
Efficacy: 77.3 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 22.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P274777

CATALOG NUMBER: 24CZ2-30HE-RDP-UNV-L940-CD1-U

### Luminous Intensity Polar Plot





TEST NUMBER: P274777

CATALOG NUMBER: 24CZ2-30HE-RDP-UNV-L940-CD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	732	732	732
5°	735	731	734
10°	733	731	734
15°	732	731	735
20°	727	730	738
25°	724	732	739
30°	718	730	742
35°	711	728	745
40°	703	727	754
45°	691	727	771
50°	676	731	794
55°	659	743	830
60°	631	758	876
65°	591	784	929
70°	537	821	1000
75°	455	866	1044
80°	360	872	845
85°	266	662	743



TEST NUMBER: P274777

CATALOG NUMBER: 24CZ2-30HE-RDP-UNV-L940-CD1-U

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.6	3.0
10°-20°	148.6	8.6
20°-30°	227.3	13.1
30°-40°	277.8	16.0
40°-50°	296.1	17.1
50°-60°	283.1	16.4
60°-70°	239.8	13.9
70°-80°	161.2	9.3
80°-90°	45.5	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	427.5	24.7
0°-40°	705.3	40.7
0°-60°	1284.5	74.2
0°-90°	1731.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1731.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	544	544	544	544	544	
5°	544	544	541	544	544	52
15°	526	526	525	529	528	148
25°	488	489	493	497	498	225
35°	433	436	443	452	453	271
45°	363	369	382	398	405	280
55°	281	291	317	342	354	250
65°	186	204	246	279	292	184
75°	88	119	167	195	201	94
85°	17	35	43	46	48	21
90°	0	0	0	0	0	



TEST NUMBER: P274777

CATALOG NUMBER: 24CZ2-30HE-RDP-UNV-L940-CD1-U

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	544.4	544.4	544.4	544.4	544.4
2.5°	545.2	545.2	542.6	544.4	544.4
5°	544.4	543.5	540.9	543.5	543.5
7.5°	541.8	540.9	539.2	541.8	540.9
10°	536.6	536.6	534.9	537.5	537.5
12.5°	532.3	531.5	530.6	534.0	533.2
15°	525.5	525.5	524.6	528.9	528.0
17.5°	516.9	517.7	518.6	522.0	522.9
20°	507.4	509.1	510.0	515.2	515.2
22.5°	498.8	499.7	501.4	506.6	506.6
25°	487.7	489.4	492.8	497.1	498.0
27.5°	476.5	477.4	481.7	487.7	488.5
30°	461.9	464.5	469.7	476.5	477.4
32.5°	449.0	451.6	457.6	464.5	466.2
35°	432.7	436.2	443.0	451.6	453.3
37.5°	418.1	420.7	429.3	438.7	441.3
40°	400.1	405.3	413.8	425.0	429.3
42.5°	382.1	387.2	397.5	412.1	417.3
45°	363.2	369.2	382.1	398.4	405.3
47.5°	344.3	351.2	365.8	384.7	392.4
50°	322.8	331.4	349.4	370.9	379.5
52.5°	302.2	312.5	332.3	356.3	367.5
55°	280.8	291.1	316.8	341.7	353.7
57.5°	256.7	270.5	298.8	327.1	340.0
60°	234.4	247.3	281.6	312.5	325.4
62.5°	210.4	227.5	264.4	297.1	310.0
65°	185.5	204.3	246.4	279.0	291.9
67.5°	163.1	183.7	228.4	261.0	273.9
70°	136.5	162.3	208.6	241.3	254.1
72.5°	111.6	140.0	188.0	219.8	231.8
75°	87.6	119.3	166.6	194.9	200.9
77.5°	65.3	98.7	144.2	156.3	152.0
80°	46.4	79.0	112.5	106.5	109.0
82.5°	30.1	60.1	69.5	79.0	81.6
85°	17.2	35.2	42.9	46.4	48.1
87.5°	7.7	12.9	17.2	17.2	16.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)