

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P391300

Luminaire Tested: **24CZ2-35VHE-RDP-UNV-L940-CD1-SWPD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P391300
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATIONS CENTER(G3)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-35VHE-RDP-UNV-L940-CD1-SWPD1-U
Description: 2x4 CRUZE LED TROFFER WITH 4000K, 90 LEDS, AND RDP LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2000.6 lumens
Efficiency: N/A
Efficacy: 87.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 22.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P391300

CATALOG NUMBER: 24CZ2-35VHE-RDP-UNV-L940-CD1-SWPD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P391300

CATALOG NUMBER: 24CZ2-35VHE-RDP-UNV-L940-CD1-SWPD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	68	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	846	846	846
5°	850	844	848
10°	847	845	849
15°	846	845	850
20°	840	844	853
25°	837	846	854
30°	829	843	857
35°	821	841	861
40°	812	840	872
45°	799	840	891
50°	781	845	918
55°	761	859	959
60°	729	876	1012
65°	682	907	1074
70°	621	948	1155
75°	526	1001	1207
80°	415	1007	976
85°	306	766	858



TEST NUMBER: P391300

CATALOG NUMBER: 24CZ2-35VHE-RDP-UNV-L940-CD1-SWPD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.7	3.0
10°-20°	171.8	8.6
20°-30°	262.6	13.1
30°-40°	321.1	16.0
40°-50°	342.2	17.1
50°-60°	327.2	16.4
60°-70°	277.2	13.9
70°-80°	186.3	9.3
80°-90°	52.5	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	494.1	24.7
0°-40°	815.2	40.7
0°-60°	1484.6	74.2
0°-90°	2000.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2000.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	629	629	629	629	629	
5°	629	628	625	628	628	60
15°	607	607	606	611	610	171
25°	564	566	570	575	576	260
35°	500	504	512	522	524	313
45°	420	427	442	460	468	324
55°	324	336	366	395	409	289
65°	214	236	285	322	337	213
75°	101	138	192	225	232	108
85°	20	41	50	54	56	25
90°	0	0	0	0	0	



TEST NUMBER: P391300

CATALOG NUMBER: 24CZ2-35VHE-RDP-UNV-L940-CD1-SWPD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	629.1	629.1	629.1	629.1	629.1
2.5°	630.1	630.1	627.1	629.1	629.1
5°	629.1	628.1	625.2	628.1	628.1
7.5°	626.2	625.2	623.2	626.2	625.2
10°	620.2	620.2	618.2	621.2	621.2
12.5°	615.2	614.2	613.3	617.2	616.2
15°	607.3	607.3	606.3	611.3	610.3
17.5°	597.4	598.4	599.4	603.3	604.3
20°	586.5	588.4	589.4	595.4	595.4
22.5°	576.5	577.5	579.5	585.5	585.5
25°	563.6	565.6	569.6	574.6	575.5
27.5°	550.7	551.7	556.7	563.6	564.6
30°	533.9	536.8	542.8	550.7	551.7
32.5°	519.0	522.0	528.9	536.8	538.8
35°	500.1	504.1	512.0	522.0	523.9
37.5°	483.3	486.2	496.2	507.1	510.1
40°	462.4	468.4	478.3	491.2	496.2
42.5°	441.6	447.5	459.4	476.3	482.3
45°	419.8	426.7	441.6	460.4	468.4
47.5°	397.9	405.9	422.7	444.6	453.5
50°	373.1	383.0	403.9	428.7	438.6
52.5°	349.3	361.2	384.0	411.8	424.7
55°	324.5	336.4	366.2	394.9	408.8
57.5°	296.7	312.6	345.3	378.1	393.0
60°	270.9	285.8	325.5	361.2	376.1
62.5°	243.1	263.0	305.6	343.3	358.2
65°	214.3	236.2	284.8	322.5	337.4
67.5°	188.5	212.4	264.0	301.7	316.6
70°	157.8	187.5	241.1	278.8	293.7
72.5°	129.0	161.7	217.3	254.0	267.9
75°	101.2	137.9	192.5	225.3	232.2
77.5°	75.4	114.1	166.7	180.6	175.6
80°	53.6	91.3	130.0	123.0	126.0
82.5°	34.7	69.5	80.4	91.3	94.3
85°	19.8	40.7	49.6	53.6	55.6
87.5°	8.9	14.9	19.8	19.8	18.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)