

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P391344

Luminaire Tested: **24CZ2-40VHE-RDP-UNV-L935-CD1-SDWPD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P391344
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATIONS CENTER(G3)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-40VHE-RDP-UNV-L935-CD1-SDWPD1-U
Description: 2x4 CRUZE LED TROFFER WITH 3500K, 90 LEDS, AND RDP LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2242.5 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 26.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P391344

CATALOG NUMBER: 24CZ2-40VHE-RDP-UNV-L935-CD1-SDWPD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P391344

CATALOG NUMBER: 24CZ2-40VHE-RDP-UNV-L935-CD1-SDWPD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	949	949	949
5°	952	947	951
10°	950	947	951
15°	948	947	953
20°	941	946	956
25°	938	948	958
30°	930	945	961
35°	921	943	965
40°	910	942	977
45°	895	942	999
50°	875	948	1029
55°	853	963	1075
60°	817	982	1135
65°	765	1016	1204
70°	696	1063	1295
75°	590	1122	1353
80°	466	1129	1095
85°	343	858	962



TEST NUMBER: P391344

CATALOG NUMBER: 24CZ2-40VHE-RDP-UNV-L935-CD1-SDWPD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.9	3.0
10°-20°	192.5	8.6
20°-30°	294.4	13.1
30°-40°	359.9	16.0
40°-50°	383.6	17.1
50°-60°	366.8	16.4
60°-70°	310.7	13.9
70°-80°	208.8	9.3
80°-90°	58.9	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	553.8	24.7
0°-40°	913.7	40.7
0°-60°	1664.1	74.2
0°-90°	2242.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2242.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	705	705	705	705	705	
5°	705	704	701	704	704	67
15°	681	681	680	685	684	192
25°	632	634	638	644	645	291
35°	561	565	574	585	587	351
45°	470	478	495	516	525	363
55°	364	377	410	443	458	324
65°	240	265	319	362	378	239
75°	114	155	216	252	260	121
85°	22	46	56	60	62	28
90°	0	0	0	0	0	



TEST NUMBER: P391344

CATALOG NUMBER: 24CZ2-40VHE-RDP-UNV-L935-CD1-SDWPD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	705.2	705.2	705.2	705.2	705.2
2.5°	706.3	706.3	703.0	705.2	705.2
5°	705.2	704.1	700.8	704.1	704.1
7.5°	701.9	700.8	698.5	701.9	700.8
10°	695.2	695.2	693.0	696.3	696.3
12.5°	689.6	688.5	687.4	691.9	690.7
15°	680.7	680.7	679.6	685.2	684.1
17.5°	669.6	670.7	671.8	676.3	677.4
20°	657.4	659.6	660.7	667.4	667.4
22.5°	646.2	647.4	649.6	656.3	656.3
25°	631.8	634.0	638.5	644.0	645.1
27.5°	617.3	618.4	624.0	631.8	632.9
30°	598.4	601.8	608.4	617.3	618.4
32.5°	581.7	585.1	592.9	601.8	604.0
35°	560.6	565.1	574.0	585.1	587.3
37.5°	541.7	545.0	556.2	568.4	571.7
40°	518.3	525.0	536.1	550.6	556.2
42.5°	495.0	501.7	515.0	533.9	540.6
45°	470.5	478.3	495.0	516.1	525.0
47.5°	446.0	454.9	473.8	498.3	508.3
50°	418.2	429.4	452.7	480.5	491.6
52.5°	391.5	404.9	430.5	461.6	476.1
55°	363.7	377.1	410.4	442.7	458.3
57.5°	332.6	350.4	387.1	423.8	440.5
60°	303.7	320.3	364.8	404.9	421.6
62.5°	272.5	294.8	342.6	384.9	401.5
65°	240.3	264.7	319.2	361.5	378.2
67.5°	211.3	238.0	295.9	338.1	354.8
70°	176.9	210.2	270.3	312.6	329.2
72.5°	144.6	181.3	243.6	284.8	300.3
75°	113.5	154.6	215.8	252.5	260.3
77.5°	84.5	127.9	186.9	202.4	196.9
80°	60.1	102.3	145.7	137.9	141.3
82.5°	38.9	77.9	90.1	102.3	105.7
85°	22.2	45.6	55.6	60.1	62.3
87.5°	10.0	16.7	22.2	22.2	21.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)