

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P391346

Luminaire Tested: **24CZ2-40VHE-RDP-UNV-L935-CD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P391346
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATIONS CENTER(G3)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-40VHE-RDP-UNV-L935-CD1-U
Description: 2x4 CRUZE LED TROFFER WITH 3500K, 90 LEDS, AND RDP LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2298.4 lumens
Efficiency: N/A
Efficacy: 87.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 26.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P391346

CATALOG NUMBER: 24CZ2-40VHE-RDP-UNV-L935-CD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P391346

CATALOG NUMBER: 24CZ2-40VHE-RDP-UNV-L935-CD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	973	973	973
5°	976	970	975
10°	973	970	975
15°	972	970	977
20°	965	970	979
25°	961	972	982
30°	953	969	985
35°	944	966	989
40°	933	965	1001
45°	918	965	1024
50°	897	971	1055
55°	875	987	1102
60°	837	1006	1163
65°	784	1042	1234
70°	713	1090	1327
75°	605	1150	1387
80°	477	1157	1122
85°	352	880	985



TEST NUMBER: P391346

CATALOG NUMBER: 24CZ2-40VHE-RDP-UNV-L935-CD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.6	3.0
10°-20°	197.3	8.6
20°-30°	301.7	13.1
30°-40°	368.9	16.0
40°-50°	393.2	17.1
50°-60°	375.9	16.4
60°-70°	318.4	13.9
70°-80°	214.0	9.3
80°-90°	60.4	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	567.6	24.7
0°-40°	936.5	40.7
0°-60°	1705.6	74.2
0°-90°	2298.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2298.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	723	723	723	723	723	
5°	723	722	718	722	722	69
15°	698	698	697	702	701	197
25°	648	650	654	660	661	298
35°	575	579	588	600	602	360
45°	482	490	507	529	538	372
55°	373	386	421	454	470	332
65°	246	271	327	370	388	244
75°	116	158	221	259	267	125
85°	23	47	57	62	64	28
90°	0	0	0	0	0	



TEST NUMBER: P391346

CATALOG NUMBER: 24CZ2-40VHE-RDP-UNV-L935-CD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	722.8	722.8	722.8	722.8	722.8
2.5°	723.9	723.9	720.5	722.8	722.8
5°	722.8	721.6	718.2	721.6	721.6
7.5°	719.4	718.2	715.9	719.4	718.2
10°	712.5	712.5	710.2	713.7	713.7
12.5°	706.8	705.7	704.5	709.1	708.0
15°	697.7	697.7	696.6	702.3	701.1
17.5°	686.3	687.4	688.6	693.1	694.3
20°	673.8	676.0	677.2	684.0	684.0
22.5°	662.4	663.5	665.8	672.6	672.6
25°	647.5	649.8	654.4	660.1	661.2
27.5°	632.7	633.9	639.6	647.5	648.7
30°	613.3	616.8	623.6	632.7	633.9
32.5°	596.2	599.7	607.6	616.8	619.0
35°	574.6	579.1	588.3	599.7	601.9
37.5°	555.2	558.6	570.0	582.6	586.0
40°	531.3	538.1	549.5	564.3	570.0
42.5°	507.3	514.2	527.8	547.2	554.1
45°	482.2	490.2	507.3	529.0	538.1
47.5°	457.2	466.3	485.7	510.7	521.0
50°	428.7	440.1	464.0	492.5	503.9
52.5°	401.3	415.0	441.2	473.1	487.9
55°	372.8	386.5	420.7	453.7	469.7
57.5°	340.9	359.1	396.7	434.4	451.5
60°	311.2	328.3	373.9	415.0	432.1
62.5°	279.3	302.1	351.1	394.5	411.6
65°	246.2	271.3	327.2	370.5	387.6
67.5°	216.6	244.0	303.2	346.6	363.7
70°	181.3	215.5	277.0	320.3	337.4
72.5°	148.2	185.8	249.7	291.8	307.8
75°	116.3	158.5	221.2	258.8	266.8
77.5°	86.6	131.1	191.5	207.5	201.8
80°	61.6	104.9	149.3	141.4	144.8
82.5°	39.9	79.8	92.3	104.9	108.3
85°	22.8	46.7	57.0	61.6	63.8
87.5°	10.3	17.1	22.8	22.8	21.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)