

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P391392

Luminaire Tested: **24CZ2-45VHE-RDP-UNV-L935-CD1-SDWPD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P391392
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATIONS CENTER(G3)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-45VHE-RDP-UNV-L935-CD1-SDWPD1-U
Description: 2x4 CRUZE LED TROFFER WITH 3500K, 90 LEDS, AND RDP LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2529.4 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 29.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P391392

CATALOG NUMBER: 24CZ2-45VHE-RDP-UNV-L935-CD1-SDWPD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P391392

CATALOG NUMBER: 24CZ2-45VHE-RDP-UNV-L935-CD1-SDWPD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1070	1070	1070
5°	1074	1068	1073
10°	1071	1068	1073
15°	1070	1068	1075
20°	1062	1067	1078
25°	1058	1069	1080
30°	1049	1066	1084
35°	1039	1063	1088
40°	1027	1062	1102
45°	1010	1062	1127
50°	987	1069	1161
55°	962	1086	1213
60°	922	1107	1280
65°	863	1146	1358
70°	785	1199	1461
75°	665	1265	1526
80°	525	1274	1234
85°	387	968	1085



TEST NUMBER: P391392

CATALOG NUMBER: 24CZ2-45VHE-RDP-UNV-L935-CD1-SDWPD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.5	3.0
10°-20°	217.2	8.6
20°-30°	332.1	13.1
30°-40°	406.0	16.0
40°-50°	432.7	17.1
50°-60°	413.7	16.4
60°-70°	350.4	13.9
70°-80°	235.5	9.3
80°-90°	66.4	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	624.7	24.7
0°-40°	1030.6	40.7
0°-60°	1877.0	74.2
0°-90°	2529.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2529.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	795	795	795	795	795	
5°	795	794	790	794	794	76
15°	768	768	767	773	772	216
25°	713	715	720	726	728	328
35°	632	637	647	660	662	396
45°	531	540	558	582	592	409
55°	410	425	463	499	517	365
65°	271	299	360	408	427	269
75°	128	174	243	285	294	137
85°	25	51	63	68	70	31
90°	0	0	0	0	0	



TEST NUMBER: P391392

CATALOG NUMBER: 24CZ2-45VHE-RDP-UNV-L935-CD1-SDWPD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	795.4	795.4	795.4	795.4	795.4
2.5°	796.7	796.7	792.9	795.4	795.4
5°	795.4	794.2	790.4	794.2	794.2
7.5°	791.7	790.4	787.9	791.7	790.4
10°	784.1	784.1	781.6	785.4	785.4
12.5°	777.9	776.6	775.4	780.4	779.1
15°	767.8	767.8	766.6	772.8	771.6
17.5°	755.3	756.5	757.8	762.8	764.1
20°	741.5	744.0	745.2	752.8	752.8
22.5°	728.9	730.2	732.7	740.2	740.2
25°	712.6	715.1	720.1	726.4	727.7
27.5°	696.3	697.6	703.8	712.6	713.9
30°	675.0	678.7	686.3	696.3	697.6
32.5°	656.2	659.9	668.7	678.7	681.3
35°	632.3	637.3	647.4	659.9	662.4
37.5°	611.0	614.8	627.3	641.1	644.9
40°	584.6	592.2	604.7	621.0	627.3
42.5°	558.3	565.8	580.9	602.2	609.7
45°	530.7	539.5	558.3	582.1	592.2
47.5°	503.1	513.1	534.5	562.1	573.4
50°	471.7	484.3	510.6	542.0	554.5
52.5°	441.6	456.7	485.5	520.7	537.0
55°	410.3	425.3	463.0	499.3	516.9
57.5°	375.1	395.2	436.6	478.0	496.8
60°	342.5	361.3	411.5	456.7	475.5
62.5°	307.4	332.5	386.4	434.1	452.9
65°	271.0	298.6	360.1	407.7	426.6
67.5°	238.4	268.5	333.7	381.4	400.2
70°	199.5	237.1	304.9	352.5	371.4
72.5°	163.1	204.5	274.8	321.2	338.7
75°	128.0	174.4	243.4	284.8	293.6
77.5°	95.4	144.3	210.8	228.3	222.1
80°	67.7	115.4	164.4	155.6	159.3
82.5°	43.9	87.8	101.6	115.4	119.2
85°	25.1	51.4	62.7	67.7	70.3
87.5°	11.3	18.8	25.1	25.1	23.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)