

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P391592

Luminaire Tested: **24CZ2-65VHE-RDP-UNV-L950-CD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P391592
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATIONS CENTER(G3)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-65VHE-RDP-UNV-L950-CD1-U
Description: 2x4 CRUZE LED TROFFER WITH 5000K, 90 LEDS, AND RDP LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4003.4 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 42.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P391592

CATALOG NUMBER: 24CZ2-65VHE-RDP-UNV-L950-CD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P391592

CATALOG NUMBER: 24CZ2-65VHE-RDP-UNV-L950-CD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	68	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1694	1694	1694
5°	1700	1690	1698
10°	1696	1690	1698
15°	1693	1690	1701
20°	1680	1689	1706
25°	1674	1692	1710
30°	1660	1688	1715
35°	1644	1683	1722
40°	1625	1681	1744
45°	1598	1682	1784
50°	1563	1692	1837
55°	1523	1719	1919
60°	1459	1753	2025
65°	1365	1814	2149
70°	1242	1898	2312
75°	1053	2002	2416
80°	831	2015	1954
85°	613	1533	1717



TEST NUMBER: P391592

CATALOG NUMBER: 24CZ2-65VHE-RDP-UNV-L950-CD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.4	3.0
10°-20°	343.7	8.6
20°-30°	525.6	13.1
30°-40°	642.5	16.0
40°-50°	684.8	17.1
50°-60°	654.8	16.4
60°-70°	554.7	13.9
70°-80°	372.8	9.3
80°-90°	105.1	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	988.7	24.7
0°-40°	1631.2	40.7
0°-60°	2970.8	74.2
0°-90°	4003.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4003.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1259	1259	1259	1259	1259	
5°	1259	1257	1251	1257	1257	120
15°	1215	1215	1213	1223	1221	343
25°	1128	1132	1140	1150	1152	520
35°	1001	1009	1025	1044	1048	627
45°	840	854	884	921	937	648
55°	649	673	733	790	818	578
65°	429	473	570	645	675	426
75°	202	276	385	451	465	217
85°	40	81	99	107	111	49
90°	0	0	0	0	0	



TEST NUMBER: P391592

CATALOG NUMBER: 24CZ2-65VHE-RDP-UNV-L950-CD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1259.0	1259.0	1259.0	1259.0	1259.0
2.5°	1260.9	1260.9	1255.0	1259.0	1259.0
5°	1259.0	1257.0	1251.0	1257.0	1257.0
7.5°	1253.0	1251.0	1247.0	1253.0	1251.0
10°	1241.1	1241.1	1237.1	1243.1	1243.1
12.5°	1231.2	1229.2	1227.2	1235.1	1233.1
15°	1215.3	1215.3	1213.3	1223.2	1221.2
17.5°	1195.4	1197.4	1199.4	1207.3	1209.3
20°	1173.6	1177.5	1179.5	1191.4	1191.4
22.5°	1153.7	1155.7	1159.7	1171.6	1171.6
25°	1127.9	1131.9	1139.8	1149.7	1151.7
27.5°	1102.1	1104.1	1114.0	1127.9	1129.9
30°	1068.3	1074.3	1086.2	1102.1	1104.1
32.5°	1038.5	1044.5	1058.4	1074.3	1078.3
35°	1000.8	1008.8	1024.6	1044.5	1048.5
37.5°	967.1	973.0	992.9	1014.7	1020.7
40°	925.4	937.3	957.1	982.9	992.9
42.5°	883.7	895.6	919.4	953.2	965.1
45°	840.0	853.9	883.7	921.4	937.3
47.5°	796.3	812.2	845.9	889.6	907.5
50°	746.6	766.5	808.2	857.8	877.7
52.5°	699.0	722.8	768.5	824.1	849.9
55°	649.3	673.2	732.7	790.3	818.1
57.5°	593.7	625.5	691.0	756.6	786.4
60°	542.1	571.9	651.3	722.8	752.6
62.5°	486.5	526.2	611.6	687.1	716.8
65°	428.9	472.6	569.9	645.4	675.1
67.5°	377.3	424.9	528.2	603.7	633.4
70°	315.7	375.3	482.5	558.0	587.8
72.5°	258.1	323.7	434.9	508.3	536.1
75°	202.5	276.0	385.2	450.8	464.7
77.5°	150.9	228.4	333.6	361.4	351.5
80°	107.2	182.7	260.1	246.2	252.2
82.5°	69.5	139.0	160.8	182.7	188.6
85°	39.7	81.4	99.3	107.2	111.2
87.5°	17.9	29.8	39.7	39.7	37.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)