

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: METALUX

Report Number: P391775

Luminaire Tested: **24CZ2-85VHE-RDP-UNV-L930-CD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P391775
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATIONS CENTER(G3)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-85VHE-RDP-UNV-L930-CD1-U
Description: 2x4 CRUZE LED TROFFER WITH 3000K, 90 LEDS, AND RDP LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4772.3 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 57.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P391775

CATALOG NUMBER: 24CZ2-85VHE-RDP-UNV-L930-CD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P391775

CATALOG NUMBER: 24CZ2-85VHE-RDP-UNV-L930-CD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89		92	89	87		88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72		80	75	71		77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60		70	64	59		67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51		62	55	50		59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43		55	48	43		53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38		50	43	37		48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33		45	38	33		44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30		41	34	29		40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27		38	31	26		37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24		35	29	24		34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2019	2019	2019
5°	2027	2014	2024
10°	2021	2015	2025
15°	2018	2015	2028
20°	2003	2013	2034
25°	1996	2017	2038
30°	1979	2012	2045
35°	1960	2006	2053
40°	1937	2004	2079
45°	1905	2004	2126
50°	1863	2017	2190
55°	1816	2049	2288
60°	1739	2089	2414
65°	1628	2163	2562
70°	1481	2263	2757
75°	1255	2387	2879
80°	990	2403	2329
85°	730	1828	2047



TEST NUMBER: P391775

CATALOG NUMBER: 24CZ2-85VHE-RDP-UNV-L930-CD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.4	3.0
10°-20°	409.7	8.6
20°-30°	626.5	13.1
30°-40°	765.9	16.0
40°-50°	816.3	17.1
50°-60°	780.5	16.4
60°-70°	661.2	13.9
70°-80°	444.4	9.3
80°-90°	125.3	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1178.6	24.7
0°-40°	1944.5	40.7
0°-60°	3541.4	74.2
0°-90°	4772.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4772.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1501	1501	1501	1501	1501	
5°	1501	1498	1491	1498	1498	143
15°	1449	1449	1446	1458	1456	408
25°	1344	1349	1359	1371	1373	620
35°	1193	1202	1221	1245	1250	747
45°	1001	1018	1053	1098	1117	772
55°	774	802	874	942	975	689
65°	511	563	679	769	805	508
75°	241	329	459	537	554	259
85°	47	97	118	128	133	59
90°	0	0	0	0	0	



TEST NUMBER: P391775

CATALOG NUMBER: 24CZ2-85VHE-RDP-UNV-L930-CD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1500.8	1500.8	1500.8	1500.8	1500.8
2.5°	1503.1	1503.1	1496.0	1500.8	1500.8
5°	1500.8	1498.4	1491.3	1498.4	1498.4
7.5°	1493.7	1491.3	1486.5	1493.7	1491.3
10°	1479.4	1479.4	1474.7	1481.8	1481.8
12.5°	1467.6	1465.2	1462.9	1472.3	1470.0
15°	1448.7	1448.7	1446.3	1458.1	1455.8
17.5°	1425.0	1427.4	1429.7	1439.2	1441.6
20°	1399.0	1403.7	1406.1	1420.3	1420.3
22.5°	1375.3	1377.7	1382.4	1396.6	1396.6
25°	1344.5	1349.3	1358.7	1370.6	1372.9
27.5°	1313.7	1316.1	1328.0	1344.5	1346.9
30°	1273.5	1280.6	1294.8	1313.7	1316.1
32.5°	1238.0	1245.1	1261.7	1280.6	1285.3
35°	1193.0	1202.5	1221.4	1245.1	1249.8
37.5°	1152.8	1159.9	1183.6	1209.6	1216.7
40°	1103.1	1117.3	1141.0	1171.7	1183.6
42.5°	1053.4	1067.6	1096.0	1136.2	1150.4
45°	1001.3	1017.9	1053.4	1098.3	1117.3
47.5°	949.2	968.2	1008.4	1060.5	1081.8
50°	890.0	913.7	963.4	1022.6	1046.3
52.5°	833.2	861.6	916.1	982.4	1013.1
55°	774.0	802.5	873.5	942.1	975.3
57.5°	707.8	745.6	823.8	901.9	937.4
60°	646.2	681.7	776.4	861.6	897.1
62.5°	579.9	627.3	729.1	819.0	854.5
65°	511.3	563.4	679.4	769.3	804.8
67.5°	449.8	506.6	629.7	719.6	755.1
70°	376.4	447.4	575.2	665.2	700.7
72.5°	307.7	385.8	518.4	606.0	639.1
75°	241.4	329.0	459.2	537.3	553.9
77.5°	179.9	272.2	397.7	430.8	419.0
80°	127.8	217.8	310.1	293.5	300.6
82.5°	82.8	165.7	191.7	217.8	224.9
85°	47.3	97.1	118.4	127.8	132.6
87.5°	21.3	35.5	47.3	47.3	45.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)