

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: METALUX

Report Number: P272073

Luminaire Tested: **24CZ2-40-UNV-L930-CD1-U**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P272073
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-15)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-40-UNV-L930-CD1-U
Description: 2'x4' TROFFER LED MODULE,RIBBED LENS, 90CRI
Light Source: (84) 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3462.0 lumens
Efficiency: N/A
Efficacy: 95.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.29 / 1.38
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 36.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P272073

CATALOG NUMBER: 24CZ2-40-UNV-L930-CD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P272073

CATALOG NUMBER: 24CZ2-40-UNV-L930-CD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	92	89	92	89	87	88	86	84	82
2	98	89	81	75	95	87	80	74	83	78	73	80	75	71	77	73	69	67
3	89	77	69	62	86	76	68	61	73	66	60	70	64	59	67	62	58	56
4	81	68	59	52	79	67	58	52	64	57	51	62	56	50	60	54	50	47
5	74	61	52	45	72	60	51	44	58	50	44	56	49	43	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	64	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	37	31	57	45	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	25	35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1536	1536	1536
5°	1539	1530	1539
10°	1530	1525	1538
15°	1517	1520	1539
20°	1498	1510	1538
25°	1475	1499	1536
30°	1447	1487	1535
35°	1419	1472	1536
40°	1386	1461	1545
45°	1353	1451	1558
50°	1313	1447	1582
55°	1280	1450	1614
60°	1230	1462	1669
65°	1174	1477	1730
70°	1112	1523	1825
75°	991	1588	1994
80°	845	1682	2038
85°	604	1667	1950



TEST NUMBER: P272073

CATALOG NUMBER: 24CZ2-40-UNV-L930-CD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.1	3.1
10°-20°	309.0	8.9
20°-30°	466.7	13.5
30°-40°	562.4	16.2
40°-50°	590.5	17.1
50°-60°	552.4	16.0
60°-70°	456.2	13.2
70°-80°	310.9	9.0
80°-90°	106.0	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	883.7	25.5
0°-40°	1446.1	41.8
0°-60°	2588.9	74.8
0°-90°	3462.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3462.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1142	1142	1142	1142	1142	
5°	1139	1138	1132	1139	1139	108
15°	1089	1090	1091	1103	1105	307
25°	994	998	1010	1029	1035	457
35°	864	873	896	926	935	540
45°	711	726	763	804	819	548
55°	546	567	618	668	688	487
65°	369	400	464	523	543	366
75°	191	234	306	363	384	203
85°	39	77	108	122	126	49
90°	0	0	0	0	0	



TEST NUMBER: P272073

CATALOG NUMBER: 24CZ2-40-UNV-L930-CD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1141.7	1141.7	1141.7	1141.7	1141.7
2.5°	1142.9	1141.7	1136.0	1141.7	1140.6
5°	1139.4	1138.3	1132.5	1139.4	1139.4
7.5°	1131.4	1131.4	1125.7	1133.7	1134.8
10°	1119.9	1119.9	1116.5	1125.7	1125.7
12.5°	1106.1	1106.1	1106.1	1115.3	1116.5
15°	1088.9	1090.0	1091.2	1102.7	1105.0
17.5°	1068.2	1070.5	1074.0	1087.8	1090.0
20°	1046.4	1048.7	1054.4	1070.5	1074.0
22.5°	1018.8	1024.6	1032.6	1051.0	1054.4
25°	993.6	998.2	1009.6	1029.2	1034.9
27.5°	962.6	969.4	984.4	1005.1	1013.1
30°	931.5	938.4	956.8	980.9	987.8
32.5°	898.2	908.6	928.1	953.4	961.4
35°	863.8	873.0	895.9	925.8	935.0
37.5°	825.9	838.5	863.8	895.9	907.4
40°	789.1	802.9	831.6	866.1	879.9
42.5°	752.4	766.1	798.3	837.4	851.1
45°	711.0	725.9	762.7	804.0	819.0
47.5°	669.7	688.0	728.2	771.9	788.0
50°	627.2	647.8	691.5	737.4	755.8
52.5°	589.2	608.8	654.7	704.1	721.3
55°	545.6	567.4	618.0	668.5	688.0
57.5°	500.8	524.9	578.9	634.0	653.6
60°	457.2	483.6	543.3	598.4	620.3
62.5°	414.7	441.1	503.1	560.5	582.4
65°	368.7	399.7	464.0	522.6	543.3
67.5°	325.1	358.4	426.1	483.6	504.2
70°	282.6	314.7	387.1	443.4	464.0
72.5°	236.6	273.4	345.7	404.3	426.1
75°	190.7	234.3	305.5	363.0	383.6
77.5°	148.2	193.0	264.2	311.3	321.6
80°	109.1	155.1	217.1	250.4	263.0
82.5°	70.1	116.0	165.4	189.5	199.9
85°	39.1	77.0	108.0	121.8	126.3
87.5°	16.1	33.3	43.6	49.4	49.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)