

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P388919

Luminaire Tested: **24CZ2-65VHE-UNV-L930-CD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P388919
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-5)
Test Lab: INNOVATIONS CENTER(G3)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-65VHE-UNV-L930-CD1-U
Description: 2x4 CRUZE LED TROFFER WITH 3000K, 90 LEDS, AND RIBBED LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5416.6 lumens
Efficiency: N/A
Efficacy: 128.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.27 / 1.37
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 42.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P388919
CATALOG NUMBER: 24CZ2-65VHE-UNV-L930-CD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P388919

CATALOG NUMBER: 24CZ2-65VHE-UNV-L930-CD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	60	68	63	58	56
4	81	69	59	52	79	67	59	52	65	57	51	62	56	51	60	55	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	39	50	44	38	49	43	38	36
7	64	50	41	35	62	49	40	34	47	40	34	46	39	34	45	38	34	32
8	59	45	37	31	58	45	36	31	43	36	30	42	35	30	41	35	30	28
9	55	42	33	28	54	41	33	28	40	33	27	39	32	27	38	32	27	25
10	52	38	30	25	51	38	30	25	37	30	25	36	29	25	35	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2447	2447	2447
5°	2447	2437	2451
10°	2433	2430	2448
15°	2412	2417	2443
20°	2379	2397	2433
25°	2340	2375	2423
30°	2295	2348	2413
35°	2245	2319	2405
40°	2188	2289	2410
45°	2133	2267	2422
50°	2074	2255	2444
55°	2010	2252	2489
60°	1931	2262	2554
65°	1830	2296	2665
70°	1700	2354	2816
75°	1551	2471	3054
80°	1275	2662	3054
85°	977	2456	2623



TEST NUMBER: P388919

CATALOG NUMBER: 24CZ2-65VHE-UNV-L930-CD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.0	3.2
10°-20°	491.0	9.1
20°-30°	738.9	13.6
30°-40°	885.5	16.3
40°-50°	922.8	17.0
50°-60°	858.6	15.9
60°-70°	707.1	13.1
70°-80°	481.6	8.9
80°-90°	159.0	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1402.0	25.9
0°-40°	2287.5	42.2
0°-60°	4068.9	75.1
0°-90°	5416.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5416.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1819	1819	1819	1819	1819	
5°	1811	1811	1804	1813	1815	172
15°	1732	1734	1735	1752	1754	488
25°	1576	1584	1600	1627	1632	726
35°	1367	1383	1412	1450	1464	854
45°	1121	1144	1191	1251	1273	864
55°	857	886	960	1036	1061	764
65°	575	624	721	806	837	571
75°	298	365	475	560	588	315
85°	63	123	159	170	170	78
90°	0	0	0	0	0	



TEST NUMBER: P388919

CATALOG NUMBER: 24CZ2-65VHE-UNV-L930-CD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1818.6	1818.6	1818.6	1818.6	1818.6
2.5°	1818.6	1818.6	1809.6	1818.6	1818.6
5°	1811.4	1811.4	1804.1	1813.2	1815.0
7.5°	1798.7	1800.5	1793.3	1804.1	1806.0
10°	1780.6	1782.4	1778.8	1789.7	1791.5
12.5°	1758.9	1760.8	1760.8	1773.4	1775.2
15°	1731.8	1733.6	1735.4	1751.7	1753.5
17.5°	1697.5	1702.9	1706.5	1726.4	1730.0
20°	1661.3	1666.8	1674.0	1695.7	1699.3
22.5°	1619.8	1627.0	1639.6	1663.1	1668.6
25°	1576.4	1583.6	1599.9	1627.0	1632.4
27.5°	1527.6	1538.4	1558.3	1587.2	1594.4
30°	1476.9	1487.8	1511.3	1542.0	1552.9
32.5°	1422.7	1437.2	1464.3	1498.6	1509.5
35°	1366.7	1382.9	1411.9	1449.8	1464.3
37.5°	1307.0	1325.1	1359.4	1401.0	1419.1
40°	1245.5	1267.2	1303.4	1352.2	1372.1
42.5°	1184.1	1204.0	1249.2	1301.6	1323.3
45°	1120.8	1144.3	1191.3	1251.0	1272.7
47.5°	1055.7	1079.2	1135.3	1198.5	1218.4
50°	990.7	1014.2	1077.4	1144.3	1167.8
52.5°	920.1	950.9	1023.2	1090.1	1113.6
55°	856.9	885.8	959.9	1035.8	1061.2
57.5°	784.6	818.9	900.3	979.8	1006.9
60°	717.7	753.8	840.6	922.0	949.1
62.5°	649.0	688.8	781.0	864.1	894.8
65°	574.9	623.7	721.3	806.3	837.0
67.5°	508.0	558.6	661.6	748.4	775.5
70°	432.1	493.5	598.4	685.1	715.9
72.5°	367.0	428.4	538.7	623.7	654.4
75°	298.3	365.2	475.4	560.4	587.5
77.5°	229.6	303.7	414.0	479.1	488.1
80°	164.5	242.2	343.5	381.4	394.1
82.5°	115.7	186.2	253.1	278.4	285.6
85°	63.3	122.9	159.1	169.9	169.9
87.5°	27.1	52.4	63.3	65.1	66.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)