

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P389735

Luminaire Tested: **24CZ2-40VHE-S-UNV-L930-CD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P389735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATIONS CENTER(G3)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-40VHE-S-UNV-L930-CD1-U
Description: 2x4 CRUZE LED TROFFER WITH 3000K, 90 LEDS, AND SMOOTH LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3504.1 lumens
Efficiency: N/A
Efficacy: 133.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 26.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P389735

CATALOG NUMBER: 24CZ2-40VHE-S-UNV-L930-CD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P389735

CATALOG NUMBER: 24CZ2-40VHE-S-UNV-L930-CD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90		93	90	88		89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74		81	76	72		78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62		71	66	61		69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53		63	57	52		61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46		57	50	45		55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40		52	45	40		50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35		47	40	35		46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32		43	36	31		42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28		40	33	28		39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26		37	30	26		36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1656	1656	1656
5°	1655	1651	1661
10°	1648	1648	1661
15°	1633	1640	1657
20°	1611	1627	1653
25°	1581	1611	1643
30°	1546	1593	1629
35°	1512	1567	1616
40°	1460	1541	1597
45°	1413	1510	1580
50°	1358	1482	1561
55°	1298	1454	1546
60°	1237	1432	1542
65°	1159	1407	1552
70°	1073	1414	1594
75°	961	1441	1684
80°	776	1526	1647
85°	584	1340	1306



TEST NUMBER: P389735

CATALOG NUMBER: 24CZ2-40VHE-S-UNV-L930-CD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.5	3.3
10°-20°	333.0	9.5
20°-30°	500.6	14.3
30°-40°	596.3	17.0
40°-50°	610.2	17.4
50°-60°	549.4	15.7
60°-70°	431.5	12.3
70°-80°	280.0	8.0
80°-90°	86.6	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	950.1	27.1
0°-40°	1546.4	44.1
0°-60°	2706.0	77.2
0°-90°	3504.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3504.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1231	1231	1231	1231	1231	
5°	1225	1228	1222	1229	1230	116
15°	1172	1175	1178	1188	1190	330
25°	1065	1074	1085	1103	1106	491
35°	920	932	954	977	984	574
45°	742	760	794	824	830	572
55°	553	578	620	652	659	496
65°	364	392	442	479	488	362
75°	185	220	277	315	324	196
85°	38	70	87	85	85	46
90°	0	0	0	0	0	



TEST NUMBER: P389735

CATALOG NUMBER: 24CZ2-40VHE-S-UNV-L930-CD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1231.0	1231.0	1231.0	1231.0	1231.0
2.5°	1232.1	1232.1	1226.6	1232.1	1233.2
5°	1225.4	1227.7	1222.1	1228.8	1229.9
7.5°	1218.8	1218.8	1215.4	1222.1	1223.2
10°	1206.5	1207.6	1206.5	1214.3	1215.4
12.5°	1190.9	1193.2	1194.3	1202.1	1203.2
15°	1172.0	1175.4	1177.6	1187.6	1189.8
17.5°	1150.9	1154.2	1159.8	1170.9	1173.1
20°	1125.3	1129.7	1136.4	1150.9	1154.2
22.5°	1097.4	1101.9	1113.0	1126.4	1132.0
25°	1065.2	1074.1	1085.2	1103.0	1106.4
27.5°	1032.9	1040.7	1055.2	1074.1	1078.5
30°	995.1	1007.3	1025.1	1044.0	1048.5
32.5°	958.3	970.6	991.7	1011.7	1017.3
35°	920.5	931.6	953.9	977.2	983.9
37.5°	877.1	891.5	916.0	939.4	946.1
40°	831.4	849.2	877.1	901.6	909.3
42.5°	788.0	806.9	834.8	861.5	870.4
45°	742.4	760.2	793.6	823.6	830.3
47.5°	695.6	715.7	751.3	781.3	792.5
50°	648.9	670.0	707.9	739.1	745.7
52.5°	602.2	624.4	664.5	697.9	701.2
55°	553.2	577.7	620.0	652.2	658.9
57.5°	508.7	529.8	575.4	608.8	616.6
60°	459.7	483.1	532.0	563.2	573.2
62.5°	412.9	437.4	488.6	519.8	528.7
65°	364.0	391.8	441.9	478.6	487.5
67.5°	321.7	348.4	401.8	437.4	446.3
70°	272.7	302.7	359.5	396.2	405.1
72.5°	230.4	261.6	318.3	353.9	367.3
75°	184.8	220.4	277.1	315.0	323.9
77.5°	140.2	181.4	239.3	268.2	268.2
80°	100.2	143.6	197.0	210.4	212.6
82.5°	65.7	108.0	145.8	144.7	144.7
85°	37.8	70.1	86.8	84.6	84.6
87.5°	14.5	28.9	31.2	31.2	30.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)