

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P389887

Luminaire Tested: **24CZ2-70VHE-S-UNV-L950-CD1-SWPD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P389887
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATIONS CENTER(G3)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-70VHE-S-UNV-L950-CD1-SWPD1-U
Description: 2x4 CRUZE LED TROFFER WITH 5000K, 90 LEDS, AND SMOOTH LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6641.7 lumens
Efficiency: N/A
Efficacy: 145.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 45.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P389887

CATALOG NUMBER: 24CZ2-70VHE-S-UNV-L950-CD1-SWPD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P389887

CATALOG NUMBER: 24CZ2-70VHE-S-UNV-L950-CD1-SWPD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3139	3139	3139
5°	3137	3129	3149
10°	3124	3124	3147
15°	3094	3109	3141
20°	3054	3084	3132
25°	2997	3054	3113
30°	2930	3019	3088
35°	2866	2970	3063
40°	2768	2920	3027
45°	2677	2862	2995
50°	2574	2808	2959
55°	2460	2757	2930
60°	2345	2714	2924
65°	2196	2666	2942
70°	2033	2681	3021
75°	1821	2731	3191
80°	1471	2893	3122
85°	1107	2541	2475



TEST NUMBER: P389887

CATALOG NUMBER: 24CZ2-70VHE-S-UNV-L950-CD1-SWPD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.9	3.3
10°-20°	631.2	9.5
20°-30°	948.8	14.3
30°-40°	1130.2	17.0
40°-50°	1156.7	17.4
50°-60°	1041.3	15.7
60°-70°	817.8	12.3
70°-80°	530.8	8.0
80°-90°	164.2	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1800.9	27.1
0°-40°	2931.0	44.1
0°-60°	5129.0	77.2
0°-90°	6641.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6641.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2333	2333	2333	2333	2333	
5°	2323	2327	2316	2329	2331	221
15°	2222	2228	2232	2251	2255	626
25°	2019	2036	2057	2091	2097	930
35°	1745	1766	1808	1852	1865	1088
45°	1407	1441	1504	1561	1574	1085
55°	1048	1095	1175	1236	1249	940
65°	690	743	838	907	924	687
75°	350	418	525	597	614	371
85°	72	133	165	160	160	87
90°	0	0	0	0	0	



TEST NUMBER: P389887

CATALOG NUMBER: 24CZ2-70VHE-S-UNV-L950-CD1-SWPD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2333.3	2333.3	2333.3	2333.3	2333.3
2.5°	2335.4	2335.4	2324.8	2335.4	2337.5
5°	2322.7	2326.9	2316.4	2329.1	2331.2
7.5°	2310.1	2310.1	2303.7	2316.4	2318.5
10°	2286.9	2289.0	2286.9	2301.6	2303.7
12.5°	2257.3	2261.5	2263.7	2278.4	2280.5
15°	2221.5	2227.8	2232.0	2251.0	2255.2
17.5°	2181.4	2187.7	2198.3	2219.4	2223.6
20°	2132.9	2141.3	2154.0	2181.4	2187.7
22.5°	2080.1	2088.6	2109.6	2135.0	2145.5
25°	2018.9	2035.8	2056.9	2090.7	2097.0
27.5°	1957.8	1972.5	1999.9	2035.8	2044.3
30°	1886.0	1909.2	1943.0	1978.9	1987.3
32.5°	1816.4	1839.6	1879.7	1917.7	1928.2
35°	1744.7	1765.8	1808.0	1852.3	1864.9
37.5°	1662.4	1689.8	1736.2	1780.5	1793.2
40°	1575.9	1609.7	1662.4	1708.8	1723.6
42.5°	1493.6	1529.5	1582.2	1632.9	1649.7
45°	1407.1	1440.9	1504.2	1561.1	1573.8
47.5°	1318.5	1356.5	1424.0	1481.0	1502.1
50°	1229.9	1270.0	1341.7	1400.8	1413.5
52.5°	1141.3	1183.5	1259.5	1322.8	1329.1
55°	1048.5	1094.9	1175.1	1236.3	1248.9
57.5°	964.1	1004.2	1090.7	1154.0	1168.7
60°	871.3	915.6	1008.4	1067.5	1086.5
62.5°	782.7	829.1	926.1	985.2	1002.1
65°	689.9	742.6	837.5	907.1	924.0
67.5°	609.7	660.3	761.6	829.1	846.0
70°	516.9	573.8	681.4	751.0	767.9
72.5°	436.7	495.8	603.4	670.9	696.2
75°	350.2	417.7	525.3	597.0	613.9
77.5°	265.8	343.9	453.6	508.4	508.4
80°	189.9	272.1	373.4	398.7	402.9
82.5°	124.5	204.6	276.4	274.3	274.3
85°	71.7	132.9	164.6	160.3	160.3
87.5°	27.4	54.9	59.1	59.1	57.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)