

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: METALUX

Report Number: P272193

Luminaire Tested: **24CZ2-75HE-S-UNV-L930-CD1-U**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P272193
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-75HE-S-UNV-L930-CD1-U
Description: 2'x4' TROFFER LED MODULE,SMOOTH LENS, 90CRI
Light Source: (392) 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6565.0 lumens
Efficiency: N/A
Efficacy: 118.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.27 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 55.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P272193
CATALOG NUMBER: 24CZ2-75HE-S-UNV-L930-CD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P272193

CATALOG NUMBER: 24CZ2-75HE-S-UNV-L930-CD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3103	3103	3103
5°	3101	3092	3112
10°	3088	3088	3111
15°	3059	3073	3105
20°	3019	3049	3096
25°	2963	3018	3077
30°	2896	2984	3052
35°	2833	2935	3028
40°	2736	2886	2992
45°	2647	2829	2960
50°	2545	2776	2924
55°	2431	2725	2896
60°	2317	2682	2890
65°	2171	2636	2908
70°	2010	2650	2986
75°	1800	2699	3154
80°	1454	2860	3086
85°	1095	2512	2447



TEST NUMBER: P272193

CATALOG NUMBER: 24CZ2-75HE-S-UNV-L930-CD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.3	3.3
10°-20°	623.9	9.5
20°-30°	937.8	14.3
30°-40°	1117.1	17.0
40°-50°	1143.3	17.4
50°-60°	1029.3	15.7
60°-70°	808.3	12.3
70°-80°	524.6	8.0
80°-90°	162.3	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1780.0	27.1
0°-40°	2897.2	44.1
0°-60°	5069.8	77.2
0°-90°	6565.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6565.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2306	2306	2306	2306	2306	
5°	2296	2300	2290	2302	2304	218
15°	2196	2202	2206	2225	2229	619
25°	1996	2012	2033	2066	2073	919
35°	1724	1745	1787	1831	1843	1076
45°	1391	1424	1487	1543	1556	1072
55°	1036	1082	1162	1222	1234	929
65°	682	734	828	897	913	679
75°	346	413	519	590	607	366
85°	71	131	163	158	158	86
90°	0	0	0	0	0	



TEST NUMBER: P272193

CATALOG NUMBER: 24CZ2-75HE-S-UNV-L930-CD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2306.3	2306.3	2306.3	2306.3	2306.3
2.5°	2308.4	2308.4	2298.0	2308.4	2310.5
5°	2295.9	2300.1	2289.6	2302.2	2304.2
7.5°	2283.4	2283.4	2277.1	2289.6	2291.7
10°	2260.5	2262.5	2260.5	2275.0	2277.1
12.5°	2231.3	2235.4	2237.5	2252.1	2254.2
15°	2195.8	2202.1	2206.2	2225.0	2229.2
17.5°	2156.2	2162.4	2172.9	2193.7	2197.9
20°	2108.2	2116.6	2129.1	2156.2	2162.4
22.5°	2056.1	2064.4	2085.3	2110.3	2120.7
25°	1995.6	2012.3	2033.2	2066.5	2072.8
27.5°	1935.1	1949.7	1976.9	2012.3	2020.6
30°	1864.2	1887.2	1920.5	1956.0	1964.3
32.5°	1795.4	1818.4	1858.0	1895.5	1906.0
35°	1724.5	1745.4	1787.1	1830.9	1843.4
37.5°	1643.2	1670.3	1716.2	1760.0	1772.5
40°	1557.7	1591.1	1643.2	1689.1	1703.7
42.5°	1476.4	1511.8	1564.0	1614.0	1630.7
45°	1390.9	1424.3	1486.8	1543.1	1555.6
47.5°	1303.3	1340.8	1407.6	1463.9	1484.7
50°	1215.7	1255.3	1326.2	1384.6	1397.1
52.5°	1128.1	1169.8	1244.9	1307.5	1313.7
55°	1036.4	1082.3	1161.5	1222.0	1234.5
57.5°	953.0	992.6	1078.1	1140.7	1155.2
60°	861.2	905.0	996.8	1055.2	1073.9
62.5°	773.6	819.5	915.4	973.8	990.5
65°	681.9	734.0	827.9	896.7	913.4
67.5°	602.6	652.7	752.8	819.5	836.2
70°	510.9	567.2	673.5	742.4	759.0
72.5°	431.7	490.0	596.4	663.1	688.1
75°	346.2	412.9	519.2	590.1	606.8
77.5°	262.7	339.9	448.3	502.6	502.6
80°	187.7	269.0	369.1	394.1	398.3
82.5°	123.0	202.3	273.2	271.1	271.1
85°	70.9	131.4	162.7	158.5	158.5
87.5°	27.1	54.2	58.4	58.4	56.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)