

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P388754

Luminaire Tested: **24CZ2-50-SQR-UNV-L930-CD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P388754
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2002-678-2)
Test Lab: INNOVATION CENTER (G2)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-50-SQR-UNV-L930-CD1-U
Description: 2x4 CRUZE LED TROFFER WITH 3000K, 90 LEDS, AND SQUARE LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3973.8 lumens
Efficiency: N/A
Efficacy: 81.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.33 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 48.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P388754
CATALOG NUMBER: 24CZ2-50-SQR-UNV-L930-CD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P388754

CATALOG NUMBER: 24CZ2-50-SQR-UNV-L930-CD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	89	86	84	82
2	98	89	81	75	95	87	80	74	83	78	73	80	75	71	77	73	69	67
3	89	77	69	62	86	76	68	61	73	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	52	64	57	51	62	55	50	60	54	49	47
5	74	61	51	44	72	60	51	44	57	50	44	55	49	43	54	48	43	41
6	68	55	45	39	66	54	45	38	52	44	38	50	43	38	48	42	37	35
7	63	49	40	34	62	49	40	34	47	39	34	45	39	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	42	35	30	40	34	30	28
9	55	41	33	27	54	41	33	27	39	32	27	38	32	27	37	31	27	25
10	52	38	30	25	50	37	30	24	36	29	24	36	29	24	35	29	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1709	1709	1709
5°	1716	1714	1714
10°	1703	1718	1725
15°	1685	1718	1736
20°	1663	1713	1744
25°	1634	1705	1749
30°	1600	1698	1759
35°	1567	1694	1776
40°	1533	1694	1800
45°	1493	1698	1835
50°	1459	1708	1884
55°	1416	1727	1942
60°	1366	1755	2013
65°	1308	1788	2097
70°	1213	1832	2204
75°	1098	1896	2306
80°	925	1901	1983
85°	709	1439	1439



TEST NUMBER: P388754

CATALOG NUMBER: 24CZ2-50-SQR-UNV-L930-CD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.6	3.0
10°-20°	346.9	8.7
20°-30°	526.9	13.3
30°-40°	640.9	16.1
40°-50°	682.4	17.2
50°-60°	649.9	16.4
60°-70°	543.5	13.7
70°-80°	362.4	9.1
80°-90°	100.3	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	994.4	25.0
0°-40°	1635.3	41.2
0°-60°	2967.6	74.7
0°-90°	3973.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3973.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1270	1270	1270	1270	1270	
5°	1270	1262	1269	1269	1269	120
15°	1210	1212	1234	1243	1247	341
25°	1101	1115	1148	1168	1178	507
35°	954	982	1031	1066	1081	597
45°	785	827	892	942	964	607
55°	604	656	736	800	828	540
65°	411	471	562	631	659	406
75°	211	278	365	426	444	224
85°	46	85	93	92	93	55
90°	0	0	0	0	0	



TEST NUMBER: P388754

CATALOG NUMBER: 24CZ2-50-SQR-UNV-L930-CD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1270.2	1270.2	1270.2	1270.2	1270.2
2.5°	1275.5	1266.3	1270.2	1270.2	1265.0
5°	1270.2	1262.3	1268.9	1268.9	1268.9
7.5°	1261.0	1254.5	1265.0	1267.6	1267.6
10°	1246.6	1244.0	1257.1	1261.0	1262.3
12.5°	1230.9	1229.5	1247.9	1253.2	1257.1
15°	1209.9	1212.5	1233.5	1242.7	1246.6
17.5°	1187.6	1192.8	1216.4	1229.5	1233.5
20°	1161.3	1169.2	1196.7	1209.9	1217.7
22.5°	1132.4	1144.2	1173.1	1188.9	1198.0
25°	1100.9	1115.4	1148.2	1167.9	1178.4
27.5°	1066.8	1085.2	1123.3	1145.6	1156.1
30°	1030.1	1051.1	1093.1	1119.3	1132.4
32.5°	992.0	1017.0	1062.9	1091.8	1107.5
35°	954.0	981.5	1031.4	1065.5	1081.3
37.5°	915.9	943.5	998.6	1035.3	1055.0
40°	872.6	905.4	964.5	1005.2	1024.8
42.5°	830.6	866.1	929.0	973.7	994.7
45°	784.7	826.7	892.3	942.2	964.5
47.5°	742.7	784.7	855.6	908.0	933.0
50°	696.8	741.4	816.2	873.9	900.2
52.5°	652.2	698.1	776.8	838.5	864.7
55°	603.6	656.1	736.2	800.4	828.0
57.5°	555.1	611.5	694.2	761.1	788.6
60°	507.8	565.6	652.2	719.1	748.0
62.5°	460.6	518.3	608.9	677.1	704.7
65°	410.7	471.1	561.6	631.2	658.7
67.5°	360.9	423.8	514.4	583.9	610.2
70°	308.4	375.3	465.8	534.1	560.3
72.5°	259.8	326.7	416.0	482.9	507.8
75°	211.3	278.2	364.8	426.5	443.5
77.5°	164.0	230.9	308.4	349.0	353.0
80°	119.4	182.4	245.4	257.2	255.9
82.5°	80.0	136.5	169.3	170.6	174.5
85°	45.9	85.3	93.2	91.9	93.2
87.5°	18.4	30.2	26.2	19.7	19.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)