

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: METALUX

Report Number: P276735

Luminaire Tested: **24CZ2-30HE-RDP-UNV-L83050-W2A1-U-4500K**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P276735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-30HE-RDP-UNV-L83050-W2A1-U-4500K
Description: CRUZE 2.0 2x4 TUNABLE WHITE LED TROFFER WITH RDP LENS
Light Source: (336) 80 CRI LEDS TUNED TO 4500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2070.0 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 20.584527
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P276735

CATALOG NUMBER: 24CZ2-30HE-RDP-UNV-L83050-W2A1-U-4500K

Luminous Intensity Polar Plot





TEST NUMBER: P276735

CATALOG NUMBER: 24CZ2-30HE-RDP-UNV-L83050-W2A1-U-4500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	876	876	876
5°	879	874	878
10°	877	874	878
15°	875	874	880
20°	869	873	882
25°	866	875	884
30°	858	873	887
35°	850	870	890
40°	840	869	902
45°	826	869	922
50°	808	875	950
55°	787	889	992
60°	754	906	1047
65°	706	938	1111
70°	642	982	1196
75°	544	1036	1249
80°	429	1042	1010
85°	316	792	888



TEST NUMBER: P276735

CATALOG NUMBER: 24CZ2-30HE-RDP-UNV-L83050-W2A1-U-4500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.7	3.0
10°-20°	177.7	8.6
20°-30°	271.8	13.1
30°-40°	332.2	16.0
40°-50°	354.1	17.1
50°-60°	338.5	16.4
60°-70°	286.8	13.9
70°-80°	192.8	9.3
80°-90°	54.4	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	511.2	24.7
0°-40°	843.5	40.7
0°-60°	1536.1	74.2
0°-90°	2070.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2070.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	651	651	651	651	651	
5°	651	650	647	650	650	62
15°	628	628	627	632	631	177
25°	583	585	589	594	596	269
35°	518	522	530	540	542	324
45°	434	442	457	476	485	335
55°	336	348	379	409	423	299
65°	222	244	295	334	349	220
75°	105	143	199	233	240	112
85°	20	42	51	55	58	25
90°	0	0	0	0	0	



TEST NUMBER: P276735

CATALOG NUMBER: 24CZ2-30HE-RDP-UNV-L83050-W2A1-U-4500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	651.0	651.0	651.0	651.0	651.0
2.5°	652.0	652.0	648.9	651.0	651.0
5°	651.0	649.9	646.8	649.9	649.9
7.5°	647.9	646.8	644.8	647.9	646.8
10°	641.7	641.7	639.7	642.7	642.7
12.5°	636.6	635.6	634.5	638.6	637.6
15°	628.4	628.4	627.3	632.5	631.4
17.5°	618.1	619.1	620.2	624.3	625.3
20°	606.8	608.9	609.9	616.0	616.0
22.5°	596.5	597.6	599.6	605.8	605.8
25°	583.2	585.2	589.4	594.5	595.5
27.5°	569.8	570.9	576.0	583.2	584.2
30°	552.4	555.5	561.6	569.8	570.9
32.5°	537.0	540.1	547.3	555.5	557.5
35°	517.5	521.6	529.8	540.1	542.1
37.5°	500.0	503.1	513.4	524.7	527.7
40°	478.5	484.6	494.9	508.2	513.4
42.5°	456.9	463.1	475.4	492.8	499.0
45°	434.3	441.5	456.9	476.4	484.6
47.5°	411.7	419.9	437.4	460.0	469.2
50°	386.1	396.3	417.9	443.6	453.8
52.5°	361.4	373.7	397.4	426.1	439.4
55°	335.7	348.1	378.9	408.6	423.0
57.5°	307.0	323.4	357.3	391.2	406.6
60°	280.3	295.7	336.8	373.7	389.1
62.5°	251.6	272.1	316.2	355.3	370.7
65°	221.8	244.4	294.7	333.7	349.1
67.5°	195.1	219.7	273.1	312.1	327.5
70°	163.3	194.1	249.5	288.5	303.9
72.5°	133.5	167.4	224.9	262.8	277.2
75°	104.7	142.7	199.2	233.1	240.3
77.5°	78.0	118.1	172.5	186.9	181.7
80°	55.4	94.5	134.5	127.3	130.4
82.5°	35.9	71.9	83.2	94.5	97.5
85°	20.5	42.1	51.3	55.4	57.5
87.5°	9.2	15.4	20.5	20.5	19.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)