

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P276704

Luminaire Tested: **24CZ2-35-S-UNV-L92765-W2A1-U-6500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P276704
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-35-S-UNV-L92765-W2A1-U-6500K
Description: CRUZE 2.0 2x4 TUNABLE WHITE LED TROFFER WITH SMOOTH LENS
Light Source: (168) 90 CRI LEDS TUNED TO 6500K CCT
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3355.7 lumens
Efficiency: N/A
Efficacy: 123.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 27.249
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P276704

CATALOG NUMBER: 24CZ2-35-S-UNV-L92765-W2A1-U-6500K

Luminous Intensity Polar Plot





TEST NUMBER: P276704

CATALOG NUMBER: 24CZ2-35-S-UNV-L92765-W2A1-U-6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1586	1586	1586
5°	1585	1581	1591
10°	1579	1579	1590
15°	1563	1571	1587
20°	1543	1558	1583
25°	1514	1543	1573
30°	1480	1525	1560
35°	1448	1500	1548
40°	1398	1475	1529
45°	1353	1446	1513
50°	1301	1419	1495
55°	1243	1393	1480
60°	1185	1371	1477
65°	1110	1347	1486
70°	1027	1354	1526
75°	920	1380	1613
80°	743	1462	1578
85°	559	1283	1250



TEST NUMBER: P276704

CATALOG NUMBER: 24CZ2-35-S-UNV-L92765-W2A1-U-6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.6	3.3
10°-20°	318.9	9.5
20°-30°	479.4	14.3
30°-40°	571.0	17.0
40°-50°	584.4	17.4
50°-60°	526.1	15.7
60°-70°	413.2	12.3
70°-80°	268.2	8.0
80°-90°	82.9	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	909.9	27.1
0°-40°	1480.9	44.1
0°-60°	2591.4	77.2
0°-90°	3355.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3355.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1179	1179	1179	1179	1179	
5°	1174	1176	1170	1177	1178	112
15°	1122	1126	1128	1137	1139	316
25°	1020	1029	1039	1056	1060	470
35°	882	892	914	936	942	550
45°	711	728	760	789	795	548
55°	530	553	594	625	631	475
65°	349	375	423	458	467	347
75°	177	211	265	302	310	187
85°	36	67	83	81	81	44
90°	0	0	0	0	0	



TEST NUMBER: P276704

CATALOG NUMBER: 24CZ2-35-S-UNV-L92765-W2A1-U-6500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1178.9	1178.9	1178.9	1178.9	1178.9
2.5°	1180.0	1180.0	1174.6	1180.0	1181.0
5°	1173.6	1175.7	1170.4	1176.8	1177.8
7.5°	1167.2	1167.2	1164.0	1170.4	1171.4
10°	1155.4	1156.5	1155.4	1162.9	1164.0
12.5°	1140.5	1142.6	1143.7	1151.2	1152.2
15°	1122.4	1125.6	1127.7	1137.3	1139.4
17.5°	1102.1	1105.3	1110.7	1121.3	1123.5
20°	1077.6	1081.9	1088.3	1102.1	1105.3
22.5°	1051.0	1055.2	1065.9	1078.7	1084.0
25°	1020.1	1028.6	1039.3	1056.3	1059.5
27.5°	989.2	996.6	1010.5	1028.6	1032.9
30°	952.9	964.6	981.7	999.8	1004.1
32.5°	917.7	929.5	949.7	968.9	974.2
35°	881.5	892.2	913.5	935.9	942.3
37.5°	839.9	853.8	877.2	899.6	906.0
40°	796.2	813.3	839.9	863.4	870.8
42.5°	754.7	772.8	799.4	825.0	833.5
45°	711.0	728.0	760.0	788.8	795.2
47.5°	666.2	685.4	719.5	748.3	758.9
50°	621.4	641.7	677.9	707.8	714.2
52.5°	576.7	598.0	636.3	668.3	671.5
55°	529.8	553.2	593.7	624.6	631.0
57.5°	487.1	507.4	551.1	583.0	590.5
60°	440.2	462.6	509.5	539.3	548.9
62.5°	395.4	418.9	467.9	497.8	506.3
65°	348.6	375.2	423.2	458.3	466.9
67.5°	308.0	333.6	384.8	418.9	427.4
70°	261.1	289.9	344.3	379.5	388.0
72.5°	220.6	250.5	304.8	339.0	351.7
75°	176.9	211.0	265.4	301.7	310.2
77.5°	134.3	173.7	229.2	256.9	256.9
80°	95.9	137.5	188.7	201.5	203.6
82.5°	62.9	103.4	139.6	138.6	138.6
85°	36.2	67.2	83.1	81.0	81.0
87.5°	13.9	27.7	29.8	29.8	28.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)