

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P276609

Luminaire Tested: **24CZ2-35HE-S-UNV-L92765-W2A1-U-4000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P276609
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-35HE-S-UNV-L92765-W2A1-U-4000K
Description: CRUZE 2.0 2x4 TUNABLE WHITE LED TROFFER WITH SMOOTH LENS
Light Source: (336) 90 CRI LEDS TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3089.3 lumens
Efficiency: N/A
Efficacy: 126.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 24.459
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P276609

CATALOG NUMBER: 24CZ2-35HE-S-UNV-L92765-W2A1-U-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P276609

CATALOG NUMBER: 24CZ2-35HE-S-UNV-L92765-W2A1-U-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1460	1460	1460
5°	1459	1455	1464
10°	1453	1453	1464
15°	1439	1446	1461
20°	1421	1435	1457
25°	1394	1420	1448
30°	1363	1404	1436
35°	1333	1381	1425
40°	1287	1358	1408
45°	1245	1331	1393
50°	1198	1306	1376
55°	1144	1282	1363
60°	1091	1262	1360
65°	1022	1240	1368
70°	946	1247	1405
75°	847	1270	1485
80°	684	1346	1452
85°	516	1181	1152



TEST NUMBER: P276609

CATALOG NUMBER: 24CZ2-35HE-S-UNV-L92765-W2A1-U-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.7	3.3
10°-20°	293.6	9.5
20°-30°	441.3	14.3
30°-40°	525.7	17.0
40°-50°	538.0	17.4
50°-60°	484.4	15.7
60°-70°	380.4	12.3
70°-80°	246.9	8.0
80°-90°	76.4	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	837.7	27.1
0°-40°	1363.3	44.1
0°-60°	2385.7	77.2
0°-90°	3089.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3089.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1085	1085	1085	1085	1085	
5°	1080	1082	1078	1083	1084	103
15°	1033	1036	1038	1047	1049	291
25°	939	947	957	972	975	433
35°	812	821	841	862	868	506
45°	654	670	700	726	732	505
55°	488	509	547	575	581	437
65°	321	345	390	422	430	319
75°	163	194	244	278	286	172
85°	33	62	76	75	75	40
90°	0	0	0	0	0	



TEST NUMBER: P276609

CATALOG NUMBER: 24CZ2-35HE-S-UNV-L92765-W2A1-U-4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1085.3	1085.3	1085.3	1085.3	1085.3
2.5°	1086.3	1086.3	1081.4	1086.3	1087.3
5°	1080.4	1082.4	1077.5	1083.3	1084.3
7.5°	1074.5	1074.5	1071.6	1077.5	1078.4
10°	1063.7	1064.7	1063.7	1070.6	1071.6
12.5°	1050.0	1051.9	1052.9	1059.8	1060.8
15°	1033.3	1036.2	1038.2	1047.0	1049.0
17.5°	1014.7	1017.6	1022.5	1032.3	1034.3
20°	992.1	996.0	1001.9	1014.7	1017.6
22.5°	967.5	971.5	981.3	993.1	998.0
25°	939.1	946.9	956.8	972.5	975.4
27.5°	910.6	917.5	930.3	946.9	950.9
30°	877.3	888.1	903.8	920.4	924.4
32.5°	844.9	855.7	874.3	892.0	896.9
35°	811.5	821.3	841.0	861.6	867.5
37.5°	773.3	786.0	807.6	828.2	834.1
40°	733.0	748.7	773.3	794.8	801.7
42.5°	694.8	711.4	736.0	759.5	767.4
45°	654.5	670.2	699.7	726.2	732.0
47.5°	613.3	631.0	662.4	688.9	698.7
50°	572.1	590.7	624.1	651.6	657.5
52.5°	530.9	550.5	585.8	615.3	618.2
55°	487.7	509.3	546.6	575.0	580.9
57.5°	448.4	467.1	507.3	536.8	543.6
60°	405.3	425.9	469.1	496.5	505.4
62.5°	364.1	385.6	430.8	458.3	466.1
65°	320.9	345.4	389.6	422.0	429.8
67.5°	283.6	307.1	354.2	385.6	393.5
70°	240.4	266.9	317.0	349.3	357.2
72.5°	203.1	230.6	280.6	312.0	323.8
75°	162.9	194.3	244.3	277.7	285.6
77.5°	123.6	159.9	211.0	236.5	236.5
80°	88.3	126.6	173.7	185.5	187.4
82.5°	57.9	95.2	128.5	127.6	127.6
85°	33.4	61.8	76.5	74.6	74.6
87.5°	12.8	25.5	27.5	27.5	26.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)