

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P276721

Luminaire Tested: **24CZ2-45-S-UNV-L92765-W2A1-U-5700K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P276721
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-45-S-UNV-L92765-W2A1-U-5700K
Description: CRUZE 2.0 2x4 TUNABLE WHITE LED TROFFER WITH SMOOTH LENS
Light Source: (168) 90 CRI LEDS TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4246.4 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 35.991
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P276721

CATALOG NUMBER: 24CZ2-45-S-UNV-L92765-W2A1-U-5700K

Luminous Intensity Polar Plot





TEST NUMBER: P276721

CATALOG NUMBER: 24CZ2-45-S-UNV-L92765-W2A1-U-5700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2007	2007	2007
5°	2006	2000	2013
10°	1998	1998	2012
15°	1978	1988	2008
20°	1952	1972	2003
25°	1916	1952	1990
30°	1873	1930	1974
35°	1832	1899	1958
40°	1770	1867	1936
45°	1712	1830	1915
50°	1646	1796	1892
55°	1573	1762	1873
60°	1499	1735	1869
65°	1404	1705	1881
70°	1300	1714	1932
75°	1164	1746	2040
80°	941	1850	1996
85°	709	1624	1582



TEST NUMBER: P276721

CATALOG NUMBER: 24CZ2-45-S-UNV-L92765-W2A1-U-5700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.2	3.3
10°-20°	403.5	9.5
20°-30°	606.6	14.3
30°-40°	722.6	17.0
40°-50°	739.5	17.4
50°-60°	665.8	15.7
60°-70°	522.9	12.3
70°-80°	339.4	8.0
80°-90°	104.9	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1151.4	27.1
0°-40°	1873.9	44.1
0°-60°	3279.2	77.2
0°-90°	4246.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4246.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1492	1492	1492	1492	1492	
5°	1485	1488	1481	1489	1490	141
15°	1420	1424	1427	1439	1442	400
25°	1291	1302	1315	1337	1341	595
35°	1116	1129	1156	1184	1192	696
45°	900	921	962	998	1006	694
55°	670	700	751	790	798	601
65°	441	475	536	580	591	439
75°	224	267	336	382	392	237
85°	46	85	105	102	102	55
90°	0	0	0	0	0	



TEST NUMBER: P276721

CATALOG NUMBER: 24CZ2-45-S-UNV-L92765-W2A1-U-5700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1491.8	1491.8	1491.8	1491.8	1491.8
2.5°	1493.1	1493.1	1486.4	1493.1	1494.5
5°	1485.0	1487.7	1481.0	1489.1	1490.4
7.5°	1476.9	1476.9	1472.9	1481.0	1482.3
10°	1462.1	1463.4	1462.1	1471.5	1472.9
12.5°	1443.2	1445.9	1447.3	1456.7	1458.0
15°	1420.3	1424.3	1427.0	1439.2	1441.9
17.5°	1394.7	1398.7	1405.4	1418.9	1421.6
20°	1363.6	1369.0	1377.1	1394.7	1398.7
22.5°	1329.9	1335.3	1348.8	1365.0	1371.7
25°	1290.8	1301.6	1315.1	1336.7	1340.7
27.5°	1251.7	1261.1	1278.7	1301.6	1307.0
30°	1205.8	1220.7	1242.2	1265.2	1270.6
32.5°	1161.3	1176.2	1201.8	1226.1	1232.8
35°	1115.5	1128.9	1155.9	1184.2	1192.3
37.5°	1062.9	1080.4	1110.1	1138.4	1146.5
40°	1007.6	1029.1	1062.9	1092.5	1102.0
42.5°	954.9	977.9	1011.6	1044.0	1054.8
45°	899.6	921.2	961.7	998.1	1006.2
47.5°	843.0	867.3	910.4	946.9	960.3
50°	786.3	812.0	857.8	895.6	903.7
52.5°	729.7	756.7	805.2	845.7	849.7
55°	670.4	700.0	751.3	790.4	798.5
57.5°	616.4	642.0	697.3	737.8	747.2
60°	557.1	585.4	644.7	682.5	694.6
62.5°	500.4	530.1	592.1	629.9	640.7
65°	441.1	474.8	535.5	580.0	590.8
67.5°	389.8	422.2	486.9	530.1	540.9
70°	330.5	366.9	435.7	480.2	491.0
72.5°	279.2	317.0	385.8	428.9	445.1
75°	223.9	267.1	335.9	381.7	392.5
77.5°	169.9	219.9	290.0	325.1	325.1
80°	121.4	174.0	238.7	254.9	257.6
82.5°	79.6	130.8	176.7	175.3	175.3
85°	45.9	85.0	105.2	102.5	102.5
87.5°	17.5	35.1	37.8	37.8	36.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)