

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: METALUX

Report Number: P276722

Luminaire Tested: **24CZ2-45-S-UNV-L92765-W2A1-U-6500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P276722
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-45-S-UNV-L92765-W2A1-U-6500K
Description: CRUZE 2.0 2x4 TUNABLE WHITE LED TROFFER WITH SMOOTH LENS
Light Source: (168) 90 CRI LEDS TUNED TO 6500K CCT
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4275.2 lumens
Efficiency: N/A
Efficacy: 116.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 36.642
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P276722

CATALOG NUMBER: 24CZ2-45-S-UNV-L92765-W2A1-U-6500K

Luminous Intensity Polar Plot





TEST NUMBER: P276722

CATALOG NUMBER: 24CZ2-45-S-UNV-L92765-W2A1-U-6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83					83			
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69					69			
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58					58			
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49					49			
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42					42			
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37					37			
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33					33			
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29					29			
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26					26			
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24					24			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2021	2021	2021
5°	2019	2014	2027
10°	2011	2011	2026
15°	1992	2001	2022
20°	1966	1985	2016
25°	1929	1966	2004
30°	1886	1943	1987
35°	1845	1912	1972
40°	1782	1880	1949
45°	1724	1842	1928
50°	1657	1808	1904
55°	1583	1774	1886
60°	1509	1747	1882
65°	1414	1716	1894
70°	1309	1725	1945
75°	1172	1758	2054
80°	947	1863	2010
85°	713	1635	1593



TEST NUMBER: P276722

CATALOG NUMBER: 24CZ2-45-S-UNV-L92765-W2A1-U-6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.2	3.3
10°-20°	406.3	9.5
20°-30°	610.7	14.3
30°-40°	727.5	17.0
40°-50°	744.5	17.4
50°-60°	670.3	15.7
60°-70°	526.4	12.3
70°-80°	341.6	8.0
80°-90°	105.7	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1159.2	27.1
0°-40°	1886.6	44.1
0°-60°	3301.5	77.2
0°-90°	4275.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4275.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1502	1502	1502	1502	1502	
5°	1495	1498	1491	1499	1500	142
15°	1430	1434	1437	1449	1452	403
25°	1300	1310	1324	1346	1350	599
35°	1123	1137	1164	1192	1200	701
45°	906	928	968	1005	1013	698
55°	675	705	756	796	804	605
65°	444	478	539	584	595	442
75°	225	269	338	384	395	239
85°	46	86	106	103	103	56
90°	0	0	0	0	0	



TEST NUMBER: P276722

CATALOG NUMBER: 24CZ2-45-S-UNV-L92765-W2A1-U-6500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1501.9	1501.9	1501.9	1501.9	1501.9
2.5°	1503.3	1503.3	1496.5	1503.3	1504.6
5°	1495.1	1497.8	1491.0	1499.2	1500.5
7.5°	1487.0	1487.0	1482.9	1491.0	1492.4
10°	1472.0	1473.4	1472.0	1481.5	1482.9
12.5°	1453.0	1455.7	1457.1	1466.6	1467.9
15°	1429.9	1434.0	1436.7	1448.9	1451.7
17.5°	1404.1	1408.2	1415.0	1428.6	1431.3
20°	1372.9	1378.3	1386.5	1404.1	1408.2
22.5°	1338.9	1344.4	1358.0	1374.2	1381.0
25°	1299.6	1310.4	1324.0	1345.7	1349.8
27.5°	1260.2	1269.7	1287.3	1310.4	1315.9
30°	1214.0	1228.9	1250.7	1273.8	1279.2
32.5°	1169.2	1184.1	1209.9	1234.4	1241.2
35°	1123.0	1136.6	1163.8	1192.3	1200.4
37.5°	1070.1	1087.7	1117.6	1146.1	1154.3
40°	1014.4	1036.1	1070.1	1099.9	1109.4
42.5°	961.4	984.5	1018.5	1051.1	1061.9
45°	905.8	927.5	968.2	1004.9	1013.0
47.5°	848.7	873.2	916.6	953.3	966.9
50°	791.7	817.5	863.7	901.7	909.8
52.5°	734.7	761.8	810.7	851.4	855.5
55°	674.9	704.8	756.4	795.8	803.9
57.5°	620.6	646.4	702.1	742.8	752.3
60°	560.8	589.4	649.1	687.1	699.3
62.5°	503.8	533.7	596.1	634.2	645.0
65°	444.1	478.0	539.1	583.9	594.8
67.5°	392.4	425.0	490.2	533.7	544.5
70°	332.7	369.4	438.6	483.4	494.3
72.5°	281.1	319.1	388.4	431.8	448.1
75°	225.4	268.9	338.1	384.3	395.2
77.5°	171.1	221.3	292.0	327.3	327.3
80°	122.2	175.2	240.4	256.7	259.4
82.5°	80.1	131.7	177.9	176.5	176.5
85°	46.2	85.6	105.9	103.2	103.2
87.5°	17.7	35.3	38.0	38.0	36.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)