

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: METALUX

Report Number: P276456

Luminaire Tested: **24CZ2-45-S-UNV-L93050-W2A1-U-5000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P276456  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: 24CZ2-45-S-UNV-L93050-W2A1-U-5000K  
Description: CRUZE 2.0 2x4 TUNABLE WHITE LED TROFFER WITH SMOOTH LENS  
Light Source: (168) 90 CRI LEDS TUNED TO 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: Sample No.   Condition   Description

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4207.5 lumens  
Efficiency: N/A  
Efficacy: 115.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 36.436656  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P276456

CATALOG NUMBER: 24CZ2-45-S-UNV-L93050-W2A1-U-5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P276456

CATALOG NUMBER: 24CZ2-45-S-UNV-L93050-W2A1-U-5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1   | 108 | 103 | 99  | 95  | 106 | 101 | 97  | 93  | 97  | 93  | 90  | 93  | 90  | 88  | 89  | 87  | 85  | 83  |
| 2   | 98  | 90  | 83  | 77  | 96  | 88  | 81  | 76  | 84  | 79  | 74  | 81  | 76  | 72  | 78  | 74  | 71  | 69  |
| 3   | 89  | 79  | 70  | 64  | 87  | 77  | 69  | 63  | 74  | 67  | 62  | 71  | 66  | 61  | 69  | 64  | 60  | 58  |
| 4   | 82  | 70  | 61  | 54  | 80  | 68  | 60  | 54  | 66  | 59  | 53  | 63  | 57  | 52  | 61  | 56  | 51  | 49  |
| 5   | 75  | 62  | 53  | 46  | 73  | 61  | 53  | 46  | 59  | 51  | 46  | 57  | 50  | 45  | 55  | 49  | 45  | 42  |
| 6   | 70  | 56  | 47  | 40  | 68  | 55  | 47  | 40  | 53  | 46  | 40  | 52  | 45  | 40  | 50  | 44  | 39  | 37  |
| 7   | 64  | 51  | 42  | 36  | 63  | 50  | 42  | 36  | 48  | 41  | 35  | 47  | 40  | 35  | 46  | 39  | 35  | 33  |
| 8   | 60  | 46  | 38  | 32  | 58  | 46  | 37  | 32  | 44  | 37  | 32  | 43  | 36  | 31  | 42  | 36  | 31  | 29  |
| 9   | 56  | 43  | 34  | 29  | 55  | 42  | 34  | 29  | 41  | 34  | 28  | 40  | 33  | 28  | 39  | 33  | 28  | 26  |
| 10  | 53  | 39  | 31  | 26  | 51  | 39  | 31  | 26  | 38  | 31  | 26  | 37  | 30  | 26  | 36  | 30  | 26  | 24  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 1989 | 1989 | 1989 |
| 5°  | 1987 | 1982 | 1995 |
| 10° | 1979 | 1979 | 1994 |
| 15° | 1960 | 1970 | 1990 |
| 20° | 1935 | 1954 | 1984 |
| 25° | 1899 | 1934 | 1972 |
| 30° | 1856 | 1912 | 1956 |
| 35° | 1815 | 1881 | 1940 |
| 40° | 1753 | 1850 | 1918 |
| 45° | 1696 | 1813 | 1897 |
| 50° | 1631 | 1779 | 1874 |
| 55° | 1558 | 1746 | 1856 |
| 60° | 1485 | 1719 | 1852 |
| 65° | 1391 | 1689 | 1864 |
| 70° | 1288 | 1698 | 1914 |
| 75° | 1154 | 1730 | 2022 |
| 80° | 932  | 1833 | 1978 |
| 85° | 701  | 1609 | 1568 |



TEST NUMBER: P276456

CATALOG NUMBER: 24CZ2-45-S-UNV-L93050-W2A1-U-5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 139.9  | 3.3       |
| 10°-20°   | 399.8  | 9.5       |
| 20°-30°   | 601.1  | 14.3      |
| 30°-40°   | 715.9  | 17.0      |
| 40°-50°   | 732.7  | 17.4      |
| 50°-60°   | 659.7  | 15.7      |
| 60°-70°   | 518.1  | 12.3      |
| 70°-80°   | 336.2  | 8.0       |
| 80°-90°   | 104.0  | 2.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1140.8 | 27.1      |
| 0°-40°    | 1856.8 | 44.1      |
| 0°-60°    | 3249.2 | 77.2      |
| 0°-90°    | 4207.5 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 4207.5 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|-----|------|-------|------|-------|------|------|
| 0°  | 1478 | 1478  | 1478 | 1478  | 1478 |      |
| 5°  | 1471 | 1474  | 1467 | 1475  | 1477 | 140  |
| 15° | 1407 | 1411  | 1414 | 1426  | 1429 | 397  |
| 25° | 1279 | 1290  | 1303 | 1324  | 1328 | 589  |
| 35° | 1105 | 1119  | 1145 | 1173  | 1181 | 689  |
| 45° | 891  | 913   | 953  | 989   | 997  | 687  |
| 55° | 664  | 694   | 744  | 783   | 791  | 595  |
| 65° | 437  | 470   | 531  | 575   | 585  | 435  |
| 75° | 222  | 265   | 333  | 378   | 389  | 235  |
| 85° | 45   | 84    | 104  | 102   | 102  | 55   |
| 90° | 0    | 0     | 0    | 0     | 0    |      |



TEST NUMBER: P276456

CATALOG NUMBER: 24CZ2-45-S-UNV-L93050-W2A1-U-5000K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|-------|--------|--------|--------|--------|--------|
| 0°    | 1478.1 | 1478.1 | 1478.1 | 1478.1 | 1478.1 |
| 2.5°  | 1479.4 | 1479.4 | 1472.8 | 1479.4 | 1480.8 |
| 5°    | 1471.4 | 1474.1 | 1467.4 | 1475.4 | 1476.8 |
| 7.5°  | 1463.4 | 1463.4 | 1459.4 | 1467.4 | 1468.8 |
| 10°   | 1448.7 | 1450.0 | 1448.7 | 1458.1 | 1459.4 |
| 12.5° | 1430.0 | 1432.7 | 1434.0 | 1443.4 | 1444.7 |
| 15°   | 1407.3 | 1411.3 | 1414.0 | 1426.0 | 1428.7 |
| 17.5° | 1381.9 | 1385.9 | 1392.6 | 1405.9 | 1408.6 |
| 20°   | 1351.1 | 1356.5 | 1364.5 | 1381.9 | 1385.9 |
| 22.5° | 1317.7 | 1323.1 | 1336.4 | 1352.5 | 1359.2 |
| 25°   | 1279.0 | 1289.7 | 1303.0 | 1324.4 | 1328.4 |
| 27.5° | 1240.2 | 1249.6 | 1267.0 | 1289.7 | 1295.0 |
| 30°   | 1194.8 | 1209.5 | 1230.9 | 1253.6 | 1258.9 |
| 32.5° | 1150.7 | 1165.4 | 1190.8 | 1214.8 | 1221.5 |
| 35°   | 1105.2 | 1118.6 | 1145.3 | 1173.4 | 1181.4 |
| 37.5° | 1053.1 | 1070.5 | 1099.9 | 1128.0 | 1136.0 |
| 40°   | 998.3  | 1019.7 | 1053.1 | 1082.5 | 1091.9 |
| 42.5° | 946.2  | 968.9  | 1002.3 | 1034.4 | 1045.1 |
| 45°   | 891.4  | 912.8  | 952.9  | 989.0  | 997.0  |
| 47.5° | 835.3  | 859.3  | 902.1  | 938.2  | 951.6  |
| 50°   | 779.1  | 804.5  | 850.0  | 887.4  | 895.4  |
| 52.5° | 723.0  | 749.7  | 797.9  | 838.0  | 842.0  |
| 55°   | 664.2  | 693.6  | 744.4  | 783.2  | 791.2  |
| 57.5° | 610.8  | 636.1  | 690.9  | 731.0  | 740.4  |
| 60°   | 552.0  | 580.0  | 638.8  | 676.2  | 688.3  |
| 62.5° | 495.8  | 525.2  | 586.7  | 624.1  | 634.8  |
| 65°   | 437.0  | 470.4  | 530.6  | 574.7  | 585.4  |
| 67.5° | 386.2  | 418.3  | 482.5  | 525.2  | 535.9  |
| 70°   | 327.4  | 363.5  | 431.7  | 475.8  | 486.5  |
| 72.5° | 276.6  | 314.1  | 382.2  | 425.0  | 441.0  |
| 75°   | 221.9  | 264.6  | 332.8  | 378.2  | 388.9  |
| 77.5° | 168.4  | 217.8  | 287.3  | 322.1  | 322.1  |
| 80°   | 120.3  | 172.4  | 236.6  | 252.6  | 255.3  |
| 82.5° | 78.9   | 129.6  | 175.1  | 173.7  | 173.7  |
| 85°   | 45.4   | 84.2   | 104.2  | 101.6  | 101.6  |
| 87.5° | 17.4   | 34.7   | 37.4   | 37.4   | 36.1   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

(END OF REPORT)