

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P276403

Luminaire Tested: **24CZ2-45HE-S-UNV-L93050-W2A1-U-3500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P276403
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-45HE-S-UNV-L93050-W2A1-U-3500K
Description: CRUZE 2.0 2x4 TUNABLE WHITE LED TROFFER WITH SMOOTH LENS
Light Source: (336) 90 CRI LEDS TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3789.4 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 32.031246
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P276403

CATALOG NUMBER: 24CZ2-45HE-S-UNV-L93050-W2A1-U-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P276403

CATALOG NUMBER: 24CZ2-45HE-S-UNV-L93050-W2A1-U-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1791	1791	1791
5°	1790	1785	1796
10°	1783	1783	1796
15°	1765	1774	1792
20°	1742	1760	1787
25°	1710	1742	1776
30°	1672	1722	1762
35°	1635	1694	1748
40°	1579	1666	1727
45°	1528	1633	1709
50°	1469	1602	1688
55°	1403	1573	1672
60°	1338	1548	1668
65°	1253	1521	1678
70°	1160	1530	1723
75°	1039	1558	1821
80°	839	1650	1781
85°	631	1450	1413



TEST NUMBER: P276403

CATALOG NUMBER: 24CZ2-45HE-S-UNV-L93050-W2A1-U-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.0	3.3
10°-20°	360.1	9.5
20°-30°	541.3	14.3
30°-40°	644.8	17.0
40°-50°	659.9	17.4
50°-60°	594.1	15.7
60°-70°	466.6	12.3
70°-80°	302.8	8.0
80°-90°	93.7	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1027.5	27.1
0°-40°	1672.3	44.1
0°-60°	2926.3	77.2
0°-90°	3789.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3789.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1331	1331	1331	1331	1331	
5°	1325	1328	1322	1329	1330	126
15°	1267	1271	1274	1284	1287	357
25°	1152	1162	1174	1193	1196	531
35°	995	1007	1032	1057	1064	621
45°	803	822	858	891	898	619
55°	598	625	670	705	713	536
65°	394	424	478	518	527	392
75°	200	238	300	341	350	211
85°	41	76	94	92	92	49
90°	0	0	0	0	0	



TEST NUMBER: P276403

CATALOG NUMBER: 24CZ2-45HE-S-UNV-L93050-W2A1-U-3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1331.2	1331.2	1331.2	1331.2	1331.2
2.5°	1332.4	1332.4	1326.4	1332.4	1333.6
5°	1325.2	1327.6	1321.6	1328.8	1330.0
7.5°	1318.0	1318.0	1314.4	1321.6	1322.8
10°	1304.7	1305.9	1304.7	1313.2	1314.4
12.5°	1287.9	1290.3	1291.5	1299.9	1301.1
15°	1267.4	1271.0	1273.5	1284.3	1286.7
17.5°	1244.6	1248.2	1254.2	1266.2	1268.6
20°	1216.9	1221.7	1228.9	1244.6	1248.2
22.5°	1186.8	1191.6	1203.6	1218.1	1224.1
25°	1151.9	1161.5	1173.5	1192.8	1196.4
27.5°	1117.0	1125.4	1141.1	1161.5	1166.3
30°	1076.1	1089.3	1108.6	1129.0	1133.8
32.5°	1036.3	1049.6	1072.4	1094.1	1100.1
35°	995.4	1007.4	1031.5	1056.8	1064.0
37.5°	948.5	964.1	990.6	1015.9	1023.1
40°	899.1	918.4	948.5	974.9	983.4
42.5°	852.2	872.6	902.7	931.6	941.2
45°	802.8	822.1	858.2	890.7	897.9
47.5°	752.3	773.9	812.5	845.0	857.0
50°	701.7	724.6	765.5	799.2	806.4
52.5°	651.2	675.2	718.6	754.7	758.3
55°	598.2	624.7	670.4	705.3	712.6
57.5°	550.1	572.9	622.3	658.4	666.8
60°	497.1	522.4	575.3	609.0	619.9
62.5°	446.6	473.0	528.4	562.1	571.7
65°	393.6	423.7	477.8	517.6	527.2
67.5°	347.9	376.7	434.5	473.0	482.7
70°	294.9	327.4	388.8	428.5	438.1
72.5°	249.2	282.9	344.2	382.8	397.2
75°	199.8	238.3	299.7	340.6	350.3
77.5°	151.7	196.2	258.8	290.1	290.1
80°	108.3	155.3	213.0	227.5	229.9
82.5°	71.0	116.8	157.7	156.5	156.5
85°	40.9	75.8	93.9	91.5	91.5
87.5°	15.6	31.3	33.7	33.7	32.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)