

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P276727

Luminaire Tested: **24CZ2-50-S-UNV-L92765-W2A1-U-4500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P276727
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-50-S-UNV-L92765-W2A1-U-4500K
Description: CRUZE 2.0 2x4 TUNABLE WHITE LED TROFFER WITH SMOOTH LENS
Light Source: (168) 90 CRI LEDS TUNED TO 4500K CCT
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4504.8 lumens
Efficiency: N/A
Efficacy: 111.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 40.455
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P276727

CATALOG NUMBER: 24CZ2-50-S-UNV-L92765-W2A1-U-4500K

Luminous Intensity Polar Plot





TEST NUMBER: P276727

CATALOG NUMBER: 24CZ2-50-S-UNV-L92765-W2A1-U-4500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2129	2129	2129
5°	2128	2122	2135
10°	2119	2119	2135
15°	2099	2109	2131
20°	2071	2092	2125
25°	2033	2071	2112
30°	1987	2047	2094
35°	1944	2014	2078
40°	1877	1980	2053
45°	1816	1941	2031
50°	1746	1905	2007
55°	1668	1870	1987
60°	1590	1841	1983
65°	1490	1809	1995
70°	1379	1818	2049
75°	1235	1852	2165
80°	998	1963	2118
85°	752	1723	1678



TEST NUMBER: P276727

CATALOG NUMBER: 24CZ2-50-S-UNV-L92765-W2A1-U-4500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.8	3.3
10°-20°	428.1	9.5
20°-30°	643.5	14.3
30°-40°	766.5	17.0
40°-50°	784.5	17.4
50°-60°	706.3	15.7
60°-70°	554.7	12.3
70°-80°	360.0	8.0
80°-90°	111.3	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1221.4	27.1
0°-40°	1988.0	44.1
0°-60°	3478.8	77.2
0°-90°	4504.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4504.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1583	1583	1583	1583	1583	
5°	1575	1578	1571	1580	1581	150
15°	1507	1511	1514	1527	1530	425
25°	1369	1381	1395	1418	1422	631
35°	1183	1198	1226	1256	1265	738
45°	954	977	1020	1059	1067	736
55°	711	743	797	838	847	638
65°	468	504	568	615	627	466
75°	238	283	356	405	416	251
85°	49	90	112	109	109	59
90°	0	0	0	0	0	



TEST NUMBER: P276727

CATALOG NUMBER: 24CZ2-50-S-UNV-L92765-W2A1-U-4500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1582.6	1582.6	1582.6	1582.6	1582.6
2.5°	1584.0	1584.0	1576.8	1584.0	1585.4
5°	1575.4	1578.3	1571.1	1579.7	1581.1
7.5°	1566.8	1566.8	1562.5	1571.1	1572.5
10°	1551.1	1552.5	1551.1	1561.1	1562.5
12.5°	1531.0	1533.9	1535.3	1545.4	1546.8
15°	1506.7	1511.0	1513.9	1526.8	1529.6
17.5°	1479.5	1483.8	1491.0	1505.3	1508.2
20°	1446.6	1452.3	1460.9	1479.5	1483.8
22.5°	1410.9	1416.6	1430.9	1448.1	1455.2
25°	1369.4	1380.8	1395.1	1418.0	1422.3
27.5°	1327.9	1337.9	1356.5	1380.8	1386.5
30°	1279.2	1295.0	1317.8	1342.2	1347.9
32.5°	1232.0	1247.7	1274.9	1300.7	1307.8
35°	1183.3	1197.7	1226.3	1256.3	1264.9
37.5°	1127.5	1146.1	1177.6	1207.7	1216.3
40°	1068.9	1091.8	1127.5	1159.0	1169.0
42.5°	1013.1	1037.4	1073.2	1107.5	1119.0
45°	954.4	977.3	1020.2	1058.9	1067.4
47.5°	894.3	920.1	965.8	1004.5	1018.8
50°	834.2	861.4	910.0	950.1	958.7
52.5°	774.1	802.7	854.2	897.2	901.5
55°	711.2	742.6	797.0	838.5	847.1
57.5°	653.9	681.1	739.8	782.7	792.7
60°	591.0	621.0	684.0	724.0	736.9
62.5°	530.9	562.3	628.2	668.2	679.7
65°	467.9	503.7	568.1	615.3	626.7
67.5°	413.5	447.9	516.5	562.3	573.8
70°	350.6	389.2	462.2	509.4	520.8
72.5°	296.2	336.3	409.2	455.0	472.2
75°	237.5	283.3	356.3	404.9	416.4
77.5°	180.3	233.2	307.6	344.8	344.8
80°	128.8	184.6	253.3	270.4	273.3
82.5°	84.4	138.8	187.4	186.0	186.0
85°	48.7	90.1	111.6	108.7	108.7
87.5°	18.6	37.2	40.1	40.1	38.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)