

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P276651

Luminaire Tested: **24CZ2-60HE-S-UNV-L92765-W2A1-U-2700K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P276651
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-60HE-S-UNV-L92765-W2A1-U-2700K
Description: CRUZE 2.0 2x4 TUNABLE WHITE LED TROFFER WITH SMOOTH LENS
Light Source: (336) 90 CRI LEDS TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4698.6 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 44.175
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P276651

CATALOG NUMBER: 24CZ2-60HE-S-UNV-L92765-W2A1-U-2700K

Luminous Intensity Polar Plot





TEST NUMBER: P276651

CATALOG NUMBER: 24CZ2-60HE-S-UNV-L92765-W2A1-U-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2221	2221	2221
5°	2219	2213	2227
10°	2210	2210	2227
15°	2189	2199	2222
20°	2161	2182	2216
25°	2120	2160	2202
30°	2073	2135	2184
35°	2027	2101	2167
40°	1958	2066	2142
45°	1894	2025	2119
50°	1821	1987	2093
55°	1740	1950	2073
60°	1659	1920	2068
65°	1554	1886	2081
70°	1439	1897	2137
75°	1288	1932	2258
80°	1041	2047	2209
85°	783	1797	1751



TEST NUMBER: P276651

CATALOG NUMBER: 24CZ2-60HE-S-UNV-L92765-W2A1-U-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.3	3.3
10°-20°	446.5	9.5
20°-30°	671.2	14.3
30°-40°	799.5	17.0
40°-50°	818.3	17.4
50°-60°	736.7	15.7
60°-70°	578.5	12.3
70°-80°	375.5	8.0
80°-90°	116.1	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1274.0	27.1
0°-40°	2073.5	44.1
0°-60°	3628.5	77.2
0°-90°	4698.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4698.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1651	1651	1651	1651	1651	
5°	1643	1646	1639	1648	1649	156
15°	1572	1576	1579	1592	1595	443
25°	1428	1440	1455	1479	1484	658
35°	1234	1249	1279	1310	1319	770
45°	996	1019	1064	1104	1113	767
55°	742	775	831	875	884	665
65°	488	525	592	642	654	486
75°	248	296	372	422	434	262
85°	51	94	116	113	113	61
90°	0	0	0	0	0	



TEST NUMBER: P276651

CATALOG NUMBER: 24CZ2-60HE-S-UNV-L92765-W2A1-U-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1650.7	1650.7	1650.7	1650.7	1650.7
2.5°	1652.1	1652.1	1644.7	1652.1	1653.6
5°	1643.2	1646.2	1638.7	1647.7	1649.2
7.5°	1634.2	1634.2	1629.8	1638.7	1640.2
10°	1617.8	1619.3	1617.8	1628.3	1629.8
12.5°	1596.9	1599.9	1601.4	1611.8	1613.3
15°	1571.6	1576.0	1579.0	1592.4	1595.4
17.5°	1543.2	1547.7	1555.1	1570.1	1573.0
20°	1508.9	1514.8	1523.8	1543.2	1547.7
22.5°	1471.6	1477.5	1492.5	1510.4	1517.8
25°	1428.3	1440.2	1455.1	1479.0	1483.5
27.5°	1385.0	1395.4	1414.8	1440.2	1446.2
30°	1334.3	1350.7	1374.5	1399.9	1405.9
32.5°	1285.0	1301.4	1329.8	1356.6	1364.1
35°	1234.3	1249.2	1279.0	1310.4	1319.3
37.5°	1176.1	1195.5	1228.3	1259.6	1268.6
40°	1114.9	1138.7	1176.1	1208.9	1219.3
42.5°	1056.7	1082.0	1119.3	1155.2	1167.1
45°	995.5	1019.3	1064.1	1104.4	1113.4
47.5°	932.8	959.6	1007.4	1047.7	1062.6
50°	870.1	898.5	949.2	991.0	999.9
52.5°	807.4	837.3	891.0	935.8	940.2
55°	741.7	774.6	831.3	874.6	883.5
57.5°	682.1	710.4	771.6	816.4	826.8
60°	616.4	647.7	713.4	755.2	768.6
62.5°	553.7	586.5	655.2	697.0	708.9
65°	488.0	525.3	592.5	641.8	653.7
67.5°	431.3	467.1	538.8	586.5	598.5
70°	365.7	405.9	482.1	531.3	543.3
72.5°	308.9	350.7	426.8	474.6	492.5
75°	247.7	295.5	371.6	422.4	434.3
77.5°	188.0	243.3	320.9	359.7	359.7
80°	134.3	192.5	264.2	282.1	285.1
82.5°	88.1	144.8	195.5	194.0	194.0
85°	50.7	94.0	116.4	113.4	113.4
87.5°	19.4	38.8	41.8	41.8	40.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)