

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P412537

Luminaire Tested: **24PD-55-PB1-L927**

Issue Date: 9/15/2020



Test Information

Test Method: LM-79-08
Report Number: P412537
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-911-45)
Test Lab: INNOVATION CENTER
Issue Date: 9/15/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24PD-55-PB1-L927
Description: 5500 LUMEN 2X4 PERCEIVE LED TROFFER WITH BEVEL PATTERN OPTICS AND 90 CRI, 2700 CCT LEDS
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4221.0 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.34 / 1.32 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 41.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P412537
CATALOG NUMBER: 24PD-55-PB1-L927

Luminous Intensity Polar Plot





TEST NUMBER: P412537

CATALOG NUMBER: 24PD-55-PB1-L927

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86
2	101	93	87	82	98	91	86	81	88	83	79	85	81	77	82	78	75	73
3	92	83	75	69	90	81	74	68	78	72	67	75	70	66	73	69	65	63
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	65	60	56	54
5	78	66	57	51	76	65	57	51	63	56	50	61	55	50	59	54	49	47
6	72	60	51	45	70	59	51	45	57	50	44	55	49	44	54	48	43	41
7	67	54	46	40	65	53	45	40	52	45	39	50	44	39	49	43	39	37
8	63	49	41	35	61	49	41	35	47	40	35	46	40	35	45	39	35	33
9	58	45	37	32	57	45	37	32	44	37	32	43	36	32	42	36	31	30
10	55	42	34	29	53	41	34	29	40	33	29	39	33	29	39	33	29	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2134	2134	2134
5°	2141	2141	2141
10°	2156	2153	2154
15°	2175	2172	2170
20°	2200	2192	2186
25°	2223	2211	2199
30°	2242	2224	2206
35°	2244	2225	2197
40°	2218	2193	2156
45°	2146	2107	2053
50°	2013	1950	1879
55°	1809	1701	1631
60°	1575	1449	1394
65°	1325	1226	1173
70°	1080	1026	984
75°	866	835	800
80°	665	612	596
85°	415	403	403



TEST NUMBER: P412537

CATALOG NUMBER: 24PD-55-PB1-L927

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.0	3.6
10°-20°	440.8	10.4
20°-30°	686.8	16.3
30°-40°	844.8	20.0
40°-50°	848.6	20.1
50°-60°	654.0	15.5
60°-70°	388.3	9.2
70°-80°	172.9	4.1
80°-90°	33.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1278.6	30.3
0°-40°	2123.4	50.3
0°-60°	3626.1	85.9
0°-90°	4221.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4221.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1586	1586	1586	1586	1586	
5°	1586	1586	1586	1584	1586	151
15°	1562	1562	1559	1557	1558	442
25°	1497	1497	1490	1483	1481	690
35°	1366	1364	1355	1343	1338	853
45°	1128	1125	1107	1089	1079	866
55°	771	756	725	703	695	690
65°	416	398	385	370	368	416
75°	166	163	161	155	154	180
85°	27	26	26	25	26	36
90°	0	0	0	0	0	



TEST NUMBER: P412537

CATALOG NUMBER: 24PD-55-PB1-L927

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1586.3	1586.3	1586.3	1586.3	1586.3
2.5°	1587.1	1586.7	1586.7	1585.0	1588.4
5°	1585.5	1585.9	1585.5	1583.8	1585.5
7.5°	1582.1	1582.5	1581.7	1580.0	1581.7
10°	1577.9	1577.9	1576.2	1575.4	1576.6
12.5°	1570.7	1570.7	1569.1	1567.8	1569.1
15°	1561.5	1561.5	1559.4	1556.9	1558.1
17.5°	1550.1	1550.1	1546.8	1543.4	1544.3
20°	1536.3	1535.9	1531.2	1526.6	1527.0
22.5°	1518.6	1518.2	1512.3	1506.8	1505.2
25°	1497.2	1496.8	1489.6	1482.9	1481.2
27.5°	1472.4	1470.7	1462.7	1455.1	1453.4
30°	1442.9	1441.7	1431.2	1423.6	1420.2
32.5°	1408.9	1405.5	1395.8	1386.6	1382.0
35°	1366.4	1364.3	1354.6	1343.3	1337.8
37.5°	1318.5	1316.4	1305.9	1293.3	1287.0
40°	1263.0	1261.3	1248.3	1235.2	1227.3
42.5°	1199.1	1197.8	1183.9	1165.9	1157.5
45°	1128.0	1125.1	1107.4	1088.9	1078.8
47.5°	1049.0	1043.9	1022.5	1004.8	993.9
50°	961.5	954.8	931.7	909.0	897.6
52.5°	866.9	855.2	831.2	805.1	794.2
55°	771.1	756.4	725.3	703.4	695.4
57.5°	677.3	655.9	626.4	610.9	602.9
60°	585.2	561.7	538.6	523.4	518.0
62.5°	497.4	477.6	457.9	442.7	439.4
65°	416.2	398.2	385.1	370.4	368.3
67.5°	340.6	332.1	320.4	307.8	306.1
70°	274.5	271.2	260.7	253.1	250.2
72.5°	219.0	215.7	208.1	202.7	201.8
75°	166.5	163.1	160.6	155.1	153.9
77.5°	118.6	119.0	116.9	113.9	114.8
80°	85.8	80.7	79.0	77.4	76.9
82.5°	52.6	49.6	48.4	47.9	48.8
85°	26.9	25.6	26.1	24.8	26.1
87.5°	9.2	9.2	9.7	9.2	10.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)