

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P#

Luminaire Tested: **4SNLED-LD5-40SL-UNV-L935-CD1-U**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27410)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 4SNLED-LD5-40SL-UNV-L935-CD1-U
Description: 4FT LINEAR SNLED LED FIXTURE
OPEN LED STIP
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3372.0 lumens
Efficiency: N/A
Efficacy: 120.4 lumens/watt
Spacing Criteria (0/90/45): 1.3 / 1.29 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.12')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: 4SNLED-LD5-40SL-UNV-L935-CD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: 4SNLED-LD5-40SL-UNV-L935-CD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	99	96	106	101	98	94	97	94	91	93	91	88	90	88	86	83
2	99	90	83	77	96	88	82	76	85	79	75	81	77	73	78	75	71	69
3	90	79	71	64	87	77	70	63	74	68	62	72	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	64	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	46	57	50	45	55	49	45	42
6	69	56	47	40	67	55	46	40	53	45	40	51	45	39	50	44	39	37
7	64	51	42	35	63	50	41	35	48	41	35	47	40	35	45	39	35	33
8	60	46	37	32	58	45	37	31	44	37	31	43	36	31	42	35	31	29
9	56	42	34	28	54	42	34	28	40	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	26	37	30	25	36	30	25	36	30	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9084	9084	9084
5°	9166	8877	8807
10°	9137	8682	8534
15°	9107	8487	8267
20°	9080	8279	7982
25°	9055	8070	7716
30°	9012	7846	7454
35°	8967	7613	7203
40°	8912	7364	6902
45°	8800	7068	6556
50°	8666	6747	6205
55°	8499	6317	5827
60°	8226	5879	5332
65°	7824	5311	4637
70°	7130	4563	3759
75°	6056	3482	2890
80°	4526	2293	1895
85°	2336	1116	846



TEST NUMBER: P#

CATALOG NUMBER: 4SNLED-LD5-40SL-UNV-L935-CD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.7	3.2
10°-20°	307.7	9.1
20°-30°	471.0	14.0
30°-40°	577.0	17.1
40°-50°	610.3	18.1
50°-60°	563.4	16.7
60°-70°	434.8	12.9
70°-80°	241.3	7.2
80°-90°	59.8	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	885.3	26.3
0°-40°	1462.4	43.4
0°-60°	2636.1	78.2
0°-90°	3372.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3372.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1124	1124	1124	1124	1124	
5°	1133	1118	1122	1119	1121	108
15°	1098	1085	1093	1089	1088	310
25°	1030	1018	1026	1017	1017	475
35°	929	919	927	917	922	581
45°	794	787	796	788	789	613
55°	630	625	632	632	635	563
65°	437	432	449	446	438	431
75°	217	230	231	231	222	230
85°	34	50	52	52	48	46
90°	0	0	0	0	0	



TEST NUMBER: P#

CATALOG NUMBER: 4SNLED-LD5-40SL-UNV-L935-CD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1124.1	1124.1	1124.1	1124.1	1124.1
2.5°	1135.8	1121.3	1124.1	1122.4	1119.0
5°	1133.0	1118.5	1121.8	1119.0	1121.3
7.5°	1128.6	1112.8	1118.5	1114.5	1116.8
10°	1119.6	1106.1	1111.7	1107.2	1108.9
12.5°	1110.0	1096.0	1103.9	1098.2	1100.5
15°	1097.7	1084.8	1092.6	1088.7	1087.6
17.5°	1084.2	1071.9	1079.7	1075.2	1073.6
20°	1067.9	1056.2	1063.5	1056.7	1055.0
22.5°	1050.0	1038.2	1046.6	1037.1	1037.6
25°	1030.3	1018.0	1026.4	1017.4	1016.9
27.5°	1007.9	996.1	1005.1	995.6	996.7
30°	983.2	971.4	980.4	970.9	972.0
32.5°	956.3	946.7	954.6	945.6	951.8
35°	928.8	918.7	927.1	917.0	922.0
37.5°	899.0	889.5	898.5	887.2	891.7
40°	867.0	858.6	866.5	856.4	860.3
42.5°	830.0	825.0	832.8	822.7	826.1
45°	794.1	786.8	796.3	787.9	789.0
47.5°	758.2	750.3	759.3	752.0	751.4
50°	715.0	712.2	720.6	715.0	714.4
52.5°	674.0	668.4	677.4	674.6	676.2
55°	630.2	625.2	632.5	631.9	635.3
57.5°	584.8	579.7	589.3	588.1	590.9
60°	536.5	532.6	544.9	542.1	544.4
62.5°	489.4	482.1	497.8	495.5	494.4
65°	436.6	432.1	449.0	446.1	437.7
67.5°	382.2	380.5	397.9	392.3	378.2
70°	327.7	328.9	345.7	335.0	323.2
72.5°	270.5	278.9	289.0	281.2	272.7
75°	216.6	229.5	231.2	230.6	222.2
77.5°	163.9	180.1	176.2	180.1	173.4
80°	114.5	132.4	129.6	133.0	127.4
82.5°	70.7	87.0	87.5	89.8	84.7
85°	34.2	50.5	51.6	52.2	48.3
87.5°	7.3	23.6	24.1	22.4	19.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)