

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P510704

Luminaire Tested: **CTN-CA8-230-722-U-T5R**

Issue Date: 4/6/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P510704  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-151-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 4/6/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: CTN-CA8-230-722-U-T5R  
Description: CELESTEON HIGH MAST LUMINAIRE  
Light Source: (8) 2200K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 31265 lumens  
Efficiency: N/A  
Efficacy: 136.9 lumens/watt  
Luminous Opening: Circular (Dia: 2.08' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B5 - U0 - G4


Input Watts (W): 228.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P510704  
 CATALOG NUMBER: CTN-CA8-230-722-U-T5R

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 2.6 fc  
 Type V - Short - N/A

REPORT NUMBER: P510704  
CATALOG NUMBER: CTN-CA8-230-722-U-T5R

### Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral      - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P510704  
 CATALOG NUMBER: CTN-CA8-230-722-U-T5R


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	15632.5	0.0	15632.5
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	15632.5	0.0	15632.5
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	31265.0	0.0	31265.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	219.1	0.7
10°-20°	678.9	2.2
20°-30°	1288.4	4.1
30°-40°	2237.8	7.2
40°-50°	3895.0	12.5
50°-60°	6654.1	21.3
60°-70°	9799.6	31.3
70°-80°	6229.4	19.9
80°-90°	262.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	31265.0	100.0
0°-180°	31265.0	100.0

**Coefficient of Utilization**




REPORT NUMBER: P510704  
 CATALOG NUMBER: CTN-CA8-230-722-U-T5R

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1093.2	3.5			
FM (30°-60°)	6393.4	20.4			
FH (60°-80°)	8014.5	25.6			G4/12000
FVH (80°-90°)	131.4	0.4			G2/225
BL (0°-30°)	1093.2	3.5	B3/2500		
BM (30°-60°)	6393.4	20.4	B4/8500		
BH (60°-80°)	8014.5	25.6	B5		G4/12000
BVH (80°-90°)	131.4	0.4			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B5-U0-G4**  
 Type V Short



REPORT NUMBER: P510704  
CATALOG NUMBER: CTN-CA8-230-722-U-T5R

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2299.7
2.5°	2300.3
5°	2295.8
7.5°	2292.0
10°	2295.8
12.5°	2320.5
15°	2368.1
17.5°	2434.6
20°	2525.0
22.5°	2631.7
25°	2757.4
27.5°	2893.7
30°	3054.0
32.5°	3250.9
35°	3509.5
37.5°	3807.1
40°	4137.9
42.5°	4509.7
45°	4950.8
47.5°	5459.7
50°	6049.0
52.5°	6685.5
55°	7383.8
57.5°	8081.2
60°	8774.7
62.5°	9470.3
65°	10298.3
67.5°	10474.2
70°	9649.8
72.5°	8207.6
75°	6231.5
77.5°	3809.7
80°	1209.2
82.5°	205.3
85°	116.0
87.5°	42.0
90°	0.0

(END OF REPORT)