

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P510654

Luminaire Tested: **CTN-CA6-230-727-U-T5R**

Issue Date: 4/6/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P510654  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-151-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 4/6/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: CTN-CA6-230-727-U-T5R  
Description: CELESTEON HIGH MAST LUMINAIRE  
Light Source: (6) 2700K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 31224 lumens  
Efficiency: N/A  
Efficacy: 137.1 lumens/watt  
Luminous Opening: Circular (Dia: 2.08' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B5 - U0 - G4


Input Watts (W): 227.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P510654  
 CATALOG NUMBER: CTN-CA6-230-727-U-T5R

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 2.6 fc  
 Type V - Short - N/A

REPORT NUMBER: P510654  
CATALOG NUMBER: CTN-CA6-230-727-U-T5R

### Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral      - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P510654  
 CATALOG NUMBER: CTN-CA6-230-727-U-T5R


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	15612.0	0.0	15612.0
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	15612.0	0.0	15612.0
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	31224.0	0.0	31224.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	218.8	0.7
10°-20°	678.0	2.2
20°-30°	1286.7	4.1
30°-40°	2234.8	7.2
40°-50°	3889.9	12.5
50°-60°	6645.4	21.3
60°-70°	9786.7	31.3
70°-80°	6221.2	19.9
80°-90°	262.4	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	31224.0	100.0
0°-180°	31224.0	100.0

**Coefficient of Utilization**




REPORT NUMBER: P510654  
 CATALOG NUMBER: CTN-CA6-230-727-U-T5R

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1091.8	3.5			
FM (30°-60°)	6385.1	20.4			
FH (60°-80°)	8004.0	25.6			G4/12000
FVH (80°-90°)	131.2	0.4			G2/225
BL (0°-30°)	1091.8	3.5	B3/2500		
BM (30°-60°)	6385.1	20.4	B4/8500		
BH (60°-80°)	8004.0	25.6	B5		G4/12000
BVH (80°-90°)	131.2	0.4			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B5-U0-G4**

Type V Short



REPORT NUMBER: P510654  
CATALOG NUMBER: CTN-CA6-230-727-U-T5R

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2296.7
2.5°	2297.3
5°	2292.7
7.5°	2289.0
10°	2292.8
12.5°	2317.5
15°	2365.0
17.5°	2431.4
20°	2521.7
22.5°	2628.3
25°	2753.8
27.5°	2889.9
30°	3050.0
32.5°	3246.6
35°	3504.9
37.5°	3802.1
40°	4132.5
42.5°	4503.7
45°	4944.3
47.5°	5452.5
50°	6041.1
52.5°	6676.8
55°	7374.2
57.5°	8070.6
60°	8763.2
62.5°	9457.8
65°	10284.8
67.5°	10460.5
70°	9637.2
72.5°	8196.9
75°	6223.3
77.5°	3804.7
80°	1207.6
82.5°	205.0
85°	115.8
87.5°	41.9
90°	0.0

(END OF REPORT)