

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P510874

Luminaire Tested: **CTN-CA8-480-760-U-T5R**

Issue Date: 4/6/2021

Test Information

Test Method: LM-79-08
Report Number: P510874
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-151-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/6/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: CTN-CA8-480-760-U-T5R
Description: CELESTEON HIGH MAST LUMINAIRE
Light Source: (8) 5700K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 75809 lumens
Efficiency: N/A
Efficacy: 157.7 lumens/watt
Luminous Opening: Circular (Dia: 2.08' x H: 0')
IES Classification: Type V - Short
BUG Rating: B5 - U0 - G5


Input Watts (W): 480.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P510874
 CATALOG NUMBER: CTN-CA8-480-760-U-T5R

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 6.2 fc
 Type V - Short - N/A

REPORT NUMBER: P510874
CATALOG NUMBER: CTN-CA8-480-760-U-T5R

Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P510874

CATALOG NUMBER: CTN-CA8-480-760-U-T5R

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	37904.5	0.0	37904.5
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	37904.5	0.0	37904.5
	% Fixture	50.0	0.0	50.0
Total	Lumens	75809.0	0.0	75809.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	531.2	0.7
10°-20°	1646.2	2.2
20°-30°	3124.0	4.1
30°-40°	5425.9	7.2
40°-50°	9444.3	12.5
50°-60°	16134.5	21.3
60°-70°	23761.3	31.3
70°-80°	15104.6	19.9
80°-90°	637.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	75809.0	100.0
0°-180°	75809.0	100.0

Coefficient of Utilization




REPORT NUMBER: P510874
 CATALOG NUMBER: CTN-CA8-480-760-U-T5R

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	2650.7	3.5			
FM (30°-60°)	15502.4	20.4			
FH (60°-80°)	19432.9	25.6			G5
FVH (80°-90°)	318.5	0.4			G3/500
BL (0°-30°)	2650.7	3.5	B4/5000		
BM (30°-60°)	15502.4	20.4	B5		
BH (60°-80°)	19432.9	25.6	B5		G5
BVH (80°-90°)	318.5	0.4			G3/500
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B5-U0-G5
 Type V Short





REPORT NUMBER: P510874
CATALOG NUMBER: CTN-CA8-480-760-U-T5R

CANDELA DISTRIBUTION (FULL):

0°	
0°	5576.2
2.5°	5577.6
5°	5566.6
7.5°	5557.4
10°	5566.7
12.5°	5626.6
15°	5741.9
17.5°	5903.3
20°	6122.4
22.5°	6381.2
25°	6686.0
27.5°	7016.5
30°	7405.0
32.5°	7882.5
35°	8509.5
37.5°	9231.2
40°	10033.3
42.5°	10934.7
45°	12004.4
47.5°	13238.2
50°	14667.2
52.5°	16210.6
55°	17903.8
57.5°	19594.8
60°	21276.3
62.5°	22962.8
65°	24970.6
67.5°	25397.0
70°	23398.1
72.5°	19901.2
75°	15109.6
77.5°	9237.5
80°	2932.0
82.5°	497.7
85°	281.2
87.5°	101.8
90°	0.0

(END OF REPORT)