

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P510814

Luminaire Tested: **CTN-CA8-330-760-U-T5R**

Issue Date: 4/6/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P510814  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-151-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 4/6/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: CTN-CA8-330-760-U-T5R  
Description: CELESTEON HIGH MAST LUMINAIRE  
Light Source: (8) 5700K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 52215.1 lumens  
Efficiency: N/A  
Efficacy: 157.5 lumens/watt  
Luminous Opening: Circular (Dia: 2.08' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B5 - U0 - G5


Input Watts (W): 331.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P510814  
 CATALOG NUMBER: CTN-CA8-330-760-U-T5R

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 4.3 fc  
 Type V - Short - N/A

REPORT NUMBER: P510814  
CATALOG NUMBER: CTN-CA8-330-760-U-T5R

### Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral      - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P510814  
 CATALOG NUMBER: CTN-CA8-330-760-U-T5R


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	26107.5	0.0	26107.5
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	26107.5	0.0	26107.5
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	52215.1	0.0	52215.1
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	365.9	0.7
10°-20°	1133.8	2.2
20°-30°	2151.7	4.1
30°-40°	3737.2	7.2
40°-50°	6504.9	12.5
50°-60°	11113.0	21.3
60°-70°	16366.1	31.3
70°-80°	10403.6	19.9
80°-90°	438.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	52215.1	100.0
0°-180°	52215.1	100.0

**Coefficient of Utilization**



REPORT NUMBER: P510814


CATALOG NUMBER: CTN-CA8-330-760-U-T5R

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1825.7	3.5			
FM (30°-60°)	10677.6	20.4			
FH (60°-80°)	13384.8	25.6			G5
FVH (80°-90°)	219.4	0.4			G2/225
BL (0°-30°)	1825.7	3.5	B3/2500		
BM (30°-60°)	10677.6	20.4	B5		
BH (60°-80°)	13384.8	25.6	B5		G5
BVH (80°-90°)	219.4	0.4			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B5-U0-G5**

Type V Short





REPORT NUMBER: P510814  
CATALOG NUMBER: CTN-CA8-330-760-U-T5R

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3840.7
2.5°	3841.7
5°	3834.1
7.5°	3827.8
10°	3834.2
12.5°	3875.4
15°	3954.9
17.5°	4066.0
20°	4217.0
22.5°	4395.2
25°	4605.2
27.5°	4832.7
30°	5100.3
32.5°	5429.2
35°	5861.1
37.5°	6358.2
40°	6910.6
42.5°	7531.5
45°	8268.3
47.5°	9118.1
50°	10102.3
52.5°	11165.4
55°	12331.6
57.5°	13496.3
60°	14654.5
62.5°	15816.1
65°	17199.0
67.5°	17492.7
70°	16116.0
72.5°	13707.4
75°	10407.1
77.5°	6362.5
80°	2019.5
82.5°	342.8
85°	193.7
87.5°	70.1
90°	0.0

(END OF REPORT)