

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P316377

Luminaire Tested: **GLEON-SA3D-722-U-5WQ**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P316377  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: GLEON-SA3D-722-U-5WQ  
Description: GALLEON AREA AND ROADWAY LUMINAIRE  
(3) 70 CRI, 2200K, 1200mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE V WIDE OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 18342 lumens  
Efficiency: N/A  
Efficacy: 96.0 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B5 - U0 - G3


Input Watts (W): 191  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P316377  
 CATALOG NUMBER: GLEON-SA3D-722-U-5WQ

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.4 fc  
 Type V - Short - N/A

REPORT NUMBER: P316377  
CATALOG NUMBER: GLEON-SA3D-722-U-5WQ

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral      - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P316377  
 CATALOG NUMBER: GLEON-SA3D-722-U-5WQ


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 9171.0   | 0.0    | 9171.0  |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Street Side</b> | Lumens    | 9171.0   | 0.0    | 9171.0  |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Total</b>       | Lumens    | 18342.0  | 0.0    | 18342.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 140.9   | 0.8       |
| 10°-20°   | 411.5   | 2.2       |
| 20°-30°   | 701.7   | 3.8       |
| 30°-40°   | 1096.4  | 6.0       |
| 40°-50°   | 1858.1  | 10.1      |
| 50°-60°   | 3388.4  | 18.5      |
| 60°-70°   | 5833.4  | 31.8      |
| 70°-80°   | 4572.5  | 24.9      |
| 80°-90°   | 339.0   | 1.8       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 18342.0 | 100.0     |
| 0°-180°   | 18342.0 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P316377  
 CATALOG NUMBER: GLEON-SA3D-722-U-5WQ

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 627.1  | 3.4       |                         |      |         |
| FM (30°-60°)   | 3171.5 | 17.3      |                         |      |         |
| FH (60°-80°)   | 5202.9 | 28.4      |                         |      | G3/7500 |
| FVH (80°-90°)  | 169.5  | 0.9       |                         |      | G2/225  |
| BL (0°-30°)    | 627.1  | 3.4       | B2/1000                 |      |         |
| BM (30°-60°)   | 3171.5 | 17.3      | B3/5000                 |      |         |
| BH (60°-80°)   | 5202.9 | 28.4      | B5                      |      | G3/7500 |
| BVH (80°-90°)  | 169.5  | 0.9       |                         |      | G2/225  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B5-U0-G3**

Type V Short





REPORT NUMBER: P316377

CATALOG NUMBER: GLEON-SA3D-722-U-5WQ

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1509.5 | 1509.5 | 1509.5 | 1509.5 | 1509.5 | 1509.5 | 1509.5 | 1509.5 | 1509.5 | 1509.5 | 1509.5 |
| 2.5°  | 1502.9 | 1504.7 | 1502.9 | 1504.1 | 1501.1 | 1502.3 | 1502.3 | 1502.3 | 1501.7 | 1502.3 | 1501.1 |
| 5°    | 1489.5 | 1490.7 | 1488.3 | 1489.5 | 1487.7 | 1489.5 | 1490.1 | 1489.5 | 1488.3 | 1488.9 | 1486.5 |
| 7.5°  | 1469.5 | 1470.7 | 1468.9 | 1470.7 | 1468.3 | 1471.3 | 1470.7 | 1468.9 | 1467.1 | 1467.1 | 1464.7 |
| 10°   | 1458.6 | 1459.2 | 1454.3 | 1452.5 | 1447.1 | 1448.3 | 1450.1 | 1451.9 | 1453.7 | 1457.4 | 1456.8 |
| 12.5° | 1459.2 | 1459.2 | 1451.9 | 1444.0 | 1436.1 | 1438.0 | 1441.0 | 1447.7 | 1454.9 | 1461.6 | 1462.2 |
| 15°   | 1465.3 | 1464.7 | 1453.7 | 1441.0 | 1435.5 | 1441.0 | 1442.8 | 1447.1 | 1458.6 | 1470.1 | 1470.7 |
| 17.5° | 1469.5 | 1469.5 | 1452.5 | 1438.0 | 1437.3 | 1445.8 | 1445.2 | 1447.1 | 1459.8 | 1476.8 | 1477.4 |
| 20°   | 1477.4 | 1477.4 | 1455.5 | 1439.8 | 1439.8 | 1448.9 | 1449.5 | 1452.5 | 1465.3 | 1484.1 | 1487.1 |
| 22.5° | 1495.0 | 1495.6 | 1472.5 | 1459.8 | 1461.0 | 1466.5 | 1468.3 | 1473.1 | 1484.7 | 1505.3 | 1508.9 |
| 25°   | 1519.9 | 1521.1 | 1497.4 | 1490.1 | 1494.4 | 1504.7 | 1503.5 | 1507.1 | 1519.9 | 1539.9 | 1543.5 |
| 27.5° | 1554.4 | 1551.4 | 1529.6 | 1526.5 | 1530.8 | 1538.1 | 1537.5 | 1538.1 | 1548.4 | 1566.6 | 1570.8 |
| 30°   | 1599.3 | 1598.1 | 1582.4 | 1584.2 | 1582.4 | 1579.9 | 1580.5 | 1585.4 | 1590.9 | 1605.4 | 1609.7 |
| 32.5° | 1643.0 | 1644.2 | 1634.5 | 1643.6 | 1657.0 | 1666.1 | 1652.1 | 1638.8 | 1632.7 | 1640.6 | 1644.2 |
| 35°   | 1721.9 | 1724.9 | 1709.8 | 1703.7 | 1721.9 | 1748.6 | 1709.2 | 1687.3 | 1699.5 | 1709.8 | 1712.8 |
| 37.5° | 1856.0 | 1857.8 | 1832.3 | 1808.1 | 1794.7 | 1820.2 | 1780.8 | 1782.6 | 1825.0 | 1844.5 | 1843.9 |
| 40°   | 2008.9 | 2009.5 | 1992.5 | 1971.3 | 1948.2 | 1954.3 | 1938.5 | 1943.4 | 1971.3 | 1988.9 | 1993.7 |
| 42.5° | 2190.9 | 2189.1 | 2162.4 | 2132.1 | 2125.4 | 2131.4 | 2104.8 | 2101.1 | 2133.3 | 2164.8 | 2165.4 |
| 45°   | 2426.9 | 2422.7 | 2388.1 | 2354.7 | 2322.6 | 2309.2 | 2302.5 | 2320.1 | 2364.4 | 2393.6 | 2394.2 |
| 47.5° | 2681.1 | 2669.6 | 2651.4 | 2624.7 | 2596.8 | 2583.5 | 2572.5 | 2581.0 | 2613.2 | 2624.7 | 2625.9 |
| 50°   | 2942.7 | 2945.1 | 2948.7 | 2938.4 | 2928.1 | 2923.8 | 2895.3 | 2878.9 | 2888.7 | 2867.4 | 2864.4 |
| 52.5° | 3252.7 | 3257.5 | 3292.7 | 3322.5 | 3340.1 | 3349.2 | 3295.2 | 3238.7 | 3207.2 | 3165.9 | 3153.8 |
| 55°   | 3618.5 | 3626.4 | 3678.0 | 3760.5 | 3845.5 | 3890.4 | 3792.7 | 3687.1 | 3589.4 | 3512.4 | 3487.5 |
| 57.5° | 4026.3 | 4040.2 | 4111.2 | 4269.6 | 4443.7 | 4549.9 | 4384.9 | 4193.1 | 4004.4 | 3893.4 | 3874.0 |
| 60°   | 4504.4 | 4517.7 | 4616.0 | 4842.9 | 5125.1 | 5284.6 | 5034.7 | 4721.0 | 4486.2 | 4380.0 | 4344.2 |
| 62.5° | 5073.5 | 5074.7 | 5195.4 | 5460.6 | 5833.1 | 6055.2 | 5716.6 | 5297.4 | 5055.3 | 4927.3 | 4892.7 |
| 65°   | 5685.7 | 5688.7 | 5813.7 | 6100.1 | 6485.4 | 6726.8 | 6344.6 | 5907.7 | 5611.7 | 5423.0 | 5396.3 |
| 67.5° | 6118.3 | 6131.0 | 6262.7 | 6607.3 | 6967.7 | 7185.5 | 6789.9 | 6296.1 | 5953.9 | 5728.8 | 5706.3 |
| 70°   | 6049.1 | 6098.9 | 6253.6 | 6655.8 | 7157.0 | 7467.7 | 6862.1 | 6249.9 | 5798.5 | 5532.8 | 5514.0 |
| 72.5° | 5275.5 | 5370.8 | 5577.1 | 6104.9 | 6906.4 | 7334.2 | 6468.4 | 5597.7 | 5086.8 | 4860.5 | 4826.6 |
| 75°   | 3592.5 | 3747.2 | 4058.4 | 4819.9 | 5900.5 | 6350.1 | 5445.4 | 4463.1 | 3982.6 | 3669.5 | 3646.5 |
| 77.5° | 1601.8 | 1637.0 | 2031.3 | 2908.1 | 4071.8 | 4560.2 | 3956.5 | 2919.6 | 2191.5 | 1748.0 | 1654.6 |
| 80°   | 446.6  | 452.0  | 603.1  | 1083.0 | 2038.0 | 2679.3 | 2187.9 | 1137.6 | 639.5  | 450.8  | 424.7  |
| 82.5° | 142.0  | 154.1  | 188.1  | 280.9  | 685.0  | 1222.6 | 703.2  | 303.4  | 216.0  | 172.3  | 155.3  |
| 85°   | 69.2   | 68.6   | 95.3   | 114.1  | 174.7  | 270.6  | 186.3  | 140.8  | 123.2  | 81.9   | 74.0   |
| 87.5° | 29.1   | 29.7   | 44.3   | 40.0   | 51.0   | 43.7   | 60.1   | 63.1   | 66.1   | 36.4   | 31.6   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-10-R4

Test Date: 10/25/2019

Luminaire Tested: SA1C-722-U-5WQ

Data in this report applies to families of products SA1C-722-U-5WQ.



**Test Information**

Test Method: LM-79-2008 Report  
 Number: SP1-1908-441-10-R4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/28/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGRAW-EDISON  
 Catalog Number: **SA1C-722-U-5WQ**  
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

\*\*\*THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.\*\*\*TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

**Spectral Parameters**

CCT (K): 2237  
 CIE u': 0.2876  
 CIE v': 0.5346  
 Duv: -0.0006  
 CIE x: 0.5005  
 CIE y: 0.4134  
 CIE z: 0.0860  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 587  
 Purity: 74.5  
 Rf: 69.8  
 Rg: 99.2

|           |      |      |       |
|-----------|------|------|-------|
| CRI (Ra): | 72.0 |      |       |
| R1:       | 68.9 | R9:  | -17.4 |
| R2:       | 83.0 | R10: | 61.3  |
| R3:       | 95.2 | R11: | 59.8  |
| R4:       | 66.2 | R12: | 50.5  |
| R5:       | 65.9 | R13: | 71.1  |
| R6:       | 76.3 | R14: | 96.9  |
| R7:       | 76.7 |      |       |
| R8:       | 43.8 |      |       |



**Test Conditions**

Stabilization Time: 71M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.7/41%  
 Sphere Temperature (°C): 25.6

REPORT NUMBER: SP1-1908-441-10-R4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/28/2019        | 12/28/2019           |
| Power Meter                    | IN0071                | 12/5/2018        | 12/5/2019            |
| AC Power Source                | IN0063                | 12/5/2018        | 12/5/2019            |
| DC Power Source                | IN0208                | 12/5/2018        | 12/5/2019            |
| Sphere Thermometer             | IN0085                | 12/5/2018        | 12/5/2019            |
| Room Thermometer               | IN0046                | 12/5/2018        | 12/5/2019            |

REPORT NUMBER: SP1-1908-441-10-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2200K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-10-R4

**Photopic Flux vs. Wavelength**




#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 1768          | NR            | 490    | 5206          | NR            | 620    | 130919        | NR            | 750    | 8553          | NR            | 880    | 2713          | NR            |
| 365    | 1569          | NR            | 495    | 7286          | NR            | 625    | 125335        | NR            | 755    | 7696          | NR            | 885    | 2316          | NR            |
| 370    | 1594          | NR            | 500    | 10654         | NR            | 630    | 118388        | NR            | 760    | 6978          | NR            | 890    | 2539          | NR            |
| 375    | 1744          | NR            | 505    | 15189         | NR            | 635    | 111855        | NR            | 765    | 6377          | NR            | 895    | 1933          | NR            |
| 380    | 1659          | NR            | 510    | 20541         | NR            | 640    | 104062        | NR            | 770    | 5600          | NR            | 900    | 2216          | NR            |
| 385    | 1504          | NR            | 515    | 26492         | NR            | 645    | 96365         | NR            | 775    | 5000          | NR            | 905    | 2067          | NR            |
| 390    | 1541          | NR            | 520    | 32294         | NR            | 650    | 88651         | NR            | 780    | 4709          | NR            | 910    | 1959          | NR            |
| 395    | 1355          | NR            | 525    | 38123         | NR            | 655    | 81152         | NR            | 785    | 4305          | NR            | 915    | 1874          | NR            |
| 400    | 1243          | NR            | 530    | 43232         | NR            | 660    | 73523         | NR            | 790    | 4040          | NR            | 920    | 1484          | NR            |
| 405    | 1417          | NR            | 535    | 48012         | NR            | 665    | 66123         | NR            | 795    | 3642          | NR            | 925    | 1914          | NR            |
| 410    | 2147          | NR            | 540    | 52623         | NR            | 670    | 58677         | NR            | 800    | 3594          | NR            | 930    | 1948          | NR            |
| 415    | 3837          | NR            | 545    | 57516         | NR            | 675    | 52349         | NR            | 805    | 3190          | NR            | 935    | 2079          | NR            |
| 420    | 7159          | NR            | 550    | 62613         | NR            | 680    | 46159         | NR            | 810    | 3241          | NR            | 940    | 2263          | NR            |
| 425    | 12599         | NR            | 555    | 68554         | NR            | 685    | 40525         | NR            | 815    | 2732          | NR            | 945    | 1688          | NR            |
| 430    | 19019         | NR            | 560    | 75325         | NR            | 690    | 35615         | NR            | 820    | 2612          | NR            | 950    | 1560          | NR            |
| 435    | 24875         | NR            | 565    | 82533         | NR            | 695    | 31158         | NR            | 825    | 2966          | NR            | 955    | 2826          | NR            |
| 440    | 29103         | NR            | 570    | 90909         | NR            | 700    | 27409         | NR            | 830    | 2574          | NR            | 960    | 1477          | NR            |
| 445    | 29901         | NR            | 575    | 99621         | NR            | 705    | 24204         | NR            | 835    | 2633          | NR            | 965    | 1568          | NR            |
| 450    | 24862         | NR            | 580    | 108484        | NR            | 710    | 21558         | NR            | 840    | 2526          | NR            | 970    | 2030          | NR            |
| 455    | 15942         | NR            | 585    | 116679        | NR            | 715    | 19222         | NR            | 845    | 2631          | NR            | 975    | 1986          | NR            |
| 460    | 9916          | NR            | 590    | 123752        | NR            | 720    | 17310         | NR            | 850    | 2079          | NR            | 980    | 2540          | NR            |
| 465    | 7051          | NR            | 595    | 129324        | NR            | 725    | 15280         | NR            | 855    | 2309          | NR            | 985    | 1139          | NR            |
| 470    | 5227          | NR            | 600    | 134082        | NR            | 730    | 13282         | NR            | 860    | 2528          | NR            | 990    | 2018          | NR            |
| 475    | 4257          | NR            | 605    | 135698        | NR            | 735    | 11753         | NR            | 865    | 2121          | NR            | 995    | 3445          | NR            |
| 480    | 4052          | NR            | 610    | 135144        | NR            | 740    | 10654         | NR            | 870    | 2751          | NR            | 1000   | 3704          | NR            |
| 485    | 4298          | NR            | 615    | 134180        | NR            | 745    | 9451          | NR            | 875    | 2317          | NR            |        |               |               |

REPORT NUMBER: SP1-1908-441-10-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 4696.9

S/P: 0.85

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 1768          | NR            | 490    | 5206          | NR            | 620    | 130919        | NR            | 750    | 8553          | NR            | 880    | 2713          | NR            |
| 365    | 1569          | NR            | 495    | 7286          | NR            | 625    | 125335        | NR            | 755    | 7696          | NR            | 885    | 2316          | NR            |
| 370    | 1594          | NR            | 500    | 10654         | NR            | 630    | 118388        | NR            | 760    | 6978          | NR            | 890    | 2539          | NR            |
| 375    | 1744          | NR            | 505    | 15189         | NR            | 635    | 111855        | NR            | 765    | 6377          | NR            | 895    | 1933          | NR            |
| 380    | 1659          | NR            | 510    | 20541         | NR            | 640    | 104062        | NR            | 770    | 5600          | NR            | 900    | 2216          | NR            |
| 385    | 1504          | NR            | 515    | 26492         | NR            | 645    | 96365         | NR            | 775    | 5000          | NR            | 905    | 2067          | NR            |
| 390    | 1541          | NR            | 520    | 32294         | NR            | 650    | 88651         | NR            | 780    | 4709          | NR            | 910    | 1959          | NR            |
| 395    | 1355          | NR            | 525    | 38123         | NR            | 655    | 81152         | NR            | 785    | 4305          | NR            | 915    | 1874          | NR            |
| 400    | 1243          | NR            | 530    | 43232         | NR            | 660    | 73523         | NR            | 790    | 4040          | NR            | 920    | 1484          | NR            |
| 405    | 1417          | NR            | 535    | 48012         | NR            | 665    | 66123         | NR            | 795    | 3642          | NR            | 925    | 1914          | NR            |
| 410    | 2147          | NR            | 540    | 52623         | NR            | 670    | 58677         | NR            | 800    | 3594          | NR            | 930    | 1948          | NR            |
| 415    | 3837          | NR            | 545    | 57516         | NR            | 675    | 52349         | NR            | 805    | 3190          | NR            | 935    | 2079          | NR            |
| 420    | 7159          | NR            | 550    | 62613         | NR            | 680    | 46159         | NR            | 810    | 3241          | NR            | 940    | 2263          | NR            |
| 425    | 12599         | NR            | 555    | 68554         | NR            | 685    | 40525         | NR            | 815    | 2732          | NR            | 945    | 1688          | NR            |
| 430    | 19019         | NR            | 560    | 75325         | NR            | 690    | 35615         | NR            | 820    | 2612          | NR            | 950    | 1560          | NR            |
| 435    | 24875         | NR            | 565    | 82533         | NR            | 695    | 31158         | NR            | 825    | 2966          | NR            | 955    | 2826          | NR            |
| 440    | 29103         | NR            | 570    | 90909         | NR            | 700    | 27409         | NR            | 830    | 2574          | NR            | 960    | 1477          | NR            |
| 445    | 29901         | NR            | 575    | 99621         | NR            | 705    | 24204         | NR            | 835    | 2633          | NR            | 965    | 1568          | NR            |
| 450    | 24862         | NR            | 580    | 108484        | NR            | 710    | 21558         | NR            | 840    | 2526          | NR            | 970    | 2030          | NR            |
| 455    | 15942         | NR            | 585    | 116679        | NR            | 715    | 19222         | NR            | 845    | 2631          | NR            | 975    | 1986          | NR            |
| 460    | 9916          | NR            | 590    | 123752        | NR            | 720    | 17310         | NR            | 850    | 2079          | NR            | 980    | 2540          | NR            |
| 465    | 7051          | NR            | 595    | 129324        | NR            | 725    | 15280         | NR            | 855    | 2309          | NR            | 985    | 1139          | NR            |
| 470    | 5227          | NR            | 600    | 134082        | NR            | 730    | 13282         | NR            | 860    | 2528          | NR            | 990    | 2018          | NR            |
| 475    | 4257          | NR            | 605    | 135698        | NR            | 735    | 11753         | NR            | 865    | 2121          | NR            | 995    | 3445          | NR            |
| 480    | 4052          | NR            | 610    | 135144        | NR            | 740    | 10654         | NR            | 870    | 2751          | NR            | 1000   | 3704          | NR            |
| 485    | 4298          | NR            | 615    | 134180        | NR            | 745    | 9451          | NR            | 875    | 2317          | NR            |        |               |               |

REPORT NUMBER: SP1-1908-441-10-R4

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 1470.8 M/P: 0.27**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 1768          | NR            | 490    | 5206          | NR            | 620    | 130919        | NR            | 750    | 8553          | NR            | 880    | 2713          | NR            |
| 365    | 1569          | NR            | 495    | 7286          | NR            | 625    | 125335        | NR            | 755    | 7696          | NR            | 885    | 2316          | NR            |
| 370    | 1594          | NR            | 500    | 10654         | NR            | 630    | 118388        | NR            | 760    | 6978          | NR            | 890    | 2539          | NR            |
| 375    | 1744          | NR            | 505    | 15189         | NR            | 635    | 111855        | NR            | 765    | 6377          | NR            | 895    | 1933          | NR            |
| 380    | 1659          | NR            | 510    | 20541         | NR            | 640    | 104062        | NR            | 770    | 5600          | NR            | 900    | 2216          | NR            |
| 385    | 1504          | NR            | 515    | 26492         | NR            | 645    | 96365         | NR            | 775    | 5000          | NR            | 905    | 2067          | NR            |
| 390    | 1541          | NR            | 520    | 32294         | NR            | 650    | 88651         | NR            | 780    | 4709          | NR            | 910    | 1959          | NR            |
| 395    | 1355          | NR            | 525    | 38123         | NR            | 655    | 81152         | NR            | 785    | 4305          | NR            | 915    | 1874          | NR            |
| 400    | 1243          | NR            | 530    | 43232         | NR            | 660    | 73523         | NR            | 790    | 4040          | NR            | 920    | 1484          | NR            |
| 405    | 1417          | NR            | 535    | 48012         | NR            | 665    | 66123         | NR            | 795    | 3642          | NR            | 925    | 1914          | NR            |
| 410    | 2147          | NR            | 540    | 52623         | NR            | 670    | 58677         | NR            | 800    | 3594          | NR            | 930    | 1948          | NR            |
| 415    | 3837          | NR            | 545    | 57516         | NR            | 675    | 52349         | NR            | 805    | 3190          | NR            | 935    | 2079          | NR            |
| 420    | 7159          | NR            | 550    | 62613         | NR            | 680    | 46159         | NR            | 810    | 3241          | NR            | 940    | 2263          | NR            |
| 425    | 12599         | NR            | 555    | 68554         | NR            | 685    | 40525         | NR            | 815    | 2732          | NR            | 945    | 1688          | NR            |
| 430    | 19019         | NR            | 560    | 75325         | NR            | 690    | 35615         | NR            | 820    | 2612          | NR            | 950    | 1560          | NR            |
| 435    | 24875         | NR            | 565    | 82533         | NR            | 695    | 31158         | NR            | 825    | 2966          | NR            | 955    | 2826          | NR            |
| 440    | 29103         | NR            | 570    | 90909         | NR            | 700    | 27409         | NR            | 830    | 2574          | NR            | 960    | 1477          | NR            |
| 445    | 29901         | NR            | 575    | 99621         | NR            | 705    | 24204         | NR            | 835    | 2633          | NR            | 965    | 1568          | NR            |
| 450    | 24862         | NR            | 580    | 108484        | NR            | 710    | 21558         | NR            | 840    | 2526          | NR            | 970    | 2030          | NR            |
| 455    | 15942         | NR            | 585    | 116679        | NR            | 715    | 19222         | NR            | 845    | 2631          | NR            | 975    | 1986          | NR            |
| 460    | 9916          | NR            | 590    | 123752        | NR            | 720    | 17310         | NR            | 850    | 2079          | NR            | 980    | 2540          | NR            |
| 465    | 7051          | NR            | 595    | 129324        | NR            | 725    | 15280         | NR            | 855    | 2309          | NR            | 985    | 1139          | NR            |
| 470    | 5227          | NR            | 600    | 134082        | NR            | 730    | 13282         | NR            | 860    | 2528          | NR            | 990    | 2018          | NR            |
| 475    | 4257          | NR            | 605    | 135698        | NR            | 735    | 11753         | NR            | 865    | 2121          | NR            | 995    | 3445          | NR            |
| 480    | 4052          | NR            | 610    | 135144        | NR            | 740    | 10654         | NR            | 870    | 2751          | NR            | 1000   | 3704          | NR            |
| 485    | 4298          | NR            | 615    | 134180        | NR            | 745    | 9451          | NR            | 875    | 2317          | NR            |        |               |               |

REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

**Summary**

$R_f = 69.8$   
 $R_g = 99.2$   
 CIE  $R_a = 72.0$   
 $R_9 = -17.4$



**Color Vector Graphics**



REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 87 | CES26 = 56 | CES51 = 74 | CES76 = 56 |
| CES02 = 65 | CES27 = 76 | CES52 = 76 | CES77 = 81 |
| CES03 = 32 | CES28 = 83 | CES53 = 65 | CES78 = 63 |
| CES04 = 72 | CES29 = 46 | CES54 = 78 | CES79 = 84 |
| CES05 = 52 | CES30 = 48 | CES55 = 75 | CES80 = 84 |
| CES06 = 52 | CES31 = 51 | CES56 = 65 | CES81 = 63 |
| CES07 = 44 | CES32 = 51 | CES57 = 62 | CES82 = 92 |
| CES08 = 42 | CES33 = 53 | CES58 = 66 | CES83 = 83 |
| CES09 = 29 | CES34 = 70 | CES59 = 84 | CES84 = 92 |
| CES10 = 78 | CES35 = 85 | CES60 = 90 | CES85 = 81 |
| CES11 = 61 | CES36 = 78 | CES61 = 84 | CES86 = 56 |
| CES12 = 68 | CES37 = 80 | CES62 = 70 | CES87 = 78 |
| CES13 = 45 | CES38 = 53 | CES63 = 68 | CES88 = 72 |
| CES14 = 75 | CES39 = 90 | CES64 = 69 | CES89 = 62 |
| CES15 = 72 | CES40 = 84 | CES65 = 67 | CES90 = 67 |
| CES16 = 49 | CES41 = 75 | CES66 = 64 | CES91 = 90 |
| CES17 = 51 | CES42 = 79 | CES67 = 63 | CES92 = 67 |
| CES18 = 57 | CES43 = 64 | CES68 = 69 | CES93 = 79 |
| CES19 = 74 | CES44 = 98 | CES69 = 80 | CES94 = 52 |
| CES20 = 68 | CES45 = 73 | CES70 = 63 | CES95 = 76 |
| CES21 = 89 | CES46 = 67 | CES71 = 63 | CES96 = 78 |
| CES22 = 81 | CES47 = 60 | CES72 = 87 | CES97 = 77 |
| CES23 = 92 | CES48 = 48 | CES73 = 56 | CES98 = 71 |
| CES24 = 92 | CES49 = 64 | CES74 = 87 | CES99 = 65 |
| CES25 = 74 | CES50 = 74 | CES75 = 66 |            |





REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Measure Comparisons



(END OF REPORT)