

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P317358

Luminaire Tested: **GLEON-SA4B-727-U-T2R**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P317358  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: GLEON-SA4B-727-U-T2R  
Description: GALLEON AREA AND ROADWAY LUMINAIRE  
(4) 70 CRI, 2700K, 800mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II  
ROADWAY OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 20085 lumens  
Efficiency: N/A  
Efficacy: 117.5 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type II - Short  
BUG Rating: B2 - U0 - G3

Input Watts (W): 171  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT






REPORT NUMBER: P317358  
 CATALOG NUMBER: GLEON-SA4B-727-U-T2R

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 7.8 fc  
 Type II - Short - N/A

REPORT NUMBER: P317358  
CATALOG NUMBER: GLEON-SA4B-727-U-T2R

### Luminous Intensity Polar Plot



— Vertical Plane Through 76-Deg Lateral      - - - Horizontal Cone Through 66-Deg Vertical

REPORT NUMBER: P317358  
 CATALOG NUMBER: GLEON-SA4B-727-U-T2R


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 3379.6   | 0.0    | 3379.6  |
|                    | % Fixture | 16.8     | 0.0    | 16.8    |
| <b>Street Side</b> | Lumens    | 16705.4  | 0.0    | 16705.4 |
|                    | % Fixture | 83.2     | 0.0    | 83.2    |
| <b>Total</b>       | Lumens    | 20085.0  | 0.0    | 20085.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 221.8   | 1.1       |
| 10°-20°   | 875.9   | 4.4       |
| 20°-30°   | 1702.1  | 8.5       |
| 30°-40°   | 2778.2  | 13.8      |
| 40°-50°   | 3795.7  | 18.9      |
| 50°-60°   | 4421.2  | 22.0      |
| 60°-70°   | 3963.7  | 19.7      |
| 70°-80°   | 2003.1  | 10.0      |
| 80°-90°   | 323.5   | 1.6       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 20085.0 | 100.0     |
| 0°-180°   | 20085.0 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P317358  
 CATALOG NUMBER: GLEON-SA4B-727-U-T2R

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 2062.7 | 10.3      |                         |      |         |
| FM (30°-60°)   | 9421.3 | 46.9      |                         |      |         |
| FH (60°-80°)   | 5030.4 | 25.0      |                         |      | G3/7500 |
| FVH (80°-90°)  | 191.0  | 1.0       |                         |      | G2/225  |
| BL (0°-30°)    | 737.1  | 3.7       | B2/1000                 |      |         |
| BM (30°-60°)   | 1573.8 | 7.8       | B2/2500                 |      |         |
| BH (60°-80°)   | 936.3  | 4.7       | B2/1000                 |      | G2/1000 |
| BVH (80°-90°)  | 132.4  | 0.7       |                         |      | G2/225  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G3**

Type II Short





REPORT NUMBER: P317358  
 CATALOG NUMBER: GLEON-SA4B-727-U-T2R

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°     | 65°     | 75°     | 76°     | 85°     |
|-------|--------|--------|--------|--------|--------|--------|---------|---------|---------|---------|---------|
| 0°    | 1834.2 | 1834.2 | 1834.2 | 1834.2 | 1834.2 | 1834.2 | 1834.2  | 1834.2  | 1834.2  | 1834.2  | 1834.2  |
| 2.5°  | 2434.9 | 2398.1 | 2394.7 | 2340.8 | 2328.6 | 2225.6 | 2149.9  | 2070.8  | 1980.8  | 1963.1  | 1892.2  |
| 5°    | 3127.7 | 3124.3 | 3077.3 | 2989.3 | 2920.4 | 2744.5 | 2570.6  | 2386.5  | 2184.7  | 2152.0  | 1992.4  |
| 7.5°  | 3750.9 | 3745.5 | 3709.3 | 3614.6 | 3515.0 | 3298.9 | 3050.7  | 2768.4  | 2441.1  | 2392.7  | 2128.1  |
| 10°   | 4224.1 | 4222.1 | 4209.8 | 4140.3 | 4055.7 | 3848.4 | 3574.3  | 3189.1  | 2739.0  | 2672.9  | 2297.9  |
| 12.5° | 4589.6 | 4593.7 | 4601.9 | 4577.4 | 4537.1 | 4360.5 | 4079.6  | 3635.0  | 3056.8  | 2991.3  | 2486.8  |
| 15°   | 4837.1 | 4849.4 | 4891.7 | 4926.5 | 4947.6 | 4839.2 | 4567.1  | 4091.2  | 3412.7  | 3334.3  | 2696.1  |
| 17.5° | 4961.9 | 4975.6 | 5048.5 | 5153.5 | 5250.4 | 5239.4 | 5023.3  | 4526.2  | 3754.3  | 3678.7  | 2921.1  |
| 20°   | 5069.7 | 5079.9 | 5161.7 | 5287.9 | 5459.0 | 5534.7 | 5413.3  | 4944.9  | 4128.7  | 4038.7  | 3159.8  |
| 22.5° | 5382.0 | 5394.9 | 5419.5 | 5491.0 | 5642.4 | 5781.5 | 5722.9  | 5341.0  | 4471.7  | 4387.8  | 3386.1  |
| 25°   | 5984.7 | 6000.4 | 5947.2 | 5886.5 | 5915.2 | 6012.0 | 6022.9  | 5702.4  | 4819.4  | 4724.6  | 3629.6  |
| 27.5° | 6710.9 | 6733.4 | 6642.7 | 6486.6 | 6350.2 | 6312.7 | 6299.7  | 5998.4  | 5151.5  | 5041.7  | 3870.3  |
| 30°   | 7422.1 | 7461.0 | 7343.0 | 7140.5 | 6890.2 | 6714.3 | 6584.1  | 6288.1  | 5478.8  | 5373.8  | 4097.3  |
| 32.5° | 8116.9 | 8101.2 | 7930.1 | 7732.3 | 7439.1 | 7218.9 | 6903.9  | 6599.1  | 5847.0  | 5726.3  | 4323.0  |
| 35°   | 8592.8 | 8598.3 | 8439.4 | 8204.9 | 7925.3 | 7756.2 | 7332.1  | 6934.6  | 6222.7  | 6111.5  | 4579.4  |
| 37.5° | 8997.9 | 8972.6 | 8792.6 | 8573.8 | 8333.1 | 8260.8 | 7833.3  | 7304.1  | 6629.8  | 6508.4  | 4852.1  |
| 40°   | 9132.9 | 9103.6 | 8985.6 | 8828.1 | 8635.1 | 8629.0 | 8386.2  | 7722.8  | 7090.0  | 6970.0  | 5159.7  |
| 42.5° | 9051.1 | 9013.6 | 8965.1 | 8922.2 | 8862.9 | 8890.1 | 8905.8  | 8213.7  | 7596.0  | 7461.6  | 5515.6  |
| 45°   | 8749.0 | 8692.4 | 8726.5 | 8819.9 | 8948.8 | 9102.9 | 9374.9  | 8757.2  | 8162.6  | 8050.1  | 5933.6  |
| 47.5° | 8284.6 | 8233.5 | 8339.9 | 8539.7 | 8890.1 | 9280.2 | 9818.8  | 9357.2  | 8839.0  | 8727.2  | 6528.8  |
| 50°   | 7631.4 | 7646.4 | 7798.5 | 8161.9 | 8691.7 | 9362.0 | 10365.7 | 10151.6 | 9822.2  | 9717.9  | 7340.9  |
| 52.5° | 6559.5 | 6562.3 | 6990.5 | 7587.1 | 8339.9 | 9319.7 | 10669.1 | 11166.9 | 11164.8 | 11038.7 | 8114.2  |
| 55°   | 5564.0 | 5624.7 | 5963.6 | 6756.6 | 7769.8 | 9150.6 | 10881.2 | 11660.6 | 12046.5 | 11898.5 | 8834.9  |
| 57.5° | 4591.7 | 4627.1 | 4948.3 | 5744.7 | 6956.4 | 8699.9 | 11098.7 | 12253.1 | 13062.5 | 12969.0 | 9730.9  |
| 60°   | 3485.7 | 3540.2 | 3872.3 | 4608.0 | 5915.8 | 7900.1 | 11119.2 | 12871.5 | 14276.9 | 14182.8 | 10731.2 |
| 62.5° | 2262.4 | 2356.5 | 2667.5 | 3356.8 | 4657.1 | 6749.8 | 10644.6 | 13275.9 | 15427.8 | 15394.4 | 11619.0 |
| 65°   | 1300.3 | 1371.2 | 1587.4 | 2119.2 | 3212.9 | 5305.6 | 9516.1  | 13120.4 | 16136.3 | 16117.2 | 11951.0 |
| 66°   | 1062.3 | 1106.7 | 1272.4 | 1656.2 | 2651.1 | 4659.2 | 8860.1  | 12792.4 | 16206.5 | 16207.2 | 11912.8 |
| 67.5° | 849.6  | 869.4  | 943.7  | 1185.8 | 1956.3 | 3693.0 | 7688.0  | 12069.0 | 16119.3 | 16143.1 | 11666.7 |
| 70°   | 703.0  | 713.2  | 736.4  | 795.1  | 1067.8 | 2227.0 | 5457.0  | 10189.1 | 15243.1 | 15261.5 | 10705.9 |
| 72.5° | 630.7  | 636.9  | 645.7  | 653.9  | 753.5  | 1244.4 | 3333.0  | 8151.0  | 13364.5 | 13388.4 | 9242.0  |
| 75°   | 571.4  | 574.8  | 573.4  | 574.1  | 632.1  | 793.0  | 1722.4  | 6085.6  | 10806.2 | 10758.4 | 7079.8  |
| 77.5° | 501.9  | 505.3  | 498.4  | 499.8  | 559.1  | 609.6  | 857.1   | 4260.3  | 7292.5  | 6955.7  | 3988.9  |
| 80°   | 424.1  | 426.8  | 424.1  | 428.9  | 486.9  | 460.3  | 498.4   | 2396.8  | 3224.5  | 3050.0  | 1418.3  |
| 82.5° | 320.5  | 332.1  | 340.3  | 359.3  | 400.9  | 327.3  | 333.4   | 933.5   | 981.9   | 934.8   | 435.0   |
| 85°   | 140.5  | 171.1  | 256.4  | 274.8  | 301.4  | 196.4  | 218.9   | 380.5   | 399.6   | 387.3   | 158.2   |
| 87.5° | 36.8   | 40.2   | 126.8  | 159.6  | 167.1  | 88.6   | 113.9   | 173.2   | 182.7   | 173.2   | 52.5    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P317358  
 CATALOG NUMBER: GLEON-SA4B-727-U-T2R

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1834.2 | 1834.2 | 1834.2 | 1834.2 | 1834.2 | 1834.2 | 1834.2 | 1834.2 | 1834.2 | 1834.2 | 1834.2 |
| 2.5°  | 1854.7 | 1821.3 | 1761.3 | 1708.1 | 1667.8 | 1640.6 | 1613.3 | 1599.7 | 1591.5 | 1583.3 | 1584.7 |
| 5°    | 1914.0 | 1846.5 | 1743.5 | 1670.6 | 1629.7 | 1603.7 | 1590.1 | 1584.7 | 1581.2 | 1573.1 | 1573.1 |
| 7.5°  | 2003.3 | 1907.9 | 1766.0 | 1691.0 | 1659.0 | 1639.2 | 1631.0 | 1628.3 | 1624.2 | 1614.7 | 1616.0 |
| 10°   | 2115.8 | 1982.2 | 1813.1 | 1740.1 | 1710.8 | 1689.0 | 1677.4 | 1673.3 | 1665.8 | 1654.9 | 1656.2 |
| 12.5° | 2248.1 | 2074.2 | 1875.1 | 1798.8 | 1763.3 | 1734.0 | 1714.9 | 1703.3 | 1690.3 | 1676.0 | 1676.7 |
| 15°   | 2392.7 | 2174.5 | 1941.9 | 1851.3 | 1802.8 | 1761.9 | 1731.3 | 1711.5 | 1691.0 | 1673.3 | 1672.6 |
| 17.5° | 2539.3 | 2271.3 | 1993.1 | 1879.9 | 1814.4 | 1760.6 | 1719.0 | 1688.3 | 1663.1 | 1641.2 | 1639.2 |
| 20°   | 2697.5 | 2358.6 | 2021.7 | 1877.2 | 1792.6 | 1728.5 | 1673.3 | 1635.1 | 1607.2 | 1585.3 | 1581.9 |
| 22.5° | 2858.4 | 2440.4 | 2026.5 | 1849.2 | 1744.2 | 1665.8 | 1607.8 | 1565.6 | 1536.9 | 1514.4 | 1506.2 |
| 25°   | 3005.7 | 2503.8 | 2006.7 | 1795.3 | 1676.7 | 1592.2 | 1535.6 | 1492.6 | 1469.4 | 1442.8 | 1434.6 |
| 27.5° | 3140.0 | 2548.1 | 1967.2 | 1726.5 | 1601.0 | 1517.8 | 1464.6 | 1427.8 | 1402.6 | 1382.1 | 1375.3 |
| 30°   | 3260.7 | 2572.0 | 1902.4 | 1644.7 | 1523.3 | 1447.6 | 1402.6 | 1377.4 | 1355.5 | 1329.6 | 1324.9 |
| 32.5° | 3375.2 | 2572.0 | 1819.2 | 1555.3 | 1446.2 | 1385.5 | 1359.0 | 1343.3 | 1318.7 | 1293.5 | 1286.7 |
| 35°   | 3489.8 | 2556.3 | 1721.0 | 1461.9 | 1375.3 | 1341.2 | 1339.9 | 1321.5 | 1283.9 | 1249.9 | 1241.0 |
| 37.5° | 3610.5 | 2524.3 | 1610.6 | 1374.6 | 1317.4 | 1321.5 | 1333.0 | 1292.1 | 1238.9 | 1190.5 | 1177.6 |
| 40°   | 3746.8 | 2479.9 | 1496.0 | 1299.0 | 1268.9 | 1312.6 | 1314.6 | 1249.9 | 1146.2 | 1101.9 | 1090.3 |
| 42.5° | 3907.1 | 2435.6 | 1389.6 | 1232.1 | 1230.8 | 1286.0 | 1279.9 | 1158.5 | 1096.4 | 1073.9 | 1067.8 |
| 45°   | 4117.8 | 2410.4 | 1288.7 | 1168.7 | 1200.8 | 1243.0 | 1220.5 | 1108.0 | 1082.1 | 1069.2 | 1063.7 |
| 47.5° | 4449.8 | 2423.3 | 1196.0 | 1118.3 | 1170.8 | 1200.1 | 1110.1 | 1087.6 | 1069.2 | 1053.5 | 1048.0 |
| 50°   | 4865.8 | 2415.8 | 1121.0 | 1083.5 | 1136.7 | 1155.1 | 1060.3 | 1061.0 | 1051.4 | 1033.7 | 1025.5 |
| 52.5° | 5178.8 | 2357.2 | 1072.6 | 1063.7 | 1106.7 | 1075.3 | 1028.9 | 1035.1 | 1030.3 | 1004.4 | 995.5  |
| 55°   | 5480.8 | 2306.7 | 1048.0 | 1056.2 | 1084.8 | 975.7  | 992.1  | 1007.1 | 1002.3 | 977.1  | 973.0  |
| 57.5° | 5856.5 | 2297.2 | 1033.0 | 1058.3 | 1066.4 | 926.0  | 956.7  | 976.4  | 973.0  | 962.1  | 960.1  |
| 60°   | 6316.8 | 2299.9 | 1019.4 | 1061.7 | 1046.0 | 889.2  | 923.2  | 948.5  | 950.5  | 948.5  | 947.1  |
| 62.5° | 6569.8 | 2225.6 | 985.3  | 1052.1 | 1009.8 | 857.1  | 888.5  | 925.3  | 926.0  | 930.1  | 929.4  |
| 65°   | 6355.0 | 2003.3 | 921.9  | 1018.7 | 949.2  | 830.5  | 858.5  | 898.7  | 888.5  | 906.9  | 906.9  |
| 66°   | 6146.3 | 1875.1 | 890.5  | 996.9  | 923.2  | 820.3  | 848.9  | 885.1  | 872.1  | 897.3  | 897.3  |
| 67.5° | 5720.2 | 1659.0 | 833.9  | 950.5  | 886.4  | 806.0  | 838.0  | 862.6  | 844.8  | 882.3  | 879.6  |
| 70°   | 4941.5 | 1283.3 | 720.0  | 845.5  | 825.7  | 784.8  | 823.0  | 817.6  | 791.6  | 848.9  | 838.0  |
| 72.5° | 4166.2 | 975.1  | 578.2  | 707.8  | 733.7  | 758.2  | 801.9  | 760.3  | 727.5  | 767.8  | 743.9  |
| 75°   | 3232.7 | 733.0  | 456.8  | 550.3  | 619.8  | 716.6  | 776.6  | 694.1  | 647.1  | 643.0  | 630.0  |
| 77.5° | 1747.6 | 503.2  | 362.1  | 420.0  | 492.3  | 664.8  | 759.6  | 623.2  | 552.3  | 535.9  | 525.7  |
| 80°   | 692.1  | 327.3  | 263.2  | 318.4  | 344.3  | 589.8  | 718.7  | 540.7  | 455.5  | 439.1  | 423.4  |
| 82.5° | 285.7  | 193.6  | 169.8  | 213.4  | 224.3  | 504.6  | 645.0  | 443.2  | 351.8  | 486.9  | 516.9  |
| 85°   | 122.7  | 106.4  | 100.9  | 110.5  | 126.8  | 353.9  | 513.4  | 338.2  | 379.8  | 338.9  | 269.3  |
| 87.5° | 36.8   | 45.0   | 43.0   | 42.3   | 46.4   | 84.6   | 273.4  | 188.2  | 278.9  | 105.7  | 79.1   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

**Test Information**

Test Method: LM-79-2008  
 Report Number: SP1-1908-441-1-R4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/28/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGRAW-EDISON  
 Catalog Number: **SA1C-727-U-5WQ**  
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

\*\*\*THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.\*\*\*TESTED IN  
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

**Spectral Parameters**

CCT (K): 2741  
 CIE u': 0.2605  
 CIE v': 0.5272  
 Duv: 0.0005  
 CIE x: 0.4573  
 CIE y: 0.4113  
 CIE z: 0.1313  
 Peak Wavelength (nm): 602  
 Dominant Wavelength (nm): 583  
 Purity: 61.2  
 Rf: 69.9  
 Rg: 98.3

|           |      |      |       |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 |      |       |
| R1:       | 69.2 | R9:  | -16.1 |
| R2:       | 79.4 | R10: | 51.4  |
| R3:       | 87.8 | R11: | 63.1  |
| R4:       | 69.4 | R12: | 42.0  |
| R5:       | 66.4 | R13: | 70.2  |
| R6:       | 69.8 | R14: | 92.4  |
| R7:       | 79.8 |      |       |
| R8:       | 50.1 |      |       |



**Test Conditions**

Stabilization Time: 56M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.3./42%  
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/28/2019        | 12/28/2019           |
| Power Meter                    | IN0071                | 12/5/2018        | 12/5/2019            |
| AC Power Source                | IN0063                | 12/5/2018        | 12/5/2019            |
| DC Power Source                | IN0208                | 12/5/2018        | 12/5/2019            |
| Sphere Thermometer             | IN0085                | 12/5/2018        | 12/5/2019            |
| Room Thermometer               | IN0046                | 12/5/2018        | 12/5/2019            |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

**Photopic Flux vs. Wavelength**




**Photopic Lumens: 6211.7**

| $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360            | 2044                              | 0.0                         | 490            | 7179                              | 1.0                         | 620            | 118034                            | 30.7                        | 750            | 8362                              | 0.0                         | 880            | 3128                              | 0.0                         |
| 365            | 2016                              | 0.0                         | 495            | 10476                             | 1.9                         | 625            | 111884                            | 24.7                        | 755            | 7635                              | 0.0                         | 885            | 3110                              | 0.0                         |
| 370            | 2020                              | 0.0                         | 500            | 15549                             | 3.4                         | 630            | 106119                            | 19.2                        | 760            | 6582                              | 0.0                         | 890            | 2632                              | 0.0                         |
| 375            | 2137                              | 0.0                         | 505            | 22477                             | 6.3                         | 635            | 99706                             | 15.0                        | 765            | 5777                              | 0.0                         | 895            | 2709                              | 0.0                         |
| 380            | 2046                              | 0.0                         | 510            | 30417                             | 10.4                        | 640            | 92142                             | 11.0                        | 770            | 5474                              | 0.0                         | 900            | 2016                              | 0.0                         |
| 385            | 1925                              | 0.0                         | 515            | 39274                             | 16.3                        | 645            | 84987                             | 8.2                         | 775            | 4977                              | 0.0                         | 905            | 1748                              | 0.0                         |
| 390            | 1893                              | 0.0                         | 520            | 47282                             | 22.9                        | 650            | 78016                             | 5.7                         | 780            | 4723                              | 0.0                         | 910            | 2046                              | 0.0                         |
| 395            | 1695                              | 0.0                         | 525            | 55413                             | 29.7                        | 655            | 71541                             | 4.1                         | 785            | 4219                              | 0.0                         | 915            | 1844                              | 0.0                         |
| 400            | 1633                              | 0.0                         | 530            | 62377                             | 36.7                        | 660            | 64863                             | 2.7                         | 790            | 3969                              | 0.0                         | 920            | 2734                              | 0.0                         |
| 405            | 2065                              | 0.0                         | 535            | 68520                             | 42.5                        | 665            | 58485                             | 1.9                         | 795            | 4122                              | 0.0                         | 925            | 2307                              | 0.0                         |
| 410            | 3449                              | 0.0                         | 540            | 73435                             | 47.8                        | 670            | 51641                             | 1.1                         | 800            | 2864                              | 0.0                         | 930            | 2039                              | 0.0                         |
| 415            | 7117                              | 0.0                         | 545            | 78677                             | 52.4                        | 675            | 46030                             | 0.8                         | 805            | 3151                              | 0.0                         | 935            | 1784                              | 0.0                         |
| 420            | 13992                             | 0.0                         | 550            | 83331                             | 56.6                        | 680            | 40590                             | 0.5                         | 810            | 3022                              | 0.0                         | 940            | 2464                              | 0.0                         |
| 425            | 25176                             | 0.1                         | 555            | 89120                             | 60.9                        | 685            | 35691                             | 0.3                         | 815            | 3471                              | 0.0                         | 945            | 2794                              | 0.0                         |
| 430            | 38151                             | 0.3                         | 560            | 94613                             | 64.3                        | 690            | 31631                             | 0.2                         | 820            | 2749                              | 0.0                         | 950            | 3090                              | 0.0                         |
| 435            | 49673                             | 0.6                         | 565            | 99818                             | 66.4                        | 695            | 27437                             | 0.1                         | 825            | 2729                              | 0.0                         | 955            | 1866                              | 0.0                         |
| 440            | 57273                             | 0.9                         | 570            | 106526                            | 69.3                        | 700            | 24589                             | 0.1                         | 830            | 2282                              | 0.0                         | 960            | 3110                              | 0.0                         |
| 445            | 54802                             | 1.1                         | 575            | 111610                            | 69.4                        | 705            | 21832                             | 0.0                         | 835            | 3140                              | 0.0                         | 965            | 3880                              | 0.0                         |
| 450            | 39184                             | 1.0                         | 580            | 117163                            | 69.6                        | 710            | 19500                             | 0.0                         | 840            | 2365                              | 0.0                         | 970            | 3243                              | 0.0                         |
| 455            | 22506                             | 0.8                         | 585            | 122201                            | 67.9                        | 715            | 17870                             | 0.0                         | 845            | 3024                              | 0.0                         | 975            | 2014                              | 0.0                         |
| 460            | 13692                             | 0.6                         | 590            | 125662                            | 65.0                        | 720            | 15924                             | 0.0                         | 850            | 2510                              | 0.0                         | 980            | 1688                              | 0.0                         |
| 465            | 9446                              | 0.5                         | 595            | 127415                            | 60.4                        | 725            | 14268                             | 0.0                         | 855            | 2739                              | 0.0                         | 985            | 2827                              | 0.0                         |
| 470            | 6698                              | 0.4                         | 600            | 129155                            | 55.7                        | 730            | 12438                             | 0.0                         | 860            | 3515                              | 0.0                         | 990            | 4172                              | 0.0                         |
| 475            | 5328                              | 0.4                         | 605            | 128057                            | 49.6                        | 735            | 11255                             | 0.0                         | 865            | 3600                              | 0.0                         | 995            | 3177                              | 0.0                         |
| 480            | 5081                              | 0.5                         | 610            | 126031                            | 43.3                        | 740            | 9951                              | 0.0                         | 870            | 3609                              | 0.0                         | 1000           | 3241                              | 0.0                         |
| 485            | 5579                              | 0.7                         | 615            | 123059                            | 37.1                        | 745            | 8870                              | 0.0                         | 875            | 3208                              | 0.0                         |                |                                   |                             |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2044          | 0.0           | 490    | 7179          | 6.0           | 620    | 118034        | 0.1           | 750    | 8362          | 0.0           | 880    | 3128          | 0.0           |
| 365    | 2016          | 0.0           | 495    | 10476         | 8.6           | 625    | 111884        | 0.1           | 755    | 7635          | 0.0           | 885    | 3110          | 0.0           |
| 370    | 2020          | 0.0           | 500    | 15549         | 12.5          | 630    | 106119        | 0.0           | 760    | 6582          | 0.0           | 890    | 2632          | 0.0           |
| 375    | 2137          | 0.0           | 505    | 22477         | 17.3          | 635    | 99706         | 0.0           | 765    | 5777          | 0.0           | 895    | 2709          | 0.0           |
| 380    | 2046          | 0.0           | 510    | 30417         | 21.8          | 640    | 92142         | 0.0           | 770    | 5474          | 0.0           | 900    | 2016          | 0.0           |
| 385    | 1925          | 0.0           | 515    | 39274         | 25.7          | 645    | 84987         | 0.0           | 775    | 4977          | 0.0           | 905    | 1748          | 0.0           |
| 390    | 1893          | 0.0           | 520    | 47282         | 27.5          | 650    | 78016         | 0.0           | 780    | 4723          | 0.0           | 910    | 2046          | 0.0           |
| 395    | 1695          | 0.0           | 525    | 55413         | 28.1          | 655    | 71541         | 0.0           | 785    | 4219          | 0.0           | 915    | 1844          | 0.0           |
| 400    | 1633          | 0.0           | 530    | 62377         | 27.0          | 660    | 64863         | 0.0           | 790    | 3969          | 0.0           | 920    | 2734          | 0.0           |
| 405    | 2065          | 0.0           | 535    | 68520         | 24.7          | 665    | 58485         | 0.0           | 795    | 4122          | 0.0           | 925    | 2307          | 0.0           |
| 410    | 3449          | 0.1           | 540    | 73435         | 21.5          | 670    | 51641         | 0.0           | 800    | 2864          | 0.0           | 930    | 2039          | 0.0           |
| 415    | 7117          | 0.5           | 545    | 78677         | 18.3          | 675    | 46030         | 0.0           | 805    | 3151          | 0.0           | 935    | 1784          | 0.0           |
| 420    | 13992         | 1.6           | 550    | 83331         | 15.0          | 680    | 40590         | 0.0           | 810    | 3022          | 0.0           | 940    | 2464          | 0.0           |
| 425    | 25176         | 3.9           | 555    | 89120         | 12.0          | 685    | 35691         | 0.0           | 815    | 3471          | 0.0           | 945    | 2794          | 0.0           |
| 430    | 38151         | 8.1           | 560    | 94613         | 9.3           | 690    | 31631         | 0.0           | 820    | 2749          | 0.0           | 950    | 3090          | 0.0           |
| 435    | 49673         | 13.3          | 565    | 99818         | 7.0           | 695    | 27437         | 0.0           | 825    | 2729          | 0.0           | 955    | 1866          | 0.0           |
| 440    | 57273         | 19.1          | 570    | 106526        | 5.2           | 700    | 24589         | 0.0           | 830    | 2282          | 0.0           | 960    | 3110          | 0.0           |
| 445    | 54802         | 21.6          | 575    | 111610        | 3.7           | 705    | 21832         | 0.0           | 835    | 3140          | 0.0           | 965    | 3880          | 0.0           |
| 450    | 39184         | 18.1          | 580    | 117163        | 2.6           | 710    | 19500         | 0.0           | 840    | 2365          | 0.0           | 970    | 3243          | 0.0           |
| 455    | 22506         | 11.8          | 585    | 122201        | 1.8           | 715    | 17870         | 0.0           | 845    | 3024          | 0.0           | 975    | 2014          | 0.0           |
| 460    | 13692         | 8.1           | 590    | 125662        | 1.2           | 720    | 15924         | 0.0           | 850    | 2510          | 0.0           | 980    | 1688          | 0.0           |
| 465    | 9446          | 6.2           | 595    | 127415        | 0.8           | 725    | 14268         | 0.0           | 855    | 2739          | 0.0           | 985    | 2827          | 0.0           |
| 470    | 6698          | 4.8           | 600    | 129155        | 0.5           | 730    | 12438         | 0.0           | 860    | 3515          | 0.0           | 990    | 4172          | 0.0           |
| 475    | 5328          | 4.1           | 605    | 128057        | 0.4           | 735    | 11255         | 0.0           | 865    | 3600          | 0.0           | 995    | 3177          | 0.0           |
| 480    | 5081          | 4.1           | 610    | 126031        | 0.2           | 740    | 9951          | 0.0           | 870    | 3609          | 0.0           | 1000   | 3241          | 0.0           |
| 485    | 5579          | 4.6           | 615    | 123059        | 0.1           | 745    | 8870          | 0.0           | 875    | 3208          | 0.0           |        |               |               |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360            | 2044                              | 0.0                         | 490            | 7179                              | 11.1                        | 620            | 118034                            | 1.5                         | 750            | 8362                              | 0.0                         | 880            | 3128                              | 0.0                         |
| 365            | 2016                              | 0.0                         | 495            | 10476                             | 16.9                        | 625            | 111884                            | 0.9                         | 755            | 7635                              | 0.0                         | 885            | 3110                              | 0.0                         |
| 370            | 2020                              | 0.0                         | 500            | 15549                             | 26.0                        | 630            | 106119                            | 0.6                         | 760            | 6582                              | 0.0                         | 890            | 2632                              | 0.0                         |
| 375            | 2137                              | 0.0                         | 505            | 22477                             | 38.2                        | 635            | 99706                             | 0.4                         | 765            | 5777                              | 0.0                         | 895            | 2709                              | 0.0                         |
| 380            | 2046                              | 0.0                         | 510            | 30417                             | 51.6                        | 640            | 92142                             | 0.2                         | 770            | 5474                              | 0.0                         | 900            | 2016                              | 0.0                         |
| 385            | 1925                              | 0.0                         | 515            | 39274                             | 65.1                        | 645            | 84987                             | 0.1                         | 775            | 4977                              | 0.0                         | 905            | 1748                              | 0.0                         |
| 390            | 1893                              | 0.0                         | 520            | 47282                             | 75.2                        | 650            | 78016                             | 0.1                         | 780            | 4723                              | 0.0                         | 910            | 2046                              | 0.0                         |
| 395            | 1695                              | 0.0                         | 525            | 55413                             | 82.9                        | 655            | 71541                             | 0.1                         | 785            | 4219                              | 0.0                         | 915            | 1844                              | 0.0                         |
| 400            | 1633                              | 0.0                         | 530            | 62377                             | 86.0                        | 660            | 64863                             | 0.0                         | 790            | 3969                              | 0.0                         | 920            | 2734                              | 0.0                         |
| 405            | 2065                              | 0.1                         | 535            | 68520                             | 85.4                        | 665            | 58485                             | 0.0                         | 795            | 4122                              | 0.0                         | 925            | 2307                              | 0.0                         |
| 410            | 3449                              | 0.2                         | 540            | 73435                             | 81.1                        | 670            | 51641                             | 0.0                         | 800            | 2864                              | 0.0                         | 930            | 2039                              | 0.0                         |
| 415            | 7117                              | 0.7                         | 545            | 78677                             | 75.4                        | 675            | 46030                             | 0.0                         | 805            | 3151                              | 0.0                         | 935            | 1784                              | 0.0                         |
| 420            | 13992                             | 2.3                         | 550            | 83331                             | 68.1                        | 680            | 40590                             | 0.0                         | 810            | 3022                              | 0.0                         | 940            | 2464                              | 0.0                         |
| 425            | 25176                             | 6.2                         | 555            | 89120                             | 60.9                        | 685            | 35691                             | 0.0                         | 815            | 3471                              | 0.0                         | 945            | 2794                              | 0.0                         |
| 430            | 38151                             | 13.0                        | 560            | 94613                             | 52.9                        | 690            | 31631                             | 0.0                         | 820            | 2749                              | 0.0                         | 950            | 3090                              | 0.0                         |
| 435            | 49673                             | 22.2                        | 565            | 99818                             | 44.8                        | 695            | 27437                             | 0.0                         | 825            | 2729                              | 0.0                         | 955            | 1866                              | 0.0                         |
| 440            | 57273                             | 32.0                        | 570            | 106526                            | 37.6                        | 700            | 24589                             | 0.0                         | 830            | 2282                              | 0.0                         | 960            | 3110                              | 0.0                         |
| 445            | 54802                             | 36.7                        | 575            | 111610                            | 30.4                        | 705            | 21832                             | 0.0                         | 835            | 3140                              | 0.0                         | 965            | 3880                              | 0.0                         |
| 450            | 39184                             | 30.4                        | 580            | 117163                            | 24.1                        | 710            | 19500                             | 0.0                         | 840            | 2365                              | 0.0                         | 970            | 3243                              | 0.0                         |
| 455            | 22506                             | 19.7                        | 585            | 122201                            | 18.7                        | 715            | 17870                             | 0.0                         | 845            | 3024                              | 0.0                         | 975            | 2014                              | 0.0                         |
| 460            | 13692                             | 13.2                        | 590            | 125662                            | 14.0                        | 720            | 15924                             | 0.0                         | 850            | 2510                              | 0.0                         | 980            | 1688                              | 0.0                         |
| 465            | 9446                              | 10.0                        | 595            | 127415                            | 10.2                        | 725            | 14268                             | 0.0                         | 855            | 2739                              | 0.0                         | 985            | 2827                              | 0.0                         |
| 470            | 6698                              | 7.7                         | 600            | 129155                            | 7.3                         | 730            | 12438                             | 0.0                         | 860            | 3515                              | 0.0                         | 990            | 4172                              | 0.0                         |
| 475            | 5328                              | 6.7                         | 605            | 128057                            | 5.0                         | 735            | 11255                             | 0.0                         | 865            | 3600                              | 0.0                         | 995            | 3177                              | 0.0                         |
| 480            | 5081                              | 6.9                         | 610            | 126031                            | 3.4                         | 740            | 9951                              | 0.0                         | 870            | 3609                              | 0.0                         | 1000           | 3241                              | 0.0                         |
| 485            | 5579                              | 8.1                         | 615            | 123059                            | 2.3                         | 745            | 8870                              | 0.0                         | 875            | 3208                              | 0.0                         |                |                                   |                             |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

**Summary**

$R_f = 69.9$   
 $R_g = 98.3$   
 CIE  $R_a = 71.5$   
 $R_9 = -16.1$



**Color Vector Graphics**





REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 |            |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)