

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P318949

Luminaire Tested: **GLEON-SA5A-727-U-T4W**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P318949
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GLEON-SA5A-727-U-T4W
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(5) 70 CRI, 2700K, 615mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV WIDE OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 19343 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G4


Input Watts (W): 162
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P318949
 CATALOG NUMBER: GLEON-SA5A-727-U-T4W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 3.9 fc
 Type IV - Short - N/A

REPORT NUMBER: P318949
CATALOG NUMBER: GLEON-SA5A-727-U-T4W

Luminous Intensity Polar Plot



— Vertical Plane Through 46-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P318949
 CATALOG NUMBER: GLEON-SA5A-727-U-T4W

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 4433.4 | 0.0 | 4433.4 |
| | % Fixture | 22.9 | 0.0 | 22.9 |
| Street Side | Lumens | 14909.6 | 0.0 | 14909.6 |
| | % Fixture | 77.1 | 0.0 | 77.1 |
| Total | Lumens | 19343.0 | 0.0 | 19343.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 200.9 | 1.0 |
| 10°-20° | 669.3 | 3.5 |
| 20°-30° | 1116.0 | 5.8 |
| 30°-40° | 1583.7 | 8.2 |
| 40°-50° | 2329.5 | 12.0 |
| 50°-60° | 3945.1 | 20.4 |
| 60°-70° | 5600.0 | 29.0 |
| 70°-80° | 3402.0 | 17.6 |
| 80°-90° | 496.5 | 2.6 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 19343.0 | 100.0 |
| 0°-180° | 19343.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P318949
 CATALOG NUMBER: GLEON-SA5A-727-U-T4W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|----------|
| | | | B | U | G |
| FL (0°-30°) | 1055.4 | 5.5 | | | |
| FM (30°-60°) | 5817.5 | 30.1 | | | |
| FH (60°-80°) | 7727.4 | 39.9 | | | G4/12000 |
| FVH (80°-90°) | 309.3 | 1.6 | | | G3/500 |
| BL (0°-30°) | 930.8 | 4.8 | B2/1000 | | |
| BM (30°-60°) | 2040.8 | 10.6 | B2/2500 | | |
| BH (60°-80°) | 1274.6 | 6.6 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 187.2 | 1.0 | | | G2/225 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G4

Type IV Short





REPORT NUMBER: P318949
 CATALOG NUMBER: GLEON-SA5A-727-U-T4W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 46° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 1970.7 | 1970.7 | 1970.7 | 1970.7 | 1970.7 | 1970.7 | 1970.7 | 1970.7 | 1970.7 | 1970.7 | 1970.7 |
| 2.5° | 2069.3 | 2070.6 | 2073.3 | 2066.7 | 2048.1 | 2042.8 | 2040.8 | 2021.6 | 2009.1 | 1990.5 | 1974.6 |
| 5° | 2234.8 | 2236.1 | 2232.1 | 2213.6 | 2172.6 | 2142.1 | 2139.5 | 2095.8 | 2056.1 | 2013.7 | 1981.9 |
| 7.5° | 2407.6 | 2409.6 | 2397.0 | 2361.9 | 2304.3 | 2251.3 | 2248.0 | 2188.5 | 2128.2 | 2064.0 | 2016.3 |
| 10° | 2560.5 | 2552.5 | 2532.0 | 2483.0 | 2414.9 | 2350.0 | 2347.3 | 2285.1 | 2215.6 | 2138.2 | 2074.6 |
| 12.5° | 2662.4 | 2655.8 | 2629.3 | 2569.8 | 2495.0 | 2435.4 | 2430.1 | 2372.5 | 2305.0 | 2220.2 | 2144.1 |
| 15° | 2718.7 | 2723.3 | 2687.6 | 2620.1 | 2547.2 | 2496.9 | 2492.3 | 2451.3 | 2391.0 | 2305.6 | 2218.2 |
| 17.5° | 2726.0 | 2729.9 | 2695.5 | 2628.7 | 2569.1 | 2534.7 | 2532.7 | 2505.5 | 2461.9 | 2379.8 | 2288.4 |
| 20° | 2683.6 | 2686.3 | 2657.8 | 2602.9 | 2563.8 | 2553.2 | 2552.5 | 2540.6 | 2508.2 | 2435.4 | 2346.7 |
| 22.5° | 2622.0 | 2624.0 | 2603.5 | 2563.8 | 2550.6 | 2567.1 | 2571.7 | 2567.1 | 2543.9 | 2475.8 | 2392.3 |
| 25° | 2606.8 | 2605.5 | 2584.3 | 2543.9 | 2555.2 | 2590.3 | 2596.2 | 2598.2 | 2582.3 | 2522.8 | 2450.6 |
| 27.5° | 2680.3 | 2675.7 | 2635.3 | 2570.4 | 2577.7 | 2620.1 | 2628.0 | 2647.2 | 2637.3 | 2585.0 | 2516.8 |
| 30° | 2892.8 | 2884.8 | 2802.1 | 2671.0 | 2635.3 | 2657.1 | 2667.1 | 2697.5 | 2699.5 | 2655.8 | 2604.8 |
| 32.5° | 3251.6 | 3241.6 | 3093.4 | 2859.0 | 2732.6 | 2694.9 | 2704.1 | 2749.8 | 2774.3 | 2740.5 | 2685.6 |
| 35° | 3705.0 | 3693.8 | 3499.2 | 3178.8 | 2895.4 | 2767.0 | 2773.6 | 2810.0 | 2859.0 | 2811.4 | 2738.6 |
| 37.5° | 4177.7 | 4150.5 | 3963.2 | 3554.8 | 3154.3 | 2921.3 | 2921.3 | 2925.9 | 2949.1 | 2849.8 | 2800.8 |
| 40° | 4647.7 | 4620.5 | 4451.1 | 3997.0 | 3489.2 | 3164.2 | 3149.0 | 3046.4 | 3027.8 | 2942.4 | 2925.9 |
| 42.5° | 5084.6 | 5076.6 | 4976.7 | 4496.7 | 3882.4 | 3403.2 | 3382.0 | 3207.9 | 3211.9 | 3158.9 | 3159.6 |
| 45° | 5549.3 | 5549.3 | 5467.8 | 5001.2 | 4340.5 | 3787.1 | 3765.9 | 3509.7 | 3549.5 | 3525.0 | 3583.9 |
| 47.5° | 5928.6 | 5940.5 | 5929.2 | 5526.8 | 4873.4 | 4275.0 | 4236.6 | 3928.1 | 4039.3 | 4123.4 | 4294.8 |
| 50° | 6315.8 | 6334.4 | 6336.3 | 6103.3 | 5517.5 | 4854.9 | 4811.2 | 4483.5 | 4731.7 | 4972.7 | 5309.6 |
| 52.5° | 6877.8 | 6919.5 | 6753.4 | 6678.6 | 6306.6 | 5543.3 | 5500.3 | 5197.8 | 5612.1 | 5950.4 | 6531.0 |
| 55° | 7398.8 | 7362.4 | 7243.9 | 7290.2 | 7151.2 | 6327.1 | 6294.6 | 6029.2 | 6593.2 | 7032.7 | 7786.7 |
| 57.5° | 7680.8 | 7678.1 | 7797.3 | 7995.9 | 8062.1 | 7293.5 | 7266.4 | 7008.2 | 7699.3 | 8029.6 | 8965.7 |
| 60° | 8011.8 | 8016.4 | 8311.6 | 8762.4 | 9035.2 | 8497.0 | 8485.1 | 8289.1 | 8773.7 | 8960.4 | 9890.4 |
| 62.5° | 8058.1 | 8141.5 | 8649.9 | 9425.7 | 9946.0 | 9903.0 | 9929.5 | 9442.9 | 9734.9 | 9703.1 | 10580.9 |
| 65° | 7525.2 | 7635.1 | 8555.2 | 9626.3 | 10851.6 | 11440.8 | 11465.3 | 10603.4 | 10492.8 | 10337.9 | 10827.8 |
| 67.5° | 6433.0 | 6595.8 | 7595.4 | 9190.1 | 11150.2 | 12577.4 | 12611.8 | 11503.0 | 11121.7 | 10553.1 | 10233.3 |
| 70° | 4681.4 | 4862.1 | 5868.3 | 7848.9 | 10617.9 | 12940.8 | 12979.8 | 11900.8 | 11145.5 | 9940.7 | 8736.0 |
| 72.5° | 2827.9 | 2969.6 | 3799.0 | 5778.3 | 8961.7 | 12278.8 | 12348.3 | 11396.4 | 10175.7 | 8420.2 | 6450.9 |
| 75° | 1241.8 | 1334.5 | 1837.0 | 3329.7 | 6415.8 | 10159.2 | 10245.9 | 9754.7 | 8268.0 | 6119.2 | 3812.9 |
| 77.5° | 528.9 | 555.4 | 753.3 | 1446.4 | 3626.9 | 6942.0 | 7061.2 | 7127.4 | 5609.5 | 3329.7 | 1611.2 |
| 80° | 329.7 | 340.3 | 426.3 | 654.7 | 1697.3 | 3899.0 | 4027.4 | 4193.6 | 2785.6 | 1224.0 | 562.7 |
| 82.5° | 200.6 | 212.5 | 283.3 | 395.9 | 883.7 | 1767.4 | 1829.0 | 1946.2 | 1081.0 | 528.9 | 291.3 |
| 85° | 120.5 | 129.1 | 173.4 | 250.2 | 503.1 | 695.1 | 694.4 | 767.9 | 509.1 | 340.3 | 153.6 |
| 87.5° | 57.6 | 64.2 | 92.7 | 129.7 | 253.5 | 260.8 | 244.3 | 276.7 | 309.1 | 223.1 | 77.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P318949
 CATALOG NUMBER: GLEON-SA5A-727-U-T4W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1970.7 | 1970.7 | 1970.7 | 1970.7 | 1970.7 | 1970.7 | 1970.7 | 1970.7 | 1970.7 | 1970.7 | 1970.7 |
| 2.5° | 1969.3 | 1966.7 | 1958.1 | 1951.5 | 1950.2 | 1946.2 | 1942.9 | 1944.9 | 1947.5 | 1948.2 | 1948.2 |
| 5° | 1968.7 | 1961.4 | 1950.2 | 1945.5 | 1951.5 | 1959.4 | 1969.3 | 1982.6 | 1990.5 | 1996.5 | 2000.5 |
| 7.5° | 2000.5 | 1986.6 | 1974.0 | 1971.3 | 1983.3 | 2004.4 | 2026.9 | 2054.7 | 2073.9 | 2087.2 | 2089.8 |
| 10° | 2053.4 | 2036.2 | 2023.6 | 2026.3 | 2047.5 | 2077.9 | 2109.7 | 2145.4 | 2174.6 | 2192.4 | 2193.8 |
| 12.5° | 2114.3 | 2097.8 | 2085.9 | 2097.1 | 2132.2 | 2169.3 | 2202.4 | 2233.5 | 2260.0 | 2277.8 | 2277.8 |
| 15° | 2184.5 | 2172.6 | 2158.7 | 2184.5 | 2232.1 | 2265.2 | 2279.1 | 2294.4 | 2308.9 | 2322.2 | 2319.5 |
| 17.5° | 2252.0 | 2240.8 | 2233.5 | 2263.9 | 2313.6 | 2328.8 | 2319.5 | 2308.3 | 2308.3 | 2315.6 | 2316.9 |
| 20° | 2310.3 | 2300.3 | 2305.0 | 2334.8 | 2360.6 | 2344.7 | 2310.3 | 2274.5 | 2260.0 | 2263.9 | 2267.9 |
| 22.5° | 2361.2 | 2356.6 | 2370.5 | 2384.4 | 2365.9 | 2310.3 | 2246.7 | 2198.4 | 2180.5 | 2179.2 | 2180.5 |
| 25° | 2420.8 | 2420.1 | 2437.4 | 2412.2 | 2330.1 | 2227.5 | 2142.1 | 2095.1 | 2085.2 | 2093.1 | 2106.4 |
| 27.5° | 2495.0 | 2502.2 | 2510.8 | 2418.8 | 2257.3 | 2102.4 | 2015.7 | 1983.3 | 1993.2 | 2012.4 | 2025.0 |
| 30° | 2589.6 | 2609.5 | 2590.9 | 2402.3 | 2152.7 | 1959.4 | 1876.7 | 1867.4 | 1894.5 | 1921.7 | 1934.9 |
| 32.5° | 2681.6 | 2712.7 | 2667.7 | 2359.2 | 2017.7 | 1807.8 | 1743.6 | 1741.0 | 1774.1 | 1800.5 | 1819.1 |
| 35° | 2755.8 | 2817.3 | 2725.3 | 2273.9 | 1861.4 | 1668.2 | 1621.2 | 1603.3 | 1615.2 | 1646.3 | 1667.5 |
| 37.5° | 2852.4 | 2955.0 | 2765.0 | 2143.4 | 1692.0 | 1553.0 | 1498.0 | 1457.0 | 1446.4 | 1459.0 | 1469.6 |
| 40° | 3029.2 | 3164.9 | 2783.6 | 1961.4 | 1526.5 | 1437.8 | 1382.2 | 1321.9 | 1280.2 | 1249.8 | 1250.5 |
| 42.5° | 3317.8 | 3438.3 | 2771.7 | 1740.3 | 1373.6 | 1325.3 | 1262.4 | 1192.9 | 1125.3 | 1056.5 | 1051.2 |
| 45° | 3786.4 | 3844.7 | 2735.9 | 1506.0 | 1239.2 | 1207.4 | 1148.5 | 1079.0 | 989.0 | 910.9 | 903.6 |
| 47.5° | 4536.5 | 4407.4 | 2680.3 | 1301.4 | 1120.7 | 1107.5 | 1053.2 | 973.1 | 877.8 | 814.9 | 809.6 |
| 50° | 5559.2 | 5219.6 | 2653.2 | 1138.6 | 1016.1 | 1020.1 | 975.7 | 891.0 | 801.0 | 754.6 | 749.3 |
| 52.5° | 6782.5 | 6165.6 | 2705.5 | 1012.8 | 932.0 | 945.9 | 912.9 | 833.4 | 758.0 | 721.5 | 716.2 |
| 55° | 8051.5 | 7145.3 | 2761.7 | 921.5 | 852.6 | 879.8 | 868.5 | 803.0 | 734.8 | 701.0 | 696.4 |
| 57.5° | 9137.8 | 7876.7 | 2649.2 | 847.3 | 781.8 | 824.1 | 834.1 | 783.8 | 722.9 | 692.4 | 687.1 |
| 60° | 9821.6 | 8171.3 | 2354.0 | 777.8 | 725.5 | 779.8 | 814.2 | 778.5 | 727.5 | 724.9 | 720.9 |
| 62.5° | 10146.0 | 8145.5 | 1911.1 | 722.9 | 690.4 | 760.6 | 828.8 | 808.3 | 780.5 | 804.3 | 806.3 |
| 65° | 10000.3 | 7756.3 | 1423.2 | 686.5 | 665.3 | 767.9 | 872.5 | 864.5 | 795.7 | 819.5 | 822.8 |
| 67.5° | 9041.8 | 6827.5 | 1053.9 | 654.7 | 637.5 | 788.4 | 951.9 | 883.1 | 765.9 | 783.1 | 772.5 |
| 70° | 7308.1 | 5412.9 | 812.9 | 618.9 | 609.0 | 785.8 | 987.7 | 871.8 | 733.5 | 737.4 | 709.0 |
| 72.5° | 5039.5 | 3691.1 | 661.3 | 585.8 | 568.0 | 716.2 | 962.5 | 844.0 | 706.3 | 675.9 | 638.1 |
| 75° | 2740.5 | 1981.3 | 562.0 | 551.4 | 495.8 | 628.9 | 916.2 | 824.1 | 681.8 | 641.4 | 620.3 |
| 77.5° | 1078.3 | 822.2 | 487.9 | 504.4 | 433.6 | 555.4 | 864.5 | 786.4 | 648.1 | 595.1 | 584.5 |
| 80° | 440.2 | 419.7 | 404.5 | 436.2 | 372.7 | 485.9 | 802.3 | 742.1 | 607.7 | 552.1 | 530.9 |
| 82.5° | 249.6 | 260.8 | 314.4 | 344.2 | 302.5 | 447.5 | 772.5 | 706.3 | 559.4 | 494.5 | 469.3 |
| 85° | 127.8 | 152.9 | 219.1 | 246.9 | 222.4 | 380.6 | 711.6 | 618.3 | 448.8 | 378.6 | 380.6 |
| 87.5° | 61.6 | 85.4 | 138.4 | 154.9 | 144.3 | 275.4 | 531.6 | 448.2 | 349.5 | 276.7 | 268.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 CIE $R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)