

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P319939

Luminaire Tested: **GLEON-SA5D-727-U-SL4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P319939
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-24)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GLEON-SA5D-727-U-SL4
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(5) 70 CRI, 2700K, 1200mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV
SPILL LIGHT ELIMINATOR OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 30817 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G5


Input Watts (W): 320
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P319939
 CATALOG NUMBER: GLEON-SA5D-727-U-SL4

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 8.8 fc
 Type IV - Short - N/A

REPORT NUMBER: P319939
CATALOG NUMBER: GLEON-SA5D-727-U-SL4

Luminous Intensity Polar Plot



— Vertical Plane Through 37-Deg Lateral - - - Horizontal Cone Through 74-Deg Vertical

REPORT NUMBER: P319939
 CATALOG NUMBER: GLEON-SA5D-727-U-SL4


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 4240.2 | 0.0 | 4240.2 |
| | % Fixture | 13.8 | 0.0 | 13.8 |
| Street Side | Lumens | 26576.8 | 0.0 | 26576.8 |
| | % Fixture | 86.2 | 0.0 | 86.2 |
| Total | Lumens | 30817.0 | 0.0 | 30817.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 478.2 | 1.6 |
| 10°-20° | 1225.6 | 4.0 |
| 20°-30° | 1888.5 | 6.1 |
| 30°-40° | 2746.1 | 8.9 |
| 40°-50° | 4041.8 | 13.1 |
| 50°-60° | 5676.0 | 18.4 |
| 60°-70° | 7184.1 | 23.3 |
| 70°-80° | 6325.9 | 20.5 |
| 80°-90° | 1250.8 | 4.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 30817.0 | 100.0 |
| 0°-180° | 30817.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P319939
 CATALOG NUMBER: GLEON-SA5D-727-U-SL4

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 2397.9 | 7.8 | | | |
| FM (30°-60°) | 10434.9 | 33.9 | | | |
| FH (60°-80°) | 12577.9 | 40.8 | | | G5 |
| FVH (80°-90°) | 1166.1 | 3.8 | | | G5 |
| BL (0°-30°) | 1194.4 | 3.9 | B3/2500 | | |
| BM (30°-60°) | 2029.1 | 6.6 | B2/2500 | | |
| BH (60°-80°) | 932.0 | 3.0 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 84.7 | 0.3 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G5
 Type IV Short





REPORT NUMBER: P319939

CATALOG NUMBER: GLEON-SA5D-727-U-SL4

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 37° | 45° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 5429.8 | 5429.8 | 5429.8 | 5429.8 | 5429.8 | 5429.8 | 5429.8 | 5429.8 | 5429.8 | 5429.8 | 5429.8 |
| 2.5° | 5615.5 | 5616.5 | 5615.5 | 5606.8 | 5586.2 | 5568.8 | 5554.7 | 5534.0 | 5488.5 | 5453.7 | 5401.6 |
| 5° | 5668.7 | 5662.1 | 5657.8 | 5641.5 | 5608.9 | 5589.4 | 5562.3 | 5523.2 | 5448.3 | 5378.8 | 5294.1 |
| 7.5° | 5643.7 | 5636.1 | 5626.3 | 5606.8 | 5569.9 | 5553.6 | 5515.6 | 5464.6 | 5374.5 | 5283.3 | 5161.7 |
| 10° | 5566.6 | 5564.4 | 5560.1 | 5555.8 | 5524.3 | 5511.3 | 5476.5 | 5422.2 | 5333.2 | 5222.5 | 5080.3 |
| 12.5° | 5480.9 | 5486.3 | 5503.7 | 5526.4 | 5512.3 | 5505.8 | 5484.1 | 5447.2 | 5356.0 | 5236.6 | 5065.1 |
| 15° | 5426.6 | 5441.8 | 5488.5 | 5548.2 | 5560.1 | 5557.9 | 5552.5 | 5528.6 | 5432.0 | 5299.6 | 5099.8 |
| 17.5° | 5408.1 | 5433.1 | 5522.1 | 5620.9 | 5655.6 | 5663.2 | 5665.4 | 5624.1 | 5516.7 | 5376.6 | 5135.7 |
| 20° | 5441.8 | 5473.3 | 5603.5 | 5739.2 | 5794.6 | 5798.9 | 5789.1 | 5717.5 | 5597.0 | 5442.9 | 5155.2 |
| 22.5° | 5543.8 | 5572.0 | 5734.9 | 5887.9 | 5950.9 | 5957.4 | 5928.1 | 5819.5 | 5681.7 | 5521.0 | 5182.3 |
| 25° | 5740.3 | 5775.0 | 5937.9 | 6090.9 | 6123.5 | 6124.6 | 6082.2 | 5947.6 | 5792.4 | 5630.7 | 5241.0 |
| 27.5° | 5996.5 | 6031.2 | 6177.8 | 6327.6 | 6310.2 | 6300.4 | 6242.9 | 6108.3 | 5936.8 | 5781.5 | 5345.2 |
| 30° | 6282.0 | 6320.0 | 6458.9 | 6565.3 | 6524.1 | 6504.5 | 6457.8 | 6284.2 | 6137.6 | 5987.8 | 5504.7 |
| 32.5° | 6577.2 | 6612.0 | 6733.6 | 6806.3 | 6754.2 | 6745.5 | 6674.9 | 6516.5 | 6399.2 | 6302.6 | 5763.1 |
| 35° | 6880.1 | 6905.1 | 7024.5 | 7065.7 | 6996.3 | 6994.1 | 6974.5 | 6829.1 | 6755.3 | 6800.9 | 6138.7 |
| 37.5° | 7189.5 | 7196.0 | 7298.0 | 7300.2 | 7279.6 | 7288.3 | 7308.9 | 7217.7 | 7238.3 | 7380.5 | 6627.2 |
| 40° | 7465.2 | 7482.6 | 7556.4 | 7579.2 | 7615.0 | 7645.4 | 7748.5 | 7688.8 | 7848.4 | 8100.2 | 7235.1 |
| 42.5° | 7669.3 | 7702.9 | 7821.3 | 7879.9 | 7996.0 | 8043.8 | 8189.3 | 8244.6 | 8565.9 | 8943.7 | 7958.0 |
| 45° | 7841.9 | 7894.0 | 8084.0 | 8204.5 | 8400.9 | 8484.5 | 8692.9 | 8878.6 | 9376.8 | 9858.8 | 8719.0 |
| 47.5° | 8028.6 | 8094.8 | 8332.6 | 8562.7 | 8829.7 | 8924.2 | 9303.0 | 9580.9 | 10242.0 | 10779.3 | 9436.5 |
| 50° | 8303.2 | 8354.3 | 8586.6 | 8948.0 | 9281.3 | 9402.9 | 9927.2 | 10325.6 | 11121.3 | 11656.5 | 10058.5 |
| 52.5° | 8686.4 | 8666.9 | 8863.4 | 9370.3 | 9817.6 | 9967.4 | 10593.7 | 11118.0 | 12012.5 | 12450.0 | 10583.9 |
| 55° | 9071.8 | 9039.2 | 9177.1 | 9812.1 | 10442.8 | 10600.2 | 11327.5 | 11913.7 | 12860.3 | 13164.3 | 10986.7 |
| 57.5° | 9500.6 | 9438.7 | 9554.9 | 10310.4 | 11154.9 | 11342.7 | 12149.3 | 12759.4 | 13694.0 | 13741.8 | 11242.9 |
| 60° | 9942.4 | 9858.8 | 9989.1 | 10928.1 | 12059.2 | 12280.6 | 13111.1 | 13584.4 | 14479.9 | 14204.2 | 11325.4 |
| 62.5° | 10328.8 | 10270.2 | 10471.1 | 11617.4 | 13078.5 | 13321.7 | 14055.5 | 14461.5 | 15255.0 | 14396.3 | 11027.9 |
| 65° | 10666.4 | 10676.2 | 11023.6 | 12392.4 | 14215.1 | 14474.5 | 15138.8 | 15542.7 | 15865.1 | 14282.4 | 10332.1 |
| 67.5° | 11069.2 | 11124.5 | 11717.2 | 13412.8 | 15645.8 | 15930.2 | 16715.0 | 16721.6 | 16205.9 | 13613.7 | 8962.2 |
| 70° | 11656.5 | 11770.4 | 12671.4 | 14828.4 | 17680.1 | 18070.9 | 18676.6 | 17414.1 | 15727.2 | 11800.8 | 7051.6 |
| 72.5° | 12177.5 | 12390.3 | 13686.4 | 16448.0 | 20159.4 | 20455.8 | 19824.0 | 17014.6 | 13726.6 | 8843.8 | 4393.2 |
| 74° | 11965.8 | 12229.6 | 13870.9 | 17245.9 | 21093.0 | 21235.2 | 19436.5 | 15848.8 | 11444.8 | 6124.6 | 2553.2 |
| 75° | 11509.9 | 11796.5 | 13601.7 | 17238.3 | 20974.7 | 20895.4 | 18500.7 | 14516.8 | 9425.7 | 4177.1 | 1698.9 |
| 77.5° | 9288.9 | 9591.8 | 11461.1 | 14774.1 | 17198.1 | 17123.2 | 14211.8 | 9738.3 | 4128.3 | 1369.9 | 863.0 |
| 80° | 5400.5 | 5631.7 | 7114.6 | 9382.3 | 11596.7 | 11732.4 | 9346.4 | 4818.7 | 1624.0 | 769.6 | 585.1 |
| 82.5° | 2399.0 | 2558.6 | 3436.8 | 4789.4 | 6998.4 | 7173.2 | 4894.7 | 2524.9 | 1003.0 | 467.9 | 351.7 |
| 85° | 1574.0 | 1692.3 | 2086.4 | 2280.7 | 3332.6 | 3452.0 | 2395.8 | 1965.9 | 662.2 | 257.3 | 258.4 |
| 87.5° | 1132.2 | 1246.2 | 1550.1 | 1353.7 | 1529.5 | 1448.1 | 1303.7 | 1819.4 | 266.0 | 146.5 | 86.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P319939
 CATALOG NUMBER: GLEON-SA5D-727-U-SL4

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 5429.8 | 5429.8 | 5429.8 | 5429.8 | 5429.8 | 5429.8 | 5429.8 | 5429.8 | 5429.8 | 5429.8 | 5429.8 |
| 2.5° | 5378.8 | 5361.4 | 5322.4 | 5248.6 | 5207.3 | 5172.6 | 5115.0 | 5081.4 | 5066.2 | 5065.1 | 5071.6 |
| 5° | 5245.3 | 5205.1 | 5104.2 | 4980.4 | 4881.6 | 4791.5 | 4679.7 | 4612.4 | 4564.7 | 4536.4 | 4544.0 |
| 7.5° | 5090.1 | 5027.1 | 4868.6 | 4671.0 | 4512.6 | 4337.8 | 4165.2 | 4062.1 | 3981.7 | 3922.0 | 3932.9 |
| 10° | 4983.7 | 4896.8 | 4665.6 | 4381.2 | 4117.4 | 3863.4 | 3625.7 | 3483.5 | 3370.6 | 3283.7 | 3290.3 |
| 12.5° | 4947.9 | 4830.6 | 4510.4 | 4130.5 | 3760.3 | 3412.9 | 3102.5 | 2884.3 | 2768.1 | 2669.3 | 2676.9 |
| 15° | 4953.3 | 4795.9 | 4380.1 | 3904.7 | 3439.0 | 3001.5 | 2624.8 | 2369.7 | 2212.3 | 2143.9 | 2145.0 |
| 17.5° | 4957.6 | 4755.7 | 4243.3 | 3662.6 | 3120.9 | 2617.2 | 2208.0 | 1949.6 | 1800.9 | 1737.9 | 1739.0 |
| 20° | 4943.5 | 4690.6 | 4074.0 | 3384.7 | 2788.7 | 2264.4 | 1868.2 | 1648.9 | 1536.0 | 1487.2 | 1487.2 |
| 22.5° | 4925.1 | 4613.5 | 3883.0 | 3105.7 | 2460.9 | 1958.3 | 1625.0 | 1457.9 | 1392.7 | 1360.2 | 1359.1 |
| 25° | 4933.7 | 4556.0 | 3687.6 | 2819.1 | 2159.1 | 1714.1 | 1463.3 | 1352.6 | 1309.2 | 1288.5 | 1287.4 |
| 27.5° | 4980.4 | 4528.8 | 3507.4 | 2533.6 | 1895.3 | 1530.6 | 1354.7 | 1276.6 | 1248.4 | 1235.3 | 1235.3 |
| 30° | 5065.1 | 4528.8 | 3319.6 | 2290.5 | 1676.1 | 1394.9 | 1271.2 | 1218.0 | 1198.4 | 1189.7 | 1189.7 |
| 32.5° | 5212.7 | 4553.8 | 3138.3 | 2049.5 | 1501.3 | 1288.5 | 1201.7 | 1165.9 | 1150.7 | 1146.3 | 1146.3 |
| 35° | 5466.7 | 4638.5 | 2961.3 | 1821.5 | 1360.2 | 1201.7 | 1135.5 | 1114.8 | 1104.0 | 1102.9 | 1106.2 |
| 37.5° | 5823.9 | 4811.1 | 2795.2 | 1653.3 | 1260.3 | 1131.1 | 1080.1 | 1063.8 | 1057.3 | 1062.7 | 1067.1 |
| 40° | 6273.3 | 5045.6 | 2644.4 | 1501.3 | 1184.3 | 1074.7 | 1029.1 | 1018.2 | 1015.0 | 1022.6 | 1029.1 |
| 42.5° | 6816.1 | 5362.5 | 2520.6 | 1391.7 | 1125.7 | 1026.9 | 985.7 | 972.6 | 969.4 | 978.1 | 986.7 |
| 45° | 7403.3 | 5703.4 | 2433.8 | 1310.2 | 1080.1 | 991.1 | 947.7 | 933.6 | 927.0 | 931.4 | 941.2 |
| 47.5° | 7937.4 | 6025.8 | 2399.0 | 1252.7 | 1036.7 | 960.7 | 914.0 | 896.7 | 885.8 | 883.6 | 891.2 |
| 50° | 8387.9 | 6265.7 | 2415.3 | 1218.0 | 1001.9 | 927.0 | 881.5 | 861.9 | 845.6 | 835.9 | 841.3 |
| 52.5° | 8715.7 | 6416.6 | 2430.5 | 1202.8 | 974.8 | 890.1 | 845.6 | 827.2 | 805.5 | 789.2 | 789.2 |
| 55° | 8953.5 | 6451.3 | 2396.9 | 1190.8 | 954.2 | 850.0 | 805.5 | 788.1 | 766.4 | 747.9 | 745.8 |
| 57.5° | 9046.8 | 6353.6 | 2272.0 | 1173.5 | 940.1 | 812.0 | 763.1 | 750.1 | 731.6 | 709.9 | 708.9 |
| 60° | 8920.9 | 6051.8 | 2031.0 | 1136.6 | 921.6 | 780.5 | 720.8 | 712.1 | 703.4 | 682.8 | 681.7 |
| 62.5° | 8415.1 | 5389.7 | 1719.5 | 1061.7 | 884.7 | 746.8 | 681.7 | 686.1 | 687.1 | 673.0 | 670.9 |
| 65° | 7497.8 | 4480.0 | 1415.5 | 964.0 | 829.3 | 706.7 | 641.5 | 662.2 | 674.1 | 671.9 | 668.7 |
| 67.5° | 6164.7 | 3486.7 | 1199.5 | 860.8 | 756.6 | 651.3 | 598.1 | 622.0 | 631.8 | 639.4 | 637.2 |
| 70° | 4575.5 | 2458.7 | 992.2 | 752.3 | 668.7 | 586.2 | 541.7 | 553.6 | 547.1 | 555.8 | 559.0 |
| 72.5° | 2551.0 | 1475.2 | 808.7 | 643.7 | 577.5 | 510.2 | 478.7 | 476.5 | 462.4 | 462.4 | 462.4 |
| 74° | 1530.6 | 1082.3 | 711.0 | 576.4 | 522.1 | 460.3 | 433.1 | 423.4 | 410.3 | 411.4 | 410.3 |
| 75° | 1231.0 | 930.3 | 652.4 | 531.9 | 483.1 | 431.0 | 403.8 | 390.8 | 381.0 | 381.0 | 379.9 |
| 77.5° | 777.2 | 706.7 | 525.4 | 423.4 | 386.4 | 355.0 | 336.5 | 319.1 | 319.1 | 318.1 | 317.0 |
| 80° | 587.3 | 562.3 | 409.2 | 320.2 | 296.4 | 272.5 | 260.5 | 252.9 | 252.9 | 256.2 | 255.1 |
| 82.5° | 402.7 | 423.4 | 287.7 | 223.6 | 211.7 | 194.3 | 192.1 | 193.2 | 190.0 | 185.6 | 184.5 |
| 85° | 294.2 | 318.1 | 194.3 | 141.1 | 129.2 | 118.3 | 127.0 | 131.3 | 125.9 | 116.2 | 111.8 |
| 87.5° | 112.9 | 208.4 | 104.2 | 58.6 | 54.3 | 46.7 | 54.3 | 56.4 | 60.8 | 47.8 | 48.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 CIE $R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)