

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P320873

Luminaire Tested: **GLEON-SA9A-727-U-AFL**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P320873  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-29)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: GLEON-SA9A-727-U-AFL  
Description: GALLEON AREA AND ROADWAY LUMINAIRE  
(9) 70 CRI, 2700K, 615mA LIGHTSQUARES WITH 16 LEDS EACH AND AUTOMOTIVE FRONTLINE OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 35743 lumens  
Efficiency: N/A  
Efficacy: 123.3 lumens/watt  
Luminous Opening: Rectangular (W 2.5' x L: 1' x H: 0')  
IES Classification: Type II - Short  
BUG Rating: B3 - U0 - G3


Input Watts (W): 290  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P320873  
 CATALOG NUMBER: GLEON-SA9A-727-U-AFL

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 17.6 fc  
 Type II - Short - N/A

REPORT NUMBER: P320873  
CATALOG NUMBER: GLEON-SA9A-727-U-AFL

### Luminous Intensity Polar Plot



— Vertical Plane Through 56-Deg Lateral      - - - Horizontal Cone Through 57-Deg Vertical

REPORT NUMBER: P320873  
 CATALOG NUMBER: GLEON-SA9A-727-U-AFL


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 6161.3   | 0.0    | 6161.3  |
|                    | % Fixture | 17.2     | 0.0    | 17.2    |
| <b>Street Side</b> | Lumens    | 29581.7  | 0.0    | 29581.7 |
|                    | % Fixture | 82.8     | 0.0    | 82.8    |
| <b>Total</b>       | Lumens    | 35743.0  | 0.0    | 35743.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 757.3   | 2.1       |
| 10°-20°   | 2141.1  | 6.0       |
| 20°-30°   | 3487.4  | 9.8       |
| 30°-40°   | 5213.3  | 14.6      |
| 40°-50°   | 7907.5  | 22.1      |
| 50°-60°   | 8862.9  | 24.8      |
| 60°-70°   | 5234.7  | 14.6      |
| 70°-80°   | 1715.1  | 4.8       |
| 80°-90°   | 423.7   | 1.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 35743.0 | 100.0     |
| 0°-180°   | 35743.0 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P320873  
 CATALOG NUMBER: GLEON-SA9A-727-U-AFL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|---------|-----------|-------------------------|------|---------|
|                |         |           | B                       | U    | G       |
| FL (0°-30°)    | 4604.2  | 12.9      |                         |      |         |
| FM (30°-60°)   | 19248.8 | 53.9      |                         |      |         |
| FH (60°-80°)   | 5542.1  | 15.5      |                         |      | G3/7500 |
| FVH (80°-90°)  | 186.6   | 0.5       |                         |      | G2/225  |
| BL (0°-30°)    | 1781.6  | 5.0       | B3/2500                 |      |         |
| BM (30°-60°)   | 2734.8  | 7.7       | B3/5000                 |      |         |
| BH (60°-80°)   | 1407.8  | 3.9       | B3/2500                 |      | G3/2500 |
| BVH (80°-90°)  | 237.2   | 0.7       |                         |      | G3/500  |
| UL (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0     | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G3**

Type II Short





REPORT NUMBER: P320873

CATALOG NUMBER: GLEON-SA9A-727-U-AFL

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 15°     | 25°     | 35°     | 45°     | 55°     | 56°     | 65°     | 75°     | 85°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 7927.8  | 7927.8  | 7927.8  | 7927.8  | 7927.8  | 7927.8  | 7927.8  | 7927.8  | 7927.8  | 7927.8  | 7927.8  |
| 2.5°  | 9103.4  | 9186.9  | 9150.0  | 9022.3  | 8924.0  | 8785.2  | 8630.5  | 8583.8  | 8420.4  | 8237.4  | 8017.5  |
| 5°    | 10544.2 | 10502.5 | 10442.3 | 10243.3 | 10033.2 | 9788.8  | 9400.6  | 9339.2  | 8975.6  | 8561.7  | 8124.4  |
| 7.5°  | 11364.8 | 11361.1 | 11325.5 | 11208.8 | 11017.2 | 10697.8 | 10229.8 | 10157.3 | 9608.2  | 8942.5  | 8264.4  |
| 10°   | 11245.6 | 11237.0 | 11296.0 | 11417.6 | 11475.3 | 11409.0 | 11014.7 | 10942.2 | 10267.9 | 9363.8  | 8426.5  |
| 12.5° | 10568.8 | 10573.7 | 10668.3 | 10923.8 | 11271.4 | 11689.1 | 11625.2 | 11589.6 | 10952.1 | 9840.4  | 8623.1  |
| 15°   | 10041.8 | 10052.9 | 10127.8 | 10350.2 | 10760.4 | 11518.3 | 11996.2 | 12008.4 | 11614.1 | 10366.1 | 8852.8  |
| 17.5° | 9810.9  | 9834.2  | 9868.6  | 10024.6 | 10400.5 | 11178.1 | 12084.6 | 12150.9 | 12193.9 | 10911.5 | 9073.9  |
| 20°   | 9884.6  | 9906.7  | 9916.5  | 10016.0 | 10324.4 | 10971.7 | 12023.2 | 12142.3 | 12638.6 | 11425.0 | 9295.0  |
| 22.5° | 10215.0 | 10228.5 | 10234.7 | 10260.5 | 10500.0 | 11030.7 | 11982.6 | 12107.9 | 12960.4 | 11885.6 | 9462.1  |
| 25°   | 10762.9 | 10753.1 | 10713.7 | 10680.6 | 10841.5 | 11264.1 | 12076.0 | 12195.1 | 13222.1 | 12303.2 | 9571.4  |
| 27.5° | 11418.8 | 11406.5 | 11330.4 | 11239.5 | 11331.6 | 11627.6 | 12345.0 | 12439.6 | 13456.7 | 12693.9 | 9626.7  |
| 30°   | 12206.2 | 12174.3 | 12030.5 | 11922.5 | 11958.1 | 12173.0 | 12788.4 | 12874.4 | 13819.0 | 13137.3 | 9680.7  |
| 32.5° | 13116.4 | 13082.0 | 12874.4 | 12695.1 | 12695.1 | 12874.4 | 13245.4 | 13316.6 | 14126.1 | 13638.5 | 9767.9  |
| 35°   | 14256.3 | 14213.3 | 13943.1 | 13642.2 | 13557.4 | 13648.3 | 13868.2 | 13918.5 | 14678.9 | 14269.8 | 9926.4  |
| 37.5° | 15600.2 | 15542.4 | 15192.3 | 14789.4 | 14604.0 | 14599.0 | 14757.5 | 14860.7 | 15562.1 | 15099.0 | 10195.4 |
| 40°   | 16947.7 | 16907.1 | 16601.3 | 16284.4 | 15920.8 | 15804.1 | 16048.5 | 16080.4 | 16716.7 | 16128.4 | 10539.3 |
| 42.5° | 17989.3 | 17981.9 | 17925.4 | 17967.2 | 17595.0 | 17359.2 | 17550.8 | 17576.6 | 18126.9 | 17242.5 | 10905.4 |
| 45°   | 18539.6 | 18551.9 | 18825.8 | 19432.6 | 19570.2 | 19398.2 | 19492.8 | 19500.2 | 19738.5 | 18366.4 | 11240.7 |
| 47.5° | 18098.6 | 18162.5 | 18855.3 | 20212.6 | 21339.1 | 21910.2 | 21753.0 | 21843.9 | 21301.0 | 19331.9 | 11503.6 |
| 50°   | 16380.2 | 16458.8 | 17638.0 | 19865.0 | 22164.5 | 24341.2 | 24258.9 | 24238.0 | 22561.3 | 20039.5 | 11646.1 |
| 52.5° | 14251.4 | 14312.8 | 15285.7 | 18058.1 | 21558.9 | 25685.0 | 26440.4 | 26332.3 | 23681.5 | 20568.9 | 11673.1 |
| 55°   | 11009.8 | 11105.6 | 12037.9 | 14451.6 | 19109.6 | 25171.5 | 28044.7 | 27947.6 | 24702.3 | 20846.5 | 11641.2 |
| 57°   | 7827.1  | 7927.8  | 8854.0  | 11029.4 | 16075.5 | 23394.1 | 28204.4 | 28307.5 | 25253.8 | 20893.2 | 11676.8 |
| 57.5° | 6984.5  | 7087.6  | 8005.2  | 10118.0 | 15129.7 | 22751.7 | 28066.8 | 28238.7 | 25353.3 | 20885.8 | 11696.4 |
| 60°   | 3516.8  | 3556.1  | 4140.8  | 5648.0  | 9564.0  | 18393.4 | 26272.1 | 26715.6 | 25443.0 | 20524.7 | 11781.2 |
| 62.5° | 2186.5  | 2158.2  | 2139.8  | 2601.7  | 4653.0  | 12197.6 | 22568.6 | 23422.4 | 23727.0 | 19650.1 | 11576.1 |
| 65°   | 1922.4  | 1869.6  | 1666.9  | 1630.0  | 2055.0  | 5924.4  | 16995.6 | 18058.1 | 20060.3 | 18271.8 | 11087.2 |
| 67.5° | 1805.7  | 1754.1  | 1525.6  | 1388.0  | 1389.3  | 2348.6  | 10551.6 | 11748.0 | 15627.2 | 15941.6 | 9933.7  |
| 70°   | 1685.3  | 1638.6  | 1424.9  | 1262.8  | 1182.9  | 1300.8  | 4854.5  | 5762.2  | 10186.8 | 12530.5 | 8302.5  |
| 72.5° | 1530.5  | 1498.6  | 1295.9  | 1128.9  | 1044.1  | 974.1   | 1858.5  | 2195.1  | 5897.4  | 8415.5  | 5765.9  |
| 75°   | 1368.4  | 1338.9  | 1165.7  | 1006.0  | 902.8   | 766.5   | 1046.6  | 1127.6  | 2996.0  | 4305.4  | 2838.7  |
| 77.5° | 1190.3  | 1173.1  | 1036.7  | 889.3   | 807.0   | 635.1   | 740.7   | 780.0   | 1284.9  | 1846.2  | 1423.7  |
| 80°   | 947.1   | 980.2   | 906.5   | 792.3   | 716.1   | 508.5   | 524.5   | 550.3   | 748.1   | 901.6   | 808.3   |
| 82.5° | 616.6   | 674.4   | 710.0   | 643.7   | 589.6   | 400.4   | 377.1   | 388.2   | 487.7   | 550.3   | 351.3   |
| 85°   | 256.7   | 288.7   | 466.8   | 421.3   | 391.8   | 292.3   | 253.0   | 258.0   | 302.2   | 313.2   | 143.7   |
| 87.5° | 114.2   | 121.6   | 205.1   | 192.9   | 165.8   | 100.7   | 108.1   | 117.9   | 160.9   | 152.3   | 55.3    |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P320873  
 CATALOG NUMBER: GLEON-SA9A-727-U-AFL

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 7927.8 | 7927.8 | 7927.8 | 7927.8 | 7927.8 | 7927.8 | 7927.8 | 7927.8 | 7927.8 | 7927.8 | 7927.8 |
| 2.5°  | 7935.2 | 7832.0 | 7655.1 | 7459.8 | 7300.1 | 7172.4 | 7043.4 | 6955.0 | 6851.8 | 6796.5 | 6768.3 |
| 5°    | 7941.3 | 7738.7 | 7366.5 | 6984.5 | 6643.0 | 6331.0 | 6033.7 | 5805.2 | 5591.5 | 5476.0 | 5444.1 |
| 7.5°  | 7967.1 | 7662.5 | 7060.6 | 6431.7 | 5824.9 | 5270.9 | 4843.4 | 4575.6 | 4382.8 | 4296.8 | 4272.2 |
| 10°   | 7988.0 | 7572.8 | 6682.3 | 5751.2 | 4925.7 | 4364.4 | 4032.7 | 3882.8 | 3816.5 | 3805.5 | 3794.4 |
| 12.5° | 8037.2 | 7480.7 | 6284.3 | 5041.2 | 4226.8 | 3838.6 | 3723.2 | 3713.3 | 3731.8 | 3758.8 | 3758.8 |
| 15°   | 8114.5 | 7389.8 | 5829.8 | 4431.9 | 3782.1 | 3645.8 | 3669.1 | 3723.2 | 3773.5 | 3815.3 | 3821.4 |
| 17.5° | 8171.0 | 7278.0 | 5340.9 | 3944.3 | 3545.0 | 3581.9 | 3665.4 | 3741.6 | 3793.2 | 3833.7 | 3837.4 |
| 20°   | 8211.6 | 7104.8 | 4818.9 | 3572.1 | 3408.7 | 3522.9 | 3627.3 | 3694.9 | 3730.5 | 3771.1 | 3777.2 |
| 22.5° | 8190.7 | 6872.7 | 4355.8 | 3305.5 | 3298.1 | 3436.9 | 3536.4 | 3617.5 | 3590.5 | 3551.2 | 3577.0 |
| 25°   | 8090.0 | 6553.3 | 3879.2 | 3106.5 | 3181.5 | 3321.5 | 3444.3 | 3390.3 | 3299.4 | 3282.2 | 3292.0 |
| 27.5° | 7910.6 | 6145.5 | 3438.2 | 2922.3 | 3046.3 | 3214.6 | 3207.2 | 3153.2 | 3121.3 | 3099.2 | 3112.7 |
| 30°   | 7717.8 | 5703.3 | 3052.5 | 2761.4 | 2896.5 | 3035.3 | 3007.0 | 3005.8 | 2973.9 | 2938.2 | 2955.4 |
| 32.5° | 7527.4 | 5258.6 | 2746.6 | 2628.7 | 2783.5 | 2801.9 | 2863.3 | 2881.7 | 2819.1 | 2744.2 | 2739.2 |
| 35°   | 7361.6 | 4838.5 | 2514.5 | 2508.3 | 2647.1 | 2649.6 | 2739.2 | 2713.4 | 2557.4 | 2480.1 | 2480.1 |
| 37.5° | 7237.5 | 4419.6 | 2337.6 | 2400.2 | 2467.8 | 2531.6 | 2577.1 | 2470.2 | 2444.4 | 2401.4 | 2400.2 |
| 40°   | 7183.4 | 4051.1 | 2227.0 | 2317.9 | 2341.3 | 2422.3 | 2305.6 | 2347.4 | 2359.7 | 2337.6 | 2337.6 |
| 42.5° | 7126.9 | 3730.5 | 2131.2 | 2255.3 | 2251.6 | 2240.5 | 2181.6 | 2235.6 | 2284.7 | 2286.0 | 2282.3 |
| 45°   | 7070.4 | 3454.1 | 2046.4 | 2121.4 | 2173.0 | 2053.8 | 2064.9 | 2122.6 | 2191.4 | 2216.0 | 2216.0 |
| 47.5° | 7007.8 | 3235.5 | 1969.1 | 1980.1 | 2060.0 | 1980.1 | 1971.5 | 2015.7 | 2096.8 | 2136.1 | 2144.7 |
| 50°   | 6870.2 | 3039.0 | 1880.6 | 1856.1 | 1878.2 | 1905.2 | 1912.6 | 1933.4 | 2023.1 | 2085.8 | 2100.5 |
| 52.5° | 6679.8 | 2863.3 | 1767.6 | 1741.8 | 1741.8 | 1843.8 | 1878.2 | 1884.3 | 1960.5 | 2035.4 | 2050.1 |
| 55°   | 6521.4 | 2751.5 | 1650.9 | 1646.0 | 1641.1 | 1778.7 | 1837.6 | 1847.5 | 1900.3 | 1959.2 | 1966.6 |
| 57°   | 6532.4 | 2742.9 | 1561.2 | 1566.2 | 1564.9 | 1712.3 | 1799.5 | 1820.4 | 1847.5 | 1897.8 | 1906.4 |
| 57.5° | 6538.6 | 2749.1 | 1541.6 | 1544.0 | 1542.8 | 1693.9 | 1788.5 | 1811.8 | 1832.7 | 1885.5 | 1894.1 |
| 60°   | 6630.7 | 2765.0 | 1461.7 | 1434.7 | 1440.9 | 1595.6 | 1725.8 | 1755.3 | 1768.8 | 1838.9 | 1849.9 |
| 62.5° | 6494.3 | 2693.8 | 1397.9 | 1332.8 | 1332.8 | 1492.5 | 1638.6 | 1685.3 | 1706.2 | 1800.8 | 1819.2 |
| 65°   | 6098.8 | 2493.6 | 1322.9 | 1217.3 | 1229.6 | 1389.3 | 1534.2 | 1610.4 | 1642.3 | 1760.2 | 1779.9 |
| 67.5° | 5488.3 | 2261.4 | 1243.1 | 1114.1 | 1126.4 | 1281.2 | 1426.1 | 1508.4 | 1558.8 | 1716.0 | 1732.0 |
| 70°   | 4693.6 | 1977.7 | 1135.0 | 1004.8 | 1019.5 | 1163.3 | 1298.4 | 1391.7 | 1466.7 | 1674.3 | 1679.2 |
| 72.5° | 3460.3 | 1621.4 | 983.9  | 884.4  | 900.4  | 1025.7 | 1169.4 | 1277.5 | 1378.2 | 1569.8 | 1567.4 |
| 75°   | 2057.5 | 1267.7 | 816.9  | 762.8  | 773.9  | 890.6  | 1052.7 | 1184.1 | 1335.2 | 1529.3 | 1552.6 |
| 77.5° | 1248.0 | 954.4  | 665.8  | 638.7  | 652.3  | 771.4  | 969.2  | 1109.2 | 1316.8 | 1442.1 | 1434.7 |
| 80°   | 754.2  | 681.7  | 531.9  | 514.7  | 528.2  | 659.6  | 896.7  | 1052.7 | 1151.0 | 1232.0 | 1232.0 |
| 82.5° | 394.3  | 416.4  | 390.6  | 377.1  | 395.5  | 535.6  | 815.6  | 918.8  | 1017.1 | 873.4  | 815.6  |
| 85°   | 160.9  | 217.4  | 237.1  | 235.8  | 246.9  | 371.0  | 703.8  | 786.1  | 655.9  | 622.8  | 637.5  |
| 87.5° | 54.0   | 92.1   | 115.5  | 99.5   | 104.4  | 233.4  | 487.7  | 379.6  | 450.8  | 314.5  | 298.5  |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

**Test Information**

Test Method: LM-79-2008  
 Report Number: SP1-1908-441-1-R4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/28/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGRAW-EDISON  
 Catalog Number: **SA1C-727-U-5WQ**  
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

\*\*\*THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.\*\*\*TESTED IN  
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

**Spectral Parameters**

CCT (K): 2741  
 CIE u': 0.2605  
 CIE v': 0.5272  
 Duv: 0.0005  
 CIE x: 0.4573  
 CIE y: 0.4113  
 CIE z: 0.1313  
 Peak Wavelength (nm): 602  
 Dominant Wavelength (nm): 583  
 Purity: 61.2

|           |      |      |       |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 |      |       |
| R1:       | 69.2 | R9:  | -16.1 |
| R2:       | 79.4 | R10: | 51.4  |
| R3:       | 87.8 | R11: | 63.1  |
| R4:       | 69.4 | R12: | 42.0  |
| R5:       | 66.4 | R13: | 70.2  |
| R6:       | 69.8 | R14: | 92.4  |
| R7:       | 79.8 |      |       |
| R8:       | 50.1 |      |       |

Rf: 69.9  
 Rg: 98.3



**Test Conditions**

Stabilization Time: 56M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.3./42%  
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/28/2019        | 12/28/2019           |
| Power Meter                    | IN0071                | 12/5/2018        | 12/5/2019            |
| AC Power Source                | IN0063                | 12/5/2018        | 12/5/2019            |
| DC Power Source                | IN0208                | 12/5/2018        | 12/5/2019            |
| Sphere Thermometer             | IN0085                | 12/5/2018        | 12/5/2019            |
| Room Thermometer               | IN0046                | 12/5/2018        | 12/5/2019            |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

**Photopic Flux vs. Wavelength**



**Photopic Lumens: 6211.7**

| $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360            | 2044                              | 0.0                         | 490            | 7179                              | 1.0                         | 620            | 118034                            | 30.7                        | 750            | 8362                              | 0.0                         | 880            | 3128                              | 0.0                         |
| 365            | 2016                              | 0.0                         | 495            | 10476                             | 1.9                         | 625            | 111884                            | 24.7                        | 755            | 7635                              | 0.0                         | 885            | 3110                              | 0.0                         |
| 370            | 2020                              | 0.0                         | 500            | 15549                             | 3.4                         | 630            | 106119                            | 19.2                        | 760            | 6582                              | 0.0                         | 890            | 2632                              | 0.0                         |
| 375            | 2137                              | 0.0                         | 505            | 22477                             | 6.3                         | 635            | 99706                             | 15.0                        | 765            | 5777                              | 0.0                         | 895            | 2709                              | 0.0                         |
| 380            | 2046                              | 0.0                         | 510            | 30417                             | 10.4                        | 640            | 92142                             | 11.0                        | 770            | 5474                              | 0.0                         | 900            | 2016                              | 0.0                         |
| 385            | 1925                              | 0.0                         | 515            | 39274                             | 16.3                        | 645            | 84987                             | 8.2                         | 775            | 4977                              | 0.0                         | 905            | 1748                              | 0.0                         |
| 390            | 1893                              | 0.0                         | 520            | 47282                             | 22.9                        | 650            | 78016                             | 5.7                         | 780            | 4723                              | 0.0                         | 910            | 2046                              | 0.0                         |
| 395            | 1695                              | 0.0                         | 525            | 55413                             | 29.7                        | 655            | 71541                             | 4.1                         | 785            | 4219                              | 0.0                         | 915            | 1844                              | 0.0                         |
| 400            | 1633                              | 0.0                         | 530            | 62377                             | 36.7                        | 660            | 64863                             | 2.7                         | 790            | 3969                              | 0.0                         | 920            | 2734                              | 0.0                         |
| 405            | 2065                              | 0.0                         | 535            | 68520                             | 42.5                        | 665            | 58485                             | 1.9                         | 795            | 4122                              | 0.0                         | 925            | 2307                              | 0.0                         |
| 410            | 3449                              | 0.0                         | 540            | 73435                             | 47.8                        | 670            | 51641                             | 1.1                         | 800            | 2864                              | 0.0                         | 930            | 2039                              | 0.0                         |
| 415            | 7117                              | 0.0                         | 545            | 78677                             | 52.4                        | 675            | 46030                             | 0.8                         | 805            | 3151                              | 0.0                         | 935            | 1784                              | 0.0                         |
| 420            | 13992                             | 0.0                         | 550            | 83331                             | 56.6                        | 680            | 40590                             | 0.5                         | 810            | 3022                              | 0.0                         | 940            | 2464                              | 0.0                         |
| 425            | 25176                             | 0.1                         | 555            | 89120                             | 60.9                        | 685            | 35691                             | 0.3                         | 815            | 3471                              | 0.0                         | 945            | 2794                              | 0.0                         |
| 430            | 38151                             | 0.3                         | 560            | 94613                             | 64.3                        | 690            | 31631                             | 0.2                         | 820            | 2749                              | 0.0                         | 950            | 3090                              | 0.0                         |
| 435            | 49673                             | 0.6                         | 565            | 99818                             | 66.4                        | 695            | 27437                             | 0.1                         | 825            | 2729                              | 0.0                         | 955            | 1866                              | 0.0                         |
| 440            | 57273                             | 0.9                         | 570            | 106526                            | 69.3                        | 700            | 24589                             | 0.1                         | 830            | 2282                              | 0.0                         | 960            | 3110                              | 0.0                         |
| 445            | 54802                             | 1.1                         | 575            | 111610                            | 69.4                        | 705            | 21832                             | 0.0                         | 835            | 3140                              | 0.0                         | 965            | 3880                              | 0.0                         |
| 450            | 39184                             | 1.0                         | 580            | 117163                            | 69.6                        | 710            | 19500                             | 0.0                         | 840            | 2365                              | 0.0                         | 970            | 3243                              | 0.0                         |
| 455            | 22506                             | 0.8                         | 585            | 122201                            | 67.9                        | 715            | 17870                             | 0.0                         | 845            | 3024                              | 0.0                         | 975            | 2014                              | 0.0                         |
| 460            | 13692                             | 0.6                         | 590            | 125662                            | 65.0                        | 720            | 15924                             | 0.0                         | 850            | 2510                              | 0.0                         | 980            | 1688                              | 0.0                         |
| 465            | 9446                              | 0.5                         | 595            | 127415                            | 60.4                        | 725            | 14268                             | 0.0                         | 855            | 2739                              | 0.0                         | 985            | 2827                              | 0.0                         |
| 470            | 6698                              | 0.4                         | 600            | 129155                            | 55.7                        | 730            | 12438                             | 0.0                         | 860            | 3515                              | 0.0                         | 990            | 4172                              | 0.0                         |
| 475            | 5328                              | 0.4                         | 605            | 128057                            | 49.6                        | 735            | 11255                             | 0.0                         | 865            | 3600                              | 0.0                         | 995            | 3177                              | 0.0                         |
| 480            | 5081                              | 0.5                         | 610            | 126031                            | 43.3                        | 740            | 9951                              | 0.0                         | 870            | 3609                              | 0.0                         | 1000           | 3241                              | 0.0                         |
| 485            | 5579                              | 0.7                         | 615            | 123059                            | 37.1                        | 745            | 8870                              | 0.0                         | 875            | 3208                              | 0.0                         |                |                                   |                             |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2044          | 0.0           | 490    | 7179          | 6.0           | 620    | 118034        | 0.1           | 750    | 8362          | 0.0           | 880    | 3128          | 0.0           |
| 365    | 2016          | 0.0           | 495    | 10476         | 8.6           | 625    | 111884        | 0.1           | 755    | 7635          | 0.0           | 885    | 3110          | 0.0           |
| 370    | 2020          | 0.0           | 500    | 15549         | 12.5          | 630    | 106119        | 0.0           | 760    | 6582          | 0.0           | 890    | 2632          | 0.0           |
| 375    | 2137          | 0.0           | 505    | 22477         | 17.3          | 635    | 99706         | 0.0           | 765    | 5777          | 0.0           | 895    | 2709          | 0.0           |
| 380    | 2046          | 0.0           | 510    | 30417         | 21.8          | 640    | 92142         | 0.0           | 770    | 5474          | 0.0           | 900    | 2016          | 0.0           |
| 385    | 1925          | 0.0           | 515    | 39274         | 25.7          | 645    | 84987         | 0.0           | 775    | 4977          | 0.0           | 905    | 1748          | 0.0           |
| 390    | 1893          | 0.0           | 520    | 47282         | 27.5          | 650    | 78016         | 0.0           | 780    | 4723          | 0.0           | 910    | 2046          | 0.0           |
| 395    | 1695          | 0.0           | 525    | 55413         | 28.1          | 655    | 71541         | 0.0           | 785    | 4219          | 0.0           | 915    | 1844          | 0.0           |
| 400    | 1633          | 0.0           | 530    | 62377         | 27.0          | 660    | 64863         | 0.0           | 790    | 3969          | 0.0           | 920    | 2734          | 0.0           |
| 405    | 2065          | 0.0           | 535    | 68520         | 24.7          | 665    | 58485         | 0.0           | 795    | 4122          | 0.0           | 925    | 2307          | 0.0           |
| 410    | 3449          | 0.1           | 540    | 73435         | 21.5          | 670    | 51641         | 0.0           | 800    | 2864          | 0.0           | 930    | 2039          | 0.0           |
| 415    | 7117          | 0.5           | 545    | 78677         | 18.3          | 675    | 46030         | 0.0           | 805    | 3151          | 0.0           | 935    | 1784          | 0.0           |
| 420    | 13992         | 1.6           | 550    | 83331         | 15.0          | 680    | 40590         | 0.0           | 810    | 3022          | 0.0           | 940    | 2464          | 0.0           |
| 425    | 25176         | 3.9           | 555    | 89120         | 12.0          | 685    | 35691         | 0.0           | 815    | 3471          | 0.0           | 945    | 2794          | 0.0           |
| 430    | 38151         | 8.1           | 560    | 94613         | 9.3           | 690    | 31631         | 0.0           | 820    | 2749          | 0.0           | 950    | 3090          | 0.0           |
| 435    | 49673         | 13.3          | 565    | 99818         | 7.0           | 695    | 27437         | 0.0           | 825    | 2729          | 0.0           | 955    | 1866          | 0.0           |
| 440    | 57273         | 19.1          | 570    | 106526        | 5.2           | 700    | 24589         | 0.0           | 830    | 2282          | 0.0           | 960    | 3110          | 0.0           |
| 445    | 54802         | 21.6          | 575    | 111610        | 3.7           | 705    | 21832         | 0.0           | 835    | 3140          | 0.0           | 965    | 3880          | 0.0           |
| 450    | 39184         | 18.1          | 580    | 117163        | 2.6           | 710    | 19500         | 0.0           | 840    | 2365          | 0.0           | 970    | 3243          | 0.0           |
| 455    | 22506         | 11.8          | 585    | 122201        | 1.8           | 715    | 17870         | 0.0           | 845    | 3024          | 0.0           | 975    | 2014          | 0.0           |
| 460    | 13692         | 8.1           | 590    | 125662        | 1.2           | 720    | 15924         | 0.0           | 850    | 2510          | 0.0           | 980    | 1688          | 0.0           |
| 465    | 9446          | 6.2           | 595    | 127415        | 0.8           | 725    | 14268         | 0.0           | 855    | 2739          | 0.0           | 985    | 2827          | 0.0           |
| 470    | 6698          | 4.8           | 600    | 129155        | 0.5           | 730    | 12438         | 0.0           | 860    | 3515          | 0.0           | 990    | 4172          | 0.0           |
| 475    | 5328          | 4.1           | 605    | 128057        | 0.4           | 735    | 11255         | 0.0           | 865    | 3600          | 0.0           | 995    | 3177          | 0.0           |
| 480    | 5081          | 4.1           | 610    | 126031        | 0.2           | 740    | 9951          | 0.0           | 870    | 3609          | 0.0           | 1000   | 3241          | 0.0           |
| 485    | 5579          | 4.6           | 615    | 123059        | 0.1           | 745    | 8870          | 0.0           | 875    | 3208          | 0.0           |        |               |               |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360            | 2044                              | 0.0                         | 490            | 7179                              | 11.1                        | 620            | 118034                            | 1.5                         | 750            | 8362                              | 0.0                         | 880            | 3128                              | 0.0                         |
| 365            | 2016                              | 0.0                         | 495            | 10476                             | 16.9                        | 625            | 111884                            | 0.9                         | 755            | 7635                              | 0.0                         | 885            | 3110                              | 0.0                         |
| 370            | 2020                              | 0.0                         | 500            | 15549                             | 26.0                        | 630            | 106119                            | 0.6                         | 760            | 6582                              | 0.0                         | 890            | 2632                              | 0.0                         |
| 375            | 2137                              | 0.0                         | 505            | 22477                             | 38.2                        | 635            | 99706                             | 0.4                         | 765            | 5777                              | 0.0                         | 895            | 2709                              | 0.0                         |
| 380            | 2046                              | 0.0                         | 510            | 30417                             | 51.6                        | 640            | 92142                             | 0.2                         | 770            | 5474                              | 0.0                         | 900            | 2016                              | 0.0                         |
| 385            | 1925                              | 0.0                         | 515            | 39274                             | 65.1                        | 645            | 84987                             | 0.1                         | 775            | 4977                              | 0.0                         | 905            | 1748                              | 0.0                         |
| 390            | 1893                              | 0.0                         | 520            | 47282                             | 75.2                        | 650            | 78016                             | 0.1                         | 780            | 4723                              | 0.0                         | 910            | 2046                              | 0.0                         |
| 395            | 1695                              | 0.0                         | 525            | 55413                             | 82.9                        | 655            | 71541                             | 0.1                         | 785            | 4219                              | 0.0                         | 915            | 1844                              | 0.0                         |
| 400            | 1633                              | 0.0                         | 530            | 62377                             | 86.0                        | 660            | 64863                             | 0.0                         | 790            | 3969                              | 0.0                         | 920            | 2734                              | 0.0                         |
| 405            | 2065                              | 0.1                         | 535            | 68520                             | 85.4                        | 665            | 58485                             | 0.0                         | 795            | 4122                              | 0.0                         | 925            | 2307                              | 0.0                         |
| 410            | 3449                              | 0.2                         | 540            | 73435                             | 81.1                        | 670            | 51641                             | 0.0                         | 800            | 2864                              | 0.0                         | 930            | 2039                              | 0.0                         |
| 415            | 7117                              | 0.7                         | 545            | 78677                             | 75.4                        | 675            | 46030                             | 0.0                         | 805            | 3151                              | 0.0                         | 935            | 1784                              | 0.0                         |
| 420            | 13992                             | 2.3                         | 550            | 83331                             | 68.1                        | 680            | 40590                             | 0.0                         | 810            | 3022                              | 0.0                         | 940            | 2464                              | 0.0                         |
| 425            | 25176                             | 6.2                         | 555            | 89120                             | 60.9                        | 685            | 35691                             | 0.0                         | 815            | 3471                              | 0.0                         | 945            | 2794                              | 0.0                         |
| 430            | 38151                             | 13.0                        | 560            | 94613                             | 52.9                        | 690            | 31631                             | 0.0                         | 820            | 2749                              | 0.0                         | 950            | 3090                              | 0.0                         |
| 435            | 49673                             | 22.2                        | 565            | 99818                             | 44.8                        | 695            | 27437                             | 0.0                         | 825            | 2729                              | 0.0                         | 955            | 1866                              | 0.0                         |
| 440            | 57273                             | 32.0                        | 570            | 106526                            | 37.6                        | 700            | 24589                             | 0.0                         | 830            | 2282                              | 0.0                         | 960            | 3110                              | 0.0                         |
| 445            | 54802                             | 36.7                        | 575            | 111610                            | 30.4                        | 705            | 21832                             | 0.0                         | 835            | 3140                              | 0.0                         | 965            | 3880                              | 0.0                         |
| 450            | 39184                             | 30.4                        | 580            | 117163                            | 24.1                        | 710            | 19500                             | 0.0                         | 840            | 2365                              | 0.0                         | 970            | 3243                              | 0.0                         |
| 455            | 22506                             | 19.7                        | 585            | 122201                            | 18.7                        | 715            | 17870                             | 0.0                         | 845            | 3024                              | 0.0                         | 975            | 2014                              | 0.0                         |
| 460            | 13692                             | 13.2                        | 590            | 125662                            | 14.0                        | 720            | 15924                             | 0.0                         | 850            | 2510                              | 0.0                         | 980            | 1688                              | 0.0                         |
| 465            | 9446                              | 10.0                        | 595            | 127415                            | 10.2                        | 725            | 14268                             | 0.0                         | 855            | 2739                              | 0.0                         | 985            | 2827                              | 0.0                         |
| 470            | 6698                              | 7.7                         | 600            | 129155                            | 7.3                         | 730            | 12438                             | 0.0                         | 860            | 3515                              | 0.0                         | 990            | 4172                              | 0.0                         |
| 475            | 5328                              | 6.7                         | 605            | 128057                            | 5.0                         | 735            | 11255                             | 0.0                         | 865            | 3600                              | 0.0                         | 995            | 3177                              | 0.0                         |
| 480            | 5081                              | 6.9                         | 610            | 126031                            | 3.4                         | 740            | 9951                              | 0.0                         | 870            | 3609                              | 0.0                         | 1000           | 3241                              | 0.0                         |
| 485            | 5579                              | 8.1                         | 615            | 123059                            | 2.3                         | 745            | 8870                              | 0.0                         | 875            | 3208                              | 0.0                         |                |                                   |                             |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

**Summary**

$R_f = 69.9$   
 $R_g = 98.3$   
 CIE  $R_a = 71.5$   
 $R_9 = -16.1$



**Color Vector Graphics**





REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**


|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 |            |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)