

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P382922

Luminaire Tested: **GLEON-SA2D-735-U-T2-HSS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P382922
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-13)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GLEON-SA2D-735-U-T2-HSS
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(2) 70 CRI, 3500K, 1200mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10520 lumens
Efficiency: N/A
Efficacy: 81.6 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type II - Medium
BUG Rating: B1 - U0 - G2


Input Watts (W): 129
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P382922
 CATALOG NUMBER: GLEON-SA2D-735-U-T2-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 3.2 fc
 Type II - Medium - N/A

REPORT NUMBER: P382922
CATALOG NUMBER: GLEON-SA2D-735-U-T2-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 66-Deg Lateral - - - Horizontal Cone Through 69-Deg Vertical

REPORT NUMBER: P382922
 CATALOG NUMBER: GLEON-SA2D-735-U-T2-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 631.0 | 0.0 | 631.0 |
| | % Fixture | 6.0 | 0.0 | 6.0 |
| Street Side | Lumens | 9888.9 | 0.0 | 9888.9 |
| | % Fixture | 94.0 | 0.0 | 94.0 |
| Total | Lumens | 10520.0 | 0.0 | 10520.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 115.7 | 1.1 |
| 10°-20° | 344.4 | 3.3 |
| 20°-30° | 599.8 | 5.7 |
| 30°-40° | 1052.3 | 10.0 |
| 40°-50° | 1761.4 | 16.7 |
| 50°-60° | 2589.0 | 24.6 |
| 60°-70° | 2658.3 | 25.3 |
| 70°-80° | 1312.3 | 12.5 |
| 80°-90° | 86.8 | 0.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 10520.0 | 100.0 |
| 0°-180° | 10520.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P382922
 CATALOG NUMBER: GLEON-SA2D-735-U-T2-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 848.9 | 8.1 | | | |
| FM (30°-60°) | 5151.1 | 49.0 | | | |
| FH (60°-80°) | 3804.3 | 36.2 | | | G2/5000 |
| FVH (80°-90°) | 84.7 | 0.8 | | | G1/100 |
| BL (0°-30°) | 211.1 | 2.0 | B1/500 | | |
| BM (30°-60°) | 251.6 | 2.4 | B1/1000 | | |
| BH (60°-80°) | 166.3 | 1.6 | B1/500 | | G1/500 |
| BVH (80°-90°) | 2.1 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2
 Type II Medium





REPORT NUMBER: P382922

CATALOG NUMBER: GLEON-SA2D-735-U-T2-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 66° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|---------|---------|---------|--------|
| 0° | 1197.2 | 1197.2 | 1197.2 | 1197.2 | 1197.2 | 1197.2 | 1197.2 | 1197.2 | 1197.2 | 1197.2 | 1197.2 |
| 2.5° | 1409.1 | 1403.1 | 1400.6 | 1389.6 | 1370.6 | 1356.1 | 1328.1 | 1295.6 | 1289.6 | 1258.1 | 1219.7 |
| 5° | 1591.9 | 1587.0 | 1583.4 | 1568.0 | 1548.5 | 1512.0 | 1461.0 | 1400.6 | 1389.1 | 1329.1 | 1252.2 |
| 7.5° | 1719.4 | 1728.4 | 1728.4 | 1718.3 | 1693.8 | 1666.4 | 1603.9 | 1521.5 | 1507.0 | 1415.0 | 1295.6 |
| 10° | 1793.8 | 1804.8 | 1813.3 | 1821.8 | 1818.3 | 1807.3 | 1748.3 | 1655.4 | 1637.9 | 1516.0 | 1346.1 |
| 12.5° | 1800.8 | 1811.8 | 1835.8 | 1871.3 | 1905.8 | 1930.7 | 1893.7 | 1803.8 | 1783.8 | 1632.9 | 1406.1 |
| 15° | 1761.8 | 1773.3 | 1810.3 | 1879.2 | 1962.7 | 2035.6 | 2047.6 | 1968.2 | 1947.7 | 1772.4 | 1481.0 |
| 17.5° | 1693.8 | 1701.4 | 1754.3 | 1849.8 | 1980.7 | 2114.6 | 2187.1 | 2144.6 | 2125.6 | 1931.8 | 1564.4 |
| 20° | 1643.4 | 1648.9 | 1695.4 | 1797.8 | 1969.7 | 2164.1 | 2319.0 | 2331.9 | 2312.0 | 2102.6 | 1654.9 |
| 22.5° | 1729.9 | 1739.9 | 1741.3 | 1789.8 | 1939.7 | 2188.6 | 2434.9 | 2516.3 | 2501.3 | 2284.0 | 1743.9 |
| 25° | 1966.2 | 1977.7 | 1939.7 | 1909.8 | 1965.2 | 2199.6 | 2534.3 | 2705.2 | 2693.2 | 2479.3 | 1833.3 |
| 27.5° | 2278.5 | 2290.5 | 2241.5 | 2152.1 | 2098.6 | 2241.0 | 2622.8 | 2897.1 | 2896.6 | 2686.2 | 1929.7 |
| 30° | 2585.3 | 2597.2 | 2547.3 | 2457.9 | 2334.9 | 2358.4 | 2699.3 | 3098.0 | 3100.9 | 2899.5 | 2032.2 |
| 32.5° | 2907.1 | 2922.1 | 2870.6 | 2755.7 | 2627.2 | 2561.3 | 2806.7 | 3299.8 | 3316.8 | 3147.0 | 2147.6 |
| 35° | 3272.8 | 3274.9 | 3202.4 | 3081.9 | 2934.1 | 2832.6 | 2979.0 | 3526.2 | 3566.6 | 3453.2 | 2293.9 |
| 37.5° | 3631.5 | 3646.1 | 3586.6 | 3396.7 | 3260.9 | 3145.9 | 3235.4 | 3809.0 | 3866.5 | 3827.4 | 2485.4 |
| 40° | 3897.4 | 3927.9 | 3919.4 | 3714.5 | 3585.6 | 3503.6 | 3553.7 | 4145.3 | 4218.2 | 4263.1 | 2726.7 |
| 42.5° | 4064.3 | 4087.3 | 4126.3 | 4002.9 | 3886.0 | 3899.5 | 3929.4 | 4537.0 | 4626.9 | 4759.8 | 3004.0 |
| 45° | 4255.7 | 4266.7 | 4299.2 | 4244.7 | 4165.7 | 4301.6 | 4328.2 | 4978.2 | 5072.6 | 5294.0 | 3311.8 |
| 47.5° | 4489.5 | 4515.5 | 4524.5 | 4474.5 | 4438.5 | 4657.4 | 4712.4 | 5379.4 | 5511.9 | 5866.1 | 3637.6 |
| 50° | 4787.3 | 4794.3 | 4809.8 | 4777.3 | 4741.4 | 4963.2 | 5057.2 | 5800.7 | 5921.1 | 6440.3 | 3958.9 |
| 52.5° | 5078.6 | 5103.6 | 5157.6 | 5137.1 | 5122.6 | 5223.6 | 5364.4 | 6180.4 | 6314.8 | 6918.9 | 4279.6 |
| 55° | 5162.5 | 5184.1 | 5370.5 | 5497.8 | 5615.7 | 5544.3 | 5658.2 | 6520.6 | 6666.1 | 7346.7 | 4588.4 |
| 57.5° | 4827.3 | 4870.8 | 5193.6 | 5525.4 | 6014.5 | 6042.9 | 6062.0 | 6870.0 | 7000.4 | 7674.4 | 4909.7 |
| 60° | 3979.9 | 3988.3 | 4518.0 | 5087.1 | 5948.6 | 6478.2 | 6651.6 | 7245.2 | 7354.7 | 7979.7 | 5294.5 |
| 62.5° | 2531.3 | 2617.7 | 3198.8 | 4002.3 | 5251.0 | 6415.3 | 7364.6 | 7812.8 | 7852.8 | 8345.9 | 5846.1 |
| 65° | 1205.7 | 1261.7 | 1680.4 | 2472.9 | 3803.5 | 5609.3 | 7856.8 | 8839.6 | 8857.6 | 9072.0 | 6583.2 |
| 67.5° | 667.5 | 694.6 | 893.9 | 1331.1 | 2223.5 | 3966.9 | 7657.9 | 10055.9 | 10072.8 | 9813.5 | 7229.7 |
| 69° | 522.1 | 545.1 | 702.0 | 1003.4 | 1507.5 | 2851.1 | 6929.9 | 10412.1 | 10462.6 | 10025.9 | 7252.7 |
| 70° | 443.2 | 465.7 | 604.6 | 847.4 | 1212.2 | 2203.0 | 6168.4 | 10323.7 | 10377.2 | 10005.8 | 7081.3 |
| 72.5° | 271.4 | 284.3 | 402.7 | 596.6 | 812.5 | 1108.3 | 3804.0 | 8730.7 | 8821.1 | 9178.4 | 6086.0 |
| 75° | 182.9 | 189.8 | 251.8 | 411.7 | 581.1 | 570.7 | 1976.2 | 6153.9 | 6349.8 | 7139.8 | 4495.0 |
| 77.5° | 130.9 | 137.4 | 168.9 | 266.3 | 407.3 | 376.7 | 894.9 | 3824.5 | 3866.5 | 4282.1 | 2451.4 |
| 80° | 74.4 | 80.5 | 119.4 | 158.4 | 276.3 | 251.3 | 355.8 | 1826.8 | 1847.8 | 1836.3 | 818.5 |
| 82.5° | 38.9 | 44.0 | 65.5 | 104.4 | 177.4 | 164.4 | 147.9 | 611.6 | 614.6 | 511.1 | 179.4 |
| 85° | 7.5 | 9.0 | 32.5 | 71.4 | 91.5 | 71.4 | 60.5 | 143.4 | 146.4 | 129.4 | 44.4 |
| 87.5° | 0.0 | 0.5 | 12.9 | 16.0 | 18.0 | 18.4 | 19.5 | 27.9 | 30.0 | 40.4 | 12.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P382922

CATALOG NUMBER: GLEON-SA2D-735-U-T2-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1197.2 | 1197.2 | 1197.2 | 1197.2 | 1197.2 | 1197.2 | 1197.2 | 1197.2 | 1197.2 | 1197.2 | 1197.2 |
| 2.5° | 1202.7 | 1184.7 | 1150.3 | 1110.2 | 1079.3 | 1048.8 | 1024.8 | 999.8 | 990.9 | 986.3 | 985.9 |
| 5° | 1214.7 | 1176.7 | 1103.8 | 1028.8 | 967.3 | 909.4 | 867.9 | 828.4 | 810.0 | 801.5 | 798.0 |
| 7.5° | 1234.7 | 1173.7 | 1056.3 | 941.9 | 853.4 | 781.0 | 723.5 | 680.6 | 659.1 | 650.0 | 646.6 |
| 10° | 1258.1 | 1169.7 | 1000.9 | 849.9 | 737.0 | 662.1 | 605.1 | 562.7 | 539.2 | 529.1 | 524.2 |
| 12.5° | 1285.6 | 1162.8 | 936.9 | 757.0 | 637.6 | 562.7 | 493.6 | 441.2 | 414.3 | 402.7 | 397.2 |
| 15° | 1319.6 | 1155.8 | 869.9 | 669.6 | 550.2 | 458.7 | 383.2 | 347.7 | 342.3 | 340.3 | 340.8 |
| 17.5° | 1353.1 | 1144.8 | 796.9 | 583.1 | 458.2 | 358.3 | 319.8 | 317.8 | 318.8 | 318.8 | 318.8 |
| 20° | 1383.1 | 1119.7 | 717.5 | 509.2 | 370.8 | 302.3 | 294.3 | 290.8 | 288.3 | 286.3 | 283.8 |
| 22.5° | 1406.5 | 1086.3 | 641.1 | 435.7 | 302.8 | 276.9 | 264.3 | 253.3 | 244.3 | 238.4 | 235.3 |
| 25° | 1422.6 | 1041.8 | 571.1 | 365.3 | 272.3 | 251.8 | 229.3 | 210.9 | 196.8 | 188.4 | 184.9 |
| 27.5° | 1434.6 | 993.9 | 508.6 | 305.8 | 251.3 | 222.8 | 193.4 | 171.4 | 156.9 | 149.4 | 146.4 |
| 30° | 1443.1 | 939.4 | 453.7 | 268.8 | 227.9 | 192.4 | 160.9 | 139.5 | 128.9 | 124.9 | 123.0 |
| 32.5° | 1451.1 | 878.9 | 401.8 | 251.3 | 205.9 | 164.4 | 134.9 | 118.4 | 112.0 | 106.9 | 105.5 |
| 35° | 1471.0 | 822.9 | 352.3 | 232.9 | 183.4 | 140.4 | 115.9 | 104.0 | 97.4 | 94.5 | 93.4 |
| 37.5° | 1518.5 | 781.5 | 304.8 | 213.9 | 160.9 | 121.4 | 101.4 | 93.0 | 86.9 | 83.9 | 82.9 |
| 40° | 1594.9 | 760.5 | 264.8 | 193.4 | 138.9 | 106.9 | 91.9 | 83.9 | 77.4 | 72.9 | 71.9 |
| 42.5° | 1707.3 | 763.5 | 236.8 | 172.9 | 121.4 | 95.4 | 82.9 | 73.4 | 66.4 | 62.4 | 61.5 |
| 45° | 1843.8 | 785.5 | 217.3 | 152.9 | 106.9 | 86.4 | 72.9 | 63.0 | 56.5 | 53.0 | 52.0 |
| 47.5° | 1991.6 | 821.0 | 201.4 | 134.9 | 95.4 | 78.0 | 63.0 | 52.4 | 46.9 | 44.0 | 43.5 |
| 50° | 2147.6 | 855.4 | 184.9 | 117.5 | 85.4 | 69.5 | 53.0 | 43.5 | 38.9 | 36.5 | 35.5 |
| 52.5° | 2305.5 | 895.4 | 169.9 | 101.4 | 76.9 | 59.4 | 44.0 | 35.5 | 32.0 | 30.0 | 29.0 |
| 55° | 2475.4 | 925.4 | 155.4 | 89.0 | 68.5 | 50.5 | 36.5 | 29.4 | 26.5 | 23.9 | 23.5 |
| 57.5° | 2675.2 | 971.9 | 140.4 | 76.9 | 58.5 | 42.0 | 30.0 | 23.5 | 21.0 | 18.4 | 18.0 |
| 60° | 2945.1 | 1026.3 | 124.5 | 67.9 | 48.0 | 34.5 | 24.5 | 19.0 | 16.0 | 14.0 | 13.5 |
| 62.5° | 3300.8 | 1086.7 | 104.4 | 59.4 | 38.9 | 27.9 | 19.5 | 15.0 | 11.5 | 9.0 | 9.0 |
| 65° | 3752.0 | 1185.2 | 85.4 | 49.9 | 32.0 | 23.0 | 15.0 | 11.0 | 6.5 | 4.0 | 4.0 |
| 67.5° | 4015.3 | 1202.2 | 68.9 | 41.0 | 26.0 | 19.5 | 12.5 | 7.5 | 2.0 | 0.5 | 0.0 |
| 69° | 3930.9 | 1103.8 | 58.5 | 34.9 | 22.5 | 18.4 | 11.5 | 5.5 | 1.0 | 0.0 | 0.0 |
| 70° | 3772.0 | 1009.3 | 51.4 | 31.0 | 20.5 | 17.5 | 11.0 | 4.0 | 1.0 | 0.0 | 0.0 |
| 72.5° | 3117.0 | 718.5 | 38.9 | 23.0 | 15.0 | 15.5 | 10.0 | 2.5 | 1.0 | 0.0 | 0.0 |
| 75° | 2270.5 | 436.7 | 27.9 | 16.0 | 9.5 | 11.5 | 7.0 | 1.0 | 0.5 | 0.0 | 0.0 |
| 77.5° | 1263.2 | 205.9 | 17.5 | 9.0 | 6.0 | 7.0 | 3.5 | 0.0 | 0.0 | 0.0 | 0.0 |
| 80° | 410.3 | 56.0 | 8.0 | 5.0 | 3.5 | 4.0 | 1.5 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 75.9 | 16.0 | 4.5 | 2.5 | 1.0 | 1.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 16.5 | 6.5 | 2.5 | 1.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 5.5 | 2.0 | 0.5 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

All Brands

Data applicable to all product families using SA light engines

Report Number: SP1-2101-121-7

Luminaire Tested: IFLD-S-SA2A-735-U-T2

Test Date: 03/04/2021


Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/04/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-735-U-T2**
 Description: STREETWORKS INF FLOOD

PROGRAMMED @ 615mA.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 3388 | CRI (Ra): | 73.1 | R9: | -34.6 |
| CIE u': | 0.2371 | R1: | 68.9 | R10: | 57.8 |
| CIE v': | 0.5177 | R2: | 81.1 | R11: | 68.6 |
| Duv: | 0.0032 | R3: | 93.1 | R12: | 53.9 |
| CIE x: | 0.4153 | R4: | 71.6 | R13: | 70.9 |
| CIE y: | 0.4030 | R5: | 69.4 | R14: | 96.2 |
| CIE z: | 0.1817 | R6: | 75.0 | | |
| Peak Wavelength (nm): | 590 | R7: | 79.5 | | |
| Dominant Wavelength (nm): | 580 | R8: | 46.4 | | |
| Purity: | 45.7 | | | | |
| Rf: | 76.9 | | | | |
| Rg: | 94.4 | | | | |



Test Conditions


Stabilization Time: 81M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0/30%
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-7

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 3388K
 CIE x = 0.4153
 CIE y = 0.4030
 Duv = 0.0032

Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-7

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 4.9 | 620 | 136720 | 35.6 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 8.0 | 625 | 126308 | 27.9 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 12.1 | 630 | 114625 | 20.7 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 18.1 | 635 | 103216 | 15.5 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 25.4 | 640 | 92605 | 11.1 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 33.9 | 645 | 83234 | 8.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 43.0 | 650 | 73263 | 5.4 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 50.1 | 655 | 64627 | 3.7 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 57.9 | 660 | 56614 | 2.4 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 64.0 | 665 | 49537 | 1.6 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.0 | 540 | 107316 | 69.9 | 670 | 42866 | 0.9 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.0 | 545 | 113101 | 75.3 | 675 | 36708 | 0.6 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 0.0 | 550 | 120690 | 82.0 | 680 | 31814 | 0.4 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 0.1 | 555 | 128583 | 87.8 | 685 | 27485 | 0.2 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 0.3 | 560 | 137796 | 93.6 | 690 | 23698 | 0.1 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 0.8 | 565 | 146577 | 97.5 | 695 | 20309 | 0.1 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 1.6 | 570 | 154581 | 100.5 | 700 | 17890 | 0.1 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 2.4 | 575 | 162633 | 101.2 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 2.5 | 580 | 168101 | 99.9 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 2.1 | 585 | 173145 | 96.2 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 1.8 | 590 | 174675 | 90.3 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 1.7 | 595 | 173724 | 82.3 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 1.5 | 600 | 171241 | 73.8 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 1.7 | 605 | 165134 | 64.0 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 2.2 | 610 | 156652 | 53.8 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 3.3 | 615 | 147879 | 44.6 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Scotopic Flux vs. Wavelength




Scotopic Lumens: 12126

S/P: 1.36

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 53.2 | 620 | 136720 | 1.7 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 71.7 | 625 | 126308 | 1.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 91.4 | 630 | 114625 | 0.6 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 110.0 | 635 | 103216 | 0.4 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 125.1 | 640 | 92605 | 0.2 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 135.7 | 645 | 83234 | 0.1 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 140.8 | 650 | 73263 | 0.1 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 139.6 | 655 | 64627 | 0.1 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 135.7 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.1 | 535 | 103269 | 128.7 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.2 | 540 | 107316 | 118.6 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.6 | 545 | 113101 | 108.4 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 2.0 | 550 | 120690 | 98.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 5.9 | 555 | 128583 | 87.9 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 14.3 | 560 | 137796 | 77.0 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 30.5 | 565 | 146577 | 65.8 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 55.5 | 570 | 154581 | 54.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 77.4 | 575 | 162633 | 44.3 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 73.6 | 580 | 168101 | 34.6 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 53.7 | 585 | 173145 | 26.5 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 41.9 | 590 | 174675 | 19.5 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 34.3 | 595 | 173724 | 13.9 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 27.9 | 600 | 171241 | 9.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 27.1 | 605 | 165134 | 6.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 31.3 | 610 | 156652 | 4.2 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 40.0 | 615 | 147879 | 2.7 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Melanopic Flux vs. Wavelength




Melanopic Lumens: 4490.7 M/P: 0.5



| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 28.8 | 620 | 136720 | 0.1 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 36.6 | 625 | 126308 | 0.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 43.9 | 630 | 114625 | 0.0 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 49.6 | 635 | 103216 | 0.0 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 53.0 | 640 | 92605 | 0.0 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 53.5 | 645 | 83234 | 0.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 51.6 | 650 | 73263 | 0.0 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 47.3 | 655 | 64627 | 0.0 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 42.5 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 37.2 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.1 | 540 | 107316 | 31.4 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.4 | 545 | 113101 | 26.3 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 1.4 | 550 | 120690 | 21.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 3.7 | 555 | 128583 | 17.3 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 8.9 | 560 | 137796 | 13.6 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 18.2 | 565 | 146577 | 10.3 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 33.2 | 570 | 154581 | 7.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 45.6 | 575 | 162633 | 5.4 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 43.8 | 580 | 168101 | 3.8 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 32.2 | 585 | 173145 | 2.6 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 25.6 | 590 | 174675 | 1.7 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 21.2 | 595 | 173724 | 1.1 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 17.4 | 600 | 171241 | 0.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 16.6 | 605 | 165134 | 0.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 18.6 | 610 | 156652 | 0.3 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 22.7 | 615 | 147879 | 0.2 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

Summary

$R_f = 76.9$
 $R_g = 94.4$
 CIE $R_a = 73.1$
 $R_g = -34.6$



Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 68 | CES51 = 90 | CES76 = 63 |
| CES02 = 62 | CES27 = 88 | CES52 = 89 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 80 | CES78 = 65 |
| CES04 = 70 | CES29 = 67 | CES54 = 84 | CES79 = 87 |
| CES05 = 48 | CES30 = 74 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 71 | CES56 = 75 | CES81 = 75 |
| CES07 = 40 | CES32 = 67 | CES57 = 74 | CES82 = 94 |
| CES08 = 39 | CES33 = 74 | CES58 = 76 | CES83 = 91 |
| CES09 = 29 | CES34 = 78 | CES59 = 87 | CES84 = 89 |
| CES10 = 75 | CES35 = 89 | CES60 = 93 | CES85 = 80 |
| CES11 = 58 | CES36 = 98 | CES61 = 86 | CES86 = 66 |
| CES12 = 64 | CES37 = 86 | CES62 = 89 | CES87 = 79 |
| CES13 = 43 | CES38 = 82 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 95 | CES64 = 74 | CES89 = 70 |
| CES15 = 71 | CES40 = 91 | CES65 = 68 | CES90 = 77 |
| CES16 = 47 | CES41 = 89 | CES66 = 71 | CES91 = 88 |
| CES17 = 50 | CES42 = 88 | CES67 = 69 | CES92 = 60 |
| CES18 = 56 | CES43 = 82 | CES68 = 74 | CES93 = 77 |
| CES19 = 72 | CES44 = 99 | CES69 = 82 | CES94 = 52 |
| CES20 = 65 | CES45 = 87 | CES70 = 67 | CES95 = 69 |
| CES21 = 86 | CES46 = 82 | CES71 = 66 | CES96 = 78 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 85 |
| CES23 = 92 | CES48 = 72 | CES73 = 59 | CES98 = 76 |
| CES24 = 91 | CES49 = 82 | CES74 = 97 | CES99 = 63 |
| CES25 = 72 | CES50 = 88 | CES75 = 66 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)