

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P383339

Luminaire Tested: **GLEON-SA6C-735-U-SLL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P383339
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-26)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GLEON-SA6C-735-U-SLL
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(6) 70 CRI, 3500K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT
ELIMINATOR LEFT OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 34631.2 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B3 - U0 - G5


Input Watts (W): 333
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P383339
 CATALOG NUMBER: GLEON-SA6C-735-U-SLL

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 21.2 fc
 Type III - Medium - N/A

REPORT NUMBER: P383339
CATALOG NUMBER: GLEON-SA6C-735-U-SLL

Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P383339
 CATALOG NUMBER: GLEON-SA6C-735-U-SLL


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 6099.4 | 0.0 | 6099.4 |
| | % Fixture | 17.6 | 0.0 | 17.6 |
| Street Side | Lumens | 28531.8 | 0.0 | 28531.8 |
| | % Fixture | 82.4 | 0.0 | 82.4 |
| Total | Lumens | 34631.2 | 0.0 | 34631.2 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 814.3 | 2.4 |
| 10°-20° | 1691.6 | 4.9 |
| 20°-30° | 2405.8 | 6.9 |
| 30°-40° | 3466.7 | 10.0 |
| 40°-50° | 4885.6 | 14.1 |
| 50°-60° | 6791.8 | 19.6 |
| 60°-70° | 8213.3 | 23.7 |
| 70°-80° | 5048.6 | 14.6 |
| 80°-90° | 1313.7 | 3.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 34631.2 | 100.0 |
| 0°-180° | 34631.2 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P383339
 CATALOG NUMBER: GLEON-SA6C-735-U-SLL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|----------|
| | | | B | U | G |
| FL (0°-30°) | 3438.5 | 9.9 | | | |
| FM (30°-60°) | 12375.4 | 35.7 | | | |
| FH (60°-80°) | 11551.8 | 33.4 | | | G4/12000 |
| FVH (80°-90°) | 1166.1 | 3.4 | | | G5 |
| BL (0°-30°) | 1473.1 | 4.3 | B3/2500 | | |
| BM (30°-60°) | 2768.7 | 8.0 | B3/5000 | | |
| BH (60°-80°) | 1710.1 | 4.9 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 147.6 | 0.4 | | | G2/225 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G5
 Type III Medium





REPORT NUMBER: P383339

CATALOG NUMBER: GLEON-SA6C-735-U-SLL

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° | 50° |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 |
| 2.5° | 11245.6 | 11393.8 | 11496.2 | 11597.3 | 11676.2 | 11753.8 | 11867.3 | 11980.8 | 12003.0 | 12023.8 | 11979.4 |
| 5° | 11179.1 | 11540.6 | 11847.9 | 12153.9 | 12437.7 | 12721.6 | 12891.9 | 13062.2 | 13096.8 | 13131.5 | 13024.8 |
| 7.5° | 10463.3 | 10996.4 | 11529.5 | 12062.5 | 12551.3 | 13040.1 | 13337.7 | 13634.0 | 13701.9 | 13768.4 | 13593.9 |
| 10° | 9649.2 | 10269.5 | 10924.4 | 11579.3 | 12223.1 | 12867.0 | 13297.6 | 13728.2 | 13814.0 | 13899.9 | 13682.5 |
| 12.5° | 9030.3 | 9707.4 | 10406.6 | 11105.8 | 11785.6 | 12464.1 | 12909.9 | 13355.7 | 13462.4 | 13568.9 | 13411.1 |
| 15° | 8792.1 | 9534.3 | 10192.0 | 10849.6 | 11442.2 | 12033.5 | 12399.0 | 12763.1 | 12807.5 | 12850.3 | 12825.5 |
| 17.5° | 9030.3 | 9848.6 | 10444.0 | 11037.9 | 11360.5 | 11681.8 | 11828.5 | 11973.9 | 12022.4 | 12069.4 | 12133.1 |
| 20° | 9726.8 | 10610.1 | 11029.6 | 11447.8 | 11433.9 | 11418.7 | 11348.1 | 11276.1 | 11263.6 | 11251.1 | 11431.1 |
| 22.5° | 10720.9 | 11746.8 | 11914.4 | 12080.5 | 11691.5 | 11302.4 | 11065.7 | 10827.5 | 10780.4 | 10732.0 | 10923.0 |
| 25° | 11888.0 | 12980.6 | 12950.1 | 12918.2 | 12177.5 | 11435.3 | 10984.0 | 10532.5 | 10479.9 | 10427.4 | 10590.7 |
| 27.5° | 13157.7 | 14201.7 | 14002.4 | 13802.9 | 12796.4 | 11789.8 | 11134.9 | 10479.9 | 10427.4 | 10374.7 | 10518.8 |
| 30° | 14150.5 | 15097.6 | 14777.7 | 14457.9 | 13318.3 | 12178.9 | 11400.7 | 10622.5 | 10536.7 | 10449.4 | 10626.7 |
| 32.5° | 14990.9 | 15796.8 | 15367.6 | 14938.3 | 13742.0 | 12545.7 | 11704.0 | 10862.1 | 10727.8 | 10593.5 | 10830.3 |
| 35° | 15866.0 | 16494.6 | 15890.9 | 15285.9 | 14120.0 | 12952.8 | 12062.5 | 11170.8 | 11006.0 | 10841.4 | 11166.7 |
| 37.5° | 16850.4 | 17372.4 | 16505.7 | 15637.5 | 14545.1 | 13452.7 | 12599.7 | 11745.4 | 11576.5 | 11407.6 | 11823.0 |
| 40° | 17890.3 | 18325.0 | 17168.9 | 16012.7 | 15010.3 | 14007.9 | 13343.3 | 12677.2 | 12516.6 | 12354.7 | 12858.7 |
| 42.5° | 18799.9 | 19117.0 | 17786.4 | 16455.8 | 15571.1 | 14684.9 | 14216.9 | 13747.6 | 13746.2 | 13743.4 | 14254.4 |
| 45° | 19485.3 | 19760.8 | 18301.5 | 16840.7 | 16118.0 | 15393.8 | 15150.1 | 14906.4 | 15101.7 | 15296.9 | 15759.4 |
| 47.5° | 20054.4 | 20241.3 | 18733.5 | 17224.3 | 16743.8 | 16263.3 | 16299.4 | 16335.3 | 16732.7 | 17130.1 | 17427.8 |
| 50° | 20705.1 | 20554.2 | 19125.3 | 17695.0 | 17546.9 | 17398.7 | 17722.7 | 18045.4 | 18502.2 | 18957.7 | 19159.9 |
| 52.5° | 21409.9 | 21009.8 | 19657.0 | 18302.9 | 18469.0 | 18635.1 | 19294.2 | 19953.3 | 20414.4 | 20875.4 | 20951.6 |
| 55° | 22676.8 | 22063.4 | 20634.5 | 19204.2 | 19524.1 | 19842.5 | 20810.4 | 21776.8 | 22136.8 | 22496.8 | 22524.4 |
| 57.5° | 24104.3 | 23560.1 | 22003.9 | 20447.6 | 20790.9 | 21134.4 | 22251.7 | 23367.7 | 23756.8 | 24144.4 | 24090.5 |
| 60° | 24654.0 | 24680.3 | 23304.0 | 21926.3 | 22272.5 | 22618.6 | 23707.0 | 24795.2 | 25242.4 | 25688.3 | 25569.2 |
| 62.5° | 24100.2 | 24749.5 | 24014.3 | 23277.7 | 23592.0 | 23904.9 | 24971.1 | 26037.2 | 26495.4 | 26953.8 | 26746.1 |
| 65° | 23004.9 | 23648.7 | 23978.3 | 24307.8 | 24411.7 | 24515.5 | 25511.0 | 26505.1 | 26856.9 | 27207.2 | 27101.9 |
| 67.5° | 21612.0 | 22132.6 | 23348.3 | 24562.6 | 24353.5 | 24144.4 | 24611.0 | 25077.6 | 25439.1 | 25800.4 | 25740.9 |
| 70° | 19999.0 | 20619.2 | 22240.6 | 23862.0 | 22834.7 | 21805.9 | 21613.4 | 21420.9 | 21811.4 | 22200.5 | 21959.6 |
| 72.5° | 17106.6 | 18042.6 | 19771.9 | 21499.8 | 19607.1 | 17714.4 | 17056.7 | 16399.1 | 16893.3 | 17387.6 | 17004.1 |
| 75° | 12920.9 | 14163.0 | 16073.7 | 17983.1 | 15724.8 | 13466.5 | 12588.7 | 11710.9 | 12135.9 | 12561.0 | 12297.9 |
| 77.5° | 8986.0 | 10543.6 | 12425.3 | 14307.0 | 12011.3 | 9714.3 | 9062.1 | 8408.6 | 8536.0 | 8662.0 | 8617.7 |
| 80° | 6126.8 | 7151.4 | 8463.9 | 9775.2 | 8246.6 | 6718.0 | 6769.3 | 6819.1 | 6759.6 | 6698.7 | 6787.3 |
| 82.5° | 3842.3 | 4563.6 | 5577.1 | 6589.2 | 5777.9 | 4966.5 | 5431.8 | 5897.0 | 5668.5 | 5438.7 | 5524.5 |
| 85° | 2164.1 | 2604.4 | 3595.8 | 4585.7 | 4274.2 | 3961.3 | 4234.1 | 4505.4 | 4151.0 | 3796.5 | 3953.0 |
| 87.5° | 412.6 | 686.7 | 1989.7 | 3291.2 | 2987.9 | 2684.7 | 2333.1 | 1981.3 | 1512.0 | 1042.6 | 1523.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P383339
 CATALOG NUMBER: GLEON-SA6C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° | 50° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P383339

CATALOG NUMBER: GLEON-SA6C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° | 105° |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 |
| 2.5° | 11935.2 | 11911.6 | 11888.0 | 11803.6 | 11717.8 | 11590.4 | 11485.1 | 11302.4 | 11202.7 | 11051.8 | 10900.9 |
| 5° | 12916.8 | 12767.3 | 12617.7 | 12360.2 | 12101.3 | 11813.3 | 11482.3 | 11115.5 | 10838.6 | 10478.6 | 10118.6 |
| 7.5° | 13419.4 | 13070.5 | 12720.2 | 12225.9 | 11730.2 | 11284.4 | 10761.1 | 10273.7 | 9858.3 | 9390.3 | 8922.3 |
| 10° | 13465.1 | 12941.7 | 12417.0 | 11774.6 | 11130.7 | 10589.4 | 9987.0 | 9445.7 | 8947.2 | 8410.0 | 7871.4 |
| 12.5° | 13251.9 | 12695.3 | 12137.3 | 11429.8 | 10720.9 | 10106.1 | 9458.1 | 8851.7 | 8299.3 | 7708.0 | 7115.4 |
| 15° | 12800.5 | 12356.0 | 11910.2 | 11247.0 | 10583.8 | 9963.5 | 9334.9 | 8616.3 | 7991.8 | 7386.8 | 6780.4 |
| 17.5° | 12195.4 | 11985.0 | 11773.2 | 11294.1 | 10813.6 | 10276.4 | 9667.2 | 8824.0 | 8092.9 | 7435.2 | 6777.6 |
| 20° | 11609.8 | 11687.3 | 11763.5 | 11572.4 | 11381.3 | 10950.7 | 10419.0 | 9472.0 | 8538.8 | 7678.9 | 6817.7 |
| 22.5° | 11112.7 | 11485.1 | 11856.3 | 12004.4 | 12151.1 | 11892.2 | 11476.9 | 10381.6 | 9146.6 | 8023.7 | 6900.8 |
| 25° | 10752.7 | 11370.3 | 11987.8 | 12480.7 | 12972.2 | 12857.3 | 12537.4 | 11486.5 | 9952.4 | 8520.8 | 7087.7 |
| 27.5° | 10662.7 | 11420.1 | 12177.5 | 12941.7 | 13704.6 | 13811.3 | 13722.6 | 12651.0 | 10913.4 | 9138.3 | 7361.8 |
| 30° | 10803.9 | 11571.0 | 12336.7 | 13267.1 | 14196.2 | 14621.3 | 14740.3 | 13621.6 | 12011.3 | 9858.3 | 7703.8 |
| 32.5° | 11067.0 | 11818.8 | 12570.7 | 13584.2 | 14596.3 | 15238.8 | 15618.1 | 14509.1 | 12777.0 | 10401.0 | 8023.7 |
| 35° | 11492.0 | 12195.4 | 12898.9 | 13953.8 | 15008.9 | 15839.7 | 16532.0 | 15425.7 | 13456.9 | 10780.4 | 8102.6 |
| 37.5° | 12237.0 | 12842.0 | 13447.1 | 14421.8 | 15395.2 | 16472.5 | 17512.3 | 16435.0 | 14192.0 | 11146.0 | 8098.5 |
| 40° | 13362.7 | 13790.5 | 14216.9 | 15040.8 | 15863.2 | 17218.7 | 18622.8 | 17560.7 | 15004.8 | 11542.0 | 8079.0 |
| 42.5° | 14765.2 | 14985.4 | 15204.2 | 15856.3 | 16508.4 | 17998.2 | 19630.7 | 18661.5 | 15780.1 | 11910.2 | 8040.3 |
| 45° | 16220.5 | 16278.6 | 16336.7 | 16748.0 | 17157.8 | 18615.8 | 20317.4 | 19488.1 | 16457.2 | 12230.1 | 8001.5 |
| 47.5° | 17724.1 | 17524.7 | 17325.4 | 17488.7 | 17652.1 | 19089.3 | 20807.6 | 20115.3 | 17137.0 | 12584.6 | 8030.6 |
| 50° | 19362.1 | 18806.8 | 18251.6 | 18165.8 | 18079.9 | 19562.9 | 21385.0 | 20912.8 | 17954.0 | 13101.0 | 8248.0 |
| 52.5° | 21026.3 | 20111.2 | 19195.9 | 18856.7 | 18516.1 | 20127.8 | 22150.6 | 21905.5 | 19119.7 | 13901.3 | 8681.4 |
| 55° | 22552.2 | 21387.8 | 20223.3 | 19766.4 | 19309.5 | 20991.8 | 23085.2 | 23363.6 | 20613.8 | 14924.5 | 9233.8 |
| 57.5° | 24035.0 | 22715.5 | 21396.1 | 20972.4 | 20548.6 | 22261.4 | 24269.1 | 24671.9 | 22123.0 | 15906.2 | 9688.0 |
| 60° | 25450.2 | 24144.4 | 22837.4 | 22498.2 | 22157.6 | 23839.8 | 25548.4 | 25254.9 | 22901.1 | 16365.8 | 9829.2 |
| 62.5° | 26538.4 | 25500.0 | 24461.5 | 24282.9 | 24103.0 | 25436.3 | 26531.5 | 25027.8 | 22406.8 | 15913.1 | 9419.3 |
| 65° | 26996.7 | 26405.5 | 25812.9 | 25980.4 | 26146.6 | 26643.7 | 26776.6 | 24363.2 | 20853.3 | 14644.8 | 8436.3 |
| 67.5° | 25680.0 | 25800.4 | 25920.9 | 26624.3 | 27326.2 | 26984.2 | 26048.2 | 23053.4 | 18642.1 | 12847.6 | 7053.1 |
| 70° | 21717.3 | 22440.1 | 23161.3 | 24825.7 | 26488.6 | 25729.8 | 24097.4 | 20702.3 | 15980.9 | 10777.6 | 5573.0 |
| 72.5° | 16619.2 | 17432.0 | 18243.3 | 20713.4 | 23182.1 | 22482.9 | 20483.6 | 17004.1 | 12813.0 | 8606.6 | 4398.9 |
| 75° | 12033.5 | 12951.4 | 13868.0 | 16592.9 | 19317.8 | 18347.2 | 15321.8 | 12174.7 | 9732.3 | 6569.8 | 3406.1 |
| 77.5° | 8572.0 | 9186.7 | 9801.5 | 12493.2 | 15183.4 | 13602.2 | 10198.9 | 8192.6 | 6736.0 | 4566.4 | 2395.4 |
| 80° | 6875.8 | 6687.6 | 6499.2 | 7998.7 | 9498.2 | 9235.2 | 6745.7 | 5261.5 | 4661.9 | 3059.9 | 1458.0 |
| 82.5° | 5608.9 | 5149.3 | 4689.6 | 5395.7 | 6101.9 | 6063.1 | 4681.3 | 3860.2 | 3469.7 | 2126.7 | 783.7 |
| 85° | 4108.0 | 3924.0 | 3739.8 | 4364.2 | 4988.7 | 4455.6 | 3170.7 | 2453.5 | 2705.5 | 1565.9 | 426.5 |
| 87.5° | 2003.5 | 2288.7 | 2572.6 | 3309.1 | 4044.4 | 3036.4 | 962.3 | 476.3 | 659.1 | 433.4 | 206.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P383339
 CATALOG NUMBER: GLEON-SA6C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° | 105° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P383339

CATALOG NUMBER: GLEON-SA6C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° | 160° |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 |
| 2.5° | 10788.7 | 10675.2 | 10546.4 | 10417.7 | 10270.9 | 10122.8 | 10035.5 | 9946.9 | 9851.3 | 9755.8 | 9647.9 |
| 5° | 9880.5 | 9642.3 | 9372.3 | 9102.2 | 8835.1 | 8567.8 | 8423.8 | 8279.9 | 8127.6 | 7973.9 | 7840.9 |
| 7.5° | 8576.1 | 8228.6 | 7854.8 | 7479.6 | 7147.2 | 6813.5 | 6607.3 | 6399.5 | 6211.3 | 6021.6 | 5862.3 |
| 10° | 7428.3 | 6985.2 | 6610.0 | 6233.5 | 5982.8 | 5732.2 | 5542.5 | 5352.9 | 5170.1 | 4985.9 | 4810.0 |
| 12.5° | 6672.3 | 6229.3 | 5991.2 | 5753.0 | 5545.3 | 5337.6 | 5118.9 | 4898.6 | 4648.0 | 4396.1 | 4211.9 |
| 15° | 6377.4 | 5974.5 | 5710.0 | 5444.2 | 5165.9 | 4886.2 | 4617.6 | 4349.0 | 4052.7 | 3756.4 | 3547.3 |
| 17.5° | 6250.0 | 5722.5 | 5352.9 | 4981.7 | 4614.8 | 4248.0 | 3936.3 | 3624.8 | 3300.8 | 2976.9 | 2765.0 |
| 20° | 6115.7 | 5413.8 | 4918.0 | 4421.0 | 3950.2 | 3479.4 | 3126.4 | 2773.3 | 2484.0 | 2194.5 | 2032.5 |
| 22.5° | 5993.9 | 5085.6 | 4463.9 | 3840.9 | 3284.3 | 2727.7 | 2381.5 | 2033.9 | 1856.8 | 1679.5 | 1614.5 |
| 25° | 5944.0 | 4799.0 | 4034.7 | 3270.4 | 2683.3 | 2094.9 | 1848.5 | 1602.0 | 1534.2 | 1464.9 | 1431.7 |
| 27.5° | 5952.3 | 4542.9 | 3673.3 | 2802.4 | 2273.5 | 1744.6 | 1575.6 | 1406.7 | 1365.2 | 1322.2 | 1301.6 |
| 30° | 5984.2 | 4264.5 | 3332.7 | 2400.9 | 1964.7 | 1528.6 | 1419.2 | 1308.5 | 1264.1 | 1219.9 | 1193.5 |
| 32.5° | 6020.2 | 4015.3 | 3069.6 | 2122.5 | 1766.8 | 1409.5 | 1319.5 | 1228.2 | 1185.2 | 1142.3 | 1116.0 |
| 35° | 5957.9 | 3811.8 | 2889.7 | 1967.5 | 1639.3 | 1309.8 | 1233.6 | 1156.1 | 1109.1 | 1062.0 | 1037.1 |
| 37.5° | 5852.6 | 3606.9 | 2749.8 | 1891.3 | 1556.2 | 1219.9 | 1164.4 | 1107.7 | 1059.2 | 1009.3 | 985.9 |
| 40° | 5757.2 | 3433.8 | 2646.0 | 1856.8 | 1510.6 | 1163.0 | 1116.0 | 1068.9 | 1019.0 | 967.8 | 940.1 |
| 42.5° | 5679.6 | 3317.4 | 2543.5 | 1769.5 | 1469.1 | 1167.2 | 1100.7 | 1032.9 | 984.5 | 936.0 | 905.6 |
| 45° | 5621.4 | 3241.3 | 2463.2 | 1685.1 | 1430.3 | 1175.5 | 1091.0 | 1006.6 | 958.1 | 908.3 | 872.3 |
| 47.5° | 5615.9 | 3201.2 | 2406.4 | 1611.7 | 1356.9 | 1100.7 | 1066.2 | 1031.5 | 960.9 | 888.9 | 847.3 |
| 50° | 5692.0 | 3136.1 | 2340.0 | 1542.5 | 1286.3 | 1030.1 | 1077.2 | 1122.9 | 1002.4 | 880.6 | 828.0 |
| 52.5° | 5851.2 | 3021.2 | 2234.7 | 1448.3 | 1200.4 | 951.2 | 1024.6 | 1096.6 | 992.8 | 887.5 | 819.7 |
| 55° | 6043.7 | 2852.2 | 2075.5 | 1297.4 | 1086.9 | 875.1 | 940.1 | 1003.8 | 938.7 | 872.3 | 790.6 |
| 57.5° | 6164.1 | 2639.0 | 1874.7 | 1110.4 | 959.5 | 808.6 | 845.9 | 882.0 | 855.7 | 829.4 | 746.3 |
| 60° | 6092.2 | 2355.1 | 1649.0 | 941.5 | 847.3 | 753.2 | 746.3 | 738.0 | 776.7 | 815.5 | 720.0 |
| 62.5° | 5740.5 | 2061.6 | 1449.7 | 837.6 | 767.0 | 695.0 | 679.8 | 663.3 | 726.9 | 789.2 | 688.1 |
| 65° | 5146.5 | 1856.8 | 1323.6 | 790.6 | 711.7 | 632.8 | 616.1 | 599.5 | 618.9 | 638.3 | 591.3 |
| 67.5° | 4391.9 | 1730.7 | 1251.6 | 772.6 | 677.0 | 580.2 | 560.8 | 541.4 | 537.2 | 533.0 | 516.4 |
| 70° | 3613.8 | 1653.2 | 1204.6 | 756.0 | 639.7 | 521.9 | 504.0 | 486.0 | 480.5 | 473.5 | 461.0 |
| 72.5° | 3021.2 | 1643.5 | 1199.1 | 754.6 | 609.2 | 463.8 | 447.2 | 430.6 | 423.7 | 415.4 | 405.7 |
| 75° | 2474.3 | 1542.5 | 1138.2 | 733.9 | 567.7 | 400.1 | 384.9 | 369.7 | 364.1 | 357.2 | 349.0 |
| 77.5° | 1836.0 | 1276.6 | 956.8 | 636.9 | 486.0 | 335.1 | 319.8 | 303.2 | 301.8 | 299.0 | 292.1 |
| 80° | 1190.7 | 923.5 | 683.9 | 444.4 | 354.5 | 263.1 | 250.6 | 236.8 | 238.1 | 239.5 | 234.0 |
| 82.5° | 661.9 | 538.6 | 418.2 | 297.7 | 242.3 | 187.0 | 181.4 | 174.5 | 178.6 | 181.4 | 174.5 |
| 85° | 349.0 | 271.4 | 224.3 | 177.3 | 139.8 | 102.5 | 102.5 | 101.1 | 106.6 | 112.2 | 106.6 |
| 87.5° | 150.9 | 95.6 | 81.7 | 66.4 | 37.4 | 6.9 | 8.3 | 8.3 | 11.1 | 13.9 | 12.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P383339
 CATALOG NUMBER: GLEON-SA6C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° | 160° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P383339
 CATALOG NUMBER: GLEON-SA6C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° | 215° |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 |
| 2.5° | 9538.4 | 9437.3 | 9334.9 | 9222.8 | 9243.5 | 9157.7 | 9071.8 | 9017.8 | 8963.8 | 8947.2 | 8930.6 |
| 5° | 7708.0 | 7593.0 | 7476.8 | 7372.9 | 7462.9 | 7402.0 | 7341.1 | 7332.8 | 7323.1 | 7323.1 | 7321.7 |
| 7.5° | 5703.1 | 5579.9 | 5455.2 | 5369.4 | 5458.0 | 5446.9 | 5435.9 | 5495.4 | 5555.0 | 5603.4 | 5650.5 |
| 10° | 4634.3 | 4484.7 | 4333.7 | 4206.4 | 4184.2 | 4120.5 | 4055.5 | 4069.3 | 4081.8 | 4134.4 | 4187.0 |
| 12.5° | 4027.7 | 3849.2 | 3670.6 | 3521.0 | 3453.2 | 3347.9 | 3241.3 | 3174.9 | 3108.4 | 3115.3 | 3120.9 |
| 15° | 3336.9 | 3163.8 | 2989.3 | 2860.6 | 2817.7 | 2736.0 | 2654.3 | 2571.2 | 2486.8 | 2452.1 | 2416.1 |
| 17.5° | 2551.8 | 2413.4 | 2273.5 | 2187.6 | 2187.6 | 2164.1 | 2140.6 | 2099.1 | 2056.1 | 2021.5 | 1985.5 |
| 20° | 1870.5 | 1797.2 | 1722.4 | 1686.5 | 1697.5 | 1698.9 | 1698.9 | 1719.6 | 1740.4 | 1729.3 | 1718.2 |
| 22.5° | 1548.0 | 1521.7 | 1495.3 | 1480.1 | 1485.6 | 1487.0 | 1488.4 | 1507.8 | 1525.8 | 1539.7 | 1552.1 |
| 25° | 1397.0 | 1380.5 | 1363.8 | 1358.3 | 1370.8 | 1372.2 | 1372.2 | 1384.6 | 1397.0 | 1410.9 | 1424.7 |
| 27.5° | 1279.4 | 1272.4 | 1265.5 | 1255.8 | 1268.3 | 1268.3 | 1266.9 | 1280.8 | 1293.2 | 1305.7 | 1316.7 |
| 30° | 1167.2 | 1169.9 | 1171.3 | 1168.6 | 1176.9 | 1182.4 | 1186.6 | 1196.3 | 1204.6 | 1214.3 | 1224.0 |
| 32.5° | 1088.3 | 1084.1 | 1079.9 | 1077.2 | 1095.2 | 1104.9 | 1114.6 | 1124.3 | 1132.6 | 1136.8 | 1140.9 |
| 35° | 1012.1 | 1002.4 | 992.8 | 985.9 | 1002.4 | 1014.9 | 1027.4 | 1045.4 | 1062.0 | 1064.8 | 1067.6 |
| 37.5° | 960.9 | 948.4 | 936.0 | 927.6 | 934.6 | 940.1 | 945.7 | 965.1 | 984.5 | 995.5 | 1005.2 |
| 40° | 912.5 | 900.0 | 887.5 | 880.6 | 884.8 | 886.2 | 887.5 | 897.2 | 905.6 | 926.3 | 945.7 |
| 42.5° | 873.7 | 858.4 | 843.2 | 834.9 | 837.6 | 840.4 | 841.8 | 840.4 | 839.0 | 858.4 | 877.8 |
| 45° | 834.9 | 818.3 | 801.7 | 792.0 | 793.4 | 793.4 | 793.4 | 790.6 | 786.4 | 796.1 | 805.8 |
| 47.5° | 804.5 | 785.0 | 765.6 | 756.0 | 753.2 | 750.5 | 747.7 | 746.3 | 743.6 | 750.5 | 756.0 |
| 50° | 774.0 | 753.2 | 731.1 | 720.0 | 713.1 | 710.3 | 707.5 | 706.1 | 703.4 | 710.3 | 715.8 |
| 52.5° | 750.5 | 725.5 | 700.6 | 682.6 | 675.7 | 671.6 | 667.4 | 668.8 | 668.8 | 671.6 | 672.9 |
| 55° | 708.9 | 686.7 | 663.3 | 650.8 | 638.3 | 635.5 | 632.8 | 636.9 | 639.7 | 639.7 | 639.7 |
| 57.5° | 663.3 | 642.5 | 620.3 | 612.0 | 600.9 | 600.9 | 599.5 | 605.0 | 609.2 | 612.0 | 614.7 |
| 60° | 623.0 | 599.5 | 576.0 | 569.1 | 564.9 | 563.5 | 562.2 | 569.1 | 574.6 | 580.2 | 585.7 |
| 62.5° | 585.7 | 560.8 | 535.8 | 527.5 | 526.1 | 527.5 | 527.5 | 534.4 | 540.0 | 545.5 | 551.1 |
| 65° | 544.1 | 519.2 | 492.9 | 484.6 | 487.4 | 491.5 | 495.7 | 501.3 | 505.4 | 511.0 | 516.4 |
| 67.5° | 498.5 | 477.7 | 455.5 | 447.2 | 448.6 | 454.1 | 459.7 | 463.8 | 466.6 | 472.1 | 477.7 |
| 70° | 448.6 | 430.6 | 412.6 | 407.1 | 405.7 | 412.6 | 418.2 | 420.9 | 423.7 | 430.6 | 436.2 |
| 72.5° | 394.6 | 379.4 | 364.1 | 359.9 | 361.3 | 365.5 | 369.7 | 373.8 | 376.6 | 383.5 | 389.1 |
| 75° | 339.3 | 325.4 | 311.5 | 308.8 | 311.5 | 315.7 | 319.8 | 322.6 | 325.4 | 333.7 | 340.6 |
| 77.5° | 285.2 | 270.0 | 253.4 | 252.0 | 256.2 | 260.3 | 263.1 | 267.3 | 271.4 | 282.4 | 293.5 |
| 80° | 228.4 | 211.8 | 193.9 | 192.5 | 196.6 | 200.7 | 204.9 | 209.0 | 213.2 | 227.1 | 239.5 |
| 82.5° | 167.5 | 148.1 | 128.7 | 126.0 | 139.8 | 144.0 | 148.1 | 155.1 | 160.6 | 173.1 | 185.6 |
| 85° | 101.1 | 81.7 | 62.3 | 60.9 | 73.4 | 80.3 | 87.2 | 95.6 | 102.5 | 113.6 | 124.6 |
| 87.5° | 11.1 | 5.5 | 0.0 | 0.0 | 1.4 | 6.9 | 12.5 | 19.4 | 26.3 | 37.4 | 47.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P383339
 CATALOG NUMBER: GLEON-SA6C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° | 215° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P383339

CATALOG NUMBER: GLEON-SA6C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° | 270° |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 |
| 2.5° | 8869.6 | 8807.4 | 8871.0 | 8933.4 | 8959.6 | 8986.0 | 8918.2 | 8848.9 | 8956.9 | 9063.5 | 9091.2 |
| 5° | 7266.4 | 7209.5 | 7252.5 | 7294.0 | 7201.2 | 7108.5 | 7098.8 | 7087.7 | 7168.0 | 7248.3 | 7260.8 |
| 7.5° | 5632.5 | 5614.5 | 5654.7 | 5694.8 | 5577.1 | 5458.0 | 5399.9 | 5341.8 | 5361.1 | 5380.5 | 5377.7 |
| 10° | 4199.4 | 4210.5 | 4260.3 | 4308.9 | 4217.5 | 4126.1 | 4086.0 | 4045.8 | 4090.1 | 4133.0 | 4173.1 |
| 12.5° | 3145.7 | 3169.3 | 3221.9 | 3273.2 | 3235.8 | 3197.0 | 3201.2 | 3205.4 | 3256.6 | 3306.4 | 3350.7 |
| 15° | 2443.8 | 2471.5 | 2508.8 | 2544.9 | 2546.3 | 2546.3 | 2582.2 | 2616.9 | 2612.7 | 2608.5 | 2639.0 |
| 17.5° | 2022.9 | 2058.9 | 2063.0 | 2067.2 | 2068.6 | 2070.0 | 2067.2 | 2064.4 | 2043.6 | 2022.9 | 2046.4 |
| 20° | 1732.1 | 1744.6 | 1755.7 | 1765.4 | 1752.9 | 1739.0 | 1704.5 | 1669.8 | 1656.0 | 1642.1 | 1664.3 |
| 22.5° | 1575.6 | 1597.8 | 1586.7 | 1574.3 | 1549.3 | 1523.1 | 1496.7 | 1469.1 | 1467.7 | 1464.9 | 1477.3 |
| 25° | 1444.1 | 1462.2 | 1442.8 | 1423.3 | 1405.3 | 1387.4 | 1369.4 | 1351.4 | 1350.0 | 1348.6 | 1354.1 |
| 27.5° | 1334.7 | 1351.4 | 1333.3 | 1315.3 | 1300.2 | 1284.9 | 1271.1 | 1257.2 | 1254.4 | 1251.6 | 1253.0 |
| 30° | 1240.6 | 1255.8 | 1240.6 | 1224.0 | 1212.9 | 1200.4 | 1190.7 | 1181.0 | 1179.7 | 1178.3 | 1178.3 |
| 32.5° | 1156.1 | 1171.3 | 1160.2 | 1149.3 | 1139.6 | 1129.8 | 1122.9 | 1116.0 | 1109.1 | 1102.1 | 1086.9 |
| 35° | 1082.7 | 1098.0 | 1091.0 | 1082.7 | 1071.7 | 1060.6 | 1048.2 | 1034.3 | 1016.3 | 996.9 | 988.6 |
| 37.5° | 1020.4 | 1035.7 | 1028.7 | 1021.8 | 1006.6 | 991.4 | 969.2 | 945.7 | 940.1 | 933.2 | 931.8 |
| 40° | 970.6 | 994.1 | 980.3 | 965.1 | 941.5 | 917.9 | 906.9 | 895.9 | 893.1 | 890.3 | 887.5 |
| 42.5° | 915.2 | 951.2 | 926.3 | 901.4 | 879.2 | 857.0 | 854.3 | 851.5 | 850.1 | 848.7 | 848.7 |
| 45° | 845.9 | 884.8 | 859.8 | 833.5 | 821.1 | 808.6 | 808.6 | 808.6 | 810.0 | 810.0 | 812.8 |
| 47.5° | 780.9 | 804.5 | 792.0 | 779.5 | 772.6 | 765.6 | 767.0 | 768.4 | 772.6 | 775.3 | 782.3 |
| 50° | 725.5 | 733.9 | 736.6 | 738.0 | 733.9 | 729.7 | 732.5 | 733.9 | 738.0 | 740.8 | 746.3 |
| 52.5° | 685.3 | 697.8 | 697.8 | 696.4 | 696.4 | 696.4 | 699.2 | 702.0 | 706.1 | 710.3 | 715.8 |
| 55° | 659.1 | 677.0 | 671.6 | 666.0 | 667.4 | 667.4 | 670.2 | 672.9 | 677.0 | 679.8 | 688.1 |
| 57.5° | 634.1 | 653.5 | 648.0 | 642.5 | 642.5 | 642.5 | 643.8 | 645.2 | 649.4 | 652.2 | 657.7 |
| 60° | 605.0 | 624.4 | 618.9 | 612.0 | 613.3 | 614.7 | 616.1 | 616.1 | 618.9 | 620.3 | 620.3 |
| 62.5° | 570.5 | 589.9 | 584.3 | 577.4 | 581.6 | 584.3 | 584.3 | 584.3 | 587.1 | 588.5 | 584.3 |
| 65° | 534.4 | 552.4 | 546.9 | 541.4 | 546.9 | 551.1 | 553.8 | 555.2 | 553.8 | 552.4 | 548.3 |
| 67.5° | 495.7 | 513.7 | 508.2 | 501.3 | 508.2 | 513.7 | 519.2 | 523.3 | 519.2 | 515.1 | 509.6 |
| 70° | 454.1 | 472.1 | 465.2 | 458.3 | 465.2 | 472.1 | 477.7 | 483.2 | 477.7 | 472.1 | 470.8 |
| 72.5° | 409.9 | 430.6 | 422.3 | 414.0 | 422.3 | 430.6 | 433.4 | 436.2 | 432.0 | 427.9 | 425.1 |
| 75° | 361.3 | 382.1 | 375.2 | 366.9 | 373.8 | 380.7 | 382.1 | 383.5 | 383.5 | 382.1 | 373.8 |
| 77.5° | 310.1 | 326.8 | 322.6 | 318.5 | 322.6 | 326.8 | 326.8 | 326.8 | 328.2 | 328.2 | 317.1 |
| 80° | 249.2 | 258.9 | 260.3 | 261.7 | 263.1 | 264.5 | 263.1 | 261.7 | 258.9 | 256.2 | 249.2 |
| 82.5° | 185.6 | 185.6 | 196.6 | 206.3 | 206.3 | 204.9 | 203.5 | 200.7 | 195.3 | 188.3 | 173.1 |
| 85° | 117.7 | 110.8 | 128.7 | 145.4 | 145.4 | 144.0 | 141.2 | 137.0 | 126.0 | 113.6 | 101.1 |
| 87.5° | 40.1 | 33.3 | 51.2 | 69.2 | 70.6 | 70.6 | 67.8 | 65.1 | 54.0 | 41.5 | 31.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P383339
 CATALOG NUMBER: GLEON-SA6C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° | 270° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P383339
 CATALOG NUMBER: GLEON-SA6C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° | 325° |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 |
| 2.5° | 9132.7 | 9150.8 | 9167.4 | 9303.1 | 9437.3 | 9595.2 | 9753.0 | 9873.5 | 9992.6 | 10115.8 | 10239.0 |
| 5° | 7303.7 | 7325.9 | 7348.0 | 7512.7 | 7676.1 | 7896.3 | 8116.5 | 8306.1 | 8495.8 | 8718.7 | 8941.6 |
| 7.5° | 5413.8 | 5462.2 | 5509.3 | 5685.1 | 5859.6 | 6096.3 | 6331.7 | 6579.5 | 6826.0 | 7116.7 | 7407.6 |
| 10° | 4252.0 | 4343.4 | 4433.4 | 4613.5 | 4793.5 | 5027.5 | 5260.1 | 5519.0 | 5777.9 | 6064.5 | 6349.7 |
| 12.5° | 3442.1 | 3563.9 | 3684.4 | 3900.4 | 4116.4 | 4396.1 | 4674.4 | 4962.4 | 5249.0 | 5501.0 | 5753.0 |
| 15° | 2719.4 | 2852.2 | 2983.7 | 3212.3 | 3440.7 | 3748.1 | 4054.1 | 4368.4 | 4681.3 | 4983.1 | 5284.9 |
| 17.5° | 2121.2 | 2230.6 | 2338.6 | 2532.4 | 2724.9 | 3022.6 | 3320.2 | 3649.8 | 3979.3 | 4347.6 | 4714.6 |
| 20° | 1711.3 | 1757.1 | 1802.7 | 1942.6 | 2081.1 | 2323.4 | 2564.3 | 2900.7 | 3237.1 | 3677.5 | 4117.7 |
| 22.5° | 1499.5 | 1523.1 | 1545.2 | 1613.1 | 1679.5 | 1836.0 | 1991.0 | 2288.7 | 2585.0 | 3065.4 | 3544.5 |
| 25° | 1372.2 | 1390.1 | 1408.1 | 1452.5 | 1496.7 | 1571.5 | 1646.2 | 1855.4 | 2064.4 | 2536.6 | 3007.3 |
| 27.5° | 1257.2 | 1284.9 | 1311.2 | 1332.0 | 1351.4 | 1402.6 | 1452.5 | 1589.5 | 1726.6 | 2166.9 | 2605.8 |
| 30° | 1174.1 | 1183.8 | 1193.5 | 1225.4 | 1255.8 | 1308.5 | 1361.1 | 1456.6 | 1552.1 | 1924.6 | 2295.6 |
| 32.5° | 1077.2 | 1091.0 | 1104.9 | 1138.2 | 1171.3 | 1219.9 | 1268.3 | 1345.8 | 1422.0 | 1740.4 | 2057.5 |
| 35° | 990.0 | 1003.8 | 1017.7 | 1050.9 | 1082.7 | 1135.4 | 1186.6 | 1251.6 | 1315.3 | 1592.3 | 1869.2 |
| 37.5° | 936.0 | 949.8 | 963.7 | 992.8 | 1020.4 | 1073.0 | 1124.3 | 1175.5 | 1225.4 | 1481.5 | 1737.6 |
| 40° | 890.3 | 904.2 | 917.9 | 945.7 | 972.0 | 1023.2 | 1073.0 | 1116.0 | 1158.9 | 1398.4 | 1637.9 |
| 42.5° | 850.1 | 865.4 | 880.6 | 908.3 | 934.6 | 980.3 | 1026.0 | 1082.7 | 1138.2 | 1326.4 | 1513.4 |
| 45° | 816.9 | 832.2 | 845.9 | 876.4 | 906.9 | 951.2 | 995.5 | 1074.4 | 1153.3 | 1289.1 | 1424.7 |
| 47.5° | 786.4 | 803.1 | 818.3 | 851.5 | 884.8 | 940.1 | 994.1 | 1060.6 | 1125.7 | 1260.0 | 1394.2 |
| 50° | 757.3 | 776.7 | 796.1 | 836.3 | 875.1 | 967.8 | 1059.2 | 1068.9 | 1077.2 | 1236.4 | 1394.2 |
| 52.5° | 729.7 | 751.9 | 774.0 | 823.9 | 872.3 | 980.3 | 1088.3 | 1053.7 | 1017.7 | 1192.1 | 1366.6 |
| 55° | 702.0 | 721.4 | 739.4 | 800.3 | 861.2 | 940.1 | 1019.0 | 973.4 | 926.3 | 1109.1 | 1291.8 |
| 57.5° | 664.6 | 685.3 | 704.7 | 769.8 | 834.9 | 890.3 | 944.3 | 902.8 | 859.8 | 1014.9 | 1168.6 |
| 60° | 625.8 | 649.4 | 672.9 | 756.0 | 837.6 | 828.0 | 816.9 | 808.6 | 798.9 | 909.7 | 1020.4 |
| 62.5° | 591.3 | 616.1 | 641.1 | 749.1 | 857.0 | 790.6 | 724.2 | 731.1 | 736.6 | 818.3 | 900.0 |
| 65° | 556.6 | 581.6 | 605.0 | 659.1 | 713.1 | 686.7 | 660.5 | 671.6 | 681.2 | 761.5 | 841.8 |
| 67.5° | 517.8 | 540.0 | 560.8 | 578.8 | 596.7 | 599.5 | 602.3 | 613.3 | 624.4 | 720.0 | 814.2 |
| 70° | 474.9 | 492.9 | 511.0 | 523.3 | 534.4 | 540.0 | 544.1 | 558.0 | 571.9 | 675.7 | 779.5 |
| 72.5° | 426.5 | 441.6 | 455.5 | 466.6 | 477.7 | 481.8 | 484.6 | 498.5 | 512.3 | 623.0 | 733.9 |
| 75° | 373.8 | 386.3 | 397.4 | 407.1 | 416.8 | 422.3 | 427.9 | 437.5 | 447.2 | 567.7 | 686.7 |
| 77.5° | 315.7 | 328.2 | 339.3 | 347.6 | 354.5 | 359.9 | 364.1 | 376.6 | 389.1 | 490.2 | 589.9 |
| 80° | 246.5 | 261.7 | 275.6 | 282.4 | 288.0 | 289.3 | 289.3 | 300.4 | 311.5 | 383.5 | 454.1 |
| 82.5° | 174.5 | 191.1 | 206.3 | 211.8 | 217.4 | 217.4 | 217.4 | 229.8 | 242.3 | 290.7 | 337.9 |
| 85° | 102.5 | 120.4 | 137.0 | 142.6 | 148.1 | 150.9 | 152.3 | 157.8 | 162.0 | 196.6 | 229.8 |
| 87.5° | 31.9 | 47.0 | 60.9 | 63.7 | 66.4 | 72.0 | 77.5 | 78.9 | 78.9 | 102.5 | 126.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P383339
 CATALOG NUMBER: GLEON-SA6C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° | 325° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P383339
 CATALOG NUMBER: GLEON-SA6C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 | 10550.5 |
| 2.5° | 10380.2 | 10521.5 | 10686.2 | 10849.6 | 10989.5 | 11129.3 | 11245.6 |
| 5° | 9225.5 | 9509.3 | 9856.9 | 10203.1 | 10511.8 | 10820.6 | 11179.1 |
| 7.5° | 7774.4 | 8141.4 | 8591.4 | 9041.3 | 9477.5 | 9912.2 | 10463.3 |
| 10° | 6723.5 | 7096.0 | 7572.3 | 8047.3 | 8537.4 | 9026.1 | 9649.2 |
| 12.5° | 6056.2 | 6358.0 | 6819.1 | 7280.1 | 7856.1 | 8430.8 | 9030.3 |
| 15° | 5615.9 | 5945.4 | 6394.0 | 6842.6 | 7472.6 | 8102.6 | 8792.1 |
| 17.5° | 5146.5 | 5577.1 | 6151.8 | 6726.3 | 7472.6 | 8217.6 | 9030.3 |
| 20° | 4654.9 | 5190.9 | 5935.7 | 6680.6 | 7685.8 | 8689.7 | 9726.8 |
| 22.5° | 4164.9 | 4785.2 | 5740.5 | 6694.5 | 8008.4 | 9321.1 | 10720.9 |
| 25° | 3723.1 | 4439.0 | 5621.4 | 6802.4 | 8477.8 | 10151.8 | 11888.0 |
| 27.5° | 3388.1 | 4169.0 | 5573.0 | 6975.5 | 9073.2 | 11170.8 | 13157.7 |
| 30° | 3090.4 | 3885.1 | 5514.9 | 7144.5 | 9646.5 | 12147.0 | 14150.5 |
| 32.5° | 2832.8 | 3608.3 | 5402.7 | 7195.7 | 10046.6 | 12897.5 | 14990.9 |
| 35° | 2630.7 | 3392.2 | 5214.3 | 7036.4 | 10297.1 | 13557.9 | 15866.0 |
| 37.5° | 2456.3 | 3174.9 | 4999.7 | 6824.6 | 10520.1 | 14215.6 | 16850.4 |
| 40° | 2290.1 | 2942.3 | 4815.6 | 6687.6 | 10827.5 | 14967.4 | 17890.3 |
| 42.5° | 2132.2 | 2751.1 | 4667.4 | 6583.7 | 11112.7 | 15640.3 | 18799.9 |
| 45° | 2014.6 | 2604.4 | 4535.9 | 6466.1 | 11296.9 | 16127.7 | 19485.3 |
| 47.5° | 1956.4 | 2517.1 | 4465.3 | 6412.0 | 11481.0 | 16548.6 | 20054.4 |
| 50° | 1948.1 | 2502.0 | 4545.6 | 6589.2 | 11879.7 | 17168.9 | 20705.1 |
| 52.5° | 1946.7 | 2526.9 | 4776.8 | 7026.8 | 12620.5 | 18212.9 | 21409.9 |
| 55° | 1917.7 | 2542.1 | 5052.3 | 7561.3 | 13614.7 | 19666.6 | 22676.8 |
| 57.5° | 1829.0 | 2489.5 | 5336.2 | 8181.5 | 14665.5 | 21148.2 | 24104.3 |
| 60° | 1692.0 | 2362.1 | 5570.2 | 8776.9 | 15371.7 | 21965.1 | 24654.0 |
| 62.5° | 1520.3 | 2139.2 | 5647.7 | 9154.9 | 15352.3 | 21549.8 | 24100.2 |
| 65° | 1373.5 | 1905.2 | 5393.0 | 8879.3 | 14575.6 | 20270.4 | 23004.9 |
| 67.5° | 1243.3 | 1671.2 | 4756.0 | 7839.5 | 13178.5 | 18516.1 | 21612.0 |
| 70° | 1149.3 | 1517.5 | 3935.0 | 6352.5 | 11429.8 | 16505.7 | 19999.0 |
| 72.5° | 1089.6 | 1444.1 | 3208.1 | 4970.6 | 9275.3 | 13578.6 | 17106.6 |
| 75° | 1007.9 | 1329.2 | 2517.1 | 3703.7 | 7098.8 | 10493.8 | 12920.9 |
| 77.5° | 855.7 | 1120.1 | 1896.9 | 2673.6 | 5208.8 | 7742.7 | 8986.0 |
| 80° | 660.5 | 865.4 | 1304.3 | 1743.2 | 3584.7 | 5426.2 | 6126.8 |
| 82.5° | 470.8 | 603.6 | 790.6 | 977.5 | 2381.5 | 3784.0 | 3842.3 |
| 85° | 290.7 | 351.7 | 452.7 | 553.8 | 1575.6 | 2597.5 | 2164.1 |
| 87.5° | 156.5 | 187.0 | 239.5 | 290.7 | 504.0 | 717.2 | 412.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P383339
CATALOG NUMBER: GLEON-SA6C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

(END OF REPORT)