

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P939583

Luminaire Tested: **GALN-SB2B-730-U-T1**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P939583
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2405-108-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GALN-SB2B-730-U-T1
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(2) 70 CRI, 3000K, 450mA LIGHTSQUARES WITH 26 LEDS EACH AND TYPE I OPTICS
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11140 lumens
Efficiency: N/A
Efficacy: 150.7 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type I - Short
BUG Rating: B3 - U0 - G3

Input Watts (W): 73.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P939583
CATALOG NUMBER: GALN-SB2B-730-U-T1



Based on 25 foot mounting height. Maximum calculated value = 3.3 fc
Type I - Short - N/A

REPORT NUMBER: P939583
CATALOG NUMBER: GALN-SB2B-730-U-T1

Luminous Intensity Polar Plot



REPORT NUMBER: P939583

CATALOG NUMBER: GALN-SB2B-730-U-T1


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	5570.0	0.0	5570.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	5570.0	0.0	5570.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	11140.0	0.0	11140.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	201.8	1.8
10°-20°	617.1	5.5
20°-30°	1029.0	9.2
30°-40°	1415.2	12.7
40°-50°	1728.4	15.5
50°-60°	1999.1	17.9
60°-70°	2383.6	21.4
70°-80°	1663.6	14.9
80°-90°	102.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11140.0	100.0
0°-180°	11140.0	100.0

Coefficient of Utilization



REPORT NUMBER: P939583


CATALOG NUMBER: GALN-SB2B-730-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	924.0	8.3			
FM	(30°-60°)	2571.3	23.1			
FH	(60°-80°)	2023.6	18.2			G2/5000
FVH	(80°-90°)	51.1	0.5			G1/100
BL	(0°-30°)	924.0	8.3	B2/1000		
BM	(30°-60°)	2571.3	23.1	B3/5000		
BH	(60°-80°)	2023.6	18.2	B3/2500		G3/2500
BVH	(80°-90°)	51.1	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type I Short



REPORT NUMBER: P939583

CATALOG NUMBER: GALN-SB2B-730-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	2081.6	2081.6	2081.6	2081.6	2081.6	2081.6	2081.6	2081.6	2081.6	2081.6	2081.6
2.5°	2083.4	2085.8	2085.8	2084.0	2088.1	2084.6	2084.6	2082.8	2084.6	2082.8	2082.8
5°	2094.1	2097.0	2098.2	2097.6	2102.9	2100.0	2100.0	2097.6	2098.2	2096.4	2096.4
7.5°	2114.2	2118.3	2120.7	2123.7	2131.4	2127.8	2125.4	2118.3	2115.4	2110.6	2110.6
10°	2120.7	2125.4	2133.1	2148.5	2166.3	2166.9	2159.8	2142.0	2128.4	2117.7	2116.0
12.5°	2100.6	2107.1	2123.1	2154.4	2194.1	2210.1	2198.9	2169.2	2142.6	2123.7	2120.7
15°	2075.1	2082.2	2106.5	2153.9	2212.5	2249.8	2248.6	2209.5	2166.9	2137.3	2132.5
17.5°	2035.4	2042.6	2077.5	2143.8	2226.7	2288.2	2304.8	2264.6	2204.8	2165.1	2158.6
20°	1963.8	1970.3	2018.9	2111.8	2231.4	2329.1	2372.3	2336.8	2262.2	2208.3	2198.3
22.5°	1870.9	1880.9	1937.8	2056.8	2220.2	2371.7	2449.3	2425.0	2329.1	2254.5	2240.9
25°	1771.4	1782.1	1848.4	1989.3	2191.2	2402.5	2540.5	2525.1	2404.9	2311.9	2293.0
27.5°	1685.5	1696.8	1769.0	1922.4	2146.2	2414.4	2630.5	2638.1	2496.6	2375.3	2355.2
30°	1618.1	1628.7	1705.7	1868.5	2088.1	2402.5	2709.2	2762.5	2590.2	2430.3	2401.3
32.5°	1544.1	1557.7	1638.8	1802.8	2019.5	2374.1	2777.9	2896.9	2698.5	2489.5	2452.8
35°	1450.5	1462.9	1548.2	1712.8	1929.5	2328.5	2835.3	3046.1	2853.7	2579.5	2538.7
37.5°	1336.8	1348.7	1433.3	1600.3	1840.1	2264.6	2879.1	3214.2	3038.4	2709.2	2654.7
40°	1222.6	1233.8	1313.2	1474.8	1732.9	2182.9	2894.5	3378.8	3250.3	2887.4	2829.4
42.5°	1117.8	1127.8	1200.7	1351.0	1612.7	2078.7	2874.4	3522.1	3440.4	3011.7	2937.1
45°	1021.3	1030.2	1094.7	1235.0	1487.8	1952.0	2814.0	3676.0	3666.5	3100.5	2999.9
47.5°	911.2	920.0	986.9	1122.5	1362.9	1803.4	2711.6	3827.6	3980.9	3301.8	3185.8
50°	776.8	784.5	853.1	992.9	1233.2	1645.3	2569.5	3946.6	4377.6	3606.7	3461.1
52.5°	617.5	625.8	692.7	832.4	1079.3	1475.4	2382.4	4024.1	4835.8	4051.9	3872.6
55°	459.4	465.3	523.4	648.9	888.7	1281.8	2147.9	4046.0	5355.6	4660.6	4436.2
57.5°	333.3	336.9	374.2	467.7	673.7	1039.6	1863.2	3989.2	5974.3	5440.9	5158.5
60°	270.0	271.2	282.4	323.8	468.3	766.1	1519.2	3793.8	6645.7	6446.8	6090.9
62.5°	245.1	245.1	248.1	259.3	316.7	505.6	1103.0	3388.9	7365.6	7717.9	7241.3
65°	227.9	227.9	229.1	234.4	249.8	322.1	696.2	2729.3	7972.5	9206.9	8604.2
67.5°	212.5	213.1	212.5	214.3	223.2	238.0	403.8	1885.1	8299.3	10749.7	10099.1
70°	196.6	197.7	194.8	194.8	201.9	202.5	252.8	1033.7	8028.1	12042.8	11871.7
72.5°	177.6	179.4	174.7	173.5	178.8	176.4	190.0	496.1	6892.6	12428.8	12878.7
75°	161.0	163.4	152.7	149.8	149.8	148.0	154.5	254.6	4473.5	10138.8	10844.5
77.5°	146.2	151.0	133.8	124.3	122.0	116.6	126.1	155.7	1956.7	4760.0	4661.2
80°	120.8	127.3	110.1	98.9	94.7	88.8	99.5	108.9	582.0	1105.3	1058.6
82.5°	90.0	93.0	78.1	70.5	66.9	62.8	74.6	75.8	189.5	391.3	442.3
85°	57.4	58.6	48.0	41.4	39.7	37.9	47.4	41.4	72.2	287.7	418.0
87.5°	20.1	23.1	18.4	16.6	17.8	14.8	21.9	12.4	20.1	203.1	251.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)