

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P950228

Luminaire Tested: **GALN-SB4D-730-U-5NQ**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P950228
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GALN-SB4D-730-U-5NQ
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(4) 70 CRI, 3000K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND TYPE V NARROW OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 42736 lumens
Efficiency: N/A
Efficacy: 145.6 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type V - Short
BUG Rating: B5 - U0 - G3

Input Watts (W): 293.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P950228

CATALOG NUMBER: GALN-SB4D-730-U-5NQ

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd
 --- 1/2 Max cd




Based on 25 foot mounting height. Maximum calculated value = 8.3 fc
 Type V - Short - N/A

REPORT NUMBER: P950228

CATALOG NUMBER: GALN-SB4D-730-U-5NQ

Luminous Intensity Polar Plot



REPORT NUMBER: P950228

CATALOG NUMBER: GALN-SB4D-730-U-5NQ

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	21368.0	0.0	21368.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	21368.0	0.0	21368.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	42736.0	0.0	42736.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	501.9	1.2
10°-20°	1637.9	3.8
20°-30°	3092.5	7.2
30°-40°	5063.8	11.8
40°-50°	7851.5	18.4
50°-60°	11598.3	27.1
60°-70°	11040.5	25.8
70°-80°	1781.5	4.2
80°-90°	167.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	42736.0	100.0
0°-180°	42736.0	100.0

Coefficient of Utilization



REPORT NUMBER: P950228


CATALOG NUMBER: GALN-SB4D-730-U-5NQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	2616.1	6.1			
FM	(30°-60°)	12256.9	28.7			
FH	(60°-80°)	6411.0	15.0			G3/7500
FVH	(80°-90°)	84.0	0.2			G1/100
BL	(0°-30°)	2616.1	6.1	B4/5000		
BM	(30°-60°)	12256.9	28.7	B5		
BH	(60°-80°)	6411.0	15.0	B5		G3/7500
BVH	(80°-90°)	84.0	0.2			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B5-U0-G3

Type V Short



REPORT NUMBER: P950228

CATALOG NUMBER: GALN-SB4D-730-U-5NQ

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	5086.0	5086.0	5086.0	5086.0	5086.0	5086.0	5086.0	5086.0	5086.0	5086.0	5086.0
2.5°	5120.3	5103.2	5116.0	5105.3	5096.7	5088.2	5092.4	5107.5	5113.9	5116.0	5116.0
5°	5188.9	5173.9	5180.4	5180.4	5165.3	5161.1	5163.2	5173.9	5186.8	5186.8	5186.8
7.5°	5300.4	5285.4	5300.4	5291.9	5279.0	5274.7	5272.6	5281.1	5300.4	5300.4	5294.0
10°	5435.5	5418.4	5426.9	5422.6	5407.6	5401.2	5399.1	5411.9	5429.1	5426.9	5422.6
12.5°	5583.5	5564.2	5574.9	5562.0	5557.7	5551.3	5551.3	5549.2	5559.9	5551.3	5555.6
15°	5748.6	5735.7	5740.0	5731.4	5737.8	5733.6	5716.4	5707.8	5712.1	5699.2	5701.4
17.5°	5943.7	5913.7	5928.7	5924.4	5924.4	5933.0	5905.1	5894.4	5902.9	5890.1	5900.8
20°	6168.8	6138.8	6145.2	6136.7	6125.9	6134.5	6100.2	6108.8	6115.2	6106.6	6125.9
22.5°	6415.4	6376.8	6374.7	6379.0	6355.4	6357.5	6333.9	6355.4	6368.2	6344.6	6368.2
25°	6668.4	6627.7	6655.6	6644.8	6614.8	6621.2	6604.1	6625.5	6636.3	6606.2	6640.5
27.5°	6936.4	6908.6	6934.3	6940.7	6904.3	6930.0	6904.3	6923.6	6934.3	6889.3	6923.6
30°	7249.5	7221.6	7245.2	7262.4	7219.5	7260.2	7238.8	7251.6	7253.8	7200.2	7232.3
32.5°	7590.4	7547.5	7607.6	7616.2	7569.0	7618.3	7590.4	7607.6	7618.3	7545.4	7594.7
35°	8006.4	7952.8	8021.4	8010.7	7969.9	8010.7	7985.0	8010.7	8036.4	7948.5	8002.1
37.5°	8454.5	8398.8	8471.7	8452.4	8413.8	8441.7	8426.7	8443.8	8484.5	8390.2	8448.1
40°	8947.7	8879.1	8977.7	8943.4	8907.0	8902.7	8911.2	8922.0	8975.6	8870.5	8904.8
42.5°	9475.2	9402.3	9550.2	9496.6	9445.1	9410.8	9438.7	9460.2	9511.6	9393.7	9455.9
45°	10077.7	9994.1	10187.0	10122.7	10041.2	9970.5	10015.5	10047.7	10122.7	9981.2	10054.1
47.5°	10742.4	10648.0	10853.9	10834.6	10701.6	10547.3	10650.2	10742.4	10798.1	10626.6	10684.5
50°	11392.1	11319.2	11589.3	11612.9	11450.0	11233.4	11377.1	11516.4	11531.4	11306.3	11334.2
52.5°	12001.0	11928.1	12320.5	12468.4	12322.6	12065.3	12217.6	12359.1	12245.5	11953.8	11962.4
55°	12487.7	12427.7	12927.3	13309.0	13358.3	13146.0	13236.1	13231.8	12858.7	12410.6	12425.6
57.5°	12605.7	12597.1	13227.5	14035.8	14550.5	14576.2	14398.2	13943.6	13139.6	12537.1	12498.5
60°	12069.6	12123.2	12989.5	14415.4	15787.6	16358.0	15588.2	14291.0	12820.1	11983.9	11885.2
62.5°	10465.8	10607.3	11651.5	13952.2	16786.8	18407.8	16542.4	13763.5	11507.9	10416.5	10352.1
65°	7500.4	7746.9	8900.5	11906.7	16696.8	20209.0	16405.2	11810.2	8986.3	7727.6	7635.4
67.5°	3402.8	3653.7	4633.6	8152.2	14514.0	19720.1	14479.7	8238.0	4865.2	3666.6	3613.0
70°	1232.9	1275.8	1591.0	3263.5	9275.8	15712.6	9672.4	3287.0	1691.8	1359.4	1342.3
72.5°	746.2	752.6	819.1	1168.6	3222.7	9539.5	3359.9	1207.2	836.2	741.9	754.8
75°	473.9	469.6	583.2	714.0	1142.9	3218.4	1198.6	714.0	581.1	529.6	533.9
77.5°	340.9	351.6	418.1	533.9	720.4	1091.4	707.6	510.3	418.1	343.1	349.5
80°	255.2	261.6	304.5	416.0	506.0	679.7	450.3	377.4	315.2	214.4	220.9
82.5°	184.4	184.4	199.4	302.3	308.8	366.7	244.4	265.9	208.0	152.2	152.2
85°	109.4	107.2	124.4	180.1	160.8	135.1	111.5	163.0	130.8	94.3	92.2
87.5°	38.6	40.7	38.6	51.5	42.9	36.5	34.3	45.0	36.5	32.2	30.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)