

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P324275

Luminaire Tested: **GLEON-SA1B-827-U-SLL-HSS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P324275  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: GLEON-SA1B-827-U-SLL-HSS  
Description: GALLEON AREA AND ROADWAY LUMINAIRE  
(1) 80 CRI, 2700K, 800mA LIGHTSQUARE WITH 16 LEDS AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3262 lumens  
Efficiency: N/A  
Efficacy: 74.1 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type III - Medium  
BUG Rating: B1 - U0 - G1


Input Watts (W): 44  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P324275  
 CATALOG NUMBER: GLEON-SA1B-827-U-SLL-HSS

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.3 fc  
 Type III - Medium - N/A

REPORT NUMBER: P324275  
CATALOG NUMBER: GLEON-SA1B-827-U-SLL-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral      - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P324275  
 CATALOG NUMBER: GLEON-SA1B-827-U-SLL-HSS


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 489.5    | 0.0    | 489.5  |
|                    | % Fixture | 15.0     | 0.0    | 15.0   |
| <b>Street Side</b> | Lumens    | 2772.5   | 0.0    | 2772.5 |
|                    | % Fixture | 85.0     | 0.0    | 85.0   |
| <b>Total</b>       | Lumens    | 3262.0   | 0.0    | 3262.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 83.0   | 2.5       |
| 10°-20°   | 163.4  | 5.0       |
| 20°-30°   | 231.2  | 7.1       |
| 30°-40°   | 340.0  | 10.4      |
| 40°-50°   | 488.7  | 15.0      |
| 50°-60°   | 687.9  | 21.1      |
| 60°-70°   | 803.4  | 24.6      |
| 70°-80°   | 409.9  | 12.6      |
| 80°-90°   | 54.4   | 1.7       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 3262.0 | 100.0     |
| 0°-180°   | 3262.0 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P324275  
 CATALOG NUMBER: GLEON-SA1B-827-U-SLL-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 349.7  | 10.7      |                         |      |         |
| FM (30°-60°)   | 1283.9 | 39.4      |                         |      |         |
| FH (60°-80°)   | 1086.2 | 33.3      |                         |      | G1/1800 |
| FVH (80°-90°)  | 52.8   | 1.6       |                         |      | G1/100  |
| BL (0°-30°)    | 128.0  | 3.9       | B1/500                  |      |         |
| BM (30°-60°)   | 232.7  | 7.1       | B1/1000                 |      |         |
| BH (60°-80°)   | 127.1  | 3.9       | B1/500                  |      | G1/500  |
| BVH (80°-90°)  | 1.7    | 0.1       |                         |      | G0/10   |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G1**  
 Type III Medium





REPORT NUMBER: P324275

CATALOG NUMBER: GLEON-SA1B-827-U-SLL-HSS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 1°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 |
| 2.5°  | 1186.3 | 1188.1 | 1197.7 | 1220.0 | 1244.2 | 1246.1 | 1262.5 | 1245.6 | 1239.9 | 1212.7 | 1184.6 |
| 5°    | 1195.2 | 1202.4 | 1235.3 | 1300.6 | 1357.3 | 1375.6 | 1388.6 | 1355.5 | 1320.7 | 1254.3 | 1183.4 |
| 7.5°  | 1123.1 | 1135.0 | 1186.8 | 1309.4 | 1410.8 | 1455.6 | 1464.1 | 1412.4 | 1327.2 | 1217.8 | 1111.2 |
| 10°   | 1030.7 | 1044.3 | 1106.7 | 1257.5 | 1396.8 | 1473.5 | 1485.3 | 1417.5 | 1295.1 | 1158.8 | 1033.2 |
| 12.5° | 955.9  | 971.8  | 1035.6 | 1199.1 | 1348.4 | 1433.4 | 1456.6 | 1400.3 | 1267.3 | 1116.9 | 979.8  |
| 15°   | 921.4  | 939.7  | 1006.7 | 1161.4 | 1294.8 | 1361.7 | 1380.8 | 1356.6 | 1251.8 | 1110.3 | 967.5  |
| 17.5° | 941.2  | 961.0  | 1030.2 | 1164.7 | 1244.4 | 1273.0 | 1288.4 | 1298.3 | 1251.8 | 1150.3 | 1003.6 |
| 20°   | 1022.3 | 1043.7 | 1116.9 | 1197.6 | 1202.7 | 1192.0 | 1208.5 | 1243.3 | 1266.3 | 1226.3 | 1090.5 |
| 22.5° | 1134.5 | 1159.6 | 1242.2 | 1254.0 | 1182.3 | 1141.9 | 1144.1 | 1198.6 | 1292.8 | 1322.7 | 1211.0 |
| 25°   | 1271.3 | 1301.9 | 1385.9 | 1338.0 | 1190.8 | 1112.1 | 1111.3 | 1161.9 | 1318.6 | 1419.3 | 1345.3 |
| 27.5° | 1407.1 | 1440.8 | 1514.7 | 1440.6 | 1225.8 | 1106.7 | 1105.2 | 1150.7 | 1343.7 | 1505.2 | 1491.9 |
| 30°   | 1521.0 | 1553.7 | 1617.4 | 1515.0 | 1263.7 | 1119.4 | 1112.0 | 1162.6 | 1358.7 | 1561.0 | 1598.9 |
| 32.5° | 1613.7 | 1640.0 | 1691.4 | 1566.1 | 1304.2 | 1143.9 | 1127.9 | 1194.5 | 1384.2 | 1608.1 | 1697.1 |
| 35°   | 1715.7 | 1743.3 | 1763.9 | 1614.8 | 1349.6 | 1179.3 | 1156.3 | 1245.0 | 1423.5 | 1656.0 | 1804.9 |
| 37.5° | 1832.0 | 1859.6 | 1857.1 | 1659.3 | 1407.3 | 1237.9 | 1223.2 | 1325.1 | 1484.5 | 1703.5 | 1925.1 |
| 40°   | 1945.9 | 1974.1 | 1954.0 | 1708.0 | 1474.9 | 1334.5 | 1323.7 | 1445.3 | 1566.3 | 1764.2 | 2066.0 |
| 42.5° | 2052.6 | 2083.0 | 2040.0 | 1754.0 | 1555.6 | 1456.2 | 1474.8 | 1600.1 | 1668.6 | 1839.0 | 2187.5 |
| 45°   | 2138.5 | 2169.5 | 2112.2 | 1798.8 | 1640.6 | 1604.0 | 1659.8 | 1771.6 | 1791.6 | 1902.2 | 2269.5 |
| 47.5° | 2200.9 | 2230.3 | 2162.3 | 1843.6 | 1749.4 | 1784.6 | 1881.8 | 1951.5 | 1902.7 | 1957.1 | 2327.8 |
| 50°   | 2240.8 | 2263.6 | 2176.9 | 1899.7 | 1892.2 | 1995.4 | 2113.1 | 2147.1 | 2007.3 | 2006.5 | 2398.5 |
| 52.5° | 2266.1 | 2276.5 | 2187.8 | 1958.3 | 2041.1 | 2224.8 | 2339.7 | 2350.3 | 2115.0 | 2060.9 | 2493.9 |
| 55°   | 2353.4 | 2361.8 | 2264.4 | 2029.2 | 2164.3 | 2425.9 | 2544.6 | 2534.7 | 2236.9 | 2167.4 | 2606.4 |
| 57.5° | 2502.4 | 2511.2 | 2422.8 | 2131.2 | 2263.9 | 2550.1 | 2693.1 | 2710.8 | 2379.8 | 2316.9 | 2726.9 |
| 60°   | 2577.2 | 2593.5 | 2562.0 | 2260.4 | 2360.5 | 2629.5 | 2794.3 | 2851.0 | 2558.5 | 2514.1 | 2843.7 |
| 62.5° | 2509.3 | 2533.1 | 2578.9 | 2403.6 | 2456.5 | 2673.3 | 2825.8 | 2901.2 | 2741.4 | 2743.9 | 2915.7 |
| 65°   | 2374.0 | 2393.0 | 2470.5 | 2482.1 | 2512.1 | 2667.9 | 2747.9 | 2831.1 | 2853.5 | 2955.0 | 2911.9 |
| 67.5° | 2210.5 | 2217.6 | 2283.4 | 2488.3 | 2431.4 | 2505.3 | 2514.0 | 2575.5 | 2764.9 | 3029.8 | 2794.9 |
| 70°   | 1975.1 | 1979.0 | 2036.5 | 2281.4 | 2089.5 | 2105.7 | 2092.9 | 2105.4 | 2377.1 | 2847.6 | 2499.6 |
| 72.5° | 1589.6 | 1599.3 | 1681.1 | 1894.6 | 1522.2 | 1475.4 | 1576.2 | 1570.6 | 1830.7 | 2405.8 | 1856.5 |
| 75°   | 1170.4 | 1187.2 | 1310.7 | 1526.1 | 1068.4 | 966.4  | 1040.0 | 1059.6 | 1301.4 | 1860.9 | 1160.9 |
| 77.5° | 819.4  | 832.0  | 951.6  | 1121.9 | 773.2  | 691.0  | 664.5  | 687.8  | 859.0  | 1346.2 | 584.9  |
| 80°   | 472.1  | 476.7  | 553.0  | 647.8  | 521.1  | 596.2  | 540.1  | 556.1  | 514.7  | 598.9  | 251.6  |
| 82.5° | 308.9  | 309.7  | 339.5  | 385.5  | 324.5  | 377.0  | 279.1  | 356.8  | 316.6  | 240.6  | 81.9   |
| 85°   | 166.9  | 167.8  | 196.9  | 273.7  | 183.7  | 103.8  | 61.0   | 125.3  | 195.8  | 55.2   | 22.4   |
| 87.5° | 18.4   | 16.8   | 59.3   | 99.5   | 51.0   | 9.4    | 3.2    | 14.1   | 31.4   | 3.6    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P324275

CATALOG NUMBER: GLEON-SA1B-827-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 |
| 2.5°  | 1170.2 | 1157.4 | 1125.4 | 1091.6 | 1064.4 | 1038.9 | 1013.2 | 981.9  | 957.6  | 952.6  | 944.6  |
| 5°    | 1145.2 | 1104.5 | 1037.5 | 970.1  | 915.9  | 847.4  | 804.0  | 770.2  | 737.1  | 735.1  | 728.4  |
| 7.5°  | 1057.7 | 1004.3 | 909.8  | 816.7  | 740.3  | 675.1  | 609.3  | 565.3  | 530.6  | 518.4  | 511.2  |
| 10°   | 973.7  | 913.6  | 795.6  | 689.3  | 621.2  | 563.6  | 517.2  | 471.1  | 429.4  | 400.7  | 387.7  |
| 12.5° | 914.9  | 848.5  | 718.5  | 626.9  | 578.1  | 523.4  | 466.8  | 409.3  | 361.3  | 326.7  | 305.5  |
| 15°   | 892.2  | 821.3  | 692.7  | 602.2  | 541.9  | 472.7  | 400.4  | 334.7  | 281.4  | 250.0  | 231.0  |
| 17.5° | 919.3  | 836.8  | 690.7  | 572.1  | 487.8  | 401.8  | 321.9  | 244.3  | 194.1  | 170.3  | 158.1  |
| 20°   | 987.9  | 885.9  | 690.0  | 535.1  | 423.6  | 317.7  | 218.0  | 160.7  | 130.3  | 117.0  | 111.3  |
| 22.5° | 1084.9 | 948.6  | 696.1  | 498.7  | 356.6  | 227.0  | 150.5  | 118.1  | 102.4  | 95.3   | 92.1   |
| 25°   | 1209.8 | 1036.7 | 713.6  | 465.6  | 293.8  | 169.4  | 117.3  | 98.9   | 87.9   | 82.4   | 80.0   |
| 27.5° | 1342.8 | 1138.1 | 740.8  | 436.8  | 242.6  | 135.1  | 100.4  | 84.7   | 76.8   | 72.9   | 70.8   |
| 30°   | 1452.5 | 1255.5 | 768.3  | 404.9  | 205.5  | 117.7  | 91.9   | 77.3   | 68.1   | 65.7   | 63.7   |
| 32.5° | 1548.5 | 1344.4 | 787.8  | 376.0  | 181.3  | 104.6  | 83.1   | 69.1   | 62.9   | 58.1   | 55.9   |
| 35°   | 1647.9 | 1418.4 | 787.1  | 355.7  | 164.6  | 94.7   | 75.7   | 61.8   | 54.4   | 48.8   | 47.1   |
| 37.5° | 1755.4 | 1502.0 | 773.7  | 338.4  | 157.3  | 86.8   | 71.5   | 57.9   | 50.5   | 45.0   | 42.8   |
| 40°   | 1881.3 | 1589.8 | 760.0  | 322.2  | 155.3  | 80.5   | 68.6   | 54.9   | 47.0   | 41.6   | 39.4   |
| 42.5° | 2004.0 | 1668.9 | 747.9  | 310.1  | 146.6  | 80.4   | 66.0   | 52.5   | 44.2   | 38.9   | 36.5   |
| 45°   | 2102.2 | 1742.6 | 745.6  | 302.9  | 137.5  | 83.1   | 64.6   | 51.0   | 42.0   | 36.8   | 34.5   |
| 47.5° | 2183.7 | 1822.6 | 760.4  | 297.8  | 128.9  | 75.9   | 68.0   | 49.9   | 40.0   | 34.9   | 32.3   |
| 50°   | 2280.8 | 1920.9 | 795.3  | 289.4  | 119.8  | 68.3   | 77.9   | 50.2   | 38.3   | 33.1   | 30.3   |
| 52.5° | 2416.2 | 2056.9 | 846.6  | 275.4  | 107.2  | 61.3   | 76.6   | 50.5   | 36.5   | 31.1   | 28.3   |
| 55°   | 2567.9 | 2226.7 | 901.8  | 252.0  | 89.8   | 52.2   | 65.7   | 48.4   | 32.9   | 28.9   | 26.3   |
| 57.5° | 2727.4 | 2380.8 | 934.6  | 224.2  | 71.4   | 45.1   | 52.5   | 44.0   | 29.1   | 26.0   | 24.3   |
| 60°   | 2752.4 | 2439.3 | 919.6  | 190.1  | 56.7   | 39.2   | 38.9   | 44.8   | 26.0   | 22.9   | 21.6   |
| 62.5° | 2690.1 | 2365.8 | 847.1  | 159.6  | 47.4   | 34.5   | 32.0   | 39.1   | 23.5   | 20.4   | 19.2   |
| 65°   | 2570.4 | 2166.9 | 729.7  | 143.9  | 44.0   | 29.5   | 26.6   | 27.5   | 20.6   | 17.8   | 16.7   |
| 67.5° | 2403.8 | 1901.4 | 599.1  | 134.9  | 43.6   | 25.3   | 22.7   | 20.9   | 17.8   | 15.5   | 14.5   |
| 70°   | 2063.2 | 1584.0 | 477.9  | 130.0  | 42.3   | 21.3   | 19.2   | 17.0   | 14.8   | 13.1   | 12.4   |
| 72.5° | 1518.5 | 1122.5 | 371.8  | 124.5  | 42.6   | 17.0   | 16.7   | 14.1   | 11.9   | 10.2   | 9.9    |
| 75°   | 877.4  | 641.3  | 243.8  | 100.9  | 40.6   | 13.1   | 13.9   | 9.9    | 8.3    | 7.1    | 7.1    |
| 77.5° | 467.6  | 391.1  | 92.9   | 42.0   | 14.8   | 8.3    | 7.9    | 5.9    | 5.3    | 4.3    | 4.2    |
| 80°   | 203.8  | 172.1  | 28.0   | 11.7   | 8.2    | 4.5    | 2.9    | 2.6    | 2.3    | 1.9    | 1.7    |
| 82.5° | 72.2   | 62.3   | 9.1    | 5.7    | 3.6    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 16.4   | 11.7   | 0.0    | 1.4    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |





REPORT NUMBER: P324275  
 CATALOG NUMBER: GLEON-SA1B-827-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 185°   | 195°   | 205°   | 215°   | 225°   | 235°   | 245°   | 255°   | 265°   | 270°   | 275°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 |
| 2.5°  | 928.2  | 924.8  | 904.7  | 905.5  | 909.1  | 914.2  | 902.1  | 907.7  | 922.7  | 937.0  | 942.4  |
| 5°    | 717.8  | 718.5  | 706.3  | 713.9  | 720.7  | 725.3  | 705.9  | 706.2  | 718.1  | 734.3  | 742.8  |
| 7.5°  | 505.8  | 504.5  | 505.1  | 523.2  | 536.0  | 526.8  | 534.0  | 508.9  | 510.4  | 522.0  | 513.3  |
| 10°   | 376.0  | 359.0  | 349.4  | 363.0  | 377.0  | 371.9  | 359.4  | 351.2  | 357.0  | 369.8  | 368.9  |
| 12.5° | 295.5  | 271.0  | 256.7  | 246.9  | 258.5  | 248.9  | 248.6  | 241.5  | 233.8  | 235.2  | 255.7  |
| 15°   | 222.2  | 204.4  | 187.4  | 171.8  | 171.5  | 168.3  | 151.7  | 133.2  | 131.7  | 132.6  | 143.2  |
| 17.5° | 152.8  | 146.8  | 139.8  | 126.4  | 122.8  | 109.2  | 93.2   | 85.8   | 82.1   | 83.8   | 87.3   |
| 20°   | 107.4  | 105.1  | 105.8  | 98.6   | 93.5   | 80.5   | 71.1   | 68.1   | 67.5   | 69.2   | 70.9   |
| 22.5° | 89.0   | 84.8   | 84.4   | 81.1   | 76.0   | 66.6   | 61.5   | 59.8   | 59.0   | 60.6   | 61.8   |
| 25°   | 77.9   | 73.7   | 72.0   | 70.0   | 64.6   | 58.1   | 55.0   | 53.5   | 52.7   | 53.6   | 54.4   |
| 27.5° | 68.6   | 64.7   | 63.2   | 61.8   | 56.6   | 51.9   | 49.4   | 48.1   | 47.4   | 47.7   | 48.5   |
| 30°   | 61.7   | 58.3   | 56.2   | 54.5   | 50.1   | 46.8   | 44.7   | 43.3   | 42.6   | 42.6   | 43.4   |
| 32.5° | 54.4   | 52.5   | 50.7   | 48.5   | 44.3   | 42.2   | 40.0   | 38.5   | 37.9   | 38.0   | 38.6   |
| 35°   | 45.3   | 44.7   | 45.1   | 43.1   | 39.6   | 37.7   | 35.5   | 33.8   | 33.4   | 33.5   | 34.1   |
| 37.5° | 40.2   | 37.4   | 39.1   | 38.0   | 36.0   | 33.5   | 30.8   | 29.2   | 28.4   | 28.9   | 29.2   |
| 40°   | 36.9   | 33.5   | 32.3   | 33.4   | 33.1   | 29.1   | 26.6   | 25.0   | 24.4   | 24.6   | 24.9   |
| 42.5° | 34.1   | 30.1   | 27.4   | 27.2   | 29.1   | 25.3   | 22.7   | 21.3   | 20.6   | 20.6   | 20.9   |
| 45°   | 31.5   | 27.2   | 23.8   | 21.2   | 24.4   | 21.5   | 19.0   | 17.8   | 16.8   | 16.8   | 17.0   |
| 47.5° | 29.5   | 24.7   | 20.7   | 17.3   | 18.4   | 17.6   | 15.6   | 14.4   | 13.4   | 13.4   | 13.6   |
| 50°   | 27.7   | 22.3   | 17.9   | 14.5   | 13.8   | 14.5   | 12.7   | 11.3   | 10.7   | 10.5   | 10.8   |
| 52.5° | 25.7   | 19.8   | 15.3   | 12.4   | 10.8   | 11.0   | 9.9    | 9.0    | 8.2    | 8.2    | 8.5    |
| 55°   | 23.6   | 17.8   | 13.3   | 10.5   | 9.0    | 8.2    | 7.9    | 7.3    | 6.6    | 6.6    | 7.0    |
| 57.5° | 21.6   | 15.6   | 11.3   | 8.7    | 7.1    | 6.5    | 6.5    | 6.0    | 5.6    | 5.6    | 5.9    |
| 60°   | 19.8   | 13.4   | 9.3    | 7.1    | 5.6    | 5.4    | 5.6    | 5.1    | 4.8    | 4.8    | 5.1    |
| 62.5° | 17.6   | 11.4   | 7.6    | 5.9    | 4.5    | 4.3    | 4.8    | 4.5    | 4.2    | 4.2    | 4.5    |
| 65°   | 15.0   | 9.7    | 6.0    | 4.5    | 3.4    | 3.4    | 4.0    | 3.7    | 3.4    | 3.4    | 3.7    |
| 67.5° | 12.7   | 8.2    | 4.6    | 3.2    | 2.5    | 2.6    | 3.4    | 3.1    | 2.9    | 2.9    | 3.2    |
| 70°   | 10.5   | 6.3    | 3.2    | 2.0    | 1.4    | 2.0    | 2.6    | 2.6    | 2.6    | 2.6    | 2.9    |
| 72.5° | 7.9    | 4.3    | 1.9    | 0.8    | 0.6    | 1.4    | 2.2    | 2.5    | 2.3    | 2.3    | 2.8    |
| 75°   | 5.1    | 2.5    | 0.6    | 0.0    | 0.0    | 0.8    | 1.7    | 2.0    | 2.0    | 1.9    | 2.3    |
| 77.5° | 2.9    | 0.8    | 0.0    | 0.0    | 0.0    | 0.0    | 1.1    | 0.9    | 0.8    | 0.6    | 1.1    |
| 80°   | 0.8    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 82.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P324275

CATALOG NUMBER: GLEON-SA1B-827-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 285°   | 295°   | 305°   | 315°   | 325°   | 335°   | 345°   | 355°   | 359°   | 360°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 | 1094.3 |
| 2.5°  | 964.2  | 982.5  | 1008.1 | 1035.3 | 1077.2 | 1110.4 | 1143.0 | 1171.0 | 1181.8 | 1186.3 |
| 5°    | 763.2  | 789.9  | 827.5  | 875.7  | 951.3  | 1019.2 | 1088.2 | 1157.5 | 1187.7 | 1195.2 |
| 7.5°  | 547.6  | 581.8  | 629.5  | 690.0  | 778.5  | 866.6  | 962.8  | 1064.7 | 1111.3 | 1123.1 |
| 10°   | 405.3  | 447.0  | 501.7  | 565.4  | 649.9  | 740.5  | 845.4  | 961.8  | 1015.1 | 1030.7 |
| 12.5° | 287.6  | 344.0  | 417.2  | 494.6  | 567.9  | 648.7  | 754.9  | 883.1  | 939.0  | 955.9  |
| 15°   | 168.9  | 223.4  | 310.1  | 413.8  | 507.6  | 589.5  | 697.4  | 842.8  | 904.4  | 921.4  |
| 17.5° | 96.9   | 124.1  | 189.6  | 305.2  | 432.5  | 545.9  | 679.3  | 852.8  | 925.4  | 941.2  |
| 20°   | 74.0   | 82.7   | 109.2  | 196.6  | 344.7  | 503.1  | 679.3  | 909.7  | 999.2  | 1022.3 |
| 22.5° | 64.7   | 71.1   | 81.9   | 117.3  | 253.7  | 457.2  | 687.2  | 991.9  | 1108.9 | 1134.5 |
| 25°   | 57.5   | 63.2   | 72.5   | 88.2   | 173.1  | 402.7  | 705.9  | 1092.8 | 1238.1 | 1271.3 |
| 27.5° | 51.5   | 56.9   | 65.2   | 77.3   | 118.4  | 336.9  | 731.1  | 1211.2 | 1380.5 | 1407.1 |
| 30°   | 46.0   | 51.1   | 58.7   | 67.2   | 91.3   | 262.2  | 752.5  | 1322.7 | 1492.4 | 1521.0 |
| 32.5° | 40.9   | 45.6   | 52.4   | 58.7   | 74.8   | 193.9  | 754.9  | 1411.1 | 1585.3 | 1613.7 |
| 35°   | 36.2   | 40.3   | 46.5   | 51.5   | 62.0   | 153.1  | 718.8  | 1487.8 | 1678.1 | 1715.7 |
| 37.5° | 31.5   | 35.5   | 40.9   | 44.7   | 54.5   | 124.9  | 663.8  | 1573.2 | 1797.3 | 1832.0 |
| 40°   | 27.2   | 30.8   | 36.3   | 38.8   | 51.6   | 96.0   | 604.0  | 1662.8 | 1914.1 | 1945.9 |
| 42.5° | 23.2   | 26.6   | 32.0   | 36.8   | 45.3   | 71.7   | 539.4  | 1746.9 | 2019.2 | 2052.6 |
| 45°   | 19.3   | 22.9   | 28.3   | 38.9   | 37.5   | 53.6   | 470.4  | 1802.7 | 2102.2 | 2138.5 |
| 47.5° | 15.6   | 19.6   | 27.0   | 37.1   | 30.0   | 39.4   | 415.7  | 1855.5 | 2165.0 | 2200.9 |
| 50°   | 12.5   | 16.5   | 30.4   | 33.1   | 24.6   | 30.1   | 392.8  | 1902.8 | 2206.3 | 2240.8 |
| 52.5° | 10.2   | 13.9   | 28.7   | 25.3   | 20.6   | 24.9   | 405.2  | 1979.5 | 2244.5 | 2266.1 |
| 55°   | 8.5    | 11.0   | 17.3   | 17.6   | 17.5   | 21.2   | 420.5  | 2089.5 | 2343.2 | 2353.4 |
| 57.5° | 7.4    | 8.8    | 12.1   | 13.6   | 14.7   | 18.9   | 420.8  | 2247.4 | 2496.0 | 2502.4 |
| 60°   | 6.3    | 7.7    | 10.0   | 11.0   | 12.7   | 16.8   | 405.5  | 2302.6 | 2556.2 | 2577.2 |
| 62.5° | 5.6    | 6.8    | 8.3    | 9.1    | 10.7   | 15.1   | 369.6  | 2222.7 | 2473.6 | 2509.3 |
| 65°   | 4.9    | 6.2    | 7.0    | 7.7    | 9.4    | 13.6   | 310.6  | 2062.9 | 2336.7 | 2374.0 |
| 67.5° | 4.3    | 5.4    | 6.2    | 7.0    | 8.5    | 12.1   | 228.7  | 1877.3 | 2179.6 | 2210.5 |
| 70°   | 3.9    | 4.8    | 5.6    | 6.2    | 7.4    | 10.2   | 138.8  | 1593.0 | 1962.3 | 1975.1 |
| 72.5° | 3.7    | 4.3    | 5.1    | 5.6    | 6.5    | 9.0    | 70.3   | 1170.7 | 1568.7 | 1589.6 |
| 75°   | 3.2    | 3.9    | 4.6    | 4.9    | 5.7    | 7.7    | 28.6   | 768.9  | 1136.8 | 1170.4 |
| 77.5° | 2.6    | 3.6    | 4.2    | 4.5    | 4.9    | 6.3    | 14.5   | 491.4  | 797.8  | 819.4  |
| 80°   | 0.9    | 2.6    | 3.6    | 3.7    | 4.2    | 4.6    | 9.6    | 269.0  | 462.8  | 472.1  |
| 82.5° | 0.0    | 1.7    | 2.8    | 2.6    | 2.9    | 3.6    | 6.2    | 127.9  | 305.5  | 308.9  |
| 85°   | 0.0    | 0.8    | 2.2    | 1.7    | 1.2    | 2.5    | 2.2    | 28.0   | 160.2  | 166.9  |
| 87.5° | 0.0    | 0.0    | 0.2    | 0.8    | 0.6    | 0.9    | 0.3    | 0.2    | 14.5   | 18.4   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-157-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/03/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Invue  
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**  
 Description: Epic Modern Light Square 40W 5WQ Optic

**Spectral Parameters**

CCT (K): 2764  
 CIE u': 0.2591  
 CIE v': 0.5290  
 Duv: 0.0020  
 CIE x: 0.4581  
 CIE y: 0.4156  
 CIE z: 0.1263  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 583  
 Purity: 62.2537  
 Rf: 84.7  
 Rg: 94.6

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 80.9 |      |      |
| R1:       | 78.8 | R9:  | -1.5 |
| R2:       | 89.9 | R10: | 77.9 |
| R3:       | 96.2 | R11: | 78.9 |
| R4:       | 79.1 | R12: | 71.6 |
| R5:       | 79.1 | R13: | 81.2 |
| R6:       | 88.8 | R14: | 98.5 |
| R7:       | 81.3 | R15: | 69.9 |
| R8:       | 54.3 |      |      |



**Test Conditions**

Stabilization Time: 81M  
 Operation Time: 2H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 2764K  
 CIE x = 0.4581  
 CIE y = 0.4156  
 Duv = 0.0020

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

**Photopic Flux vs. Wavelength**




**Photopic Lumens: 4337.9**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | 0.0                            | 490               | 18018                                | 2.6                            | 620               | 87426                                | 22.8                           | 750               | 2680                                 | 0.0                            | 880               | 58                                   | 0.0                            |
| 365               | 0                                    | 0.0                            | 495               | 22295                                | 3.9                            | 625               | 83013                                | 18.2                           | 755               | 2287                                 | 0.0                            | 885               | 46                                   | 0.0                            |
| 370               | 0                                    | 0.0                            | 500               | 26478                                | 5.8                            | 630               | 78077                                | 14.1                           | 760               | 1944                                 | 0.0                            | 890               | 45                                   | 0.0                            |
| 375               | 0                                    | 0.0                            | 505               | 30524                                | 8.5                            | 635               | 72080                                | 10.7                           | 765               | 1653                                 | 0.0                            | 895               | 41                                   | 0.0                            |
| 380               | 0                                    | 0.0                            | 510               | 33611                                | 11.5                           | 640               | 66249                                | 7.9                            | 770               | 1413                                 | 0.0                            | 900               | 38                                   | 0.0                            |
| 385               | 0                                    | 0.0                            | 515               | 36490                                | 15.2                           | 645               | 59973                                | 5.7                            | 775               | 1198                                 | 0.0                            | 905               | 33                                   | 0.0                            |
| 390               | 0                                    | 0.0                            | 520               | 38610                                | 18.7                           | 650               | 53972                                | 3.9                            | 780               | 1025                                 | 0.0                            | 910               | 30                                   | 0.0                            |
| 395               | 0                                    | 0.0                            | 525               | 40511                                | 21.9                           | 655               | 48369                                | 2.7                            | 785               | 874                                  | 0.0                            | 915               | 23                                   | 0.0                            |
| 400               | 48                                   | 0.0                            | 530               | 42223                                | 24.9                           | 660               | 42641                                | 1.8                            | 790               | 747                                  | 0.0                            | 920               | 24                                   | 0.0                            |
| 405               | 201                                  | 0.0                            | 535               | 44137                                | 27.6                           | 665               | 37602                                | 1.1                            | 795               | 639                                  | 0.0                            | 925               | 22                                   | 0.0                            |
| 410               | 457                                  | 0.0                            | 540               | 46032                                | 30.0                           | 670               | 32798                                | 0.7                            | 800               | 547                                  | 0.0                            | 930               | 22                                   | 0.0                            |
| 415               | 925                                  | 0.0                            | 545               | 48553                                | 32.5                           | 675               | 28558                                | 0.5                            | 805               | 473                                  | 0.0                            | 935               | 17                                   | 0.0                            |
| 420               | 1816                                 | 0.0                            | 550               | 51408                                | 34.9                           | 680               | 24782                                | 0.3                            | 810               | 401                                  | 0.0                            | 940               | 13                                   | 0.0                            |
| 425               | 3217                                 | 0.0                            | 555               | 54711                                | 37.4                           | 685               | 21386                                | 0.2                            | 815               | 351                                  | 0.0                            | 945               | 6                                    | 0.0                            |
| 430               | 5520                                 | 0.0                            | 560               | 58847                                | 40.0                           | 690               | 18413                                | 0.1                            | 820               | 307                                  | 0.0                            | 950               | 10                                   | 0.0                            |
| 435               | 9225                                 | 0.1                            | 565               | 63386                                | 42.4                           | 695               | 15721                                | 0.1                            | 825               | 261                                  | 0.0                            | 955               | 11                                   | 0.0                            |
| 440               | 15522                                | 0.2                            | 570               | 68196                                | 44.3                           | 700               | 13432                                | 0.0                            | 830               | 228                                  | 0.0                            | 960               | 8                                    | 0.0                            |
| 445               | 27642                                | 0.6                            | 575               | 73613                                | 46.0                           | 705               | 11513                                | 0.0                            | 835               | 193                                  | 0.0                            | 965               | 12                                   | 0.0                            |
| 450               | 36602                                | 0.9                            | 580               | 79207                                | 47.1                           | 710               | 9780                                 | 0.0                            | 840               | 174                                  | 0.0                            | 970               | 3                                    | 0.0                            |
| 455               | 28292                                | 0.9                            | 585               | 84248                                | 47.0                           | 715               | 8356                                 | 0.0                            | 845               | 151                                  | 0.0                            | 975               | 8                                    | 0.0                            |
| 460               | 21166                                | 0.9                            | 590               | 88397                                | 45.7                           | 720               | 7161                                 | 0.0                            | 850               | 123                                  | 0.0                            | 980               | 2                                    | 0.0                            |
| 465               | 19092                                | 1.0                            | 595               | 91428                                | 43.4                           | 725               | 6067                                 | 0.0                            | 855               | 106                                  | 0.0                            | 985               | 13                                   | 0.0                            |
| 470               | 14951                                | 0.9                            | 600               | 93452                                | 40.3                           | 730               | 5164                                 | 0.0                            | 860               | 95                                   | 0.0                            | 990               | 16                                   | 0.0                            |
| 475               | 12606                                | 1.0                            | 605               | 93959                                | 36.4                           | 735               | 4393                                 | 0.0                            | 865               | 82                                   | 0.0                            | 995               | 20                                   | 0.0                            |
| 480               | 13323                                | 1.3                            | 610               | 93079                                | 32.0                           | 740               | 3694                                 | 0.0                            | 870               | 77                                   | 0.0                            | 1000              | 0                                    | 0.0                            |
| 485               | 15164                                | 1.8                            | 615               | 90707                                | 27.3                           | 745               | 3157                                 | 0.0                            | 875               | 65                                   | 0.0                            |                   |                                      |                                |

REPORT NUMBER: SP1-2407-157-9

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 5286.7**

**S/P: 1.22**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | 0.0                            | 490               | 18018                                | 75.9                           | 620               | 87426                                | 0.4                            | 750               | 2680                                 | 0.0                            | 880               | 58                                   | 0.0                            |
| 365               | 0                                    | 0.0                            | 495               | 22295                                | 93.2                           | 625               | 83013                                | 0.2                            | 755               | 2287                                 | 0.0                            | 885               | 46                                   | 0.0                            |
| 370               | 0                                    | 0.0                            | 500               | 26478                                | 107.8                          | 630               | 78077                                | 0.1                            | 760               | 1944                                 | 0.0                            | 890               | 45                                   | 0.0                            |
| 375               | 0                                    | 0.0                            | 505               | 30524                                | 118.7                          | 635               | 72080                                | 0.1                            | 765               | 1653                                 | 0.0                            | 895               | 41                                   | 0.0                            |
| 380               | 0                                    | 0.0                            | 510               | 33611                                | 122.2                          | 640               | 66249                                | 0.1                            | 770               | 1413                                 | 0.0                            | 900               | 38                                   | 0.0                            |
| 385               | 0                                    | 0.0                            | 515               | 36490                                | 120.8                          | 645               | 59973                                | 0.0                            | 775               | 1198                                 | 0.0                            | 905               | 33                                   | 0.0                            |
| 390               | 0                                    | 0.0                            | 520               | 38610                                | 113.9                          | 650               | 53972                                | 0.0                            | 780               | 1025                                 | 0.0                            | 910               | 30                                   | 0.0                            |
| 395               | 0                                    | 0.0                            | 525               | 40511                                | 104.1                          | 655               | 48369                                | 0.0                            | 785               | 874                                  | 0.0                            | 915               | 23                                   | 0.0                            |
| 400               | 48                                   | 0.0                            | 530               | 42223                                | 92.4                           | 660               | 42641                                | 0.0                            | 790               | 747                                  | 0.0                            | 920               | 24                                   | 0.0                            |
| 405               | 201                                  | 0.0                            | 535               | 44137                                | 80.5                           | 665               | 37602                                | 0.0                            | 795               | 639                                  | 0.0                            | 925               | 22                                   | 0.0                            |
| 410               | 457                                  | 0.1                            | 540               | 46032                                | 68.2                           | 670               | 32798                                | 0.0                            | 800               | 547                                  | 0.0                            | 930               | 22                                   | 0.0                            |
| 415               | 925                                  | 0.3                            | 545               | 48553                                | 57.1                           | 675               | 28558                                | 0.0                            | 805               | 473                                  | 0.0                            | 935               | 17                                   | 0.0                            |
| 420               | 1816                                 | 1.1                            | 550               | 51408                                | 46.7                           | 680               | 24782                                | 0.0                            | 810               | 401                                  | 0.0                            | 940               | 13                                   | 0.0                            |
| 425               | 3217                                 | 2.5                            | 555               | 54711                                | 37.4                           | 685               | 21386                                | 0.0                            | 815               | 351                                  | 0.0                            | 945               | 6                                    | 0.0                            |
| 430               | 5520                                 | 5.9                            | 560               | 58847                                | 29.4                           | 690               | 18413                                | 0.0                            | 820               | 307                                  | 0.0                            | 950               | 10                                   | 0.0                            |
| 435               | 9225                                 | 12.5                           | 565               | 63386                                | 22.5                           | 695               | 15721                                | 0.0                            | 825               | 261                                  | 0.0                            | 955               | 11                                   | 0.0                            |
| 440               | 15522                                | 26.3                           | 570               | 68196                                | 16.9                           | 700               | 13432                                | 0.0                            | 830               | 228                                  | 0.0                            | 960               | 8                                    | 0.0                            |
| 445               | 27642                                | 55.2                           | 575               | 73613                                | 12.4                           | 705               | 11513                                | 0.0                            | 835               | 193                                  | 0.0                            | 965               | 12                                   | 0.0                            |
| 450               | 36602                                | 85.4                           | 580               | 79207                                | 9.0                            | 710               | 9780                                 | 0.0                            | 840               | 174                                  | 0.0                            | 970               | 3                                    | 0.0                            |
| 455               | 28292                                | 75.1                           | 585               | 84248                                | 6.3                            | 715               | 8356                                 | 0.0                            | 845               | 151                                  | 0.0                            | 975               | 8                                    | 0.0                            |
| 460               | 21166                                | 63.2                           | 590               | 88397                                | 4.4                            | 720               | 7161                                 | 0.0                            | 850               | 123                                  | 0.0                            | 980               | 2                                    | 0.0                            |
| 465               | 19092                                | 63.2                           | 595               | 91428                                | 3.0                            | 725               | 6067                                 | 0.0                            | 855               | 106                                  | 0.0                            | 985               | 13                                   | 0.0                            |
| 470               | 14951                                | 54.2                           | 600               | 93452                                | 2.0                            | 730               | 5164                                 | 0.0                            | 860               | 95                                   | 0.0                            | 990               | 16                                   | 0.0                            |
| 475               | 12606                                | 48.8                           | 605               | 93959                                | 1.3                            | 735               | 4393                                 | 0.0                            | 865               | 82                                   | 0.0                            | 995               | 20                                   | 0.0                            |
| 480               | 13323                                | 54.2                           | 610               | 93079                                | 0.9                            | 740               | 3694                                 | 0.0                            | 870               | 77                                   | 0.0                            | 1000              | 0                                    | 0.0                            |
| 485               | 15164                                | 63.3                           | 615               | 90707                                | 0.5                            | 745               | 3157                                 | 0.0                            | 875               | 65                                   | 0.0                            |                   |                                      |                                |



REPORT NUMBER: SP1-2407-157-9

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 9797**

**M/P: 2.26**


| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 0             | 0.0           | 490    | 18018         | 27.7          | 620    | 87426         | 1.1           | 750    | 2680          | 0.0           | 880    | 58            | 0.0           |
| 365    | 0             | 0.0           | 495    | 22295         | 36.0          | 625    | 83013         | 0.7           | 755    | 2287          | 0.0           | 885    | 46            | 0.0           |
| 370    | 0             | 0.0           | 500    | 26478         | 44.2          | 630    | 78077         | 0.4           | 760    | 1944          | 0.0           | 890    | 45            | 0.0           |
| 375    | 0             | 0.0           | 505    | 30524         | 51.8          | 635    | 72080         | 0.3           | 765    | 1653          | 0.0           | 895    | 41            | 0.0           |
| 380    | 0             | 0.0           | 510    | 33611         | 57.0          | 640    | 66249         | 0.2           | 770    | 1413          | 0.0           | 900    | 38            | 0.0           |
| 385    | 0             | 0.0           | 515    | 36490         | 60.5          | 645    | 59973         | 0.1           | 775    | 1198          | 0.0           | 905    | 33            | 0.0           |
| 390    | 0             | 0.0           | 520    | 38610         | 61.4          | 650    | 53972         | 0.1           | 780    | 1025          | 0.0           | 910    | 30            | 0.0           |
| 395    | 0             | 0.0           | 525    | 40511         | 60.6          | 655    | 48369         | 0.0           | 785    | 874           | 0.0           | 915    | 23            | 0.0           |
| 400    | 48            | 0.0           | 530    | 42223         | 58.2          | 660    | 42641         | 0.0           | 790    | 747           | 0.0           | 920    | 24            | 0.0           |
| 405    | 201           | 0.0           | 535    | 44137         | 55.0          | 665    | 37602         | 0.0           | 795    | 639           | 0.0           | 925    | 22            | 0.0           |
| 410    | 457           | 0.0           | 540    | 46032         | 50.9          | 670    | 32798         | 0.0           | 800    | 547           | 0.0           | 930    | 22            | 0.0           |
| 415    | 925           | 0.1           | 545    | 48553         | 46.6          | 675    | 28558         | 0.0           | 805    | 473           | 0.0           | 935    | 17            | 0.0           |
| 420    | 1816          | 0.3           | 550    | 51408         | 42.0          | 680    | 24782         | 0.0           | 810    | 401           | 0.0           | 940    | 13            | 0.0           |
| 425    | 3217          | 0.8           | 555    | 54711         | 37.4          | 685    | 21386         | 0.0           | 815    | 351           | 0.0           | 945    | 6             | 0.0           |
| 430    | 5520          | 1.9           | 560    | 58847         | 32.9          | 690    | 18413         | 0.0           | 820    | 307           | 0.0           | 950    | 10            | 0.0           |
| 435    | 9225          | 4.1           | 565    | 63386         | 28.4          | 695    | 15721         | 0.0           | 825    | 261           | 0.0           | 955    | 11            | 0.0           |
| 440    | 15522         | 8.7           | 570    | 68196         | 24.1          | 700    | 13432         | 0.0           | 830    | 228           | 0.0           | 960    | 8             | 0.0           |
| 445    | 27642         | 18.5          | 575    | 73613         | 20.0          | 705    | 11513         | 0.0           | 835    | 193           | 0.0           | 965    | 12            | 0.0           |
| 450    | 36602         | 28.3          | 580    | 79207         | 16.3          | 710    | 9780          | 0.0           | 840    | 174           | 0.0           | 970    | 3             | 0.0           |
| 455    | 28292         | 24.7          | 585    | 84248         | 12.9          | 715    | 8356          | 0.0           | 845    | 151           | 0.0           | 975    | 8             | 0.0           |
| 460    | 21166         | 20.4          | 590    | 88397         | 9.8           | 720    | 7161          | 0.0           | 850    | 123           | 0.0           | 980    | 2             | 0.0           |
| 465    | 19092         | 20.1          | 595    | 91428         | 7.3           | 725    | 6067          | 0.0           | 855    | 106           | 0.0           | 985    | 13            | 0.0           |
| 470    | 14951         | 17.2          | 600    | 93452         | 5.3           | 730    | 5164          | 0.0           | 860    | 95            | 0.0           | 990    | 16            | 0.0           |
| 475    | 12606         | 15.7          | 605    | 93959         | 3.7           | 735    | 4393          | 0.0           | 865    | 82            | 0.0           | 995    | 20            | 0.0           |
| 480    | 13323         | 18.0          | 610    | 93079         | 2.5           | 740    | 3694          | 0.0           | 870    | 77            | 0.0           | 1000   | 0             | 0.0           |
| 485    | 15164         | 21.9          | 615    | 90707         | 1.7           | 745    | 3157          | 0.0           | 875    | 65            | 0.0           |        |               |               |

**Summary**

$R_f = 84.7$   
 $R_g = 94.6$   
 CIE  $R_a = 80.9$   
 $R_9 = -1.5$




**Color Vector Graphics**




**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)