

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P318958

Luminaire Tested: **GLEON-SA4B-727-U-T4W**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P318958
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GLEON-SA4B-727-U-T4W
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(4) 70 CRI, 2700K, 800mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV WIDE OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 19142 lumens
Efficiency: N/A
Efficacy: 111.9 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G4


Input Watts (W): 171
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P318958
 CATALOG NUMBER: GLEON-SA4B-727-U-T4W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 3.9 fc
 Type IV - Short - N/A

REPORT NUMBER: P318958
CATALOG NUMBER: GLEON-SA4B-727-U-T4W

Luminous Intensity Polar Plot



— Vertical Plane Through 46-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P318958
 CATALOG NUMBER: GLEON-SA4B-727-U-T4W


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 4387.3 | 0.0 | 4387.3 |
| | % Fixture | 22.9 | 0.0 | 22.9 |
| Street Side | Lumens | 14754.7 | 0.0 | 14754.7 |
| | % Fixture | 77.1 | 0.0 | 77.1 |
| Total | Lumens | 19142.0 | 0.0 | 19142.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 198.8 | 1.0 |
| 10°-20° | 662.4 | 3.5 |
| 20°-30° | 1104.4 | 5.8 |
| 30°-40° | 1567.2 | 8.2 |
| 40°-50° | 2305.3 | 12.0 |
| 50°-60° | 3904.1 | 20.4 |
| 60°-70° | 5541.8 | 29.0 |
| 70°-80° | 3366.7 | 17.6 |
| 80°-90° | 491.3 | 2.6 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 19142.0 | 100.0 |
| 0°-180° | 19142.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P318958
 CATALOG NUMBER: GLEON-SA4B-727-U-T4W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|----------|
| | | | B | U | G |
| FL (0°-30°) | 1044.5 | 5.5 | | | |
| FM (30°-60°) | 5757.1 | 30.1 | | | |
| FH (60°-80°) | 7647.1 | 39.9 | | | G4/12000 |
| FVH (80°-90°) | 306.1 | 1.6 | | | G3/500 |
| BL (0°-30°) | 921.1 | 4.8 | B2/1000 | | |
| BM (30°-60°) | 2019.6 | 10.6 | B2/2500 | | |
| BH (60°-80°) | 1261.3 | 6.6 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 185.3 | 1.0 | | | G2/225 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G4
 Type IV Short





REPORT NUMBER: P318958
 CATALOG NUMBER: GLEON-SA4B-727-U-T4W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 46° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 1950.2 | 1950.2 | 1950.2 | 1950.2 | 1950.2 | 1950.2 | 1950.2 | 1950.2 | 1950.2 | 1950.2 | 1950.2 |
| 2.5° | 2047.8 | 2049.1 | 2051.7 | 2045.2 | 2026.8 | 2021.6 | 2019.6 | 2000.6 | 1988.2 | 1969.8 | 1954.1 |
| 5° | 2211.6 | 2212.9 | 2209.0 | 2190.6 | 2150.0 | 2119.9 | 2117.2 | 2074.0 | 2034.7 | 1992.8 | 1961.3 |
| 7.5° | 2382.6 | 2384.5 | 2372.1 | 2337.4 | 2280.4 | 2228.0 | 2224.7 | 2165.7 | 2106.1 | 2042.6 | 1995.4 |
| 10° | 2533.9 | 2526.0 | 2505.7 | 2457.2 | 2389.8 | 2325.6 | 2322.9 | 2261.4 | 2192.6 | 2115.9 | 2053.0 |
| 12.5° | 2634.8 | 2628.2 | 2602.0 | 2543.0 | 2469.0 | 2410.1 | 2404.8 | 2347.8 | 2281.0 | 2197.2 | 2121.8 |
| 15° | 2690.4 | 2695.0 | 2659.7 | 2592.8 | 2520.8 | 2471.0 | 2466.4 | 2425.8 | 2366.2 | 2281.7 | 2195.2 |
| 17.5° | 2697.6 | 2701.6 | 2667.5 | 2601.4 | 2542.4 | 2508.3 | 2506.4 | 2479.5 | 2436.3 | 2355.0 | 2264.6 |
| 20° | 2655.7 | 2658.3 | 2630.2 | 2575.8 | 2537.2 | 2526.7 | 2526.0 | 2514.2 | 2482.1 | 2410.1 | 2322.3 |
| 22.5° | 2594.8 | 2596.8 | 2576.5 | 2537.2 | 2524.1 | 2540.4 | 2545.0 | 2540.4 | 2517.5 | 2450.0 | 2367.5 |
| 25° | 2579.7 | 2578.4 | 2557.5 | 2517.5 | 2528.6 | 2563.4 | 2569.3 | 2571.2 | 2555.5 | 2496.5 | 2425.1 |
| 27.5° | 2652.4 | 2647.9 | 2607.9 | 2543.7 | 2550.9 | 2592.8 | 2600.7 | 2619.7 | 2609.9 | 2558.1 | 2490.6 |
| 30° | 2862.7 | 2854.9 | 2773.0 | 2643.3 | 2607.9 | 2629.5 | 2639.3 | 2669.5 | 2671.4 | 2628.2 | 2577.8 |
| 32.5° | 3217.8 | 3208.0 | 3061.2 | 2829.3 | 2704.2 | 2666.9 | 2676.0 | 2721.2 | 2745.5 | 2712.1 | 2657.7 |
| 35° | 3666.5 | 3655.4 | 3462.8 | 3145.7 | 2865.4 | 2738.3 | 2744.8 | 2780.8 | 2829.3 | 2782.2 | 2710.1 |
| 37.5° | 4134.3 | 4107.4 | 3922.0 | 3517.8 | 3121.5 | 2890.9 | 2890.9 | 2895.5 | 2918.4 | 2820.2 | 2771.7 |
| 40° | 4599.4 | 4572.5 | 4404.8 | 3955.4 | 3453.0 | 3131.3 | 3116.3 | 3014.7 | 2996.4 | 2911.9 | 2895.5 |
| 42.5° | 5031.7 | 5023.9 | 4924.9 | 4450.0 | 3842.1 | 3367.8 | 3346.8 | 3174.6 | 3178.5 | 3126.1 | 3126.7 |
| 45° | 5491.6 | 5491.6 | 5411.0 | 4949.2 | 4295.4 | 3747.8 | 3726.8 | 3473.3 | 3512.6 | 3488.3 | 3546.6 |
| 47.5° | 5867.0 | 5878.8 | 5867.6 | 5469.3 | 4822.8 | 4230.6 | 4192.6 | 3887.3 | 3997.3 | 4080.5 | 4250.2 |
| 50° | 6250.2 | 6268.5 | 6270.5 | 6039.9 | 5460.2 | 4804.4 | 4761.2 | 4436.9 | 4682.6 | 4921.0 | 5254.5 |
| 52.5° | 6806.4 | 6847.6 | 6683.2 | 6609.2 | 6241.0 | 5485.7 | 5443.1 | 5143.7 | 5553.8 | 5888.6 | 6463.1 |
| 55° | 7321.9 | 7285.9 | 7168.6 | 7214.5 | 7076.9 | 6261.3 | 6229.2 | 5966.5 | 6524.7 | 6959.6 | 7705.8 |
| 57.5° | 7601.0 | 7598.4 | 7716.3 | 7912.8 | 7978.3 | 7217.8 | 7190.9 | 6935.4 | 7619.3 | 7946.2 | 8872.5 |
| 60° | 7928.5 | 7933.1 | 8225.3 | 8671.4 | 8941.3 | 8408.7 | 8396.9 | 8203.0 | 8682.5 | 8867.3 | 9787.7 |
| 62.5° | 7974.4 | 8056.9 | 8560.0 | 9327.8 | 9842.7 | 9800.1 | 9826.3 | 9344.8 | 9633.7 | 9602.3 | 10470.9 |
| 65° | 7447.0 | 7555.8 | 8466.3 | 9526.3 | 10738.8 | 11321.9 | 11346.1 | 10493.2 | 10383.8 | 10230.5 | 10715.3 |
| 67.5° | 6366.1 | 6527.3 | 7516.5 | 9094.6 | 11034.3 | 12446.7 | 12480.7 | 11383.5 | 11006.1 | 10443.4 | 10127.0 |
| 70° | 4632.8 | 4811.6 | 5807.3 | 7767.4 | 10507.6 | 12806.3 | 12845.0 | 11777.2 | 11029.7 | 9837.4 | 8645.2 |
| 72.5° | 2798.5 | 2938.7 | 3759.5 | 5718.3 | 8868.6 | 12151.2 | 12220.0 | 11278.0 | 10070.0 | 8332.7 | 6383.8 |
| 75° | 1228.9 | 1320.7 | 1817.9 | 3295.1 | 6349.1 | 10053.6 | 10139.4 | 9653.4 | 8182.0 | 6055.6 | 3773.3 |
| 77.5° | 523.4 | 549.6 | 745.5 | 1431.4 | 3589.2 | 6869.9 | 6987.8 | 7053.3 | 5551.2 | 3295.1 | 1594.5 |
| 80° | 326.2 | 336.7 | 421.9 | 647.9 | 1679.6 | 3858.5 | 3985.6 | 4150.0 | 2756.6 | 1211.3 | 556.8 |
| 82.5° | 198.5 | 210.3 | 280.4 | 391.7 | 874.5 | 1749.1 | 1810.0 | 1926.0 | 1069.8 | 523.4 | 288.2 |
| 85° | 119.2 | 127.7 | 171.6 | 247.6 | 497.9 | 687.8 | 687.2 | 759.9 | 503.8 | 336.7 | 152.0 |
| 87.5° | 57.0 | 63.5 | 91.7 | 128.4 | 250.9 | 258.1 | 241.7 | 273.8 | 305.9 | 220.8 | 76.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P318958
 CATALOG NUMBER: GLEON-SA4B-727-U-T4W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1950.2 | 1950.2 | 1950.2 | 1950.2 | 1950.2 | 1950.2 | 1950.2 | 1950.2 | 1950.2 | 1950.2 | 1950.2 |
| 2.5° | 1948.9 | 1946.3 | 1937.7 | 1931.2 | 1929.9 | 1926.0 | 1922.7 | 1924.6 | 1927.3 | 1927.9 | 1927.9 |
| 5° | 1948.2 | 1941.0 | 1929.9 | 1925.3 | 1931.2 | 1939.1 | 1948.9 | 1962.0 | 1969.8 | 1975.7 | 1979.7 |
| 7.5° | 1979.7 | 1965.9 | 1953.5 | 1950.9 | 1962.6 | 1983.6 | 2005.9 | 2033.4 | 2052.4 | 2065.5 | 2068.1 |
| 10° | 2032.1 | 2015.0 | 2002.6 | 2005.2 | 2026.2 | 2056.3 | 2087.8 | 2123.1 | 2152.0 | 2169.6 | 2171.0 |
| 12.5° | 2092.3 | 2076.0 | 2064.2 | 2075.3 | 2110.0 | 2146.7 | 2179.5 | 2210.3 | 2236.5 | 2254.2 | 2254.2 |
| 15° | 2161.8 | 2150.0 | 2136.2 | 2161.8 | 2209.0 | 2241.7 | 2255.5 | 2270.5 | 2284.9 | 2298.0 | 2295.4 |
| 17.5° | 2228.6 | 2217.5 | 2210.3 | 2240.4 | 2289.5 | 2304.6 | 2295.4 | 2284.3 | 2284.3 | 2291.5 | 2292.8 |
| 20° | 2286.3 | 2276.4 | 2281.0 | 2310.5 | 2336.0 | 2320.3 | 2286.3 | 2250.9 | 2236.5 | 2240.4 | 2244.3 |
| 22.5° | 2336.7 | 2332.1 | 2345.9 | 2359.6 | 2341.3 | 2286.3 | 2223.4 | 2175.5 | 2157.9 | 2156.5 | 2157.9 |
| 25° | 2395.7 | 2395.0 | 2412.0 | 2387.1 | 2305.9 | 2204.4 | 2119.9 | 2073.4 | 2063.5 | 2071.4 | 2084.5 |
| 27.5° | 2469.0 | 2476.2 | 2484.7 | 2393.7 | 2233.8 | 2080.6 | 1994.7 | 1962.6 | 1972.5 | 1991.5 | 2003.9 |
| 30° | 2562.7 | 2582.4 | 2564.0 | 2377.3 | 2130.3 | 1939.1 | 1857.2 | 1848.0 | 1874.9 | 1901.7 | 1914.8 |
| 32.5° | 2653.8 | 2684.5 | 2640.0 | 2334.7 | 1996.7 | 1789.0 | 1725.5 | 1722.9 | 1755.6 | 1781.8 | 1800.2 |
| 35° | 2727.1 | 2788.1 | 2697.0 | 2250.2 | 1842.1 | 1650.8 | 1604.3 | 1586.6 | 1598.4 | 1629.2 | 1650.2 |
| 37.5° | 2822.8 | 2924.3 | 2736.3 | 2121.2 | 1674.4 | 1536.8 | 1482.5 | 1441.8 | 1431.4 | 1443.8 | 1454.3 |
| 40° | 2997.7 | 3132.0 | 2754.6 | 1941.0 | 1510.6 | 1422.8 | 1367.8 | 1308.2 | 1266.9 | 1236.8 | 1237.5 |
| 42.5° | 3283.3 | 3402.5 | 2742.9 | 1722.2 | 1359.3 | 1311.5 | 1249.3 | 1180.5 | 1113.6 | 1045.5 | 1040.3 |
| 45° | 3747.1 | 3804.7 | 2707.5 | 1490.3 | 1226.3 | 1194.9 | 1136.6 | 1067.8 | 978.7 | 901.4 | 894.2 |
| 47.5° | 4489.3 | 4361.6 | 2652.4 | 1287.9 | 1109.1 | 1096.0 | 1042.2 | 963.0 | 868.6 | 806.4 | 801.2 |
| 50° | 5501.4 | 5165.4 | 2625.6 | 1126.8 | 1005.6 | 1009.5 | 965.6 | 881.7 | 792.7 | 746.8 | 741.6 |
| 52.5° | 6712.0 | 6101.5 | 2677.3 | 1002.3 | 922.4 | 936.1 | 903.4 | 824.8 | 750.1 | 714.0 | 708.8 |
| 55° | 7967.8 | 7071.0 | 2733.0 | 911.9 | 843.8 | 870.6 | 859.5 | 794.6 | 727.1 | 693.7 | 689.2 |
| 57.5° | 9042.8 | 7794.9 | 2621.7 | 838.5 | 773.7 | 815.6 | 825.4 | 775.6 | 715.4 | 685.2 | 680.0 |
| 60° | 9719.5 | 8086.4 | 2329.5 | 769.7 | 718.0 | 771.7 | 805.8 | 770.4 | 719.9 | 717.3 | 713.4 |
| 62.5° | 10040.5 | 8060.9 | 1891.2 | 715.4 | 683.3 | 752.7 | 820.2 | 799.9 | 772.3 | 795.9 | 797.9 |
| 65° | 9896.4 | 7675.7 | 1408.4 | 679.3 | 658.4 | 759.9 | 863.4 | 855.5 | 787.4 | 811.0 | 814.3 |
| 67.5° | 8947.8 | 6756.6 | 1042.9 | 647.9 | 630.8 | 780.2 | 942.0 | 873.9 | 757.9 | 775.0 | 764.5 |
| 70° | 7232.2 | 5356.6 | 804.4 | 612.5 | 602.7 | 777.6 | 977.4 | 862.8 | 725.8 | 729.8 | 701.6 |
| 72.5° | 4987.2 | 3652.8 | 654.4 | 579.8 | 562.1 | 708.8 | 952.5 | 835.2 | 699.0 | 668.8 | 631.5 |
| 75° | 2712.1 | 1960.7 | 556.2 | 545.7 | 490.7 | 622.3 | 906.6 | 815.6 | 674.7 | 634.8 | 613.8 |
| 77.5° | 1067.1 | 813.6 | 482.8 | 499.2 | 429.1 | 549.6 | 855.5 | 778.2 | 641.3 | 588.9 | 578.4 |
| 80° | 435.6 | 415.3 | 400.3 | 431.7 | 368.8 | 480.8 | 794.0 | 734.4 | 601.4 | 546.3 | 525.4 |
| 82.5° | 247.0 | 258.1 | 311.2 | 340.6 | 299.4 | 442.8 | 764.5 | 699.0 | 553.5 | 489.4 | 464.5 |
| 85° | 126.4 | 151.3 | 216.8 | 244.3 | 220.1 | 376.7 | 704.2 | 611.9 | 444.1 | 374.7 | 376.7 |
| 87.5° | 60.9 | 84.5 | 136.9 | 153.3 | 142.8 | 272.5 | 526.0 | 443.5 | 345.9 | 273.8 | 265.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3 S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 CIE $R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)