

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P321510

Luminaire Tested: **GLEON-SA6A-727-U-T3R-HSS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P321510
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-11)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GLEON-SA6A-727-U-T3R-HSS
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(6) 70 CRI, 2700K, 615mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III
ROADWAY OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 17928 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B2 - U0 - G3


Input Watts (W): 193
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P321510
 CATALOG NUMBER: GLEON-SA6A-727-U-T3R-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5.7 fc
 Type III - Medium - N/A

REPORT NUMBER: P321510
CATALOG NUMBER: GLEON-SA6A-727-U-T3R-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 55-Deg Lateral - - - Horizontal Cone Through 71-Deg Vertical

REPORT NUMBER: P321510
 CATALOG NUMBER: GLEON-SA6A-727-U-T3R-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 1419.4 | 0.0 | 1419.4 |
| | % Fixture | 7.9 | 0.0 | 7.9 |
| Street Side | Lumens | 16508.6 | 0.0 | 16508.6 |
| | % Fixture | 92.1 | 0.0 | 92.1 |
| Total | Lumens | 17928.0 | 0.0 | 17928.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 294.8 | 1.6 |
| 10°-20° | 665.5 | 3.7 |
| 20°-30° | 1069.5 | 6.0 |
| 30°-40° | 1817.2 | 10.1 |
| 40°-50° | 2820.5 | 15.7 |
| 50°-60° | 3792.1 | 21.2 |
| 60°-70° | 4638.9 | 25.9 |
| 70°-80° | 2712.3 | 15.1 |
| 80°-90° | 117.2 | 0.7 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 17928.0 | 100.0 |
| 0°-180° | 17928.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P321510
 CATALOG NUMBER: GLEON-SA6A-727-U-T3R-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1391.0 | 7.8 | | | |
| FM (30°-60°) | 7841.2 | 43.7 | | | |
| FH (60°-80°) | 7161.0 | 39.9 | | | G3/7500 |
| FVH (80°-90°) | 115.4 | 0.6 | | | G2/225 |
| BL (0°-30°) | 638.9 | 3.6 | B2/1000 | | |
| BM (30°-60°) | 588.5 | 3.3 | B1/1000 | | |
| BH (60°-80°) | 190.2 | 1.1 | B1/500 | | G1/500 |
| BVH (80°-90°) | 1.8 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G3
 Type III Medium





REPORT NUMBER: P321510

CATALOG NUMBER: GLEON-SA6A-727-U-T3R-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 54° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|---------|---------|---------|---------|---------|---------|--------|
| 0° | 3457.5 | 3457.5 | 3457.5 | 3457.5 | 3457.5 | 3457.5 | 3457.5 | 3457.5 | 3457.5 | 3457.5 | 3457.5 |
| 2.5° | 3356.0 | 3360.1 | 3374.6 | 3381.0 | 3396.3 | 3422.1 | 3434.9 | 3435.7 | 3456.7 | 3464.7 | 3471.2 |
| 5° | 3118.6 | 3142.7 | 3166.9 | 3192.6 | 3239.3 | 3301.3 | 3362.5 | 3368.1 | 3435.7 | 3485.7 | 3512.2 |
| 7.5° | 2914.1 | 2935.8 | 2964.8 | 3005.9 | 3071.9 | 3169.3 | 3271.5 | 3283.6 | 3411.6 | 3525.1 | 3584.7 |
| 10° | 2704.0 | 2721.7 | 2763.6 | 2823.9 | 2914.9 | 3045.3 | 3183.0 | 3203.1 | 3389.9 | 3578.2 | 3682.9 |
| 12.5° | 2479.4 | 2489.9 | 2540.6 | 2627.5 | 2761.2 | 2927.0 | 3108.1 | 3134.7 | 3376.2 | 3639.4 | 3798.8 |
| 15° | 2308.7 | 2313.6 | 2361.9 | 2452.0 | 2605.0 | 2820.7 | 3050.1 | 3082.3 | 3379.4 | 3712.7 | 3925.2 |
| 17.5° | 2265.3 | 2267.7 | 2293.4 | 2355.4 | 2490.7 | 2725.7 | 3004.3 | 3043.7 | 3389.1 | 3784.3 | 4052.4 |
| 20° | 2441.6 | 2424.7 | 2398.1 | 2388.4 | 2446.4 | 2668.6 | 2976.9 | 3021.2 | 3401.9 | 3847.9 | 4166.7 |
| 22.5° | 2925.4 | 2875.5 | 2765.2 | 2617.9 | 2528.5 | 2672.6 | 2984.1 | 3028.4 | 3443.0 | 3926.0 | 4298.7 |
| 25° | 3643.4 | 3574.2 | 3386.6 | 3096.8 | 2818.3 | 2788.5 | 3044.5 | 3089.6 | 3522.7 | 4019.4 | 4425.1 |
| 27.5° | 4460.5 | 4392.1 | 4162.7 | 3748.9 | 3273.9 | 3017.9 | 3183.0 | 3224.8 | 3641.0 | 4102.3 | 4521.7 |
| 30° | 5243.0 | 5223.7 | 4953.2 | 4483.1 | 3847.1 | 3389.9 | 3361.7 | 3397.1 | 3728.8 | 4152.2 | 4598.2 |
| 32.5° | 5906.3 | 5875.7 | 5658.4 | 5201.1 | 4503.2 | 3836.6 | 3571.8 | 3582.3 | 3794.8 | 4216.6 | 4698.0 |
| 35° | 6521.3 | 6483.5 | 6292.7 | 5860.4 | 5176.2 | 4382.4 | 3895.4 | 3880.1 | 3938.9 | 4346.2 | 4842.9 |
| 37.5° | 7058.2 | 7092.9 | 6881.1 | 6469.8 | 5779.9 | 4950.0 | 4331.7 | 4285.8 | 4164.3 | 4557.1 | 5053.0 |
| 40° | 7507.4 | 7507.4 | 7397.2 | 7054.2 | 6432.0 | 5536.8 | 4825.2 | 4764.8 | 4503.2 | 4882.3 | 5319.4 |
| 42.5° | 7669.2 | 7703.9 | 7744.9 | 7550.9 | 7015.6 | 6147.0 | 5375.0 | 5312.2 | 4980.5 | 5343.6 | 5655.9 |
| 45° | 7678.9 | 7733.6 | 7943.7 | 7942.9 | 7542.9 | 6753.2 | 5994.8 | 5965.1 | 5592.3 | 5936.1 | 6072.9 |
| 47.5° | 7542.9 | 7611.3 | 7957.4 | 8153.9 | 7960.7 | 7317.5 | 6672.7 | 6635.6 | 6311.2 | 6662.2 | 6509.2 |
| 50° | 7332.8 | 7408.4 | 7810.9 | 8236.8 | 8244.8 | 7808.5 | 7386.7 | 7331.1 | 7102.5 | 7492.1 | 6960.0 |
| 52.5° | 6956.8 | 7103.3 | 7679.7 | 8256.1 | 8431.6 | 8232.7 | 8066.1 | 8042.0 | 7988.0 | 8291.5 | 7319.1 |
| 55° | 6152.6 | 6315.2 | 7350.5 | 8262.5 | 8604.7 | 8608.7 | 8702.9 | 8709.3 | 8818.0 | 9038.6 | 7586.3 |
| 57.5° | 5772.7 | 5864.4 | 6775.7 | 8293.1 | 8861.5 | 9035.3 | 9351.7 | 9401.6 | 9569.9 | 9747.8 | 7891.4 |
| 60° | 5533.6 | 5642.3 | 6492.3 | 8251.3 | 9264.8 | 9594.8 | 9953.0 | 9969.9 | 10150.3 | 10479.5 | 8304.4 |
| 62.5° | 5342.8 | 5449.9 | 6313.6 | 8090.3 | 9718.0 | 10267.8 | 10540.7 | 10542.3 | 10677.5 | 11351.3 | 8773.7 |
| 65° | 4871.9 | 4962.0 | 5952.2 | 7909.1 | 10017.4 | 10933.5 | 11223.3 | 11212.9 | 11323.1 | 12270.6 | 9318.7 |
| 67.5° | 4190.8 | 4260.1 | 5214.0 | 7222.5 | 9904.7 | 11538.9 | 12253.7 | 12219.1 | 12085.5 | 13065.2 | 9532.8 |
| 70° | 3240.1 | 3265.1 | 4109.5 | 6019.0 | 8848.6 | 11771.5 | 13249.5 | 13231.8 | 12553.2 | 12922.7 | 8747.9 |
| 71° | 2678.2 | 2760.3 | 3621.7 | 5312.2 | 8141.0 | 11556.6 | 13346.1 | 13356.6 | 12435.7 | 12534.7 | 8207.8 |
| 72.5° | 1555.3 | 1625.3 | 2625.1 | 4079.7 | 6911.7 | 10659.8 | 12845.4 | 12921.1 | 11886.6 | 11401.2 | 7010.8 |
| 75° | 333.3 | 356.6 | 973.2 | 1974.7 | 3802.0 | 7471.2 | 10139.0 | 10408.7 | 9688.2 | 7756.2 | 4225.5 |
| 77.5° | 231.8 | 250.4 | 417.0 | 896.0 | 1256.6 | 3691.7 | 6298.3 | 6602.6 | 5788.0 | 2914.9 | 1352.4 |
| 80° | 183.5 | 204.5 | 325.2 | 442.8 | 339.7 | 1190.6 | 2950.3 | 3136.3 | 1930.4 | 650.4 | 227.8 |
| 82.5° | 102.2 | 121.6 | 253.6 | 239.1 | 130.4 | 226.2 | 825.9 | 933.8 | 386.4 | 131.2 | 53.9 |
| 85° | 29.8 | 36.2 | 163.4 | 173.9 | 55.5 | 43.5 | 140.9 | 174.7 | 73.3 | 34.6 | 24.2 |
| 87.5° | 0.0 | 0.0 | 78.9 | 66.8 | 16.1 | 6.4 | 12.9 | 14.5 | 14.5 | 14.5 | 16.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P321510

CATALOG NUMBER: GLEON-SA6A-727-U-T3R-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3457.5 | 3457.5 | 3457.5 | 3457.5 | 3457.5 | 3457.5 | 3457.5 | 3457.5 | 3457.5 | 3457.5 | 3457.5 |
| 2.5° | 3471.2 | 3476.8 | 3456.7 | 3430.1 | 3401.9 | 3367.3 | 3331.1 | 3302.9 | 3302.1 | 3288.4 | 3274.7 |
| 5° | 3513.8 | 3510.6 | 3455.1 | 3370.5 | 3270.7 | 3166.9 | 3067.9 | 2956.0 | 2918.9 | 2873.0 | 2857.8 |
| 7.5° | 3592.7 | 3570.2 | 3452.6 | 3267.5 | 3048.5 | 2831.2 | 2606.6 | 2380.4 | 2283.8 | 2196.8 | 2181.6 |
| 10° | 3691.7 | 3649.1 | 3437.4 | 3112.9 | 2711.2 | 2310.4 | 1971.4 | 1663.9 | 1528.7 | 1424.9 | 1420.0 |
| 12.5° | 3794.8 | 3729.6 | 3394.7 | 2879.5 | 2269.3 | 1705.8 | 1315.4 | 1012.7 | 900.0 | 827.5 | 834.0 |
| 15° | 3902.6 | 3805.2 | 3302.9 | 2564.7 | 1766.2 | 1157.6 | 808.2 | 630.3 | 585.2 | 566.7 | 571.6 |
| 17.5° | 4012.9 | 3857.6 | 3174.9 | 2185.6 | 1269.5 | 747.0 | 559.5 | 509.6 | 509.6 | 513.6 | 515.2 |
| 20° | 4108.7 | 3885.7 | 2986.6 | 1760.5 | 860.5 | 544.2 | 489.4 | 482.2 | 486.2 | 492.7 | 493.5 |
| 22.5° | 4203.7 | 3887.3 | 2741.0 | 1329.9 | 602.1 | 476.6 | 466.1 | 462.9 | 465.3 | 472.5 | 473.3 |
| 25° | 4281.0 | 3868.0 | 2433.5 | 945.9 | 480.6 | 449.2 | 444.4 | 442.8 | 444.4 | 453.2 | 453.2 |
| 27.5° | 4312.4 | 3798.0 | 2058.4 | 664.9 | 430.7 | 418.6 | 417.0 | 418.6 | 421.0 | 427.5 | 428.3 |
| 30° | 4315.6 | 3675.6 | 1649.4 | 481.4 | 390.4 | 377.5 | 380.8 | 386.4 | 384.0 | 382.4 | 384.0 |
| 32.5° | 4323.7 | 3534.0 | 1251.0 | 396.1 | 356.6 | 336.5 | 332.5 | 332.5 | 322.8 | 317.2 | 314.0 |
| 35° | 4350.2 | 3367.3 | 907.2 | 355.8 | 322.0 | 298.7 | 283.4 | 265.7 | 247.1 | 237.5 | 235.1 |
| 37.5° | 4392.1 | 3192.6 | 649.6 | 329.2 | 291.4 | 264.8 | 235.9 | 204.5 | 177.9 | 170.7 | 170.7 |
| 40° | 4468.6 | 3012.3 | 480.6 | 308.3 | 267.3 | 234.3 | 190.8 | 149.7 | 125.6 | 121.6 | 121.6 |
| 42.5° | 4589.3 | 2822.3 | 383.2 | 289.8 | 246.3 | 202.9 | 145.7 | 108.7 | 91.0 | 88.6 | 87.7 |
| 45° | 4714.9 | 2613.0 | 334.9 | 272.1 | 223.8 | 166.6 | 107.9 | 80.5 | 70.0 | 67.6 | 67.6 |
| 47.5° | 4840.5 | 2390.0 | 311.5 | 255.2 | 202.1 | 129.6 | 80.5 | 63.6 | 58.8 | 58.8 | 59.6 |
| 50° | 4946.7 | 2157.4 | 294.6 | 236.7 | 173.9 | 98.2 | 63.6 | 53.9 | 52.3 | 55.5 | 56.4 |
| 52.5° | 4973.3 | 1928.8 | 273.7 | 213.3 | 139.3 | 74.9 | 52.3 | 47.5 | 47.5 | 47.5 | 47.5 |
| 55° | 4957.2 | 1751.7 | 246.3 | 184.3 | 103.0 | 59.6 | 45.1 | 41.9 | 41.1 | 41.1 | 41.1 |
| 57.5° | 5011.9 | 1647.0 | 197.2 | 143.3 | 74.1 | 48.3 | 39.4 | 37.0 | 35.4 | 34.6 | 34.6 |
| 60° | 5122.2 | 1578.6 | 140.9 | 103.0 | 55.5 | 40.3 | 33.8 | 31.4 | 29.0 | 27.4 | 27.4 |
| 62.5° | 5268.7 | 1519.0 | 104.7 | 76.5 | 42.7 | 32.2 | 28.2 | 25.8 | 22.5 | 20.9 | 20.9 |
| 65° | 5381.4 | 1412.8 | 79.7 | 57.2 | 32.2 | 25.8 | 21.7 | 20.9 | 16.1 | 14.5 | 13.7 |
| 67.5° | 5209.2 | 1179.3 | 64.4 | 41.9 | 24.2 | 20.1 | 16.9 | 16.1 | 9.7 | 8.1 | 8.1 |
| 70° | 4467.8 | 821.1 | 51.5 | 30.6 | 17.7 | 16.1 | 13.7 | 10.5 | 7.2 | 6.4 | 6.4 |
| 71° | 4051.6 | 685.9 | 46.7 | 25.8 | 15.3 | 15.3 | 12.9 | 8.9 | 6.4 | 5.6 | 5.6 |
| 72.5° | 3365.7 | 487.0 | 39.4 | 20.1 | 13.7 | 16.1 | 13.7 | 8.1 | 6.4 | 5.6 | 4.8 |
| 75° | 1953.7 | 203.7 | 27.4 | 13.7 | 10.5 | 19.3 | 17.7 | 7.2 | 4.8 | 4.0 | 4.0 |
| 77.5° | 587.7 | 74.9 | 15.3 | 8.9 | 8.1 | 16.9 | 20.1 | 6.4 | 2.4 | 0.8 | 0.8 |
| 80° | 107.1 | 32.2 | 9.7 | 5.6 | 5.6 | 10.5 | 15.3 | 3.2 | 0.0 | 0.0 | 0.0 |
| 82.5° | 37.8 | 16.1 | 5.6 | 3.2 | 2.4 | 4.8 | 7.2 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 21.7 | 11.3 | 3.2 | 1.6 | 0.0 | 0.8 | 1.6 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 14.5 | 3.2 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2
 Rf: 69.9
 Rg: 98.3

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 CIE $R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)