

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P322473

Luminaire Tested: **GLEON-SA9A-727-U-T4FT-HSS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P322473  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: GLEON-SA9A-727-U-T4FT-HSS  
Description: GALLEON AREA AND ROADWAY LUMINAIRE  
(9) 70 CRI, 2700K, 615mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV  
FORWARD THROW OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 24744 lumens  
Efficiency: N/A  
Efficacy: 85.3 lumens/watt  
Luminous Opening: Rectangular (W 2.5' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B2 - U0 - G4


Input Watts (W): 290  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P322473  
 CATALOG NUMBER: GLEON-SA9A-727-U-T4FT-HSS

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 6.8 fc  
 Type IV - Short - N/A

REPORT NUMBER: P322473  
CATALOG NUMBER: GLEON-SA9A-727-U-T4FT-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 31-Deg Lateral      - - - Horizontal Cone Through 73-Deg Vertical

REPORT NUMBER: P322473  
 CATALOG NUMBER: GLEON-SA9A-727-U-T4FT-HSS


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 2255.5   | 0.0    | 2255.5  |
|                    | % Fixture | 9.1      | 0.0    | 9.1     |
| <b>Street Side</b> | Lumens    | 22488.5  | 0.0    | 22488.5 |
|                    | % Fixture | 90.9     | 0.0    | 90.9    |
| <b>Total</b>       | Lumens    | 24744.0  | 0.0    | 24744.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 353.0   | 1.4       |
| 10°-20°   | 766.4   | 3.1       |
| 20°-30°   | 1148.3  | 4.6       |
| 30°-40°   | 1827.0  | 7.4       |
| 40°-50°   | 3262.5  | 13.2      |
| 50°-60°   | 5062.5  | 20.5      |
| 60°-70°   | 6729.9  | 27.2      |
| 70°-80°   | 5062.3  | 20.5      |
| 80°-90°   | 531.9   | 2.1       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 24744.0 | 100.0     |
| 0°-180°   | 24744.0 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P322473  
 CATALOG NUMBER: GLEON-SA9A-727-U-T4FT-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |          |
|----------------|---------|-----------|-------------------------|------|----------|
|                |         |           | B                       | U    | G        |
| FL (0°-30°)    | 1447.6  | 5.9       |                         |      |          |
| FM (30°-60°)   | 8991.1  | 36.3      |                         |      |          |
| FH (60°-80°)   | 11522.4 | 46.6      |                         |      | G4/12000 |
| FVH (80°-90°)  | 527.5   | 2.1       |                         |      | G4/750   |
| BL (0°-30°)    | 820.2   | 3.3       | B2/1000                 |      |          |
| BM (30°-60°)   | 1161.0  | 4.7       | B2/2500                 |      |          |
| BH (60°-80°)   | 269.9   | 1.1       | B1/500                  |      | G1/500   |
| BVH (80°-90°)  | 4.5     | 0.0       |                         |      | G0/10    |
| UL (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |          |
| UH (100°-180°) | 0.0     | 0.0       |                         | U0/0 |          |

**BUG Rating: B2-U0-G4**  
 Type IV Short





REPORT NUMBER: P322473

CATALOG NUMBER: GLEON-SA9A-727-U-T4FT-HSS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 15°     | 25°     | 31°     | 35°     | 45°     | 55°     | 65°     | 75°     | 85°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 4257.3  | 4257.3  | 4257.3  | 4257.3  | 4257.3  | 4257.3  | 4257.3  | 4257.3  | 4257.3  | 4257.3  | 4257.3  |
| 2.5°  | 4034.5  | 4051.4  | 4069.6  | 4073.2  | 4103.5  | 4104.7  | 4148.3  | 4181.0  | 4213.7  | 4245.1  | 4256.0  |
| 5°    | 3620.4  | 3648.2  | 3680.9  | 3713.6  | 3777.8  | 3803.2  | 3909.7  | 4018.7  | 4122.9  | 4222.1  | 4270.6  |
| 7.5°  | 3178.4  | 3209.9  | 3255.9  | 3337.0  | 3408.5  | 3458.1  | 3626.4  | 3820.1  | 4013.9  | 4196.7  | 4302.1  |
| 10°   | 2775.2  | 2804.3  | 2852.7  | 2938.7  | 3048.9  | 3116.7  | 3343.1  | 3611.9  | 3896.4  | 4173.7  | 4349.3  |
| 12.5° | 2518.5  | 2534.3  | 2560.9  | 2652.9  | 2752.2  | 2828.5  | 3094.9  | 3427.8  | 3799.6  | 4172.5  | 4425.6  |
| 15°   | 2471.3  | 2476.1  | 2454.3  | 2495.5  | 2573.0  | 2646.9  | 2916.9  | 3278.9  | 3725.7  | 4191.9  | 4524.8  |
| 17.5° | 2546.4  | 2543.9  | 2471.3  | 2466.4  | 2528.2  | 2588.7  | 2829.7  | 3176.0  | 3673.6  | 4236.7  | 4653.2  |
| 20°   | 2660.2  | 2651.7  | 2525.8  | 2502.8  | 2568.2  | 2625.1  | 2823.6  | 3137.2  | 3654.3  | 4311.7  | 4809.4  |
| 22.5° | 2811.5  | 2797.0  | 2599.6  | 2575.4  | 2645.6  | 2705.0  | 2898.7  | 3174.8  | 3671.2  | 4412.2  | 4991.0  |
| 25°   | 2999.2  | 2977.4  | 2726.8  | 2700.1  | 2771.6  | 2830.9  | 3033.1  | 3282.5  | 3722.1  | 4534.5  | 5221.1  |
| 27.5° | 3211.1  | 3179.6  | 2930.2  | 2861.2  | 2942.3  | 3004.1  | 3212.3  | 3447.2  | 3802.0  | 4664.1  | 5503.2  |
| 30°   | 3410.9  | 3369.7  | 3144.5  | 3030.7  | 3130.0  | 3199.0  | 3406.0  | 3643.4  | 3930.3  | 4863.9  | 5889.4  |
| 32.5° | 3611.9  | 3565.9  | 3335.8  | 3200.2  | 3289.8  | 3364.9  | 3605.8  | 3913.4  | 4171.3  | 5169.0  | 6402.8  |
| 35°   | 4074.4  | 4026.0  | 3743.9  | 3519.9  | 3518.7  | 3561.0  | 3885.5  | 4282.7  | 4489.7  | 5594.0  | 7015.5  |
| 37.5° | 4853.0  | 4825.1  | 4556.3  | 4131.3  | 4017.5  | 3970.3  | 4266.9  | 4723.4  | 4947.4  | 6178.8  | 7706.9  |
| 40°   | 5705.4  | 5681.2  | 5379.7  | 4994.6  | 4821.5  | 4705.3  | 4814.2  | 5337.3  | 5594.0  | 6893.2  | 8412.8  |
| 42.5° | 6668.0  | 6553.0  | 6015.4  | 5900.3  | 5745.4  | 5657.0  | 5558.9  | 6094.1  | 6388.3  | 7670.6  | 9112.7  |
| 45°   | 7542.2  | 7348.5  | 6651.1  | 6476.7  | 6441.6  | 6463.4  | 6517.9  | 7111.2  | 7281.9  | 8594.4  | 9810.1  |
| 47.5° | 8062.9  | 7910.3  | 7375.1  | 7208.0  | 7198.3  | 7342.4  | 7754.1  | 8260.2  | 8171.8  | 9399.6  | 10424.0 |
| 50°   | 8558.1  | 8420.1  | 7975.7  | 8016.9  | 8061.7  | 8257.8  | 9157.5  | 9442.0  | 8984.3  | 10129.8 | 10987.0 |
| 52.5° | 8958.9  | 8748.2  | 8515.7  | 8747.0  | 8967.4  | 9283.4  | 10605.6 | 10502.7 | 9560.7  | 10710.9 | 11468.9 |
| 55°   | 9190.2  | 9094.5  | 9207.1  | 9439.6  | 9853.7  | 10367.1 | 11972.6 | 11385.4 | 9982.0  | 11241.3 | 11789.8 |
| 57.5° | 10037.7 | 9850.1  | 10074.1 | 10275.0 | 10815.1 | 11533.1 | 13143.5 | 12042.9 | 10285.9 | 11569.4 | 11863.6 |
| 60°   | 11063.3 | 10911.9 | 11043.9 | 11378.1 | 12107.0 | 12951.0 | 14238.1 | 12579.2 | 10444.6 | 11780.1 | 11672.3 |
| 62.5° | 12695.5 | 12495.7 | 12413.4 | 12787.5 | 13753.7 | 14675.2 | 15068.7 | 12951.0 | 10409.5 | 11686.9 | 11016.1 |
| 65°   | 14882.2 | 14675.2 | 14307.1 | 14646.1 | 15875.1 | 16525.3 | 15997.4 | 13029.7 | 10167.3 | 10932.5 | 9357.2  |
| 67.5° | 17122.3 | 16972.1 | 16657.3 | 17228.8 | 18337.9 | 18547.4 | 16979.4 | 12838.4 | 9387.5  | 8864.4  | 6611.1  |
| 70°   | 18601.9 | 18537.7 | 18742.3 | 20006.4 | 20995.7 | 20935.1 | 17880.2 | 11810.4 | 7317.0  | 5451.1  | 3270.4  |
| 72.5° | 17535.1 | 17842.7 | 19353.8 | 21645.9 | 22854.3 | 22360.3 | 17417.7 | 9069.1  | 4182.2  | 2097.1  | 945.7   |
| 73°   | 16651.2 | 17044.8 | 19078.9 | 21707.6 | 23000.8 | 22459.6 | 17029.0 | 8324.4  | 3564.7  | 1655.2  | 716.8   |
| 75°   | 11583.9 | 12067.1 | 15795.2 | 20217.1 | 22315.5 | 21398.9 | 14194.5 | 5095.1  | 1651.6  | 733.8   | 289.4   |
| 77.5° | 5624.3  | 5981.5  | 8697.3  | 14607.4 | 17354.7 | 16719.1 | 8836.6  | 1898.6  | 745.9   | 458.9   | 133.2   |
| 80°   | 2099.6  | 2334.5  | 3775.3  | 7434.5  | 10029.3 | 10292.0 | 3886.7  | 718.0   | 496.4   | 369.3   | 67.8    |
| 82.5° | 549.7   | 612.7   | 1392.4  | 3315.2  | 5139.9  | 5379.7  | 1225.4  | 362.0   | 363.2   | 303.9   | 41.2    |
| 85°   | 175.6   | 201.0   | 434.7   | 1488.1  | 2421.6  | 2126.2  | 319.7   | 175.6   | 264.0   | 226.4   | 23.0    |
| 87.5° | 21.8    | 27.8    | 138.0   | 349.9   | 534.0   | 296.7   | 49.6    | 52.1    | 112.6   | 125.9   | 13.3    |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P322473

CATALOG NUMBER: GLEON-SA9A-727-U-T4FT-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 4257.3 | 4257.3 | 4257.3 | 4257.3 | 4257.3 | 4257.3 | 4257.3 | 4257.3 | 4257.3 | 4257.3 | 4257.3 |
| 2.5°  | 4266.9 | 4260.9 | 4262.1 | 4230.6 | 4210.0 | 4168.9 | 4126.5 | 4107.1 | 4086.5 | 4078.1 | 4086.5 |
| 5°    | 4288.7 | 4277.8 | 4246.4 | 4149.5 | 4046.6 | 3913.4 | 3788.7 | 3694.2 | 3575.6 | 3542.9 | 3576.8 |
| 7.5°  | 4322.6 | 4300.8 | 4208.8 | 4011.5 | 3782.6 | 3528.3 | 3242.6 | 3034.3 | 2863.6 | 2753.4 | 2793.4 |
| 10°   | 4372.3 | 4331.1 | 4145.9 | 3810.5 | 3401.2 | 2950.8 | 2545.2 | 2229.1 | 2005.1 | 1913.1 | 1909.5 |
| 12.5° | 4455.8 | 4378.3 | 4068.4 | 3548.9 | 2935.0 | 2334.5 | 1802.9 | 1460.3 | 1278.6 | 1161.2 | 1158.8 |
| 15°   | 4547.9 | 4434.0 | 3970.3 | 3235.3 | 2392.6 | 1672.1 | 1161.2 | 900.9  | 783.4  | 745.9  | 741.0  |
| 17.5° | 4660.5 | 4498.2 | 3843.2 | 2849.1 | 1824.7 | 1107.9 | 758.0  | 682.9  | 678.1  | 674.4  | 674.4  |
| 20°   | 4802.1 | 4574.5 | 3679.7 | 2407.1 | 1294.4 | 739.8  | 644.2  | 649.0  | 651.4  | 646.6  | 647.8  |
| 22.5° | 4966.8 | 4652.0 | 3484.8 | 1932.5 | 875.4  | 618.7  | 616.3  | 622.4  | 624.8  | 622.4  | 623.6  |
| 25°   | 5158.1 | 4741.6 | 3247.4 | 1434.8 | 632.0  | 587.2  | 593.3  | 601.8  | 607.8  | 607.8  | 607.8  |
| 27.5° | 5395.4 | 4850.6 | 2961.7 | 1001.4 | 546.1  | 554.6  | 571.5  | 587.2  | 595.7  | 598.1  | 598.1  |
| 30°   | 5704.2 | 4986.2 | 2619.0 | 686.5  | 496.4  | 511.0  | 542.4  | 572.7  | 588.5  | 590.9  | 592.1  |
| 32.5° | 6094.1 | 5138.7 | 2221.9 | 507.3  | 454.1  | 465.0  | 498.9  | 549.7  | 580.0  | 584.8  | 584.8  |
| 35°   | 6540.9 | 5315.5 | 1794.4 | 442.0  | 423.8  | 427.4  | 454.1  | 512.2  | 565.5  | 578.8  | 580.0  |
| 37.5° | 7030.0 | 5489.9 | 1364.6 | 412.9  | 398.4  | 398.4  | 417.7  | 467.4  | 530.3  | 571.5  | 576.4  |
| 40°   | 7486.5 | 5595.2 | 956.6  | 389.9  | 375.4  | 375.4  | 392.3  | 428.6  | 488.0  | 549.7  | 563.0  |
| 42.5° | 7907.9 | 5631.5 | 666.0  | 368.1  | 353.6  | 357.2  | 371.7  | 400.8  | 445.6  | 507.3  | 519.4  |
| 45°   | 8341.4 | 5625.5 | 485.5  | 342.7  | 331.8  | 342.7  | 353.6  | 375.4  | 408.0  | 443.2  | 445.6  |
| 47.5° | 8668.3 | 5574.6 | 385.0  | 318.4  | 311.2  | 325.7  | 335.4  | 349.9  | 368.1  | 365.7  | 365.7  |
| 50°   | 8974.6 | 5451.1 | 310.0  | 285.8  | 290.6  | 307.5  | 312.4  | 317.2  | 318.4  | 295.4  | 293.0  |
| 52.5° | 9207.1 | 5258.6 | 248.2  | 250.6  | 270.0  | 287.0  | 282.1  | 274.9  | 262.7  | 234.9  | 230.1  |
| 55°   | 9284.6 | 4888.1 | 194.9  | 207.1  | 239.7  | 261.5  | 243.4  | 227.6  | 204.6  | 181.6  | 176.8  |
| 57.5° | 9144.1 | 4409.8 | 158.6  | 161.0  | 202.2  | 220.4  | 199.8  | 181.6  | 156.2  | 136.8  | 133.2  |
| 60°   | 8846.3 | 3878.3 | 130.8  | 121.1  | 156.2  | 171.9  | 158.6  | 140.5  | 117.4  | 102.9  | 101.7  |
| 62.5° | 8255.4 | 3311.6 | 107.8  | 94.4   | 118.7  | 132.0  | 123.5  | 110.2  | 90.8   | 81.1   | 79.9   |
| 65°   | 7013.1 | 2649.3 | 87.2   | 76.3   | 92.0   | 102.9  | 95.7   | 86.0   | 71.4   | 64.2   | 63.0   |
| 67.5° | 4895.4 | 1790.8 | 71.4   | 63.0   | 72.6   | 81.1   | 75.1   | 70.2   | 56.9   | 55.7   | 56.9   |
| 70°   | 2361.1 | 863.3  | 59.3   | 50.9   | 56.9   | 63.0   | 60.5   | 56.9   | 54.5   | 63.0   | 72.6   |
| 72.5° | 676.9  | 289.4  | 47.2   | 42.4   | 46.0   | 49.6   | 52.1   | 50.9   | 59.3   | 76.3   | 88.4   |
| 73°   | 520.7  | 233.7  | 44.8   | 40.0   | 43.6   | 48.4   | 50.9   | 49.6   | 60.5   | 77.5   | 88.4   |
| 75°   | 222.8  | 112.6  | 33.9   | 32.7   | 36.3   | 42.4   | 44.8   | 44.8   | 60.5   | 78.7   | 84.8   |
| 77.5° | 100.5  | 60.5   | 21.8   | 25.4   | 31.5   | 33.9   | 37.5   | 37.5   | 48.4   | 60.5   | 60.5   |
| 80°   | 56.9   | 32.7   | 17.0   | 19.4   | 23.0   | 23.0   | 23.0   | 20.6   | 21.8   | 24.2   | 26.6   |
| 82.5° | 36.3   | 21.8   | 13.3   | 15.7   | 14.5   | 12.1   | 9.7    | 9.7    | 8.5    | 9.7    | 12.1   |
| 85°   | 20.6   | 12.1   | 12.1   | 9.7    | 6.1    | 4.8    | 6.1    | 4.8    | 1.2    | 0.0    | 1.2    |
| 87.5° | 12.1   | 7.3    | 3.6    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

**Test Information**

Test Method: LM-79-2008  
 Report Number: SP1-1908-441-1-R4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/28/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGRAW-EDISON  
 Catalog Number: **SA1C-727-U-5WQ**  
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

\*\*\*THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.\*\*\*TESTED IN  
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

**Spectral Parameters**

CCT (K): 2741  
 CIE u': 0.2605  
 CIE v': 0.5272  
 Duv: 0.0005  
 CIE x: 0.4573  
 CIE y: 0.4113  
 CIE z: 0.1313  
 Peak Wavelength (nm): 602  
 Dominant Wavelength (nm): 583  
 Purity: 61.2

|           |      |      |       |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 |      |       |
| R1:       | 69.2 | R9:  | -16.1 |
| R2:       | 79.4 | R10: | 51.4  |
| R3:       | 87.8 | R11: | 63.1  |
| R4:       | 69.4 | R12: | 42.0  |
| R5:       | 66.4 | R13: | 70.2  |
| R6:       | 69.8 | R14: | 92.4  |
| R7:       | 79.8 |      |       |
| R8:       | 50.1 |      |       |

Rf: 69.9  
 Rg: 98.3



**Test Conditions**

Stabilization Time: 56M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.3./42%  
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/28/2019        | 12/28/2019           |
| Power Meter                    | IN0071                | 12/5/2018        | 12/5/2019            |
| AC Power Source                | IN0063                | 12/5/2018        | 12/5/2019            |
| DC Power Source                | IN0208                | 12/5/2018        | 12/5/2019            |
| Sphere Thermometer             | IN0085                | 12/5/2018        | 12/5/2019            |
| Room Thermometer               | IN0046                | 12/5/2018        | 12/5/2019            |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

**Photopic Flux vs. Wavelength**



**Photopic Lumens: 6211.7**

| $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360            | 2044                              | 0.0                         | 490            | 7179                              | 1.0                         | 620            | 118034                            | 30.7                        | 750            | 8362                              | 0.0                         | 880            | 3128                              | 0.0                         |
| 365            | 2016                              | 0.0                         | 495            | 10476                             | 1.9                         | 625            | 111884                            | 24.7                        | 755            | 7635                              | 0.0                         | 885            | 3110                              | 0.0                         |
| 370            | 2020                              | 0.0                         | 500            | 15549                             | 3.4                         | 630            | 106119                            | 19.2                        | 760            | 6582                              | 0.0                         | 890            | 2632                              | 0.0                         |
| 375            | 2137                              | 0.0                         | 505            | 22477                             | 6.3                         | 635            | 99706                             | 15.0                        | 765            | 5777                              | 0.0                         | 895            | 2709                              | 0.0                         |
| 380            | 2046                              | 0.0                         | 510            | 30417                             | 10.4                        | 640            | 92142                             | 11.0                        | 770            | 5474                              | 0.0                         | 900            | 2016                              | 0.0                         |
| 385            | 1925                              | 0.0                         | 515            | 39274                             | 16.3                        | 645            | 84987                             | 8.2                         | 775            | 4977                              | 0.0                         | 905            | 1748                              | 0.0                         |
| 390            | 1893                              | 0.0                         | 520            | 47282                             | 22.9                        | 650            | 78016                             | 5.7                         | 780            | 4723                              | 0.0                         | 910            | 2046                              | 0.0                         |
| 395            | 1695                              | 0.0                         | 525            | 55413                             | 29.7                        | 655            | 71541                             | 4.1                         | 785            | 4219                              | 0.0                         | 915            | 1844                              | 0.0                         |
| 400            | 1633                              | 0.0                         | 530            | 62377                             | 36.7                        | 660            | 64863                             | 2.7                         | 790            | 3969                              | 0.0                         | 920            | 2734                              | 0.0                         |
| 405            | 2065                              | 0.0                         | 535            | 68520                             | 42.5                        | 665            | 58485                             | 1.9                         | 795            | 4122                              | 0.0                         | 925            | 2307                              | 0.0                         |
| 410            | 3449                              | 0.0                         | 540            | 73435                             | 47.8                        | 670            | 51641                             | 1.1                         | 800            | 2864                              | 0.0                         | 930            | 2039                              | 0.0                         |
| 415            | 7117                              | 0.0                         | 545            | 78677                             | 52.4                        | 675            | 46030                             | 0.8                         | 805            | 3151                              | 0.0                         | 935            | 1784                              | 0.0                         |
| 420            | 13992                             | 0.0                         | 550            | 83331                             | 56.6                        | 680            | 40590                             | 0.5                         | 810            | 3022                              | 0.0                         | 940            | 2464                              | 0.0                         |
| 425            | 25176                             | 0.1                         | 555            | 89120                             | 60.9                        | 685            | 35691                             | 0.3                         | 815            | 3471                              | 0.0                         | 945            | 2794                              | 0.0                         |
| 430            | 38151                             | 0.3                         | 560            | 94613                             | 64.3                        | 690            | 31631                             | 0.2                         | 820            | 2749                              | 0.0                         | 950            | 3090                              | 0.0                         |
| 435            | 49673                             | 0.6                         | 565            | 99818                             | 66.4                        | 695            | 27437                             | 0.1                         | 825            | 2729                              | 0.0                         | 955            | 1866                              | 0.0                         |
| 440            | 57273                             | 0.9                         | 570            | 106526                            | 69.3                        | 700            | 24589                             | 0.1                         | 830            | 2282                              | 0.0                         | 960            | 3110                              | 0.0                         |
| 445            | 54802                             | 1.1                         | 575            | 111610                            | 69.4                        | 705            | 21832                             | 0.0                         | 835            | 3140                              | 0.0                         | 965            | 3880                              | 0.0                         |
| 450            | 39184                             | 1.0                         | 580            | 117163                            | 69.6                        | 710            | 19500                             | 0.0                         | 840            | 2365                              | 0.0                         | 970            | 3243                              | 0.0                         |
| 455            | 22506                             | 0.8                         | 585            | 122201                            | 67.9                        | 715            | 17870                             | 0.0                         | 845            | 3024                              | 0.0                         | 975            | 2014                              | 0.0                         |
| 460            | 13692                             | 0.6                         | 590            | 125662                            | 65.0                        | 720            | 15924                             | 0.0                         | 850            | 2510                              | 0.0                         | 980            | 1688                              | 0.0                         |
| 465            | 9446                              | 0.5                         | 595            | 127415                            | 60.4                        | 725            | 14268                             | 0.0                         | 855            | 2739                              | 0.0                         | 985            | 2827                              | 0.0                         |
| 470            | 6698                              | 0.4                         | 600            | 129155                            | 55.7                        | 730            | 12438                             | 0.0                         | 860            | 3515                              | 0.0                         | 990            | 4172                              | 0.0                         |
| 475            | 5328                              | 0.4                         | 605            | 128057                            | 49.6                        | 735            | 11255                             | 0.0                         | 865            | 3600                              | 0.0                         | 995            | 3177                              | 0.0                         |
| 480            | 5081                              | 0.5                         | 610            | 126031                            | 43.3                        | 740            | 9951                              | 0.0                         | 870            | 3609                              | 0.0                         | 1000           | 3241                              | 0.0                         |
| 485            | 5579                              | 0.7                         | 615            | 123059                            | 37.1                        | 745            | 8870                              | 0.0                         | 875            | 3208                              | 0.0                         |                |                                   |                             |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2044          | 0.0           | 490    | 7179          | 6.0           | 620    | 118034        | 0.1           | 750    | 8362          | 0.0           | 880    | 3128          | 0.0           |
| 365    | 2016          | 0.0           | 495    | 10476         | 8.6           | 625    | 111884        | 0.1           | 755    | 7635          | 0.0           | 885    | 3110          | 0.0           |
| 370    | 2020          | 0.0           | 500    | 15549         | 12.5          | 630    | 106119        | 0.0           | 760    | 6582          | 0.0           | 890    | 2632          | 0.0           |
| 375    | 2137          | 0.0           | 505    | 22477         | 17.3          | 635    | 99706         | 0.0           | 765    | 5777          | 0.0           | 895    | 2709          | 0.0           |
| 380    | 2046          | 0.0           | 510    | 30417         | 21.8          | 640    | 92142         | 0.0           | 770    | 5474          | 0.0           | 900    | 2016          | 0.0           |
| 385    | 1925          | 0.0           | 515    | 39274         | 25.7          | 645    | 84987         | 0.0           | 775    | 4977          | 0.0           | 905    | 1748          | 0.0           |
| 390    | 1893          | 0.0           | 520    | 47282         | 27.5          | 650    | 78016         | 0.0           | 780    | 4723          | 0.0           | 910    | 2046          | 0.0           |
| 395    | 1695          | 0.0           | 525    | 55413         | 28.1          | 655    | 71541         | 0.0           | 785    | 4219          | 0.0           | 915    | 1844          | 0.0           |
| 400    | 1633          | 0.0           | 530    | 62377         | 27.0          | 660    | 64863         | 0.0           | 790    | 3969          | 0.0           | 920    | 2734          | 0.0           |
| 405    | 2065          | 0.0           | 535    | 68520         | 24.7          | 665    | 58485         | 0.0           | 795    | 4122          | 0.0           | 925    | 2307          | 0.0           |
| 410    | 3449          | 0.1           | 540    | 73435         | 21.5          | 670    | 51641         | 0.0           | 800    | 2864          | 0.0           | 930    | 2039          | 0.0           |
| 415    | 7117          | 0.5           | 545    | 78677         | 18.3          | 675    | 46030         | 0.0           | 805    | 3151          | 0.0           | 935    | 1784          | 0.0           |
| 420    | 13992         | 1.6           | 550    | 83331         | 15.0          | 680    | 40590         | 0.0           | 810    | 3022          | 0.0           | 940    | 2464          | 0.0           |
| 425    | 25176         | 3.9           | 555    | 89120         | 12.0          | 685    | 35691         | 0.0           | 815    | 3471          | 0.0           | 945    | 2794          | 0.0           |
| 430    | 38151         | 8.1           | 560    | 94613         | 9.3           | 690    | 31631         | 0.0           | 820    | 2749          | 0.0           | 950    | 3090          | 0.0           |
| 435    | 49673         | 13.3          | 565    | 99818         | 7.0           | 695    | 27437         | 0.0           | 825    | 2729          | 0.0           | 955    | 1866          | 0.0           |
| 440    | 57273         | 19.1          | 570    | 106526        | 5.2           | 700    | 24589         | 0.0           | 830    | 2282          | 0.0           | 960    | 3110          | 0.0           |
| 445    | 54802         | 21.6          | 575    | 111610        | 3.7           | 705    | 21832         | 0.0           | 835    | 3140          | 0.0           | 965    | 3880          | 0.0           |
| 450    | 39184         | 18.1          | 580    | 117163        | 2.6           | 710    | 19500         | 0.0           | 840    | 2365          | 0.0           | 970    | 3243          | 0.0           |
| 455    | 22506         | 11.8          | 585    | 122201        | 1.8           | 715    | 17870         | 0.0           | 845    | 3024          | 0.0           | 975    | 2014          | 0.0           |
| 460    | 13692         | 8.1           | 590    | 125662        | 1.2           | 720    | 15924         | 0.0           | 850    | 2510          | 0.0           | 980    | 1688          | 0.0           |
| 465    | 9446          | 6.2           | 595    | 127415        | 0.8           | 725    | 14268         | 0.0           | 855    | 2739          | 0.0           | 985    | 2827          | 0.0           |
| 470    | 6698          | 4.8           | 600    | 129155        | 0.5           | 730    | 12438         | 0.0           | 860    | 3515          | 0.0           | 990    | 4172          | 0.0           |
| 475    | 5328          | 4.1           | 605    | 128057        | 0.4           | 735    | 11255         | 0.0           | 865    | 3600          | 0.0           | 995    | 3177          | 0.0           |
| 480    | 5081          | 4.1           | 610    | 126031        | 0.2           | 740    | 9951          | 0.0           | 870    | 3609          | 0.0           | 1000   | 3241          | 0.0           |
| 485    | 5579          | 4.6           | 615    | 123059        | 0.1           | 745    | 8870          | 0.0           | 875    | 3208          | 0.0           |        |               |               |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2044          | 0.0           | 490    | 7179          | 11.1          | 620    | 118034        | 1.5           | 750    | 8362          | 0.0           | 880    | 3128          | 0.0           |
| 365    | 2016          | 0.0           | 495    | 10476         | 16.9          | 625    | 111884        | 0.9           | 755    | 7635          | 0.0           | 885    | 3110          | 0.0           |
| 370    | 2020          | 0.0           | 500    | 15549         | 26.0          | 630    | 106119        | 0.6           | 760    | 6582          | 0.0           | 890    | 2632          | 0.0           |
| 375    | 2137          | 0.0           | 505    | 22477         | 38.2          | 635    | 99706         | 0.4           | 765    | 5777          | 0.0           | 895    | 2709          | 0.0           |
| 380    | 2046          | 0.0           | 510    | 30417         | 51.6          | 640    | 92142         | 0.2           | 770    | 5474          | 0.0           | 900    | 2016          | 0.0           |
| 385    | 1925          | 0.0           | 515    | 39274         | 65.1          | 645    | 84987         | 0.1           | 775    | 4977          | 0.0           | 905    | 1748          | 0.0           |
| 390    | 1893          | 0.0           | 520    | 47282         | 75.2          | 650    | 78016         | 0.1           | 780    | 4723          | 0.0           | 910    | 2046          | 0.0           |
| 395    | 1695          | 0.0           | 525    | 55413         | 82.9          | 655    | 71541         | 0.1           | 785    | 4219          | 0.0           | 915    | 1844          | 0.0           |
| 400    | 1633          | 0.0           | 530    | 62377         | 86.0          | 660    | 64863         | 0.0           | 790    | 3969          | 0.0           | 920    | 2734          | 0.0           |
| 405    | 2065          | 0.1           | 535    | 68520         | 85.4          | 665    | 58485         | 0.0           | 795    | 4122          | 0.0           | 925    | 2307          | 0.0           |
| 410    | 3449          | 0.2           | 540    | 73435         | 81.1          | 670    | 51641         | 0.0           | 800    | 2864          | 0.0           | 930    | 2039          | 0.0           |
| 415    | 7117          | 0.7           | 545    | 78677         | 75.4          | 675    | 46030         | 0.0           | 805    | 3151          | 0.0           | 935    | 1784          | 0.0           |
| 420    | 13992         | 2.3           | 550    | 83331         | 68.1          | 680    | 40590         | 0.0           | 810    | 3022          | 0.0           | 940    | 2464          | 0.0           |
| 425    | 25176         | 6.2           | 555    | 89120         | 60.9          | 685    | 35691         | 0.0           | 815    | 3471          | 0.0           | 945    | 2794          | 0.0           |
| 430    | 38151         | 13.0          | 560    | 94613         | 52.9          | 690    | 31631         | 0.0           | 820    | 2749          | 0.0           | 950    | 3090          | 0.0           |
| 435    | 49673         | 22.2          | 565    | 99818         | 44.8          | 695    | 27437         | 0.0           | 825    | 2729          | 0.0           | 955    | 1866          | 0.0           |
| 440    | 57273         | 32.0          | 570    | 106526        | 37.6          | 700    | 24589         | 0.0           | 830    | 2282          | 0.0           | 960    | 3110          | 0.0           |
| 445    | 54802         | 36.7          | 575    | 111610        | 30.4          | 705    | 21832         | 0.0           | 835    | 3140          | 0.0           | 965    | 3880          | 0.0           |
| 450    | 39184         | 30.4          | 580    | 117163        | 24.1          | 710    | 19500         | 0.0           | 840    | 2365          | 0.0           | 970    | 3243          | 0.0           |
| 455    | 22506         | 19.7          | 585    | 122201        | 18.7          | 715    | 17870         | 0.0           | 845    | 3024          | 0.0           | 975    | 2014          | 0.0           |
| 460    | 13692         | 13.2          | 590    | 125662        | 14.0          | 720    | 15924         | 0.0           | 850    | 2510          | 0.0           | 980    | 1688          | 0.0           |
| 465    | 9446          | 10.0          | 595    | 127415        | 10.2          | 725    | 14268         | 0.0           | 855    | 2739          | 0.0           | 985    | 2827          | 0.0           |
| 470    | 6698          | 7.7           | 600    | 129155        | 7.3           | 730    | 12438         | 0.0           | 860    | 3515          | 0.0           | 990    | 4172          | 0.0           |
| 475    | 5328          | 6.7           | 605    | 128057        | 5.0           | 735    | 11255         | 0.0           | 865    | 3600          | 0.0           | 995    | 3177          | 0.0           |
| 480    | 5081          | 6.9           | 610    | 126031        | 3.4           | 740    | 9951          | 0.0           | 870    | 3609          | 0.0           | 1000   | 3241          | 0.0           |
| 485    | 5579          | 8.1           | 615    | 123059        | 2.3           | 745    | 8870          | 0.0           | 875    | 3208          | 0.0           |        |               |               |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

**Summary**

$R_f = 69.9$   
 $R_g = 98.3$   
 $CIE R_a = 71.5$   
 $R_9 = -16.1$



**Color Vector Graphics**





REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**


|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 |            |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)