

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P318953

Luminaire Tested: **GLEON-SA9A-727-U-T4W**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P318953
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GLEON-SA9A-727-U-T4W
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(9) 70 CRI, 2700K, 615mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV WIDE OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 34598 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Luminous Opening: Rectangular (W 2.5' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G5


Input Watts (W): 290
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P318953
 CATALOG NUMBER: GLEON-SA9A-727-U-T4W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 7 fc
 Type IV - Short - N/A

REPORT NUMBER: P318953
CATALOG NUMBER: GLEON-SA9A-727-U-T4W

Luminous Intensity Polar Plot



— Vertical Plane Through 46-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P318953
 CATALOG NUMBER: GLEON-SA9A-727-U-T4W

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 7929.8 | 0.0 | 7929.8 |
| | % Fixture | 22.9 | 0.0 | 22.9 |
| Street Side | Lumens | 26668.2 | 0.0 | 26668.2 |
| | % Fixture | 77.1 | 0.0 | 77.1 |
| Total | Lumens | 34598.0 | 0.0 | 34598.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 359.3 | 1.0 |
| 10°-20° | 1197.2 | 3.5 |
| 20°-30° | 1996.2 | 5.8 |
| 30°-40° | 2832.7 | 8.2 |
| 40°-50° | 4166.7 | 12.0 |
| 50°-60° | 7056.4 | 20.4 |
| 60°-70° | 10016.4 | 29.0 |
| 70°-80° | 6085.0 | 17.6 |
| 80°-90° | 888.0 | 2.6 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 34598.0 | 100.0 |
| 0°-180° | 34598.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P318953
 CATALOG NUMBER: GLEON-SA9A-727-U-T4W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1887.8 | 5.5 | | | |
| FM (30°-60°) | 10405.5 | 30.1 | | | |
| FH (60°-80°) | 13821.7 | 39.9 | | | G5 |
| FVH (80°-90°) | 553.2 | 1.6 | | | G4/750 |
| BL (0°-30°) | 1664.9 | 4.8 | B3/2500 | | |
| BM (30°-60°) | 3650.3 | 10.6 | B3/5000 | | |
| BH (60°-80°) | 2279.7 | 6.6 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 334.9 | 1.0 | | | G3/500 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G5
 Type IV Short





REPORT NUMBER: P318953
 CATALOG NUMBER: GLEON-SA9A-727-U-T4W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 46° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 3524.9 | 3524.9 | 3524.9 | 3524.9 | 3524.9 | 3524.9 | 3524.9 | 3524.9 | 3524.9 | 3524.9 | 3524.9 |
| 2.5° | 3701.3 | 3703.6 | 3708.4 | 3696.5 | 3663.4 | 3653.9 | 3650.4 | 3616.0 | 3593.5 | 3560.4 | 3532.0 |
| 5° | 3997.3 | 3999.7 | 3992.6 | 3959.4 | 3886.0 | 3831.5 | 3826.8 | 3748.6 | 3677.6 | 3601.8 | 3545.0 |
| 7.5° | 4306.3 | 4309.9 | 4287.4 | 4224.6 | 4121.6 | 4026.9 | 4021.0 | 3914.4 | 3806.7 | 3691.8 | 3606.6 |
| 10° | 4579.8 | 4565.6 | 4528.9 | 4441.3 | 4319.3 | 4203.3 | 4198.6 | 4087.3 | 3963.0 | 3824.4 | 3710.8 |
| 12.5° | 4762.2 | 4750.3 | 4703.0 | 4596.4 | 4462.6 | 4356.0 | 4346.6 | 4243.6 | 4122.8 | 3971.2 | 3835.1 |
| 15° | 4862.8 | 4871.1 | 4807.2 | 4686.4 | 4556.1 | 4466.2 | 4457.9 | 4384.5 | 4276.7 | 4124.0 | 3967.7 |
| 17.5° | 4875.8 | 4882.9 | 4821.4 | 4701.8 | 4595.2 | 4533.7 | 4530.1 | 4481.6 | 4403.4 | 4256.6 | 4093.2 |
| 20° | 4800.1 | 4804.8 | 4753.9 | 4655.6 | 4585.8 | 4566.8 | 4565.6 | 4544.3 | 4486.3 | 4356.0 | 4197.4 |
| 22.5° | 4689.9 | 4693.5 | 4656.8 | 4585.8 | 4562.1 | 4591.7 | 4600.0 | 4591.7 | 4550.2 | 4428.3 | 4279.1 |
| 25° | 4662.7 | 4660.3 | 4622.5 | 4550.2 | 4570.4 | 4633.1 | 4643.8 | 4647.3 | 4618.9 | 4512.3 | 4383.3 |
| 27.5° | 4794.1 | 4785.9 | 4713.6 | 4597.6 | 4610.6 | 4686.4 | 4700.6 | 4734.9 | 4717.2 | 4623.6 | 4501.7 |
| 30° | 5174.2 | 5160.0 | 5012.0 | 4777.6 | 4713.6 | 4752.7 | 4770.5 | 4824.9 | 4828.5 | 4750.3 | 4659.2 |
| 32.5° | 5816.0 | 5798.2 | 5533.0 | 5113.8 | 4887.7 | 4820.2 | 4836.8 | 4918.5 | 4962.3 | 4901.9 | 4803.6 |
| 35° | 6627.0 | 6606.9 | 6258.8 | 5685.7 | 5178.9 | 4949.2 | 4961.1 | 5026.2 | 5113.8 | 5028.6 | 4898.3 |
| 37.5° | 7472.4 | 7423.9 | 7088.8 | 6358.2 | 5641.9 | 5225.1 | 5225.1 | 5233.4 | 5274.9 | 5097.3 | 5009.6 |
| 40° | 8313.1 | 8264.5 | 7961.4 | 7149.2 | 6241.0 | 5659.7 | 5632.4 | 5448.9 | 5415.8 | 5263.0 | 5233.4 |
| 42.5° | 9094.5 | 9080.3 | 8901.5 | 8043.1 | 6944.3 | 6087.1 | 6049.2 | 5737.8 | 5744.9 | 5650.2 | 5651.4 |
| 45° | 9925.7 | 9925.7 | 9780.1 | 8945.4 | 7763.7 | 6773.8 | 6735.9 | 6277.7 | 6348.8 | 6305.0 | 6410.3 |
| 47.5° | 10604.2 | 10625.5 | 10605.4 | 9885.5 | 8716.8 | 7646.5 | 7577.8 | 7026.0 | 7225.0 | 7375.3 | 7682.0 |
| 50° | 11296.8 | 11330.0 | 11333.5 | 10916.8 | 9868.9 | 8683.7 | 8605.5 | 8019.4 | 8463.5 | 8894.4 | 9497.1 |
| 52.5° | 12302.1 | 12376.7 | 12079.5 | 11945.7 | 11280.3 | 9915.1 | 9838.1 | 9297.0 | 10038.2 | 10643.3 | 11681.6 |
| 55° | 13233.9 | 13168.8 | 12956.8 | 13039.7 | 12791.1 | 11317.0 | 11258.9 | 10784.2 | 11792.9 | 12579.1 | 13927.8 |
| 57.5° | 13738.3 | 13733.6 | 13946.7 | 14301.9 | 14420.3 | 13045.6 | 12997.1 | 12535.3 | 13771.5 | 14362.3 | 16036.5 |
| 60° | 14330.3 | 14338.6 | 14866.7 | 15673.0 | 16160.8 | 15198.2 | 15176.9 | 14826.4 | 15693.1 | 16027.0 | 17690.6 |
| 62.5° | 14413.2 | 14562.4 | 15471.7 | 16859.4 | 17790.1 | 17713.1 | 17760.5 | 16890.2 | 17412.4 | 17355.5 | 18925.5 |
| 65° | 13460.1 | 13656.6 | 15302.4 | 17218.2 | 19409.8 | 20463.6 | 20507.4 | 18965.8 | 18768.1 | 18491.0 | 19367.2 |
| 67.5° | 11506.4 | 11797.7 | 13585.6 | 16437.9 | 19943.8 | 22496.6 | 22558.2 | 20574.9 | 19892.9 | 18875.8 | 18303.9 |
| 70° | 8373.5 | 8696.7 | 10496.4 | 14039.1 | 18991.9 | 23146.6 | 23216.5 | 21286.5 | 19935.5 | 17780.6 | 15625.7 |
| 72.5° | 5058.2 | 5311.6 | 6795.2 | 10335.4 | 16029.4 | 21962.6 | 22086.9 | 20384.3 | 18200.9 | 15060.9 | 11538.4 |
| 75° | 2221.2 | 2387.0 | 3285.7 | 5955.7 | 11475.6 | 18171.3 | 18326.4 | 17447.9 | 14788.5 | 10945.2 | 6820.0 |
| 77.5° | 946.0 | 993.4 | 1347.4 | 2587.1 | 6487.3 | 12416.9 | 12630.1 | 12748.5 | 10033.5 | 5955.7 | 2881.9 |
| 80° | 589.6 | 608.6 | 762.5 | 1171.0 | 3035.9 | 6973.9 | 7203.6 | 7500.8 | 4982.4 | 2189.3 | 1006.4 |
| 82.5° | 358.8 | 380.1 | 506.8 | 708.1 | 1580.7 | 3161.4 | 3271.5 | 3481.0 | 1933.5 | 946.0 | 521.0 |
| 85° | 215.5 | 230.9 | 310.2 | 447.6 | 899.9 | 1243.2 | 1242.0 | 1373.5 | 910.5 | 608.6 | 274.7 |
| 87.5° | 103.0 | 114.9 | 165.8 | 232.1 | 453.5 | 466.5 | 436.9 | 494.9 | 552.9 | 399.0 | 138.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P318953
 CATALOG NUMBER: GLEON-SA9A-727-U-T4W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3524.9 | 3524.9 | 3524.9 | 3524.9 | 3524.9 | 3524.9 | 3524.9 | 3524.9 | 3524.9 | 3524.9 | 3524.9 |
| 2.5° | 3522.5 | 3517.8 | 3502.4 | 3490.5 | 3488.2 | 3481.0 | 3475.1 | 3478.7 | 3483.4 | 3484.6 | 3484.6 |
| 5° | 3521.3 | 3508.3 | 3488.2 | 3479.9 | 3490.5 | 3504.7 | 3522.5 | 3546.2 | 3560.4 | 3571.0 | 3578.1 |
| 7.5° | 3578.1 | 3553.3 | 3530.8 | 3526.0 | 3547.4 | 3585.2 | 3625.5 | 3675.2 | 3709.6 | 3733.2 | 3738.0 |
| 10° | 3672.9 | 3642.1 | 3619.6 | 3624.3 | 3662.2 | 3716.7 | 3773.5 | 3837.4 | 3889.5 | 3921.5 | 3923.9 |
| 12.5° | 3781.8 | 3752.2 | 3730.9 | 3751.0 | 3813.8 | 3880.1 | 3939.3 | 3994.9 | 4042.3 | 4074.2 | 4074.2 |
| 15° | 3907.3 | 3886.0 | 3861.1 | 3907.3 | 3992.6 | 4051.8 | 4076.6 | 4103.8 | 4129.9 | 4153.6 | 4148.8 |
| 17.5° | 4028.1 | 4007.9 | 3994.9 | 4049.4 | 4138.2 | 4165.4 | 4148.8 | 4128.7 | 4128.7 | 4141.7 | 4144.1 |
| 20° | 4132.3 | 4114.5 | 4122.8 | 4176.1 | 4222.3 | 4193.8 | 4132.3 | 4068.3 | 4042.3 | 4049.4 | 4056.5 |
| 22.5° | 4223.4 | 4215.1 | 4240.0 | 4264.9 | 4231.7 | 4132.3 | 4018.6 | 3932.2 | 3900.2 | 3897.8 | 3900.2 |
| 25° | 4330.0 | 4328.8 | 4359.6 | 4314.6 | 4167.8 | 3984.3 | 3831.5 | 3747.5 | 3729.7 | 3743.9 | 3767.6 |
| 27.5° | 4462.6 | 4475.6 | 4491.0 | 4326.4 | 4037.5 | 3760.5 | 3605.4 | 3547.4 | 3565.1 | 3599.5 | 3621.9 |
| 30° | 4631.9 | 4667.4 | 4634.3 | 4296.8 | 3850.5 | 3504.7 | 3356.7 | 3340.2 | 3388.7 | 3437.2 | 3460.9 |
| 32.5° | 4796.5 | 4852.2 | 4771.6 | 4219.9 | 3608.9 | 3233.6 | 3118.7 | 3114.0 | 3173.2 | 3220.6 | 3253.7 |
| 35° | 4929.1 | 5039.2 | 4874.7 | 4067.1 | 3329.5 | 2983.8 | 2899.7 | 2867.7 | 2889.0 | 2944.7 | 2982.6 |
| 37.5° | 5102.0 | 5285.5 | 4945.7 | 3833.9 | 3026.4 | 2777.7 | 2679.5 | 2606.1 | 2587.1 | 2609.6 | 2628.5 |
| 40° | 5418.1 | 5660.9 | 4978.8 | 3508.3 | 2730.4 | 2571.7 | 2472.3 | 2364.5 | 2289.9 | 2235.4 | 2236.6 |
| 42.5° | 5934.4 | 6149.9 | 4957.5 | 3112.8 | 2456.9 | 2370.4 | 2257.9 | 2133.6 | 2012.9 | 1889.7 | 1880.2 |
| 45° | 6772.7 | 6876.8 | 4893.6 | 2693.7 | 2216.5 | 2159.7 | 2054.3 | 1930.0 | 1768.9 | 1629.2 | 1616.2 |
| 47.5° | 8114.2 | 7883.3 | 4794.1 | 2327.8 | 2004.6 | 1980.9 | 1883.8 | 1740.5 | 1570.0 | 1457.5 | 1448.1 |
| 50° | 9943.5 | 9336.1 | 4745.6 | 2036.5 | 1817.5 | 1824.6 | 1745.3 | 1593.7 | 1432.7 | 1349.8 | 1340.3 |
| 52.5° | 12131.6 | 11028.1 | 4839.1 | 1811.6 | 1667.1 | 1692.0 | 1632.8 | 1490.7 | 1355.7 | 1290.6 | 1281.1 |
| 55° | 14401.4 | 12780.4 | 4939.8 | 1648.2 | 1525.0 | 1573.6 | 1553.4 | 1436.2 | 1314.3 | 1253.9 | 1245.6 |
| 57.5° | 16344.4 | 14088.8 | 4738.5 | 1515.6 | 1398.3 | 1474.1 | 1491.9 | 1401.9 | 1293.0 | 1238.5 | 1229.0 |
| 60° | 17567.5 | 14615.7 | 4210.4 | 1391.2 | 1297.7 | 1394.8 | 1456.4 | 1392.4 | 1301.2 | 1296.5 | 1289.4 |
| 62.5° | 18147.6 | 14569.5 | 3418.3 | 1293.0 | 1234.9 | 1360.5 | 1482.4 | 1445.7 | 1396.0 | 1438.6 | 1442.1 |
| 65° | 17887.1 | 13873.3 | 2545.7 | 1227.8 | 1190.0 | 1373.5 | 1560.6 | 1546.3 | 1423.2 | 1465.8 | 1471.7 |
| 67.5° | 16172.7 | 12212.1 | 1885.0 | 1171.0 | 1140.2 | 1410.2 | 1702.6 | 1579.5 | 1369.9 | 1400.7 | 1381.8 |
| 70° | 13071.7 | 9681.8 | 1454.0 | 1107.1 | 1089.3 | 1405.4 | 1766.6 | 1559.4 | 1311.9 | 1319.0 | 1268.1 |
| 72.5° | 9014.0 | 6602.2 | 1182.8 | 1047.9 | 1015.9 | 1281.1 | 1721.6 | 1509.6 | 1263.4 | 1208.9 | 1141.4 |
| 75° | 4901.9 | 3543.8 | 1005.2 | 986.3 | 886.8 | 1124.8 | 1638.7 | 1474.1 | 1219.6 | 1147.3 | 1109.4 |
| 77.5° | 1928.8 | 1470.6 | 872.6 | 902.2 | 775.5 | 993.4 | 1546.3 | 1406.6 | 1159.2 | 1064.4 | 1045.5 |
| 80° | 787.4 | 750.7 | 723.4 | 780.3 | 666.6 | 869.1 | 1435.0 | 1327.3 | 1086.9 | 987.5 | 949.6 |
| 82.5° | 446.4 | 466.5 | 562.4 | 615.7 | 541.1 | 800.4 | 1381.8 | 1263.4 | 1000.5 | 884.5 | 839.5 |
| 85° | 228.5 | 273.5 | 391.9 | 441.6 | 397.8 | 680.8 | 1272.8 | 1105.9 | 802.8 | 677.3 | 680.8 |
| 87.5° | 110.1 | 152.7 | 247.5 | 277.1 | 258.1 | 492.6 | 950.8 | 801.6 | 625.2 | 494.9 | 479.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 $CIE R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)