

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P321552

Luminaire Tested: **GLEON-SA8A-730-U-T3R-HSS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P321552  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: GLEON-SA8A-730-U-T3R-HSS  
Description: GALLEON AREA AND ROADWAY LUMINAIRE  
(8) 70 CRI, 3000K, 615mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III  
ROADWAY OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 26160 lumens  
Efficiency: N/A  
Efficacy: 101.8 lumens/watt  
Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')  
IES Classification: Type III - Medium  
BUG Rating: B2 - U0 - G4


Input Watts (W): 257  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P321552  
 CATALOG NUMBER: GLEON-SA8A-730-U-T3R-HSS

## Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 8.3 fc  
 Type III - Medium - N/A

REPORT NUMBER: P321552  
CATALOG NUMBER: GLEON-SA8A-730-U-T3R-HSS

## Luminous Intensity Polar Plot



REPORT NUMBER: P321552  
 CATALOG NUMBER: GLEON-SA8A-730-U-T3R-HSS

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 2071.2   | 0.0    | 2071.2  |
|                    | % Fixture | 7.9      | 0.0    | 7.9     |
| <b>Street Side</b> | Lumens    | 24088.8  | 0.0    | 24088.8 |
|                    | % Fixture | 92.1     | 0.0    | 92.1    |
| <b>Total</b>       | Lumens    | 26160.0  | 0.0    | 26160.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 430.2   | 1.6       |
| 10°-20°   | 971.1   | 3.7       |
| 20°-30°   | 1560.6  | 6.0       |
| 30°-40°   | 2651.6  | 10.1      |
| 40°-50°   | 4115.6  | 15.7      |
| 50°-60°   | 5533.3  | 21.2      |
| 60°-70°   | 6769.0  | 25.9      |
| 70°-80°   | 3957.7  | 15.1      |
| 80°-90°   | 171.1   | 0.7       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 26160.0 | 100.0     |
| 0°-180°   | 26160.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P321552


CATALOG NUMBER: GLEON-SA8A-730-U-T3R-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |          |
|------|-------------|---------|-----------|-------------------------|------|----------|
|      |             |         |           | B                       | U    | G        |
| FL   | (0°-30°)    | 2029.7  | 7.8       |                         |      |          |
| FM   | (30°-60°)   | 11441.6 | 43.7      |                         |      |          |
| FH   | (60°-80°)   | 10449.2 | 39.9      |                         |      | G4/12000 |
| FVH  | (80°-90°)   | 168.4   | 0.6       |                         |      | G2/225   |
| BL   | (0°-30°)    | 932.2   | 3.6       | B2/1000                 |      |          |
| BM   | (30°-60°)   | 858.7   | 3.3       | B1/1000                 |      |          |
| BH   | (60°-80°)   | 277.5   | 1.1       | B1/500                  |      | G1/500   |
| BVH  | (80°-90°)   | 2.7     | 0.0       |                         |      | G0/10    |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |          |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |          |

**BUG Rating: B2-U0-G4**

Type III Medium





REPORT NUMBER: P321552

CATALOG NUMBER: GLEON-SA8A-730-U-T3R-HSS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 15°     | 25°     | 35°     | 45°     | 54°     | 55°     | 65°     | 75°     | 85°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 5045.0  | 5045.0  | 5045.0  | 5045.0  | 5045.0  | 5045.0  | 5045.0  | 5045.0  | 5045.0  | 5045.0  | 5045.0  |
| 2.5°  | 4897.0  | 4902.9  | 4924.1  | 4933.5  | 4955.8  | 4993.4  | 5012.2  | 5013.3  | 5043.9  | 5055.6  | 5065.0  |
| 5°    | 4550.5  | 4585.8  | 4621.0  | 4658.6  | 4726.7  | 4817.2  | 4906.4  | 4914.7  | 5013.3  | 5086.2  | 5124.9  |
| 7.5°  | 4252.2  | 4283.9  | 4326.2  | 4386.1  | 4482.4  | 4624.5  | 4773.7  | 4791.3  | 4978.1  | 5143.7  | 5230.6  |
| 10°   | 3945.6  | 3971.4  | 4032.5  | 4120.6  | 4253.3  | 4443.6  | 4644.5  | 4673.9  | 4946.4  | 5221.2  | 5373.9  |
| 12.5° | 3617.9  | 3633.1  | 3707.1  | 3834.0  | 4029.0  | 4271.0  | 4535.3  | 4574.0  | 4926.4  | 5310.5  | 5543.1  |
| 15°   | 3368.8  | 3375.9  | 3446.4  | 3577.9  | 3801.1  | 4115.9  | 4450.7  | 4497.7  | 4931.1  | 5417.4  | 5727.5  |
| 17.5° | 3305.4  | 3308.9  | 3346.5  | 3437.0  | 3634.3  | 3977.3  | 4383.7  | 4441.3  | 4945.2  | 5522.0  | 5913.1  |
| 20°   | 3562.7  | 3538.0  | 3499.2  | 3485.1  | 3569.7  | 3893.9  | 4343.8  | 4408.4  | 4964.0  | 5614.7  | 6079.9  |
| 22.5° | 4268.6  | 4195.8  | 4034.9  | 3819.9  | 3689.5  | 3899.8  | 4354.4  | 4419.0  | 5023.9  | 5728.7  | 6272.5  |
| 25°   | 5316.4  | 5215.4  | 4941.7  | 4518.8  | 4112.4  | 4068.9  | 4442.5  | 4508.2  | 5140.2  | 5864.9  | 6457.0  |
| 27.5° | 6508.6  | 6408.8  | 6074.0  | 5470.3  | 4777.2  | 4403.7  | 4644.5  | 4705.6  | 5312.9  | 5985.9  | 6597.9  |
| 30°   | 7650.4  | 7622.2  | 7227.5  | 6541.5  | 5613.6  | 4946.4  | 4905.3  | 4957.0  | 5440.9  | 6058.8  | 6709.5  |
| 32.5° | 8618.3  | 8573.6  | 8256.5  | 7589.3  | 6570.9  | 5598.3  | 5211.8  | 5227.1  | 5537.2  | 6152.7  | 6855.2  |
| 35°   | 9515.7  | 9460.5  | 9182.1  | 8551.3  | 7552.9  | 6394.7  | 5684.1  | 5661.7  | 5747.5  | 6341.8  | 7066.6  |
| 37.5° | 10299.2 | 10349.7 | 10040.8 | 9440.5  | 8433.9  | 7222.8  | 6320.7  | 6253.7  | 6076.4  | 6649.6  | 7373.2  |
| 40°   | 10954.6 | 10954.6 | 10793.7 | 10293.3 | 9385.3  | 8079.1  | 7040.8  | 6952.7  | 6570.9  | 7124.2  | 7762.0  |
| 42.5° | 11190.7 | 11241.2 | 11301.1 | 11018.1 | 10236.9 | 8969.5  | 7843.0  | 7751.4  | 7267.5  | 7797.2  | 8253.0  |
| 45°   | 11204.8 | 11284.7 | 11591.3 | 11590.1 | 11006.3 | 9854.0  | 8747.5  | 8704.0  | 8160.2  | 8661.7  | 8861.4  |
| 47.5° | 11006.3 | 11106.2 | 11611.2 | 11897.9 | 11615.9 | 10677.4 | 9736.5  | 9682.5  | 9209.1  | 9721.3  | 9498.1  |
| 50°   | 10699.7 | 10810.1 | 11397.5 | 12018.8 | 12030.6 | 11393.9 | 10778.4 | 10697.4 | 10363.8 | 10932.3 | 10155.9 |
| 52.5° | 10151.2 | 10365.0 | 11206.0 | 12047.0 | 12303.1 | 12013.0 | 11769.8 | 11734.6 | 11655.9 | 12098.7 | 10679.8 |
| 55°   | 8977.7  | 9215.0  | 10725.6 | 12056.4 | 12555.7 | 12561.5 | 12699.0 | 12708.4 | 12866.9 | 13188.8 | 11069.7 |
| 57.5° | 8423.3  | 8557.2  | 9886.9  | 12101.1 | 12930.4 | 13184.1 | 13645.7 | 13718.5 | 13964.0 | 14223.6 | 11514.9 |
| 60°   | 8074.4  | 8233.0  | 9473.4  | 12040.0 | 13518.9 | 14000.5 | 14523.2 | 14547.8 | 14811.0 | 15291.4 | 12117.5 |
| 62.5° | 7796.0  | 7952.3  | 9212.6  | 11805.1 | 14180.2 | 14982.4 | 15380.6 | 15383.0 | 15580.3 | 16563.5 | 12802.3 |
| 65°   | 7108.9  | 7240.4  | 8685.2  | 11540.8 | 14617.1 | 15953.9 | 16376.7 | 16361.5 | 16522.4 | 17904.9 | 13597.6 |
| 67.5° | 6115.1  | 6216.2  | 7608.1  | 10538.8 | 14452.7 | 16837.2 | 17880.3 | 17829.8 | 17634.8 | 19064.3 | 13910.0 |
| 70°   | 4727.9  | 4764.3  | 5996.5  | 8782.7  | 12911.6 | 17176.7 | 19333.3 | 19307.4 | 18317.2 | 18856.4 | 12764.7 |
| 71°   | 3908.0  | 4027.8  | 5284.7  | 7751.4  | 11879.1 | 16863.0 | 19474.2 | 19489.5 | 18145.7 | 18290.2 | 11976.6 |
| 72.5° | 2269.4  | 2371.6  | 3830.5  | 5953.0  | 10085.4 | 15554.5 | 18743.6 | 18854.0 | 17344.6 | 16636.3 | 10229.9 |
| 75°   | 486.3   | 520.4   | 1420.1  | 2881.4  | 5547.8  | 10901.8 | 14794.5 | 15188.0 | 14136.7 | 11317.6 | 6165.6  |
| 77.5° | 338.3   | 365.3   | 608.5   | 1307.4  | 1833.6  | 5386.9  | 9190.3  | 9634.3  | 8445.6  | 4253.3  | 1973.4  |
| 80°   | 267.8   | 298.4   | 474.6   | 646.0   | 495.7   | 1737.3  | 4305.0  | 4576.4  | 2816.8  | 949.1   | 332.4   |
| 82.5° | 149.2   | 177.4   | 370.0   | 348.9   | 190.3   | 330.1   | 1205.2  | 1362.6  | 563.8   | 191.5   | 78.7    |
| 85°   | 43.5    | 52.9    | 238.5   | 253.7   | 81.0    | 63.4    | 205.6   | 254.9   | 106.9   | 50.5    | 35.2    |
| 87.5° | 0.0     | 0.0     | 115.1   | 97.5    | 23.5    | 9.4     | 18.8    | 21.1    | 21.1    | 21.1    | 23.5    |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P321552

CATALOG NUMBER: GLEON-SA8A-730-U-T3R-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 5045.0 | 5045.0 | 5045.0 | 5045.0 | 5045.0 | 5045.0 | 5045.0 | 5045.0 | 5045.0 | 5045.0 | 5045.0 |
| 2.5°  | 5065.0 | 5073.2 | 5043.9 | 5005.1 | 4964.0 | 4913.5 | 4860.6 | 4819.5 | 4818.3 | 4798.4 | 4778.4 |
| 5°    | 5127.3 | 5122.6 | 5041.5 | 4918.2 | 4772.5 | 4621.0 | 4476.5 | 4313.3 | 4259.2 | 4192.3 | 4169.9 |
| 7.5°  | 5242.4 | 5209.5 | 5038.0 | 4767.8 | 4448.3 | 4131.2 | 3803.5 | 3473.4 | 3332.4 | 3205.6 | 3183.3 |
| 10°   | 5386.9 | 5324.6 | 5015.7 | 4542.3 | 3956.2 | 3371.2 | 2876.7 | 2428.0 | 2230.6 | 2079.1 | 2072.1 |
| 12.5° | 5537.2 | 5442.1 | 4953.4 | 4201.7 | 3311.3 | 2489.0 | 1919.4 | 1477.7 | 1313.2 | 1207.5 | 1216.9 |
| 15°   | 5694.6 | 5552.5 | 4819.5 | 3742.4 | 2577.1 | 1689.1 | 1179.3 | 919.7  | 854.0  | 826.9  | 834.0  |
| 17.5° | 5855.5 | 5628.8 | 4632.8 | 3189.1 | 1852.4 | 1090.1 | 816.4  | 743.5  | 743.5  | 749.4  | 751.8  |
| 20°   | 5995.3 | 5670.0 | 4357.9 | 2568.9 | 1255.7 | 794.1  | 714.2  | 703.6  | 709.5  | 718.9  | 720.1  |
| 22.5° | 6133.9 | 5672.3 | 3999.6 | 1940.5 | 878.6  | 695.4  | 680.1  | 675.4  | 678.9  | 689.5  | 690.7  |
| 25°   | 6246.7 | 5644.1 | 3550.9 | 1380.2 | 701.3  | 655.4  | 648.4  | 646.0  | 648.4  | 661.3  | 661.3  |
| 27.5° | 6292.5 | 5541.9 | 3003.5 | 970.2  | 628.4  | 610.8  | 608.5  | 610.8  | 614.3  | 623.7  | 624.9  |
| 30°   | 6297.2 | 5363.4 | 2406.8 | 702.4  | 569.7  | 550.9  | 555.6  | 563.8  | 560.3  | 558.0  | 560.3  |
| 32.5° | 6309.0 | 5156.6 | 1825.4 | 577.9  | 520.4  | 491.0  | 485.1  | 485.1  | 471.0  | 462.8  | 458.1  |
| 35°   | 6347.7 | 4913.5 | 1323.8 | 519.2  | 469.9  | 435.8  | 413.5  | 387.6  | 360.6  | 346.5  | 343.0  |
| 37.5° | 6408.8 | 4658.6 | 947.9  | 480.4  | 425.2  | 386.5  | 344.2  | 298.4  | 259.6  | 249.0  | 249.0  |
| 40°   | 6520.4 | 4395.5 | 701.3  | 449.9  | 390.0  | 341.8  | 278.4  | 218.5  | 183.2  | 177.4  | 177.4  |
| 42.5° | 6696.6 | 4118.3 | 559.1  | 422.9  | 359.4  | 296.0  | 212.6  | 158.6  | 132.7  | 129.2  | 128.0  |
| 45°   | 6879.8 | 3812.9 | 488.6  | 397.0  | 326.5  | 243.1  | 157.4  | 117.5  | 102.2  | 98.7   | 98.7   |
| 47.5° | 7063.1 | 3487.5 | 454.6  | 372.4  | 294.8  | 189.1  | 117.5  | 92.8   | 85.7   | 85.7   | 86.9   |
| 50°   | 7218.1 | 3148.0 | 429.9  | 345.3  | 253.7  | 143.3  | 92.8   | 78.7   | 76.4   | 81.0   | 82.2   |
| 52.5° | 7256.9 | 2814.4 | 399.4  | 311.3  | 203.2  | 109.2  | 76.4   | 69.3   | 69.3   | 69.3   | 69.3   |
| 55°   | 7233.4 | 2556.0 | 359.4  | 269.0  | 150.4  | 86.9   | 65.8   | 61.1   | 59.9   | 59.9   | 59.9   |
| 57.5° | 7313.3 | 2403.3 | 287.8  | 209.1  | 108.1  | 70.5   | 57.6   | 54.0   | 51.7   | 50.5   | 50.5   |
| 60°   | 7474.2 | 2303.5 | 205.6  | 150.4  | 81.0   | 58.7   | 49.3   | 45.8   | 42.3   | 39.9   | 39.9   |
| 62.5° | 7688.0 | 2216.5 | 152.7  | 111.6  | 62.3   | 47.0   | 41.1   | 37.6   | 32.9   | 30.5   | 30.5   |
| 65°   | 7852.4 | 2061.5 | 116.3  | 83.4   | 47.0   | 37.6   | 31.7   | 30.5   | 23.5   | 21.1   | 20.0   |
| 67.5° | 7601.1 | 1720.8 | 94.0   | 61.1   | 35.2   | 29.4   | 24.7   | 23.5   | 14.1   | 11.7   | 11.7   |
| 70°   | 6519.2 | 1198.1 | 75.2   | 44.6   | 25.8   | 23.5   | 20.0   | 15.3   | 10.6   | 9.4    | 9.4    |
| 71°   | 5911.9 | 1000.8 | 68.1   | 37.6   | 22.3   | 22.3   | 18.8   | 12.9   | 9.4    | 8.2    | 8.2    |
| 72.5° | 4911.1 | 710.7  | 57.6   | 29.4   | 20.0   | 23.5   | 20.0   | 11.7   | 9.4    | 8.2    | 7.0    |
| 75°   | 2850.8 | 297.2  | 39.9   | 20.0   | 15.3   | 28.2   | 25.8   | 10.6   | 7.0    | 5.9    | 5.9    |
| 77.5° | 857.5  | 109.2  | 22.3   | 12.9   | 11.7   | 24.7   | 29.4   | 9.4    | 3.5    | 1.2    | 1.2    |
| 80°   | 156.2  | 47.0   | 14.1   | 8.2    | 8.2    | 15.3   | 22.3   | 4.7    | 0.0    | 0.0    | 0.0    |
| 82.5° | 55.2   | 23.5   | 8.2    | 4.7    | 3.5    | 7.0    | 10.6   | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 31.7   | 16.4   | 4.7    | 2.3    | 0.0    | 1.2    | 2.3    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 21.1   | 4.7    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-2-R4

Test Date: 10/03/2019

Luminaire Tested: SA1C-730-U-5WQ

Data in this report applies to families of products SA1C-730-U-5WQ .

### Test Information

Test Method: LM-79-2008  
Report Number: SP1-1908-441-2-R4  
Test Lab: COOPER LIGHTING SOLUTIONS  
Photometer: SP1 - 76IN SPHERE  
Measurement Geometry:  $4\pi$   
Issue Date: 10/28/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: MCGRAW-EDISON  
Catalog Number: **SA1C-730-U-5WQ**  
Description: MCGRAW EDISON ROADWAY AND AREA LUMINAIRE

\*\*\*THIS IS A REVISION OF SP1-1908-441-2-R3. TO UPDATE THE CATALOG INFORMATION.\*\*\*TESTED IN SITU. (1) 70 CRI, 3000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

### Spectral Parameters

|                           |        |           |      |      |       |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K):                  | 2993   | CRI (Ra): | 71.8 |      |       |
| CIE u':                   | 0.2508 | R1:       | 67.5 | R9:  | -38.3 |
| CIE v':                   | 0.5215 | R2:       | 82.9 | R10: | 62.5  |
| Duv:                      | 0.0000 | R3:       | 94.7 | R11: | 63.7  |
| CIE x:                    | 0.4374 | R4:       | 67.7 | R12: | 57.8  |
| CIE y:                    | 0.4043 | R5:       | 67.9 | R13: | 70.4  |
| CIE z:                    | 0.1583 | R6:       | 77.6 | R14: | 97.3  |
| Peak Wavelength (nm):     | 593    | R7:       | 76.0 |      |       |
| Dominant Wavelength (nm): | 582    | R8:       | 40.5 |      |       |
| Purity:                   | 53     |           |      |      |       |
| Rf:                       | 75.7   |           |      |      |       |
| Rg:                       | 93.9   |           |      |      |       |



### Test Conditions

Stabilization Time: 53M  
Operation Time: 12H  
Room Temperature (°C) / RH%: 25.0./44%  
Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-2-R4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/28/2019        | 12/28/2019           |
| Power Meter                    | IN0071                | 12/5/2018        | 12/5/2019            |
| AC Power Source                | IN0063                | 12/5/2018        | 12/5/2019            |
| DC Power Source                | IN0208                | 12/5/2018        | 12/5/2019            |
| Sphere Thermometer             | IN0085                | 12/5/2018        | 12/5/2019            |
| Room Thermometer               | IN0046                | 12/5/2018        | 12/5/2019            |

REPORT NUMBER: SP1-1908-441-2-R4

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-2-R4

**Photopic Flux vs. Wavelength**



#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2397             | NR               | 490       | 24908            | NR               | 620       | 118784           | NR               | 750       | 5037             | NR               | 880       | 2677             | NR               |
| 365       | 2084             | NR               | 495       | 30998            | NR               | 625       | 108951           | NR               | 755       | 4413             | NR               | 885       | 2940             | NR               |
| 370       | 2143             | NR               | 500       | 37103            | NR               | 630       | 99573            | NR               | 760       | 4189             | NR               | 890       | 3116             | NR               |
| 375       | 2413             | NR               | 505       | 42987            | NR               | 635       | 90444            | NR               | 765       | 3677             | NR               | 895       | 3345             | NR               |
| 380       | 2172             | NR               | 510       | 48702            | NR               | 640       | 80749            | NR               | 770       | 3366             | NR               | 900       | 2312             | NR               |
| 385       | 1997             | NR               | 515       | 53741            | NR               | 645       | 71664            | NR               | 775       | 3211             | NR               | 905       | 2829             | NR               |
| 390       | 1830             | NR               | 520       | 57283            | NR               | 650       | 63936            | NR               | 780       | 2682             | NR               | 910       | 2783             | NR               |
| 395       | 1861             | NR               | 525       | 61876            | NR               | 655       | 56611            | NR               | 785       | 2804             | NR               | 915       | 2662             | NR               |
| 400       | 1717             | NR               | 530       | 65398            | NR               | 660       | 49763            | NR               | 790       | 2581             | NR               | 920       | 3047             | NR               |
| 405       | 1761             | NR               | 535       | 69597            | NR               | 665       | 42891            | NR               | 795       | 2711             | NR               | 925       | 2256             | NR               |
| 410       | 2680             | NR               | 540       | 74214            | NR               | 670       | 36939            | NR               | 800       | 2609             | NR               | 930       | 2976             | NR               |
| 415       | 4374             | NR               | 545       | 79911            | NR               | 675       | 31946            | NR               | 805       | 2581             | NR               | 935       | 3503             | NR               |
| 420       | 8071             | NR               | 550       | 86153            | NR               | 680       | 27385            | NR               | 810       | 2404             | NR               | 940       | 4226             | NR               |
| 425       | 15169            | NR               | 555       | 93952            | NR               | 685       | 23504            | NR               | 815       | 2556             | NR               | 945       | 2930             | NR               |
| 430       | 26038            | NR               | 560       | 102904           | NR               | 690       | 20210            | NR               | 820       | 2742             | NR               | 950       | 2115             | NR               |
| 435       | 41316            | NR               | 565       | 112009           | NR               | 695       | 17459            | NR               | 825       | 2014             | NR               | 955       | 2634             | NR               |
| 440       | 59674            | NR               | 570       | 121662           | NR               | 700       | 15207            | NR               | 830       | 2488             | NR               | 960       | 4200             | NR               |
| 445       | 72751            | NR               | 575       | 130476           | NR               | 705       | 13322            | NR               | 835       | 2625             | NR               | 965       | 1982             | NR               |
| 450       | 65091            | NR               | 580       | 137926           | NR               | 710       | 11676            | NR               | 840       | 2754             | NR               | 970       | 3613             | NR               |
| 455       | 44894            | NR               | 585       | 143406           | NR               | 715       | 10626            | NR               | 845       | 2708             | NR               | 975       | 4034             | NR               |
| 460       | 32712            | NR               | 590       | 147039           | NR               | 720       | 9416             | NR               | 850       | 2608             | NR               | 980       | 3922             | NR               |
| 465       | 25296            | NR               | 595       | 147365           | NR               | 725       | 8333             | NR               | 855       | 2605             | NR               | 985       | 1909             | NR               |
| 470       | 19318            | NR               | 600       | 145800           | NR               | 730       | 7134             | NR               | 860       | 1765             | NR               | 990       | 3617             | NR               |
| 475       | 17265            | NR               | 605       | 141363           | NR               | 735       | 6437             | NR               | 865       | 2581             | NR               | 995       | 4767             | NR               |
| 480       | 18260            | NR               | 610       | 134199           | NR               | 740       | 5834             | NR               | 870       | 3016             | NR               | 1000      | 2528             | NR               |
| 485       | 20845            | NR               | 615       | 127683           | NR               | 745       | 5500             | NR               | 875       | 3952             | NR               |           |                  |                  |

REPORT NUMBER: SP1-1908-441-2-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 8494.8

S/P: 1.23

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2397             | NR               | 490       | 24908            | NR               | 620       | 118784           | NR               | 750       | 5037             | NR               | 880       | 2677             | NR               |
| 365       | 2084             | NR               | 495       | 30998            | NR               | 625       | 108951           | NR               | 755       | 4413             | NR               | 885       | 2940             | NR               |
| 370       | 2143             | NR               | 500       | 37103            | NR               | 630       | 99573            | NR               | 760       | 4189             | NR               | 890       | 3116             | NR               |
| 375       | 2413             | NR               | 505       | 42987            | NR               | 635       | 90444            | NR               | 765       | 3677             | NR               | 895       | 3345             | NR               |
| 380       | 2172             | NR               | 510       | 48702            | NR               | 640       | 80749            | NR               | 770       | 3366             | NR               | 900       | 2312             | NR               |
| 385       | 1997             | NR               | 515       | 53741            | NR               | 645       | 71664            | NR               | 775       | 3211             | NR               | 905       | 2829             | NR               |
| 390       | 1830             | NR               | 520       | 57283            | NR               | 650       | 63936            | NR               | 780       | 2682             | NR               | 910       | 2783             | NR               |
| 395       | 1861             | NR               | 525       | 61876            | NR               | 655       | 56611            | NR               | 785       | 2804             | NR               | 915       | 2662             | NR               |
| 400       | 1717             | NR               | 530       | 65398            | NR               | 660       | 49763            | NR               | 790       | 2581             | NR               | 920       | 3047             | NR               |
| 405       | 1761             | NR               | 535       | 69597            | NR               | 665       | 42891            | NR               | 795       | 2711             | NR               | 925       | 2256             | NR               |
| 410       | 2680             | NR               | 540       | 74214            | NR               | 670       | 36939            | NR               | 800       | 2609             | NR               | 930       | 2976             | NR               |
| 415       | 4374             | NR               | 545       | 79911            | NR               | 675       | 31946            | NR               | 805       | 2581             | NR               | 935       | 3503             | NR               |
| 420       | 8071             | NR               | 550       | 86153            | NR               | 680       | 27385            | NR               | 810       | 2404             | NR               | 940       | 4226             | NR               |
| 425       | 15169            | NR               | 555       | 93952            | NR               | 685       | 23504            | NR               | 815       | 2556             | NR               | 945       | 2930             | NR               |
| 430       | 26038            | NR               | 560       | 102904           | NR               | 690       | 20210            | NR               | 820       | 2742             | NR               | 950       | 2115             | NR               |
| 435       | 41316            | NR               | 565       | 112009           | NR               | 695       | 17459            | NR               | 825       | 2014             | NR               | 955       | 2634             | NR               |
| 440       | 59674            | NR               | 570       | 121662           | NR               | 700       | 15207            | NR               | 830       | 2488             | NR               | 960       | 4200             | NR               |
| 445       | 72751            | NR               | 575       | 130476           | NR               | 705       | 13322            | NR               | 835       | 2625             | NR               | 965       | 1982             | NR               |
| 450       | 65091            | NR               | 580       | 137926           | NR               | 710       | 11676            | NR               | 840       | 2754             | NR               | 970       | 3613             | NR               |
| 455       | 44894            | NR               | 585       | 143406           | NR               | 715       | 10626            | NR               | 845       | 2708             | NR               | 975       | 4034             | NR               |
| 460       | 32712            | NR               | 590       | 147039           | NR               | 720       | 9416             | NR               | 850       | 2608             | NR               | 980       | 3922             | NR               |
| 465       | 25296            | NR               | 595       | 147365           | NR               | 725       | 8333             | NR               | 855       | 2605             | NR               | 985       | 1909             | NR               |
| 470       | 19318            | NR               | 600       | 145800           | NR               | 730       | 7134             | NR               | 860       | 1765             | NR               | 990       | 3617             | NR               |
| 475       | 17265            | NR               | 605       | 141363           | NR               | 735       | 6437             | NR               | 865       | 2581             | NR               | 995       | 4767             | NR               |
| 480       | 18260            | NR               | 610       | 134199           | NR               | 740       | 5834             | NR               | 870       | 3016             | NR               | 1000      | 2528             | NR               |
| 485       | 20845            | NR               | 615       | 127683           | NR               | 745       | 5500             | NR               | 875       | 3952             | NR               |           |                  |                  |

REPORT NUMBER: SP1-1908-441-2-R4

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 3101.5 M/P: 0.45**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2397             | NR               | 490       | 24908            | NR               | 620       | 118784           | NR               | 750       | 5037             | NR               | 880       | 2677             | NR               |
| 365       | 2084             | NR               | 495       | 30998            | NR               | 625       | 108951           | NR               | 755       | 4413             | NR               | 885       | 2940             | NR               |
| 370       | 2143             | NR               | 500       | 37103            | NR               | 630       | 99573            | NR               | 760       | 4189             | NR               | 890       | 3116             | NR               |
| 375       | 2413             | NR               | 505       | 42987            | NR               | 635       | 90444            | NR               | 765       | 3677             | NR               | 895       | 3345             | NR               |
| 380       | 2172             | NR               | 510       | 48702            | NR               | 640       | 80749            | NR               | 770       | 3366             | NR               | 900       | 2312             | NR               |
| 385       | 1997             | NR               | 515       | 53741            | NR               | 645       | 71664            | NR               | 775       | 3211             | NR               | 905       | 2829             | NR               |
| 390       | 1830             | NR               | 520       | 57283            | NR               | 650       | 63936            | NR               | 780       | 2682             | NR               | 910       | 2783             | NR               |
| 395       | 1861             | NR               | 525       | 61876            | NR               | 655       | 56611            | NR               | 785       | 2804             | NR               | 915       | 2662             | NR               |
| 400       | 1717             | NR               | 530       | 65398            | NR               | 660       | 49763            | NR               | 790       | 2581             | NR               | 920       | 3047             | NR               |
| 405       | 1761             | NR               | 535       | 69597            | NR               | 665       | 42891            | NR               | 795       | 2711             | NR               | 925       | 2256             | NR               |
| 410       | 2680             | NR               | 540       | 74214            | NR               | 670       | 36939            | NR               | 800       | 2609             | NR               | 930       | 2976             | NR               |
| 415       | 4374             | NR               | 545       | 79911            | NR               | 675       | 31946            | NR               | 805       | 2581             | NR               | 935       | 3503             | NR               |
| 420       | 8071             | NR               | 550       | 86153            | NR               | 680       | 27385            | NR               | 810       | 2404             | NR               | 940       | 4226             | NR               |
| 425       | 15169            | NR               | 555       | 93952            | NR               | 685       | 23504            | NR               | 815       | 2556             | NR               | 945       | 2930             | NR               |
| 430       | 26038            | NR               | 560       | 102904           | NR               | 690       | 20210            | NR               | 820       | 2742             | NR               | 950       | 2115             | NR               |
| 435       | 41316            | NR               | 565       | 112009           | NR               | 695       | 17459            | NR               | 825       | 2014             | NR               | 955       | 2634             | NR               |
| 440       | 59674            | NR               | 570       | 121662           | NR               | 700       | 15207            | NR               | 830       | 2488             | NR               | 960       | 4200             | NR               |
| 445       | 72751            | NR               | 575       | 130476           | NR               | 705       | 13322            | NR               | 835       | 2625             | NR               | 965       | 1982             | NR               |
| 450       | 65091            | NR               | 580       | 137926           | NR               | 710       | 11676            | NR               | 840       | 2754             | NR               | 970       | 3613             | NR               |
| 455       | 44894            | NR               | 585       | 143406           | NR               | 715       | 10626            | NR               | 845       | 2708             | NR               | 975       | 4034             | NR               |
| 460       | 32712            | NR               | 590       | 147039           | NR               | 720       | 9416             | NR               | 850       | 2608             | NR               | 980       | 3922             | NR               |
| 465       | 25296            | NR               | 595       | 147365           | NR               | 725       | 8333             | NR               | 855       | 2605             | NR               | 985       | 1909             | NR               |
| 470       | 19318            | NR               | 600       | 145800           | NR               | 730       | 7134             | NR               | 860       | 1765             | NR               | 990       | 3617             | NR               |
| 475       | 17265            | NR               | 605       | 141363           | NR               | 735       | 6437             | NR               | 865       | 2581             | NR               | 995       | 4767             | NR               |
| 480       | 18260            | NR               | 610       | 134199           | NR               | 740       | 5834             | NR               | 870       | 3016             | NR               | 1000      | 2528             | NR               |
| 485       | 20845            | NR               | 615       | 127683           | NR               | 745       | 5500             | NR               | 875       | 3952             | NR               |           |                  |                  |

REPORT NUMBER: SP1-1908-441-2-R4

**TM-30-18**

**Summary**

$R_f = 75.7$   
 $R_g = 93.9$   
 CIE  $R_a = 71.8$   
 $R_g = -38.3$



**Color Vector Graphics**



REPORT NUMBER: SP1-1908-441-2-R4

**TM-30-18**

**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 67 | CES51 = 87 | CES76 = 63 |
| CES02 = 63 | CES27 = 88 | CES52 = 86 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 66 | CES54 = 84 | CES79 = 87 |
| CES05 = 49 | CES30 = 73 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 70 | CES56 = 75 | CES81 = 71 |
| CES07 = 41 | CES32 = 65 | CES57 = 74 | CES82 = 94 |
| CES08 = 40 | CES33 = 73 | CES58 = 76 | CES83 = 90 |
| CES09 = 29 | CES34 = 79 | CES59 = 85 | CES84 = 89 |
| CES10 = 76 | CES35 = 89 | CES60 = 93 | CES85 = 77 |
| CES11 = 59 | CES36 = 97 | CES61 = 84 | CES86 = 61 |
| CES12 = 65 | CES37 = 87 | CES62 = 91 | CES87 = 78 |
| CES13 = 43 | CES38 = 81 | CES63 = 77 | CES88 = 77 |
| CES14 = 74 | CES39 = 95 | CES64 = 72 | CES89 = 67 |
| CES15 = 71 | CES40 = 92 | CES65 = 68 | CES90 = 76 |
| CES16 = 47 | CES41 = 88 | CES66 = 69 | CES91 = 89 |
| CES17 = 50 | CES42 = 89 | CES67 = 67 | CES92 = 58 |
| CES18 = 56 | CES43 = 79 | CES68 = 72 | CES93 = 74 |
| CES19 = 73 | CES44 = 99 | CES69 = 81 | CES94 = 49 |
| CES20 = 66 | CES45 = 85 | CES70 = 66 | CES95 = 68 |
| CES21 = 87 | CES46 = 80 | CES71 = 67 | CES96 = 76 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 69 | CES73 = 59 | CES98 = 75 |
| CES24 = 91 | CES49 = 80 | CES74 = 95 | CES99 = 62 |
| CES25 = 73 | CES50 = 87 | CES75 = 69 |            |



REPORT NUMBER: SP1-1908-441-2-R4

**TM-30-18**

**Color Rendition by Hue-Angle Bin**



REPORT NUMBER: SP1-1908-441-2-R4

**TM-30-18**

**Measure Comparisons**



(END OF REPORT)