

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P324488

Luminaire Tested: **GLEON-SA4C-740-U-SLR-HSS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P324488  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-28)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: GLEON-SA4C-740-U-SLR-HSS  
Description: GALLEON AREA AND ROADWAY LUMINAIRE  
(4) 70 CRI, 4000K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT  
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 21152 lumens  
Efficiency: N/A  
Efficacy: 94.0 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Medium  
BUG Rating: B2 - U0 - G3


Input Watts (W): 225  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P324488  
 CATALOG NUMBER: GLEON-SA4C-740-U-SLR-HSS

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 11 fc  
 Type IV - Medium - N/A

REPORT NUMBER: P324488  
CATALOG NUMBER: GLEON-SA4C-740-U-SLR-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 345-Deg Lateral    - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P324488  
 CATALOG NUMBER: GLEON-SA4C-740-U-SLR-HSS


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 2560.1   | 0.0    | 2560.1  |
|                    | % Fixture | 12.1     | 0.0    | 12.1    |
| <b>Street Side</b> | Lumens    | 18591.9  | 0.0    | 18591.9 |
|                    | % Fixture | 87.9     | 0.0    | 87.9    |
| <b>Total</b>       | Lumens    | 21152.0  | 0.0    | 21152.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 528.8   | 2.5       |
| 10°-20°   | 1052.6  | 5.0       |
| 20°-30°   | 1494.7  | 7.1       |
| 30°-40°   | 2207.8  | 10.4      |
| 40°-50°   | 3184.1  | 15.1      |
| 50°-60°   | 4469.8  | 21.1      |
| 60°-70°   | 5210.4  | 24.6      |
| 70°-80°   | 2663.7  | 12.6      |
| 80°-90°   | 340.2   | 1.6       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 21152.0 | 100.0     |
| 0°-180°   | 21152.0 | 100.0     |




REPORT NUMBER: P324488  
 CATALOG NUMBER: GLEON-SA4C-740-U-SLR-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 2320.0 | 11.0      |                         |      |         |
| FM   | (30°-60°)   | 8702.3 | 41.1      |                         |      |         |
| FH   | (60°-80°)   | 7250.2 | 34.3      |                         |      | G3/7500 |
| FVH  | (80°-90°)   | 319.5  | 1.5       |                         |      | G3/500  |
| BL   | (0°-30°)    | 756.2  | 3.6       | B2/1000                 |      |         |
| BM   | (30°-60°)   | 1159.3 | 5.5       | B2/2500                 |      |         |
| BH   | (60°-80°)   | 624.0  | 2.9       | B2/1000                 |      | G2/1000 |
| BVH  | (80°-90°)   | 20.7   | 0.1       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G3**  
 Type IV Medium





REPORT NUMBER: P324488

CATALOG NUMBER: GLEON-SA4C-740-U-SLR-HSS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 1°      | 5°      | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    |
|-------|---------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 6890.2  | 6890.2  | 6890.2  | 6890.2 | 6890.2 | 6890.2 | 6890.2 | 6890.2 | 6890.2 | 6890.2 | 6890.2 |
| 2.5°  | 7544.6  | 7486.5  | 7422.3  | 7212.9 | 7018.5 | 6796.0 | 6614.7 | 6488.4 | 6330.1 | 6124.6 | 6072.5 |
| 5°    | 7490.5  | 7428.3  | 7226.9  | 6761.0 | 6353.1 | 5956.3 | 5573.5 | 5349.0 | 5070.5 | 4787.9 | 4717.7 |
| 7.5°  | 6946.3  | 6881.2  | 6590.6  | 5952.3 | 5403.2 | 4830.0 | 4332.9 | 4025.3 | 3710.7 | 3452.1 | 3314.8 |
| 10°   | 6380.2  | 6309.0  | 5982.4  | 5207.8 | 4531.4 | 4013.3 | 3648.5 | 3354.9 | 3057.3 | 2780.7 | 2560.3 |
| 12.5° | 5990.4  | 5897.2  | 5542.4  | 4664.6 | 4075.4 | 3723.7 | 3383.0 | 3031.3 | 2628.4 | 2331.8 | 2089.3 |
| 15°   | 5827.0  | 5720.8  | 5346.0  | 4455.2 | 3914.1 | 3501.2 | 3057.3 | 2625.4 | 2153.4 | 1813.7 | 1591.3 |
| 17.5° | 5953.3  | 5815.0  | 5413.2  | 4441.2 | 3711.7 | 3149.5 | 2588.3 | 2081.3 | 1569.2 | 1225.5 | 1067.2 |
| 20°   | 6382.2  | 6200.8  | 5690.7  | 4437.2 | 3466.2 | 2731.6 | 2020.2 | 1447.0 | 1034.1 | 831.7  | 748.5  |
| 22.5° | 7057.6  | 6818.1  | 6089.6  | 4469.2 | 3212.6 | 2292.7 | 1459.0 | 983.0  | 776.6  | 671.4  | 622.3  |
| 25°   | 7873.3  | 7595.7  | 6663.8  | 4582.5 | 2990.2 | 1865.9 | 1060.2 | 776.6  | 655.4  | 578.2  | 537.1  |
| 27.5° | 8648.9  | 8423.4  | 7389.3  | 4745.8 | 2817.8 | 1521.1 | 860.8  | 658.4  | 560.2  | 509.1  | 476.0  |
| 30°   | 9423.5  | 9139.9  | 8133.8  | 4940.2 | 2610.4 | 1287.7 | 756.6  | 600.2  | 502.0  | 447.9  | 426.9  |
| 32.5° | 9986.6  | 9751.1  | 8717.0  | 5080.5 | 2388.9 | 1135.3 | 676.4  | 549.1  | 469.0  | 413.9  | 382.8  |
| 35°   | 10649.0 | 10382.4 | 9217.0  | 5111.6 | 2246.6 | 1039.1 | 608.3  | 494.0  | 406.8  | 357.7  | 324.7  |
| 37.5° | 11364.5 | 11032.8 | 9794.2  | 5043.4 | 2135.4 | 992.0  | 557.2  | 469.0  | 379.8  | 329.7  | 294.6  |
| 40°   | 12156.1 | 11781.3 | 10348.4 | 4945.2 | 2026.2 | 976.0  | 518.1  | 449.9  | 358.7  | 307.6  | 271.6  |
| 42.5° | 12989.8 | 12547.9 | 10828.4 | 4842.0 | 1957.0 | 920.9  | 514.1  | 430.9  | 342.7  | 287.6  | 251.5  |
| 45°   | 13690.3 | 13242.3 | 11321.4 | 4807.9 | 1907.9 | 860.8  | 531.1  | 417.9  | 331.7  | 271.6  | 236.5  |
| 47.5° | 14248.4 | 13824.5 | 11826.4 | 4884.1 | 1879.9 | 805.7  | 484.0  | 434.9  | 325.7  | 257.5  | 223.5  |
| 50°   | 14914.8 | 14434.8 | 12537.9 | 5111.6 | 1838.8 | 750.5  | 437.9  | 498.0  | 325.7  | 248.5  | 212.4  |
| 52.5° | 15750.5 | 15275.5 | 13331.5 | 5464.3 | 1756.6 | 674.4  | 393.8  | 499.0  | 328.7  | 236.5  | 198.4  |
| 55°   | 16801.7 | 16457.0 | 14464.9 | 5851.1 | 1625.4 | 562.2  | 340.7  | 428.9  | 316.7  | 214.4  | 185.4  |
| 57.5° | 17809.8 | 17528.2 | 15498.0 | 6115.6 | 1450.0 | 438.9  | 296.6  | 345.7  | 289.6  | 188.4  | 165.3  |
| 59°   | 18085.3 | 17777.7 | 15876.8 | 6127.7 | 1318.7 | 382.8  | 274.6  | 285.6  | 283.6  | 176.4  | 153.3  |
| 60°   | 18085.3 | 17758.7 | 15986.0 | 6063.5 | 1223.5 | 351.7  | 260.5  | 254.5  | 295.6  | 168.3  | 146.3  |
| 62.5° | 17757.7 | 17298.7 | 15631.3 | 5629.6 | 998.1  | 299.6  | 227.5  | 210.4  | 265.5  | 151.3  | 129.3  |
| 65°   | 17076.3 | 16407.9 | 14422.8 | 4845.0 | 889.8  | 274.6  | 196.4  | 172.4  | 184.4  | 133.3  | 113.2  |
| 67.5° | 15939.9 | 15034.0 | 12680.2 | 3914.1 | 846.7  | 267.6  | 169.3  | 146.3  | 139.3  | 114.2  | 99.2   |
| 70°   | 13938.8 | 12933.7 | 10564.8 | 3077.4 | 809.7  | 264.5  | 142.3  | 123.3  | 112.2  | 96.2   | 84.2   |
| 72.5° | 10144.9 | 9096.8  | 7500.5  | 2406.0 | 787.6  | 270.6  | 114.2  | 103.2  | 92.2   | 75.2   | 65.1   |
| 75°   | 5803.0  | 5116.6  | 4215.7  | 1589.3 | 671.4  | 258.5  | 88.2   | 86.2   | 66.1   | 54.1   | 45.1   |
| 77.5° | 2998.2  | 2907.0  | 2526.2  | 610.3  | 321.7  | 113.2  | 58.1   | 50.1   | 39.1   | 33.1   | 27.1   |
| 80°   | 1293.7  | 1279.6  | 1107.3  | 176.4  | 85.2   | 63.1   | 33.1   | 21.0   | 18.0   | 14.0   | 11.0   |
| 82.5° | 446.9   | 446.9   | 393.8   | 59.1   | 38.1   | 31.1   | 4.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 90.2    | 101.2   | 71.1    | 0.0    | 13.0   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P324488

CATALOG NUMBER: GLEON-SA4C-740-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 6890.2 | 6890.2 | 6890.2 | 6890.2 | 6890.2 | 6890.2 | 6890.2 | 6890.2 | 6890.2 | 6890.2 | 6890.2 |
| 2.5°  | 6009.4 | 5888.2 | 5880.1 | 5804.0 | 5708.8 | 5665.7 | 5640.6 | 5684.7 | 5738.8 | 5744.9 | 5826.0 |
| 5°    | 4664.6 | 4537.4 | 4590.5 | 4455.2 | 4482.3 | 4455.2 | 4411.1 | 4419.1 | 4443.2 | 4368.0 | 4461.2 |
| 7.5°  | 3275.8 | 3179.6 | 3240.7 | 3204.6 | 3252.7 | 3271.8 | 3244.7 | 3204.6 | 3086.4 | 3072.3 | 3153.5 |
| 10°   | 2469.1 | 2359.9 | 2294.7 | 2226.6 | 2241.6 | 2272.7 | 2262.7 | 2233.6 | 2158.5 | 2162.5 | 2240.6 |
| 12.5° | 1984.1 | 1861.8 | 1732.6 | 1565.2 | 1524.1 | 1547.2 | 1524.1 | 1507.1 | 1435.0 | 1441.0 | 1510.1 |
| 15°   | 1505.1 | 1404.9 | 1269.6 | 1135.3 | 1062.2 | 1069.2 | 1005.1 | 960.0  | 914.9  | 860.8  | 902.9  |
| 17.5° | 1016.1 | 955.0  | 914.9  | 874.8  | 787.6  | 767.6  | 686.4  | 599.2  | 565.2  | 540.1  | 558.2  |
| 20°   | 719.5  | 686.4  | 670.4  | 668.4  | 618.3  | 593.2  | 514.1  | 459.9  | 442.9  | 437.9  | 448.9  |
| 22.5° | 601.2  | 577.2  | 554.1  | 541.1  | 516.1  | 487.0  | 426.9  | 399.8  | 387.8  | 381.8  | 389.8  |
| 25°   | 523.1  | 505.0  | 481.0  | 458.9  | 448.9  | 417.9  | 374.8  | 354.7  | 346.7  | 340.7  | 344.7  |
| 27.5° | 465.0  | 448.9  | 420.9  | 406.8  | 398.8  | 371.8  | 334.7  | 318.7  | 311.6  | 309.6  | 308.6  |
| 30°   | 418.9  | 403.8  | 377.8  | 361.7  | 347.7  | 323.7  | 301.6  | 285.6  | 278.6  | 276.6  | 274.6  |
| 32.5° | 372.8  | 360.7  | 343.7  | 327.7  | 312.6  | 290.6  | 271.6  | 258.5  | 247.5  | 245.5  | 244.5  |
| 35°   | 314.6  | 302.6  | 293.6  | 292.6  | 278.6  | 257.5  | 243.5  | 226.5  | 217.4  | 214.4  | 215.4  |
| 37.5° | 279.6  | 263.5  | 243.5  | 250.5  | 246.5  | 231.5  | 212.4  | 195.4  | 186.4  | 184.4  | 184.4  |
| 40°   | 257.5  | 240.5  | 217.4  | 205.4  | 217.4  | 214.4  | 184.4  | 167.3  | 158.3  | 157.3  | 155.3  |
| 42.5° | 236.5  | 219.5  | 193.4  | 173.4  | 179.4  | 188.4  | 159.3  | 143.3  | 134.3  | 132.3  | 129.3  |
| 45°   | 221.5  | 203.4  | 174.4  | 151.3  | 139.3  | 158.3  | 136.3  | 116.2  | 111.2  | 107.2  | 105.2  |
| 47.5° | 207.4  | 190.4  | 157.3  | 131.3  | 111.2  | 114.2  | 109.2  | 95.2   | 89.2   | 85.2   | 84.2   |
| 50°   | 195.4  | 177.4  | 142.3  | 112.2  | 92.2   | 84.2   | 88.2   | 75.2   | 70.1   | 66.1   | 64.1   |
| 52.5° | 181.4  | 164.3  | 126.3  | 97.2   | 77.2   | 66.1   | 67.1   | 59.1   | 54.1   | 51.1   | 50.1   |
| 55°   | 170.4  | 153.3  | 113.2  | 85.2   | 68.1   | 54.1   | 48.1   | 46.1   | 43.1   | 41.1   | 40.1   |
| 57.5° | 155.3  | 139.3  | 100.2  | 72.1   | 58.1   | 44.1   | 37.1   | 37.1   | 36.1   | 34.1   | 33.1   |
| 59°   | 146.3  | 132.3  | 92.2   | 65.1   | 53.1   | 38.1   | 33.1   | 34.1   | 33.1   | 31.1   | 30.1   |
| 60°   | 139.3  | 126.3  | 86.2   | 60.1   | 50.1   | 35.1   | 30.1   | 32.1   | 31.1   | 29.1   | 28.1   |
| 62.5° | 123.3  | 114.2  | 74.2   | 50.1   | 44.1   | 28.1   | 25.1   | 27.1   | 27.1   | 26.1   | 25.1   |
| 65°   | 108.2  | 98.2   | 63.1   | 42.1   | 41.1   | 24.0   | 20.0   | 24.0   | 25.1   | 23.0   | 21.0   |
| 67.5° | 94.2   | 84.2   | 55.1   | 34.1   | 38.1   | 19.0   | 15.0   | 20.0   | 27.1   | 21.0   | 19.0   |
| 70°   | 80.2   | 70.1   | 43.1   | 27.1   | 40.1   | 13.0   | 12.0   | 18.0   | 32.1   | 23.0   | 18.0   |
| 72.5° | 62.1   | 54.1   | 30.1   | 20.0   | 43.1   | 9.0    | 9.0    | 15.0   | 36.1   | 25.1   | 17.0   |
| 75°   | 43.1   | 35.1   | 18.0   | 12.0   | 35.1   | 6.0    | 6.0    | 14.0   | 34.1   | 23.0   | 16.0   |
| 77.5° | 25.1   | 19.0   | 6.0    | 1.0    | 18.0   | 0.0    | 1.0    | 10.0   | 24.0   | 14.0   | 7.0    |
| 80°   | 9.0    | 4.0    | 0.0    | 0.0    | 11.0   | 0.0    | 0.0    | 0.0    | 2.0    | 0.0    | 0.0    |
| 82.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |





REPORT NUMBER: P324488

CATALOG NUMBER: GLEON-SA4C-740-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 185°   | 195°   | 205°   | 215°   | 225°   | 235°   | 245°   | 255°   | 265°    | 270°    | 275°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|---------|---------|---------|
| 0°    | 6890.2 | 6890.2 | 6890.2 | 6890.2 | 6890.2 | 6890.2 | 6890.2 | 6890.2 | 6890.2  | 6890.2  | 6890.2  |
| 2.5°  | 5847.1 | 5982.4 | 6103.6 | 6287.0 | 6504.4 | 6754.9 | 6970.4 | 7201.9 | 7419.3  | 7509.5  | 7571.6  |
| 5°    | 4480.2 | 4647.6 | 4843.0 | 5112.6 | 5471.3 | 5913.2 | 6327.1 | 6795.0 | 7298.1  | 7549.6  | 7786.1  |
| 7.5°  | 3167.5 | 3337.9 | 3580.4 | 3867.0 | 4300.9 | 4827.0 | 5368.1 | 6014.4 | 6695.8  | 7093.6  | 7485.5  |
| 10°   | 2277.7 | 2487.1 | 2713.6 | 3105.4 | 3546.3 | 4045.4 | 4602.5 | 5324.0 | 6083.6  | 6524.5  | 6996.4  |
| 12.5° | 1550.2 | 1788.7 | 2131.4 | 2570.3 | 3088.4 | 3577.4 | 4061.4 | 4749.8 | 5631.6  | 6068.5  | 6574.6  |
| 15°   | 929.9  | 1062.2 | 1424.9 | 1933.0 | 2568.3 | 3177.6 | 3707.7 | 4398.1 | 5338.0  | 5873.1  | 6399.2  |
| 17.5° | 573.2  | 634.3  | 831.7  | 1248.6 | 1916.0 | 2686.5 | 3413.0 | 4278.8 | 5380.1  | 6031.5  | 6594.6  |
| 20°   | 456.9  | 481.0  | 544.1  | 737.5  | 1269.6 | 2145.4 | 3081.4 | 4254.8 | 5723.8  | 6525.5  | 7129.7  |
| 22.5° | 396.8  | 419.9  | 462.0  | 536.1  | 798.6  | 1606.3 | 2766.7 | 4276.8 | 6216.8  | 7266.0  | 7971.5  |
| 25°   | 349.7  | 369.8  | 409.8  | 471.0  | 585.2  | 1131.3 | 2430.0 | 4375.0 | 6859.2  | 8184.9  | 8934.4  |
| 27.5° | 312.6  | 329.7  | 366.8  | 422.9  | 502.0  | 789.6  | 2048.2 | 4494.3 | 7620.7  | 9124.8  | 9864.4  |
| 30°   | 278.6  | 293.6  | 326.7  | 378.8  | 435.9  | 607.3  | 1629.4 | 4575.4 | 8383.3  | 9864.4  | 10528.7 |
| 32.5° | 249.5  | 260.5  | 290.6  | 334.7  | 378.8  | 484.0  | 1238.6 | 4562.4 | 8949.5  | 10479.6 | 11006.7 |
| 35°   | 219.5  | 230.5  | 256.5  | 294.6  | 329.7  | 399.8  | 974.0  | 4318.9 | 9442.5  | 11118.0 | 11553.9 |
| 37.5° | 186.4  | 200.4  | 225.5  | 259.5  | 283.6  | 351.7  | 787.6  | 4025.3 | 9942.5  | 11847.5 | 12164.1 |
| 40°   | 158.3  | 172.4  | 194.4  | 231.5  | 246.5  | 333.7  | 605.2  | 3667.6 | 10504.7 | 12663.1 | 12833.5 |
| 42.5° | 131.3  | 144.3  | 167.3  | 199.4  | 232.5  | 287.6  | 447.9  | 3258.7 | 11044.8 | 13360.6 | 13443.8 |
| 45°   | 106.2  | 119.2  | 143.3  | 175.4  | 248.5  | 238.5  | 346.7  | 2820.8 | 11480.7 | 13940.8 | 13967.8 |
| 47.5° | 84.2   | 96.2   | 121.3  | 165.3  | 231.5  | 190.4  | 247.5  | 2477.1 | 11846.5 | 14393.7 | 14322.6 |
| 50°   | 65.1   | 75.2   | 101.2  | 189.4  | 202.4  | 157.3  | 187.4  | 2362.9 | 12174.1 | 14674.3 | 14489.9 |
| 52.5° | 51.1   | 60.1   | 83.2   | 177.4  | 157.3  | 130.3  | 157.3  | 2470.1 | 12623.1 | 14906.8 | 14584.1 |
| 55°   | 41.1   | 50.1   | 65.1   | 101.2  | 107.2  | 110.2  | 134.3  | 2570.3 | 13397.7 | 15451.9 | 15140.3 |
| 57.5° | 34.1   | 43.1   | 53.1   | 71.1   | 81.2   | 93.2   | 119.2  | 2581.3 | 14310.5 | 16357.8 | 16063.2 |
| 59°   | 31.1   | 39.1   | 48.1   | 63.1   | 71.1   | 85.2   | 112.2  | 2521.2 | 14632.2 | 16687.5 | 16540.1 |
| 60°   | 29.1   | 37.1   | 45.1   | 58.1   | 66.1   | 80.2   | 108.2  | 2464.1 | 14646.2 | 16675.4 | 16743.6 |
| 62.5° | 25.1   | 33.1   | 40.1   | 49.1   | 56.1   | 68.1   | 97.2   | 2252.7 | 14053.0 | 16129.3 | 16621.3 |
| 65°   | 22.0   | 29.1   | 36.1   | 42.1   | 48.1   | 61.1   | 88.2   | 1866.9 | 13039.9 | 15248.5 | 15784.6 |
| 67.5° | 20.0   | 25.1   | 33.1   | 37.1   | 43.1   | 54.1   | 78.2   | 1330.7 | 11774.3 | 14171.3 | 14519.0 |
| 70°   | 18.0   | 24.0   | 30.1   | 34.1   | 39.1   | 47.1   | 67.1   | 764.6  | 9942.5  | 12594.0 | 12841.5 |
| 72.5° | 17.0   | 23.0   | 27.1   | 32.1   | 35.1   | 42.1   | 61.1   | 359.7  | 7280.0  | 10088.8 | 10735.2 |
| 75°   | 15.0   | 21.0   | 25.1   | 30.1   | 33.1   | 38.1   | 52.1   | 172.4  | 4842.0  | 7301.1  | 8035.6  |
| 77.5° | 9.0    | 17.0   | 23.0   | 27.1   | 29.1   | 33.1   | 43.1   | 99.2   | 3090.4  | 5053.4  | 5952.3  |
| 80°   | 0.0    | 6.0    | 17.0   | 23.0   | 25.1   | 28.1   | 33.1   | 78.2   | 1653.4  | 2887.0  | 3465.2  |
| 82.5° | 0.0    | 0.0    | 12.0   | 18.0   | 17.0   | 19.0   | 25.1   | 49.1   | 745.5   | 1886.9  | 2126.4  |
| 85°   | 0.0    | 0.0    | 4.0    | 14.0   | 12.0   | 9.0    | 17.0   | 17.0   | 163.3   | 955.0   | 1191.5  |
| 87.5° | 0.0    | 0.0    | 0.0    | 1.0    | 6.0    | 4.0    | 7.0    | 2.0    | 1.0     | 71.1    | 288.6   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P324488

CATALOG NUMBER: GLEON-SA4C-740-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 285°    | 295°    | 305°    | 315°    | 325°    | 335°    | 345°    | 355°    | 359°    | 360°    |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 6890.2  | 6890.2  | 6890.2  | 6890.2  | 6890.2  | 6890.2  | 6890.2  | 6890.2  | 6890.2  | 6890.2  |
| 2.5°  | 7789.1  | 7863.2  | 7988.5  | 8047.6  | 8018.6  | 7895.3  | 7748.0  | 7597.7  | 7509.5  | 7544.6  |
| 5°    | 8268.1  | 8649.9  | 8870.3  | 8943.5  | 8821.2  | 8544.6  | 8182.9  | 7705.9  | 7536.6  | 7490.5  |
| 7.5°  | 8268.1  | 8986.6  | 9441.5  | 9521.7  | 9249.1  | 8707.0  | 8028.6  | 7284.0  | 7036.5  | 6946.3  |
| 10°   | 7977.5  | 8955.5  | 9589.8  | 9717.1  | 9336.3  | 8525.6  | 7616.7  | 6767.0  | 6473.4  | 6380.2  |
| 12.5° | 7649.8  | 8703.0  | 9371.3  | 9546.7  | 9234.1  | 8345.2  | 7331.1  | 6417.2  | 6071.5  | 5990.4  |
| 15°   | 7448.4  | 8392.3  | 8945.5  | 9072.7  | 8940.5  | 8240.0  | 7263.0  | 6312.0  | 5905.2  | 5827.0  |
| 17.5° | 7520.5  | 8151.8  | 8351.2  | 8425.4  | 8514.6  | 8202.9  | 7448.4  | 6542.5  | 6027.4  | 5953.3  |
| 20°   | 7792.1  | 7898.3  | 7795.1  | 7888.3  | 8128.8  | 8239.0  | 7890.3  | 7099.7  | 6481.4  | 6382.2  |
| 22.5° | 8253.0  | 7767.0  | 7477.4  | 7514.5  | 7807.1  | 8358.3  | 8565.7  | 7895.3  | 7181.8  | 7057.6  |
| 25°   | 8790.1  | 7873.3  | 7301.1  | 7268.0  | 7568.6  | 8515.6  | 9183.0  | 8761.1  | 8010.5  | 7873.3  |
| 27.5° | 9465.5  | 8111.7  | 7265.0  | 7231.9  | 7485.5  | 8662.9  | 9696.0  | 9616.9  | 8883.3  | 8648.9  |
| 30°   | 9986.6  | 8346.2  | 7372.2  | 7296.1  | 7568.6  | 8765.1  | 10107.9 | 10343.4 | 9578.8  | 9423.5  |
| 32.5° | 10360.4 | 8622.8  | 7546.6  | 7436.4  | 7803.1  | 8941.5  | 10425.5 | 11008.7 | 10222.1 | 9986.6  |
| 35°   | 10645.0 | 8923.4  | 7828.2  | 7646.8  | 8125.8  | 9209.0  | 10723.1 | 11717.2 | 10906.5 | 10649.0 |
| 37.5° | 10911.5 | 9345.3  | 8268.1  | 8051.6  | 8631.8  | 9639.9  | 11037.8 | 12520.8 | 11672.1 | 11364.5 |
| 40°   | 11283.3 | 9823.3  | 8946.5  | 8754.1  | 9482.6  | 10227.1 | 11430.6 | 13358.6 | 12542.9 | 12156.1 |
| 42.5° | 11655.1 | 10336.3 | 9640.9  | 9693.0  | 10543.8 | 10940.6 | 11937.6 | 14244.4 | 13402.7 | 12989.8 |
| 45°   | 11994.8 | 10865.4 | 10629.9 | 10870.4 | 11528.8 | 11723.2 | 12441.7 | 14756.5 | 14089.1 | 13690.3 |
| 47.5° | 12297.4 | 11526.8 | 11613.0 | 12253.3 | 12649.1 | 12431.7 | 12818.5 | 15198.4 | 14600.1 | 14248.4 |
| 50°   | 12649.1 | 12382.6 | 12908.6 | 13814.5 | 13938.8 | 13073.0 | 13161.2 | 15721.5 | 15197.4 | 14914.8 |
| 52.5° | 13033.9 | 13284.4 | 14343.6 | 15142.3 | 15102.2 | 13769.4 | 13505.9 | 16307.7 | 16016.1 | 15750.5 |
| 55°   | 13470.8 | 14012.9 | 15607.2 | 16384.8 | 16350.8 | 14547.0 | 14077.1 | 17032.2 | 17042.2 | 16801.7 |
| 57.5° | 14119.1 | 14640.2 | 16465.0 | 17389.9 | 17447.0 | 15444.9 | 15045.1 | 17843.8 | 17970.1 | 17809.8 |
| 59°   | 14584.1 | 15047.1 | 16804.7 | 17809.8 | 18042.2 | 16139.3 | 15752.5 | 18314.8 | 18231.6 | 18085.3 |
| 60°   | 14928.8 | 15305.6 | 16973.0 | 18029.2 | 18388.0 | 16610.3 | 16274.6 | 18591.4 | 18262.7 | 18085.3 |
| 62.5° | 15781.6 | 15868.8 | 17276.7 | 18277.7 | 18785.8 | 17656.5 | 17743.6 | 19062.4 | 18047.3 | 17757.7 |
| 65°   | 16179.4 | 16224.5 | 17272.7 | 17832.8 | 18401.0 | 18471.1 | 19076.4 | 19076.4 | 17521.2 | 17076.3 |
| 67.5° | 16013.1 | 15795.6 | 16415.9 | 16357.8 | 16924.9 | 17987.1 | 19577.4 | 18376.9 | 16515.1 | 15939.9 |
| 70°   | 14660.3 | 13823.5 | 13548.0 | 13573.0 | 14006.9 | 15645.3 | 18585.4 | 16318.7 | 14611.2 | 13938.8 |
| 72.5° | 12198.2 | 10191.0 | 9510.6  | 10287.2 | 10400.5 | 12023.8 | 15838.7 | 12289.4 | 10775.2 | 10144.9 |
| 75°   | 9811.3  | 7183.8  | 6077.5  | 6897.2  | 7089.6  | 8799.2  | 12252.3 | 7653.8  | 6294.0  | 5803.0  |
| 77.5° | 7048.6  | 5156.6  | 4361.0  | 4303.9  | 4552.4  | 5580.5  | 8693.9  | 3852.0  | 3212.6  | 2998.2  |
| 80°   | 4004.3  | 3394.0  | 3654.5  | 3448.1  | 3573.4  | 3489.2  | 4130.5  | 1689.5  | 1383.9  | 1293.7  |
| 82.5° | 2417.0  | 2006.1  | 2172.5  | 1808.7  | 2288.7  | 1993.1  | 1591.3  | 541.1   | 470.0   | 446.9   |
| 85°   | 1572.2  | 1096.3  | 571.2   | 382.8   | 788.6   | 1273.6  | 355.7   | 147.3   | 113.2   | 90.2    |
| 87.5° | 542.1   | 279.6   | 28.1    | 12.0    | 84.2    | 237.5   | 13.0    | 0.0     | 0.0     | 0.0     |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINIAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021

**Test Information**

Test Method: LM-79-08  
 Report Number: SP1-2101-121-2  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry: 4π  
 Issue Date: 03/05/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**  
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

**Spectral Parameters**

|                           |         |           |      |      |       |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K):                  | 3905    | CRI (Ra): | 71.2 | R9:  | -29.7 |
| CIE u':                   | 0.2273  | R1:       | 68.9 | R10: | 46.2  |
| CIE v':                   | 0.5024  | R2:       | 77.0 | R11: | 68.8  |
| Duv:                      | -0.0008 | R3:       | 84.0 | R12: | 45.6  |
| CIE x:                    | 0.3841  | R4:       | 71.6 | R13: | 69.5  |
| CIE y:                    | 0.3774  | R5:       | 68.9 | R14: | 90.7  |
| CIE z:                    | 0.2385  | R6:       | 68.3 |      |       |
| Peak Wavelength (nm):     | 443     | R7:       | 78.7 |      |       |
| Dominant Wavelength (nm): | 579     | R8:       | 52.2 |      |       |
| Purity:                   | 28.7    |           |      |      |       |
| Rf:                       | 71.7    |           |      |      |       |
| Rg:                       | 96.9    |           |      |      |       |



**Test Conditions**

Stabilization Time: 211M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.8/312%  
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2101-121-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

**Photopic Flux vs. Wavelength**




#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 2.7           | 620    | 97577         | 25.4          | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 4.8           | 625    | 90158         | 19.9          | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 8.0           | 630    | 82240         | 14.9          | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 13.3          | 635    | 74361         | 11.2          | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 20.2          | 640    | 66994         | 8.0           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 28.5          | 645    | 60405         | 5.8           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 37.4          | 650    | 53806         | 3.9           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 44.9          | 655    | 47610         | 2.7           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 52.6          | 660    | 42018         | 1.8           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.0           | 535    | 94097         | 58.4          | 665    | 36742         | 1.2           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.0           | 540    | 96845         | 63.1          | 670    | 32105         | 0.7           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.0           | 545    | 100829        | 67.1          | 675    | 27946         | 0.5           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 0.1           | 550    | 105648        | 71.8          | 680    | 24146         | 0.3           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 0.2           | 555    | 110017        | 75.1          | 685    | 21191         | 0.2           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 0.5           | 560    | 114586        | 77.9          | 690    | 18544         | 0.1           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 1.2           | 565    | 118987        | 79.1          | 695    | 16058         | 0.1           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 2.1           | 570    | 122326        | 79.5          | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 2.9           | 575    | 125968        | 78.4          | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 2.7           | 580    | 127613        | 75.8          | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 2.0           | 585    | 129466        | 71.9          | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 1.5           | 590    | 128813        | 66.6          | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 1.3           | 595    | 126387        | 59.9          | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 1.0           | 600    | 123477        | 53.2          | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 1.1           | 605    | 118718        | 46.0          | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 1.2           | 610    | 112091        | 38.5          | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 1.7           | 615    | 105039        | 31.7          | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

REPORT NUMBER: SP1-2101-121-2

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 10425.8 S/P: 1.47**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 29.3          | 620    | 97577         | 1.2           | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 43.0          | 625    | 90158         | 0.8           | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 60.8          | 630    | 82240         | 0.5           | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 81.1          | 635    | 74361         | 0.3           | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 99.6          | 640    | 66994         | 0.2           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 113.9         | 645    | 60405         | 0.1           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 122.6         | 650    | 53806         | 0.1           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 125.0         | 655    | 47610         | 0.0           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 123.1         | 660    | 42018         | 0.0           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.1           | 535    | 94097         | 117.3         | 665    | 36742         | 0.0           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.2           | 540    | 96845         | 107.0         | 670    | 32105         | 0.0           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.9           | 545    | 100829        | 96.7          | 675    | 27946         | 0.0           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 3.0           | 550    | 105648        | 86.4          | 680    | 24146         | 0.0           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 9.3           | 555    | 110017        | 75.2          | 685    | 21191         | 0.0           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 23.0          | 560    | 114586        | 64.0          | 690    | 18544         | 0.0           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 45.7          | 565    | 118987        | 53.4          | 695    | 16058         | 0.0           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 75.5          | 570    | 122326        | 43.2          | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 93.8          | 575    | 125968        | 34.3          | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 79.3          | 580    | 127613        | 26.3          | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 51.3          | 585    | 129466        | 19.8          | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 35.6          | 590    | 128813        | 14.3          | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 26.0          | 595    | 126387        | 10.1          | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 19.3          | 600    | 123477        | 7.0           | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 16.8          | 605    | 118718        | 4.7           | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 17.7          | 610    | 112091        | 3.0           | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 21.4          | 615    | 105039        | 1.9           | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |



REPORT NUMBER: SP1-2101-121-2

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 3927.2 M/P: 0.55**


| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 15.8          | 620    | 97577         | 0.1           | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 22.0          | 625    | 90158         | 0.0           | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 29.2          | 630    | 82240         | 0.0           | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 36.6          | 635    | 74361         | 0.0           | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 42.2          | 640    | 66994         | 0.0           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 44.9          | 645    | 60405         | 0.0           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 44.9          | 650    | 53806         | 0.0           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 42.4          | 655    | 47610         | 0.0           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 38.6          | 660    | 42018         | 0.0           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.0           | 535    | 94097         | 33.9          | 665    | 36742         | 0.0           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.2           | 540    | 96845         | 28.3          | 670    | 32105         | 0.0           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.6           | 545    | 100829        | 23.4          | 675    | 27946         | 0.0           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 2.1           | 550    | 105648        | 19.0          | 680    | 24146         | 0.0           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 5.9           | 555    | 110017        | 14.8          | 685    | 21191         | 0.0           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 14.3          | 560    | 114586        | 11.3          | 690    | 18544         | 0.0           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 27.3          | 565    | 118987        | 8.4           | 695    | 16058         | 0.0           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 45.1          | 570    | 122326        | 6.0           | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 55.3          | 575    | 125968        | 4.2           | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 47.2          | 580    | 127613        | 2.9           | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 30.8          | 585    | 129466        | 1.9           | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 21.7          | 590    | 128813        | 1.3           | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 16.1          | 595    | 126387        | 0.8           | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 12.0          | 600    | 123477        | 0.5           | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 10.3          | 605    | 118718        | 0.3           | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 10.5          | 610    | 112091        | 0.2           | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 12.1          | 615    | 105039        | 0.1           | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

**Summary**

$R_f = 71.7$   
 $R_g = 96.9$   
 CIE  $R_a = 71.2$   
 $R_g = -29.7$




**Color Vector Graphics**



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)