

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P320763

Luminaire Tested: **GLEON-SA9B-827-U-SLR**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P320763
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-26)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GLEON-SA9B-827-U-SLR
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(9) 80 CRI, 2700K, 800mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 33005 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Luminous Opening: Rectangular (W 2.5' x L: 1' x H: 0')
IES Classification: Type IV - Medium
BUG Rating: B3 - U0 - G5


Input Watts (W): 374
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P320763
 CATALOG NUMBER: GLEON-SA9B-827-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 16.1 fc
 Type IV - Medium - N/A

REPORT NUMBER: P320763
CATALOG NUMBER: GLEON-SA9B-827-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 345-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P320763
 CATALOG NUMBER: GLEON-SA9B-827-U-SLR

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 5705.9 | 0.0 | 5705.9 |
| | % Fixture | 17.3 | 0.0 | 17.3 |
| Street Side | Lumens | 27299.1 | 0.0 | 27299.1 |
| | % Fixture | 82.7 | 0.0 | 82.7 |
| Total | Lumens | 33005.0 | 0.0 | 33005.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 776.0 | 2.4 |
| 10°-20° | 1612.1 | 4.9 |
| 20°-30° | 2292.8 | 6.9 |
| 30°-40° | 3303.9 | 10.0 |
| 40°-50° | 4656.2 | 14.1 |
| 50°-60° | 6472.9 | 19.6 |
| 60°-70° | 7827.6 | 23.7 |
| 70°-80° | 4811.5 | 14.6 |
| 80°-90° | 1252.0 | 3.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 33005.0 | 100.0 |
| 0°-180° | 33005.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P320763
 CATALOG NUMBER: GLEON-SA9B-827-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|----------|
| | | | B | U | G |
| FL (0°-30°) | 3295.6 | 10.0 | | | |
| FM (30°-60°) | 11932.1 | 36.2 | | | |
| FH (60°-80°) | 10976.3 | 33.3 | | | G4/12000 |
| FVH (80°-90°) | 1095.0 | 3.3 | | | G5 |
| BL (0°-30°) | 1385.3 | 4.2 | B3/2500 | | |
| BM (30°-60°) | 2500.8 | 7.6 | B3/5000 | | |
| BH (60°-80°) | 1662.8 | 5.0 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 156.9 | 0.5 | | | G2/225 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G5
 Type IV Medium





REPORT NUMBER: P320763
 CATALOG NUMBER: GLEON-SA9B-827-U-SLR

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° | 50° |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 |
| 2.5° | 10771.7 | 10676.7 | 10532.9 | 10389.1 | 10282.2 | 10174.0 | 10051.2 | 9928.5 | 9788.6 | 9647.5 | 9564.3 |
| 5° | 10593.6 | 10329.7 | 9986.6 | 9643.5 | 9416.5 | 9189.6 | 8932.2 | 8674.9 | 8420.2 | 8165.6 | 8028.3 |
| 7.5° | 9791.3 | 9395.4 | 8949.4 | 8503.4 | 8173.5 | 7842.3 | 7486.0 | 7128.4 | 6811.7 | 6493.7 | 6297.0 |
| 10° | 9002.2 | 8527.1 | 8015.1 | 7501.8 | 7079.5 | 6657.3 | 6299.7 | 5940.8 | 5701.9 | 5463.1 | 5282.3 |
| 12.5° | 8436.1 | 7909.6 | 7346.1 | 6781.3 | 6359.1 | 5936.8 | 5709.8 | 5482.9 | 5284.9 | 5087.0 | 4878.5 |
| 15° | 8211.7 | 7616.6 | 7040.0 | 6462.0 | 6078.0 | 5694.0 | 5441.9 | 5188.6 | 4923.4 | 4656.8 | 4400.8 |
| 17.5° | 8409.7 | 7712.9 | 7086.1 | 6459.3 | 5956.6 | 5453.8 | 5101.5 | 4747.8 | 4398.2 | 4048.5 | 3751.6 |
| 20° | 9027.2 | 8137.9 | 7318.4 | 6497.6 | 5828.6 | 5159.6 | 4687.1 | 4213.4 | 3764.8 | 3316.1 | 2979.6 |
| 22.5° | 9894.2 | 8717.1 | 7647.0 | 6576.8 | 5712.5 | 4846.8 | 4254.3 | 3660.5 | 3130.0 | 2599.6 | 2269.7 |
| 25° | 10947.2 | 9485.1 | 8120.7 | 6754.9 | 5665.0 | 4573.7 | 3845.3 | 3116.8 | 2557.3 | 1996.5 | 1761.6 |
| 27.5° | 12057.0 | 10400.9 | 8709.2 | 7016.2 | 5672.9 | 4329.5 | 3500.8 | 2670.8 | 2166.8 | 1662.7 | 1501.7 |
| 30° | 12982.0 | 11447.4 | 9395.4 | 7342.1 | 5703.2 | 4064.3 | 3176.2 | 2288.2 | 1872.5 | 1456.8 | 1352.6 |
| 32.5° | 13827.9 | 12177.1 | 9912.7 | 7647.0 | 5737.5 | 3826.8 | 2925.5 | 2022.9 | 1683.8 | 1343.3 | 1257.6 |
| 35° | 14701.4 | 12825.0 | 10274.3 | 7722.2 | 5678.2 | 3632.8 | 2754.0 | 1875.1 | 1562.4 | 1248.3 | 1175.7 |
| 37.5° | 15663.4 | 13525.7 | 10622.6 | 7718.2 | 5577.9 | 3437.5 | 2620.7 | 1802.5 | 1483.2 | 1162.6 | 1109.8 |
| 40° | 16736.2 | 14300.3 | 11000.0 | 7699.8 | 5486.8 | 3272.6 | 2521.7 | 1769.6 | 1439.7 | 1108.4 | 1063.6 |
| 42.5° | 17785.3 | 15039.3 | 11351.0 | 7662.8 | 5412.9 | 3161.7 | 2424.1 | 1686.4 | 1400.1 | 1112.4 | 1049.1 |
| 45° | 18573.1 | 15684.5 | 11655.9 | 7625.9 | 5357.5 | 3089.1 | 2347.5 | 1605.9 | 1363.1 | 1120.3 | 1039.8 |
| 47.5° | 19170.9 | 16332.4 | 11993.7 | 7653.6 | 5352.2 | 3050.9 | 2293.4 | 1536.0 | 1293.2 | 1049.1 | 1016.1 |
| 50° | 19930.9 | 17111.0 | 12485.9 | 7860.7 | 5424.8 | 2988.8 | 2230.1 | 1470.0 | 1225.9 | 981.8 | 1026.6 |
| 52.5° | 20877.1 | 18222.1 | 13248.6 | 8273.8 | 5576.5 | 2879.3 | 2129.8 | 1380.3 | 1144.1 | 906.6 | 976.5 |
| 55° | 22266.6 | 19645.9 | 14223.8 | 8800.3 | 5760.0 | 2718.3 | 1978.1 | 1236.4 | 1035.9 | 834.0 | 896.0 |
| 57.5° | 23513.6 | 21084.3 | 15159.3 | 9233.1 | 5874.8 | 2515.1 | 1786.7 | 1058.3 | 914.5 | 770.6 | 806.3 |
| 60° | 24069.1 | 21825.9 | 15597.4 | 9367.7 | 5806.2 | 2244.6 | 1571.6 | 897.3 | 807.6 | 717.9 | 711.3 |
| 62.5° | 23852.7 | 21354.8 | 15165.9 | 8977.1 | 5471.0 | 1964.9 | 1381.6 | 798.3 | 731.0 | 662.4 | 647.9 |
| 65° | 23219.3 | 19874.2 | 13957.2 | 8040.2 | 4904.9 | 1769.6 | 1261.5 | 753.5 | 678.3 | 603.0 | 587.2 |
| 67.5° | 21971.0 | 17766.8 | 12244.4 | 6721.9 | 4185.7 | 1649.5 | 1192.9 | 736.3 | 645.3 | 552.9 | 534.4 |
| 70° | 19730.4 | 15230.6 | 10271.6 | 5311.3 | 3444.1 | 1575.6 | 1148.0 | 720.5 | 609.6 | 497.5 | 480.3 |
| 72.5° | 16205.8 | 12211.4 | 8202.5 | 4192.3 | 2879.3 | 1566.3 | 1142.8 | 719.2 | 580.6 | 442.1 | 426.2 |
| 75° | 11603.1 | 9275.3 | 6261.4 | 3246.2 | 2358.1 | 1470.0 | 1084.7 | 699.4 | 541.0 | 381.4 | 366.8 |
| 77.5° | 7808.0 | 6419.8 | 4352.0 | 2282.9 | 1749.8 | 1216.7 | 911.8 | 607.0 | 463.2 | 319.3 | 304.8 |
| 80° | 5014.4 | 4443.0 | 2916.3 | 1389.5 | 1134.8 | 880.2 | 651.9 | 423.6 | 337.8 | 250.7 | 238.8 |
| 82.5° | 3679.0 | 3306.9 | 2026.9 | 746.9 | 630.8 | 513.3 | 398.5 | 283.7 | 230.9 | 178.1 | 172.9 |
| 85° | 2338.3 | 2578.5 | 1492.4 | 406.4 | 332.5 | 258.6 | 213.8 | 168.9 | 133.3 | 97.6 | 97.6 |
| 87.5° | 453.9 | 628.1 | 413.0 | 196.6 | 143.8 | 91.1 | 77.9 | 63.3 | 35.6 | 6.6 | 7.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P320763
 CATALOG NUMBER: GLEON-SA9B-827-U-SLR

CANDELA DISTRIBUTION (continued):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° | 50° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P320763
 CATALOG NUMBER: GLEON-SA9B-827-U-SLR

CANDELA DISTRIBUTION (continued):

| | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° | 105° |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 |
| 2.5° | 9479.9 | 9388.8 | 9297.8 | 9194.8 | 9090.6 | 8994.3 | 8896.6 | 8789.7 | 8809.5 | 8727.7 | 8645.9 |
| 5° | 7891.1 | 7745.9 | 7599.5 | 7472.8 | 7346.1 | 7236.6 | 7125.7 | 7026.8 | 7112.5 | 7054.5 | 6996.4 |
| 7.5° | 6099.1 | 5919.6 | 5738.9 | 5587.1 | 5435.4 | 5317.9 | 5199.1 | 5117.3 | 5201.8 | 5191.2 | 5180.7 |
| 10° | 5101.5 | 4927.3 | 4751.8 | 4584.2 | 4416.6 | 4274.1 | 4130.3 | 4008.9 | 3987.8 | 3927.1 | 3865.1 |
| 12.5° | 4668.7 | 4429.8 | 4189.7 | 4014.2 | 3838.7 | 3668.4 | 3498.2 | 3355.7 | 3291.0 | 3190.7 | 3089.1 |
| 15° | 4144.8 | 3862.4 | 3580.0 | 3380.8 | 3180.2 | 3015.2 | 2849.0 | 2726.3 | 2685.3 | 2607.5 | 2529.6 |
| 17.5° | 3454.7 | 3145.9 | 2837.1 | 2635.2 | 2432.0 | 2300.0 | 2166.8 | 2084.9 | 2084.9 | 2062.5 | 2040.1 |
| 20° | 2643.1 | 2367.3 | 2091.5 | 1937.1 | 1782.8 | 1712.8 | 1641.6 | 1607.2 | 1617.8 | 1619.1 | 1619.1 |
| 22.5° | 1938.5 | 1769.6 | 1600.7 | 1538.6 | 1475.3 | 1450.2 | 1425.1 | 1410.6 | 1415.9 | 1417.2 | 1418.5 |
| 25° | 1526.8 | 1462.1 | 1396.1 | 1364.4 | 1331.5 | 1315.6 | 1299.8 | 1294.5 | 1306.4 | 1307.7 | 1307.7 |
| 27.5° | 1340.7 | 1301.1 | 1260.2 | 1240.4 | 1219.3 | 1212.7 | 1206.1 | 1196.9 | 1208.7 | 1208.7 | 1207.4 |
| 30° | 1247.0 | 1204.8 | 1162.6 | 1137.5 | 1112.4 | 1115.0 | 1116.4 | 1113.7 | 1121.6 | 1126.9 | 1130.9 |
| 32.5° | 1170.5 | 1129.6 | 1088.7 | 1063.6 | 1037.2 | 1033.2 | 1029.3 | 1026.6 | 1043.8 | 1053.0 | 1062.3 |
| 35° | 1101.8 | 1057.0 | 1012.1 | 988.4 | 964.6 | 955.4 | 946.1 | 939.5 | 955.4 | 967.3 | 979.1 |
| 37.5° | 1055.7 | 1009.5 | 962.0 | 939.5 | 915.8 | 903.9 | 892.0 | 884.1 | 890.7 | 896.0 | 901.3 |
| 40° | 1018.7 | 971.2 | 922.4 | 896.0 | 869.6 | 857.7 | 845.9 | 839.3 | 843.2 | 844.5 | 845.9 |
| 42.5° | 984.4 | 938.2 | 892.0 | 863.0 | 832.7 | 818.1 | 803.6 | 795.7 | 798.3 | 801.0 | 802.3 |
| 45° | 959.3 | 913.1 | 865.6 | 831.3 | 795.7 | 779.9 | 764.0 | 754.8 | 756.1 | 756.1 | 756.1 |
| 47.5° | 983.1 | 915.8 | 847.2 | 807.6 | 766.7 | 748.2 | 729.7 | 720.5 | 717.9 | 715.2 | 712.6 |
| 50° | 1070.2 | 955.4 | 839.3 | 789.1 | 737.6 | 717.9 | 696.7 | 686.2 | 679.6 | 676.9 | 674.3 |
| 52.5° | 1045.1 | 946.1 | 845.9 | 781.2 | 715.2 | 691.5 | 667.7 | 650.6 | 644.0 | 640.0 | 636.0 |
| 55° | 956.7 | 894.7 | 831.3 | 753.5 | 675.6 | 654.5 | 632.1 | 620.2 | 608.3 | 605.7 | 603.0 |
| 57.5° | 840.6 | 815.5 | 790.4 | 711.3 | 632.1 | 612.3 | 591.2 | 583.3 | 572.7 | 572.7 | 571.4 |
| 60° | 703.3 | 740.3 | 777.2 | 686.2 | 593.8 | 571.4 | 548.9 | 542.3 | 538.4 | 537.1 | 535.7 |
| 62.5° | 632.1 | 692.8 | 752.2 | 655.8 | 558.2 | 534.4 | 510.7 | 502.8 | 501.4 | 502.8 | 502.8 |
| 65° | 571.4 | 589.9 | 608.3 | 563.5 | 518.6 | 494.8 | 469.8 | 461.9 | 464.5 | 468.5 | 472.4 |
| 67.5° | 516.0 | 512.0 | 508.0 | 492.2 | 475.0 | 455.3 | 434.1 | 426.2 | 427.5 | 432.8 | 438.1 |
| 70° | 463.2 | 457.9 | 451.3 | 439.4 | 427.5 | 410.4 | 393.2 | 388.0 | 386.6 | 393.2 | 398.5 |
| 72.5° | 410.4 | 403.8 | 395.9 | 386.6 | 376.1 | 361.6 | 347.0 | 343.1 | 344.4 | 348.4 | 352.3 |
| 75° | 352.3 | 347.0 | 340.5 | 332.5 | 323.3 | 310.1 | 296.9 | 294.3 | 296.9 | 300.9 | 304.8 |
| 77.5° | 289.0 | 287.7 | 285.0 | 278.4 | 271.8 | 257.3 | 241.5 | 240.2 | 244.1 | 248.1 | 250.7 |
| 80° | 225.6 | 227.0 | 228.3 | 223.0 | 217.7 | 201.9 | 184.7 | 183.4 | 187.4 | 191.3 | 195.3 |
| 82.5° | 166.3 | 170.2 | 172.9 | 166.3 | 159.7 | 141.2 | 122.7 | 120.1 | 133.3 | 137.2 | 141.2 |
| 85° | 96.3 | 101.6 | 106.9 | 101.6 | 96.3 | 77.9 | 59.4 | 58.1 | 69.9 | 76.5 | 83.1 |
| 87.5° | 7.9 | 10.6 | 13.2 | 11.9 | 10.6 | 5.3 | 0.0 | 0.0 | 1.3 | 6.6 | 11.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P320763
 CATALOG NUMBER: GLEON-SA9B-827-U-SLR

CANDELA DISTRIBUTION (continued):

| | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° | 105° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P320763
 CATALOG NUMBER: GLEON-SA9B-827-U-SLR

CANDELA DISTRIBUTION (continued):

| | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° | 160° |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 |
| 2.5° | 8594.4 | 8543.0 | 8527.1 | 8511.3 | 8453.2 | 8393.9 | 8454.6 | 8513.9 | 8539.0 | 8564.1 | 8499.4 |
| 5° | 6988.5 | 6979.3 | 6979.3 | 6977.9 | 6925.2 | 6871.1 | 6912.0 | 6951.5 | 6863.1 | 6774.7 | 6765.5 |
| 7.5° | 5237.4 | 5294.2 | 5340.3 | 5385.2 | 5368.1 | 5350.9 | 5389.2 | 5427.4 | 5315.3 | 5201.8 | 5146.4 |
| 10° | 3878.2 | 3890.1 | 3940.3 | 3990.4 | 4002.3 | 4012.8 | 4060.3 | 4106.5 | 4019.4 | 3932.3 | 3894.1 |
| 12.5° | 3025.8 | 2962.5 | 2969.1 | 2974.3 | 2998.1 | 3020.5 | 3070.7 | 3119.5 | 3083.9 | 3046.9 | 3050.9 |
| 15° | 2450.5 | 2370.0 | 2337.0 | 2302.7 | 2329.1 | 2355.5 | 2391.1 | 2425.4 | 2426.7 | 2426.7 | 2461.0 |
| 17.5° | 2000.5 | 1959.6 | 1926.6 | 1892.3 | 1927.9 | 1962.2 | 1966.2 | 1970.1 | 1971.5 | 1972.8 | 1970.1 |
| 20° | 1638.9 | 1658.7 | 1648.2 | 1637.6 | 1650.8 | 1662.7 | 1673.2 | 1682.5 | 1670.6 | 1657.4 | 1624.4 |
| 22.5° | 1437.0 | 1454.2 | 1467.4 | 1479.2 | 1501.7 | 1522.8 | 1512.2 | 1500.4 | 1476.6 | 1451.5 | 1426.5 |
| 25° | 1319.6 | 1331.5 | 1344.7 | 1357.8 | 1376.3 | 1393.5 | 1375.0 | 1356.5 | 1339.4 | 1322.2 | 1305.1 |
| 27.5° | 1220.6 | 1232.5 | 1244.4 | 1254.9 | 1272.1 | 1287.9 | 1270.8 | 1253.6 | 1239.1 | 1224.6 | 1211.4 |
| 30° | 1140.1 | 1148.0 | 1157.3 | 1166.5 | 1182.3 | 1196.9 | 1182.3 | 1166.5 | 1156.0 | 1144.1 | 1134.8 |
| 32.5° | 1071.5 | 1079.4 | 1083.4 | 1087.3 | 1101.8 | 1116.4 | 1105.8 | 1095.3 | 1086.0 | 1076.8 | 1070.2 |
| 35° | 996.3 | 1012.1 | 1014.8 | 1017.4 | 1031.9 | 1046.4 | 1039.8 | 1031.9 | 1021.4 | 1010.8 | 998.9 |
| 37.5° | 919.7 | 938.2 | 948.8 | 958.0 | 972.5 | 987.0 | 980.4 | 973.9 | 959.3 | 944.8 | 923.7 |
| 40° | 855.1 | 863.0 | 882.8 | 901.3 | 925.0 | 947.5 | 934.3 | 919.7 | 897.3 | 874.9 | 864.3 |
| 42.5° | 801.0 | 799.7 | 818.1 | 836.6 | 872.2 | 906.6 | 882.8 | 859.0 | 837.9 | 816.8 | 814.2 |
| 45° | 753.5 | 749.5 | 758.8 | 768.0 | 806.3 | 843.2 | 819.5 | 794.4 | 782.5 | 770.6 | 770.6 |
| 47.5° | 711.3 | 708.6 | 715.2 | 720.5 | 744.2 | 766.7 | 754.8 | 742.9 | 736.3 | 729.7 | 731.0 |
| 50° | 673.0 | 670.3 | 676.9 | 682.2 | 691.5 | 699.4 | 702.0 | 703.3 | 699.4 | 695.4 | 698.1 |
| 52.5° | 637.4 | 637.4 | 640.0 | 641.3 | 653.2 | 665.1 | 665.1 | 663.7 | 663.7 | 663.7 | 666.4 |
| 55° | 607.0 | 609.6 | 609.6 | 609.6 | 628.1 | 645.3 | 640.0 | 634.7 | 636.0 | 636.0 | 638.7 |
| 57.5° | 576.7 | 580.6 | 583.3 | 585.9 | 604.4 | 622.8 | 617.6 | 612.3 | 612.3 | 612.3 | 613.6 |
| 60° | 542.3 | 547.6 | 552.9 | 558.2 | 576.7 | 595.1 | 589.9 | 583.3 | 584.6 | 585.9 | 587.2 |
| 62.5° | 509.4 | 514.6 | 519.9 | 525.2 | 543.7 | 562.1 | 556.9 | 550.3 | 554.2 | 556.9 | 556.9 |
| 65° | 477.7 | 481.6 | 486.9 | 492.2 | 509.4 | 526.5 | 521.2 | 516.0 | 521.2 | 525.2 | 527.8 |
| 67.5° | 442.1 | 444.7 | 450.0 | 455.3 | 472.4 | 489.6 | 484.3 | 477.7 | 484.3 | 489.6 | 494.8 |
| 70° | 401.2 | 403.8 | 410.4 | 415.7 | 432.8 | 450.0 | 443.4 | 436.8 | 443.4 | 450.0 | 455.3 |
| 72.5° | 356.3 | 358.9 | 365.5 | 370.8 | 390.6 | 410.4 | 402.5 | 394.6 | 402.5 | 410.4 | 413.0 |
| 75° | 307.5 | 310.1 | 318.0 | 324.6 | 344.4 | 364.2 | 357.6 | 349.7 | 356.3 | 362.9 | 364.2 |
| 77.5° | 254.7 | 258.6 | 269.2 | 279.8 | 295.6 | 311.4 | 307.5 | 303.5 | 307.5 | 311.4 | 311.4 |
| 80° | 199.3 | 203.2 | 216.4 | 228.3 | 237.5 | 246.8 | 248.1 | 249.4 | 250.7 | 252.0 | 250.7 |
| 82.5° | 147.8 | 153.1 | 164.9 | 176.8 | 176.8 | 176.8 | 187.4 | 196.6 | 196.6 | 195.3 | 194.0 |
| 85° | 91.1 | 97.6 | 108.2 | 118.8 | 112.2 | 105.6 | 122.7 | 138.6 | 138.6 | 137.2 | 134.6 |
| 87.5° | 18.5 | 25.1 | 35.6 | 44.9 | 38.3 | 31.7 | 48.8 | 66.0 | 67.3 | 67.3 | 64.7 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P320763
 CATALOG NUMBER: GLEON-SA9B-827-U-SLR

CANDELA DISTRIBUTION (continued):

| | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° | 160° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P320763

CATALOG NUMBER: GLEON-SA9B-827-U-SLR

CANDELA DISTRIBUTION (continued):

| | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° | 215° |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 |
| 2.5° | 8433.4 | 8536.4 | 8638.0 | 8664.4 | 8704.0 | 8721.1 | 8736.9 | 8866.3 | 8994.3 | 9144.7 | 9295.1 |
| 5° | 6754.9 | 6831.5 | 6908.0 | 6919.9 | 6960.8 | 6981.9 | 7003.0 | 7160.0 | 7315.8 | 7525.6 | 7735.4 |
| 7.5° | 5090.9 | 5109.4 | 5127.9 | 5125.2 | 5159.6 | 5205.7 | 5250.6 | 5418.2 | 5584.5 | 5810.1 | 6034.4 |
| 10° | 3855.8 | 3898.0 | 3938.9 | 3977.2 | 4052.4 | 4139.5 | 4225.3 | 4396.8 | 4568.4 | 4791.4 | 5013.1 |
| 12.5° | 3054.8 | 3103.7 | 3151.2 | 3193.4 | 3280.5 | 3396.6 | 3511.4 | 3717.3 | 3923.1 | 4189.7 | 4454.9 |
| 15° | 2494.0 | 2490.0 | 2486.1 | 2515.1 | 2591.7 | 2718.3 | 2843.7 | 3061.4 | 3279.2 | 3572.1 | 3863.7 |
| 17.5° | 1967.5 | 1947.7 | 1927.9 | 1950.3 | 2021.6 | 2125.8 | 2228.8 | 2413.5 | 2596.9 | 2880.6 | 3164.4 |
| 20° | 1591.4 | 1578.2 | 1565.0 | 1586.1 | 1631.0 | 1674.5 | 1718.1 | 1851.4 | 1983.3 | 2214.3 | 2443.9 |
| 22.5° | 1400.1 | 1398.8 | 1396.1 | 1408.0 | 1429.1 | 1451.5 | 1472.7 | 1537.3 | 1600.7 | 1749.8 | 1897.6 |
| 25° | 1287.9 | 1286.6 | 1285.3 | 1290.5 | 1307.7 | 1324.9 | 1342.0 | 1384.2 | 1426.5 | 1497.7 | 1569.0 |
| 27.5° | 1198.2 | 1195.5 | 1192.9 | 1194.2 | 1198.2 | 1224.6 | 1249.6 | 1269.4 | 1287.9 | 1336.7 | 1384.2 |
| 30° | 1125.6 | 1124.3 | 1123.0 | 1123.0 | 1119.0 | 1128.2 | 1137.5 | 1167.8 | 1196.9 | 1247.0 | 1297.1 |
| 32.5° | 1063.6 | 1057.0 | 1050.4 | 1035.9 | 1026.6 | 1039.8 | 1053.0 | 1084.7 | 1116.4 | 1162.6 | 1208.7 |
| 35° | 985.7 | 968.6 | 950.1 | 942.2 | 943.5 | 956.7 | 969.9 | 1001.6 | 1031.9 | 1082.1 | 1130.9 |
| 37.5° | 901.3 | 896.0 | 889.4 | 888.1 | 892.0 | 905.2 | 918.4 | 946.1 | 972.5 | 1022.7 | 1071.5 |
| 40° | 853.8 | 851.1 | 848.5 | 845.9 | 848.5 | 861.7 | 874.9 | 901.3 | 926.3 | 975.2 | 1022.7 |
| 42.5° | 811.5 | 810.2 | 808.9 | 808.9 | 810.2 | 824.7 | 839.3 | 865.6 | 890.7 | 934.3 | 977.8 |
| 45° | 770.6 | 772.0 | 772.0 | 774.6 | 778.6 | 793.1 | 806.3 | 835.3 | 864.3 | 906.6 | 948.8 |
| 47.5° | 732.4 | 736.3 | 739.0 | 745.6 | 749.5 | 765.4 | 779.9 | 811.5 | 843.2 | 896.0 | 947.5 |
| 50° | 699.4 | 703.3 | 706.0 | 711.3 | 721.8 | 740.3 | 758.8 | 797.0 | 834.0 | 922.4 | 1009.5 |
| 52.5° | 669.0 | 673.0 | 676.9 | 682.2 | 695.4 | 716.5 | 737.6 | 785.2 | 831.3 | 934.3 | 1037.2 |
| 55° | 641.3 | 645.3 | 647.9 | 655.8 | 669.0 | 687.5 | 704.7 | 762.7 | 820.8 | 896.0 | 971.2 |
| 57.5° | 614.9 | 618.9 | 621.5 | 626.8 | 633.4 | 653.2 | 671.7 | 733.7 | 795.7 | 848.5 | 900.0 |
| 60° | 587.2 | 589.9 | 591.2 | 591.2 | 596.5 | 618.9 | 641.3 | 720.5 | 798.3 | 789.1 | 778.6 |
| 62.5° | 556.9 | 559.5 | 560.8 | 556.9 | 563.5 | 587.2 | 611.0 | 713.9 | 816.8 | 753.5 | 690.1 |
| 65° | 529.2 | 527.8 | 526.5 | 522.6 | 530.5 | 554.2 | 576.7 | 628.1 | 679.6 | 654.5 | 629.4 |
| 67.5° | 498.8 | 494.8 | 490.9 | 485.6 | 493.5 | 514.6 | 534.4 | 551.6 | 568.7 | 571.4 | 574.0 |
| 70° | 460.5 | 455.3 | 450.0 | 448.7 | 452.6 | 469.8 | 486.9 | 498.8 | 509.4 | 514.6 | 518.6 |
| 72.5° | 415.7 | 411.7 | 407.8 | 405.1 | 406.4 | 420.9 | 434.1 | 444.7 | 455.3 | 459.2 | 461.9 |
| 75° | 365.5 | 365.5 | 364.2 | 356.3 | 356.3 | 368.2 | 378.7 | 388.0 | 397.2 | 402.5 | 407.8 |
| 77.5° | 311.4 | 312.7 | 312.7 | 302.2 | 300.9 | 312.7 | 323.3 | 331.2 | 337.8 | 343.1 | 347.0 |
| 80° | 249.4 | 246.8 | 244.1 | 237.5 | 234.9 | 249.4 | 262.6 | 269.2 | 274.5 | 275.8 | 275.8 |
| 82.5° | 191.3 | 186.1 | 179.5 | 164.9 | 166.3 | 182.1 | 196.6 | 201.9 | 207.2 | 207.2 | 207.2 |
| 85° | 130.6 | 120.1 | 108.2 | 96.3 | 97.6 | 114.8 | 130.6 | 135.9 | 141.2 | 143.8 | 145.2 |
| 87.5° | 62.0 | 51.5 | 39.6 | 30.4 | 30.4 | 44.9 | 58.1 | 60.7 | 63.3 | 68.6 | 73.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P320763
 CATALOG NUMBER: GLEON-SA9B-827-U-SLR

CANDELA DISTRIBUTION (continued):

| | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° | 215° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P320763
 CATALOG NUMBER: GLEON-SA9B-827-U-SLR

CANDELA DISTRIBUTION (continued):

| | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° | 270° |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 |
| 2.5° | 9409.9 | 9523.4 | 9640.9 | 9758.3 | 9892.9 | 10027.5 | 10184.5 | 10340.2 | 10473.5 | 10606.8 | 10717.6 |
| 5° | 7916.2 | 8096.9 | 8309.4 | 8521.8 | 8792.4 | 9062.9 | 9394.1 | 9724.0 | 10018.3 | 10312.5 | 10654.3 |
| 7.5° | 6270.6 | 6505.5 | 6782.6 | 7059.8 | 7409.4 | 7759.1 | 8188.0 | 8616.9 | 9032.5 | 9446.9 | 9972.1 |
| 10° | 5259.8 | 5506.6 | 5779.8 | 6051.6 | 6407.9 | 6762.8 | 7216.8 | 7669.4 | 8136.5 | 8602.3 | 9196.2 |
| 12.5° | 4729.4 | 5002.5 | 5242.7 | 5482.9 | 5771.8 | 6059.5 | 6498.9 | 6938.4 | 7487.3 | 8034.9 | 8606.3 |
| 15° | 4163.3 | 4461.5 | 4749.2 | 5036.8 | 5352.2 | 5666.3 | 6093.8 | 6521.4 | 7121.8 | 7722.2 | 8379.3 |
| 17.5° | 3478.4 | 3792.5 | 4143.5 | 4493.2 | 4904.9 | 5315.3 | 5862.9 | 6410.5 | 7121.8 | 7831.7 | 8606.3 |
| 20° | 2764.5 | 3085.2 | 3504.8 | 3924.4 | 4436.4 | 4947.1 | 5657.0 | 6367.0 | 7325.0 | 8281.7 | 9270.1 |
| 22.5° | 2181.3 | 2463.7 | 2921.6 | 3378.1 | 3969.3 | 4560.5 | 5471.0 | 6380.2 | 7632.5 | 8883.4 | 10217.5 |
| 25° | 1768.2 | 1967.5 | 2417.5 | 2866.1 | 3548.4 | 4230.6 | 5357.5 | 6483.1 | 8079.8 | 9675.2 | 11329.9 |
| 27.5° | 1514.9 | 1645.5 | 2065.1 | 2483.5 | 3229.0 | 3973.3 | 5311.3 | 6648.0 | 8647.2 | 10646.4 | 12540.0 |
| 30° | 1388.2 | 1479.2 | 1834.2 | 2187.9 | 2945.3 | 3702.7 | 5255.9 | 6809.0 | 9193.5 | 11576.7 | 13486.1 |
| 32.5° | 1282.6 | 1355.2 | 1658.7 | 1960.9 | 2699.9 | 3438.8 | 5149.0 | 6857.9 | 9574.9 | 12291.9 | 14287.1 |
| 35° | 1192.9 | 1253.6 | 1517.5 | 1781.4 | 2507.2 | 3233.0 | 4969.5 | 6706.1 | 9813.7 | 12921.3 | 15121.1 |
| 37.5° | 1120.3 | 1167.8 | 1412.0 | 1656.1 | 2340.9 | 3025.8 | 4765.0 | 6504.2 | 10026.2 | 13548.1 | 16059.3 |
| 40° | 1063.6 | 1104.5 | 1332.8 | 1561.1 | 2182.6 | 2804.1 | 4589.5 | 6373.6 | 10319.1 | 14264.7 | 17050.3 |
| 42.5° | 1031.9 | 1084.7 | 1264.2 | 1442.3 | 2032.2 | 2622.0 | 4448.3 | 6274.6 | 10591.0 | 14906.0 | 17917.3 |
| 45° | 1024.0 | 1099.2 | 1228.5 | 1357.8 | 1920.0 | 2482.1 | 4322.9 | 6162.4 | 10766.5 | 15370.5 | 18570.5 |
| 47.5° | 1010.8 | 1072.8 | 1200.8 | 1328.8 | 1864.6 | 2399.0 | 4255.6 | 6111.0 | 10942.0 | 15771.6 | 19112.8 |
| 50° | 1018.7 | 1026.6 | 1178.4 | 1328.8 | 1856.6 | 2384.5 | 4332.2 | 6279.9 | 11322.0 | 16362.8 | 19733.0 |
| 52.5° | 1004.2 | 969.9 | 1136.2 | 1302.4 | 1855.3 | 2408.2 | 4552.6 | 6696.9 | 12028.0 | 17357.8 | 20404.7 |
| 55° | 927.7 | 882.8 | 1057.0 | 1231.2 | 1827.6 | 2422.7 | 4815.1 | 7206.2 | 12975.4 | 18743.3 | 21612.1 |
| 57.5° | 860.4 | 819.5 | 967.3 | 1113.7 | 1743.2 | 2372.6 | 5085.7 | 7797.4 | 13977.0 | 20155.3 | 22972.6 |
| 60° | 770.6 | 761.4 | 867.0 | 972.5 | 1612.5 | 2251.2 | 5308.7 | 8364.8 | 14650.0 | 20933.8 | 23496.4 |
| 62.5° | 696.7 | 702.0 | 779.9 | 857.7 | 1448.9 | 2038.8 | 5382.6 | 8725.1 | 14631.5 | 20537.9 | 22968.6 |
| 65° | 640.0 | 649.2 | 725.8 | 802.3 | 1309.0 | 1815.7 | 5139.8 | 8462.5 | 13891.2 | 19318.7 | 21924.8 |
| 67.5° | 584.6 | 595.1 | 686.2 | 775.9 | 1185.0 | 1592.7 | 4532.8 | 7471.5 | 12559.8 | 17646.7 | 20597.3 |
| 70° | 531.8 | 545.0 | 644.0 | 742.9 | 1095.3 | 1446.3 | 3750.2 | 6054.2 | 10893.1 | 15730.7 | 19060.0 |
| 72.5° | 475.0 | 488.2 | 593.8 | 699.4 | 1038.5 | 1376.3 | 3057.5 | 4737.3 | 8839.9 | 12941.1 | 16303.4 |
| 75° | 417.0 | 426.2 | 541.0 | 654.5 | 960.7 | 1266.8 | 2399.0 | 3529.9 | 6765.5 | 10001.1 | 12314.3 |
| 77.5° | 358.9 | 370.8 | 467.1 | 562.1 | 815.5 | 1067.5 | 1807.8 | 2548.1 | 4964.3 | 7379.1 | 8564.1 |
| 80° | 286.3 | 296.9 | 365.5 | 432.8 | 629.4 | 824.7 | 1243.0 | 1661.4 | 3416.4 | 5171.4 | 5839.1 |
| 82.5° | 219.1 | 230.9 | 277.1 | 322.0 | 448.7 | 575.3 | 753.5 | 931.6 | 2269.7 | 3606.4 | 3661.8 |
| 85° | 150.4 | 154.4 | 187.4 | 219.1 | 277.1 | 335.2 | 431.5 | 527.8 | 1501.7 | 2475.5 | 2062.5 |
| 87.5° | 75.2 | 75.2 | 97.6 | 120.1 | 149.1 | 178.1 | 228.3 | 277.1 | 480.3 | 683.5 | 393.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P320763
 CATALOG NUMBER: GLEON-SA9B-827-U-SLR

CANDELA DISTRIBUTION (continued):

| | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° | 270° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P320763

CATALOG NUMBER: GLEON-SA9B-827-U-SLR

CANDELA DISTRIBUTION (continued):

| | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° | 325° |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 |
| 2.5° | 10858.8 | 10955.2 | 11052.8 | 11126.7 | 11201.9 | 11310.1 | 11418.3 | 11438.1 | 11459.2 | 11417.0 | 11374.8 |
| 5° | 10998.7 | 11290.3 | 11583.3 | 11853.8 | 12124.3 | 12286.6 | 12448.9 | 12481.9 | 12514.9 | 12413.3 | 12310.4 |
| 7.5° | 10480.1 | 10988.1 | 11496.2 | 11962.0 | 12427.8 | 12710.2 | 12993.9 | 13057.2 | 13121.9 | 12955.6 | 12789.4 |
| 10° | 9787.3 | 10411.5 | 11035.7 | 11649.3 | 12262.9 | 12673.2 | 13083.6 | 13165.5 | 13247.3 | 13040.1 | 12832.9 |
| 12.5° | 9251.6 | 9918.0 | 10584.4 | 11230.9 | 11878.9 | 12303.8 | 12728.7 | 12830.3 | 12931.9 | 12781.5 | 12629.7 |
| 15° | 9086.6 | 9713.4 | 10340.2 | 10903.7 | 11468.5 | 11815.5 | 12163.9 | 12204.8 | 12247.0 | 12223.3 | 12199.5 |
| 17.5° | 9386.2 | 9952.3 | 10519.7 | 10825.8 | 11133.3 | 11271.9 | 11411.7 | 11456.6 | 11502.8 | 11562.2 | 11622.9 |
| 20° | 10111.9 | 10510.5 | 10910.3 | 10897.1 | 10882.6 | 10815.3 | 10746.7 | 10734.8 | 10722.9 | 10893.1 | 11064.7 |
| 22.5° | 11195.3 | 11353.7 | 11513.3 | 11142.5 | 10771.7 | 10546.1 | 10319.1 | 10274.3 | 10228.1 | 10408.8 | 10591.0 |
| 25° | 12371.1 | 12342.0 | 12311.7 | 11605.7 | 10898.4 | 10468.2 | 10038.0 | 9987.9 | 9937.8 | 10092.2 | 10247.9 |
| 27.5° | 13534.9 | 13344.9 | 13154.9 | 12195.6 | 11236.2 | 10612.1 | 9987.9 | 9937.8 | 9887.6 | 10024.9 | 10162.1 |
| 30° | 14388.7 | 14083.9 | 13779.1 | 12693.0 | 11607.0 | 10865.4 | 10123.8 | 10042.0 | 9958.9 | 10127.8 | 10296.7 |
| 32.5° | 15055.1 | 14646.0 | 14237.0 | 13096.8 | 11956.7 | 11154.4 | 10352.1 | 10224.1 | 10096.1 | 10321.8 | 10547.4 |
| 35° | 15720.2 | 15144.8 | 14568.2 | 13457.1 | 12344.7 | 11496.2 | 10646.4 | 10489.3 | 10332.3 | 10642.4 | 10952.5 |
| 37.5° | 16556.8 | 15730.7 | 14903.3 | 13862.2 | 12821.0 | 12008.2 | 11194.0 | 11033.0 | 10872.0 | 11266.6 | 11662.5 |
| 40° | 17464.6 | 16362.8 | 15260.9 | 14305.6 | 13350.2 | 12716.8 | 12082.1 | 11929.0 | 11774.6 | 12254.9 | 12735.3 |
| 42.5° | 18219.4 | 16951.3 | 15683.2 | 14840.0 | 13995.5 | 13549.5 | 13102.1 | 13100.8 | 13098.2 | 13585.1 | 14072.0 |
| 45° | 18833.1 | 17442.2 | 16050.1 | 15361.2 | 14671.1 | 14438.8 | 14206.6 | 14392.7 | 14578.7 | 15018.1 | 15458.9 |
| 47.5° | 19290.9 | 17853.9 | 16415.6 | 15957.7 | 15499.8 | 15534.1 | 15568.4 | 15947.1 | 16325.8 | 16608.2 | 16891.9 |
| 50° | 19589.2 | 18227.4 | 16864.2 | 16723.0 | 16581.8 | 16889.3 | 17198.1 | 17632.2 | 18067.7 | 18260.4 | 18453.0 |
| 52.5° | 20023.3 | 18734.1 | 17443.5 | 17601.9 | 17760.2 | 18388.4 | 19016.5 | 19455.9 | 19895.3 | 19966.6 | 20039.1 |
| 55° | 21027.5 | 19665.7 | 18302.6 | 18606.1 | 18910.9 | 19832.0 | 20754.4 | 21097.4 | 21440.5 | 21466.9 | 21493.3 |
| 57.5° | 22454.0 | 20970.8 | 19487.6 | 19814.8 | 20142.1 | 21205.7 | 22270.6 | 22640.0 | 23010.8 | 22959.4 | 22906.6 |
| 60° | 23521.5 | 22209.9 | 20896.9 | 21226.8 | 21556.7 | 22593.9 | 23631.0 | 24055.9 | 24482.2 | 24368.7 | 24255.2 |
| 62.5° | 23587.5 | 22886.8 | 22184.8 | 22483.0 | 22782.6 | 23798.6 | 24814.7 | 25251.5 | 25688.3 | 25490.3 | 25292.4 |
| 65° | 22538.4 | 22852.5 | 23166.6 | 23265.5 | 23364.5 | 24311.9 | 25260.7 | 25594.6 | 25929.8 | 25829.5 | 25729.2 |
| 67.5° | 21093.5 | 22250.8 | 23409.4 | 23210.1 | 23010.8 | 23455.5 | 23900.2 | 24244.6 | 24589.1 | 24532.3 | 24474.3 |
| 70° | 19651.2 | 21196.4 | 22741.6 | 21762.5 | 20782.1 | 20598.6 | 20415.2 | 20786.0 | 21158.2 | 20928.5 | 20697.6 |
| 72.5° | 17195.5 | 18842.3 | 20490.4 | 18686.6 | 16882.7 | 16255.9 | 15629.1 | 16100.2 | 16571.3 | 16205.8 | 15838.9 |
| 75° | 13498.0 | 15317.7 | 17138.7 | 14986.5 | 12834.2 | 11997.6 | 11161.0 | 11566.1 | 11971.2 | 11720.5 | 11468.5 |
| 77.5° | 10048.6 | 11841.9 | 13635.2 | 11447.4 | 9258.2 | 8636.7 | 8013.8 | 8133.9 | 8255.3 | 8213.1 | 8169.5 |
| 80° | 6815.6 | 8065.3 | 9316.2 | 7859.4 | 6402.6 | 6450.1 | 6498.9 | 6442.2 | 6384.1 | 6468.6 | 6553.0 |
| 82.5° | 4349.3 | 5313.9 | 6279.9 | 5506.6 | 4733.3 | 5176.7 | 5620.1 | 5402.4 | 5183.3 | 5263.8 | 5345.6 |
| 85° | 2482.1 | 3425.6 | 4370.4 | 4073.5 | 3775.3 | 4034.0 | 4293.9 | 3956.1 | 3618.3 | 3766.1 | 3915.2 |
| 87.5° | 654.5 | 1894.9 | 3136.6 | 2847.7 | 2558.7 | 2223.5 | 1888.3 | 1441.0 | 993.6 | 1451.5 | 1909.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P320763
 CATALOG NUMBER: GLEON-SA9B-827-U-SLR

CANDELA DISTRIBUTION (continued):

| | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° | 325° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P320763

CATALOG NUMBER: GLEON-SA9B-827-U-SLR

CANDELA DISTRIBUTION (continued):

| | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 | 10055.2 |
| 2.5° | 11352.3 | 11329.9 | 11249.4 | 11167.6 | 11046.2 | 10945.9 | 10771.7 |
| 5° | 12167.8 | 12025.3 | 11779.9 | 11533.1 | 11258.7 | 10943.3 | 10593.6 |
| 7.5° | 12456.8 | 12123.0 | 11651.9 | 11179.5 | 10754.6 | 10255.8 | 9791.3 |
| 10° | 12334.1 | 11834.0 | 11221.7 | 10608.1 | 10092.2 | 9518.1 | 9002.2 |
| 12.5° | 12099.2 | 11567.4 | 10893.1 | 10217.5 | 9630.3 | 9014.1 | 8436.1 |
| 15° | 11775.9 | 11351.0 | 10719.0 | 10086.9 | 9495.7 | 8896.6 | 8211.7 |
| 17.5° | 11422.3 | 11220.4 | 10763.8 | 10305.9 | 9793.9 | 9213.3 | 8409.7 |
| 20° | 11137.3 | 11211.2 | 11029.1 | 10847.0 | 10436.6 | 9929.8 | 9027.2 |
| 22.5° | 10944.6 | 11299.6 | 11439.4 | 11580.6 | 11333.9 | 10938.0 | 9894.2 |
| 25° | 10836.4 | 11424.9 | 11893.4 | 12363.1 | 12253.6 | 11948.8 | 10947.2 |
| 27.5° | 10883.9 | 11605.7 | 12332.8 | 13061.2 | 13162.8 | 13078.4 | 12057.0 |
| 30° | 11026.4 | 11757.5 | 12642.9 | 13529.7 | 13934.8 | 14048.3 | 12982.0 |
| 32.5° | 11263.9 | 11980.5 | 12945.1 | 13911.0 | 14523.3 | 14884.9 | 13827.9 |
| 35° | 11622.9 | 12293.2 | 13298.7 | 14304.3 | 15096.0 | 15755.8 | 14701.4 |
| 37.5° | 12239.1 | 12815.8 | 13743.4 | 14672.4 | 15699.0 | 16690.1 | 15663.4 |
| 40° | 13141.7 | 13549.5 | 14333.3 | 15118.4 | 16410.3 | 17748.4 | 16736.2 |
| 42.5° | 14280.5 | 14490.3 | 15111.8 | 15733.4 | 17153.2 | 18709.0 | 17785.3 |
| 45° | 15514.3 | 15569.7 | 15960.3 | 16352.2 | 17741.8 | 19363.5 | 18573.1 |
| 47.5° | 16701.9 | 16511.9 | 16667.6 | 16823.3 | 18193.1 | 19830.7 | 19170.9 |
| 50° | 17923.9 | 17394.7 | 17312.9 | 17231.1 | 18644.4 | 20380.9 | 19930.9 |
| 52.5° | 19166.9 | 18294.7 | 17971.4 | 17646.7 | 19182.7 | 21110.6 | 20877.1 |
| 55° | 20383.6 | 19273.8 | 18838.3 | 18402.9 | 20006.2 | 22001.4 | 22266.6 |
| 57.5° | 21649.0 | 20391.5 | 19987.7 | 19583.9 | 21216.2 | 23129.6 | 23513.6 |
| 60° | 23010.8 | 21765.2 | 21441.9 | 21117.2 | 22720.5 | 24348.9 | 24069.1 |
| 62.5° | 24302.7 | 23313.0 | 23142.8 | 22971.3 | 24242.0 | 25285.8 | 23852.7 |
| 65° | 25165.7 | 24600.9 | 24759.3 | 24919.0 | 25392.7 | 25519.4 | 23219.3 |
| 67.5° | 24589.1 | 24703.9 | 25372.9 | 26043.2 | 25717.3 | 24825.3 | 21971.0 |
| 70° | 21385.1 | 22073.9 | 23658.8 | 25244.9 | 24521.8 | 22966.0 | 19730.4 |
| 72.5° | 16612.2 | 17386.8 | 19739.6 | 22093.7 | 21427.3 | 19521.9 | 16205.8 |
| 75° | 12342.0 | 13216.9 | 15813.9 | 18410.8 | 17485.8 | 14602.5 | 11603.1 |
| 77.5° | 8755.4 | 9341.3 | 11905.3 | 14470.5 | 12962.2 | 9720.0 | 7808.0 |
| 80° | 6373.6 | 6194.1 | 7623.2 | 9052.3 | 8801.6 | 6429.0 | 5014.4 |
| 82.5° | 4907.5 | 4469.4 | 5142.4 | 5815.4 | 5778.4 | 4461.5 | 3679.0 |
| 85° | 3739.7 | 3564.2 | 4159.3 | 4754.4 | 4245.1 | 3021.8 | 2338.3 |
| 87.5° | 2179.9 | 2451.8 | 3152.5 | 3854.5 | 2892.5 | 917.1 | 453.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P320763
CATALOG NUMBER: GLEON-SA9B-827-U-SLR

CANDELA DISTRIBUTION (continued):

| | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

(END OF REPORT)