

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P322314

Luminaire Tested: **GLEON-SA0A-760-U-T3-HSS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P322314
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-15)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GLEON-SA0A-760-U-T3-HSS
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(10) 70 CRI, 5700K, 615mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 33613 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Luminous Opening: Rectangular (W 2.5' x L: 1' x H: 0')
IES Classification: Type III - Short
BUG Rating: B3 - U0 - G5


Input Watts (W): 323
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P322314
 CATALOG NUMBER: GLEON-SA0A-760-U-T3-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 8.2 fc
 Type III - Short - N/A

REPORT NUMBER: P322314
CATALOG NUMBER: GLEON-SA0A-760-U-T3-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 57-Deg Lateral - - - Horizontal Cone Through 68-Deg Vertical

REPORT NUMBER: P322314
 CATALOG NUMBER: GLEON-SA0A-760-U-T3-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 3685.9 | 0.0 | 3685.9 |
| | % Fixture | 11.0 | 0.0 | 11.0 |
| Street Side | Lumens | 29927.1 | 0.0 | 29927.1 |
| | % Fixture | 89.0 | 0.0 | 89.0 |
| Total | Lumens | 33613.0 | 0.0 | 33613.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 373.8 | 1.1 |
| 10°-20° | 1035.8 | 3.1 |
| 20°-30° | 1786.9 | 5.3 |
| 30°-40° | 3084.0 | 9.2 |
| 40°-50° | 5275.3 | 15.7 |
| 50°-60° | 8440.0 | 25.1 |
| 60°-70° | 9751.4 | 29.0 |
| 70°-80° | 3726.2 | 11.1 |
| 80°-90° | 139.7 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 33613.0 | 100.0 |
| 0°-180° | 33613.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P322314
 CATALOG NUMBER: GLEON-SA0A-760-U-T3-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 2031.6 | 6.0 | | | |
| FM (30°-60°) | 15031.5 | 44.7 | | | |
| FH (60°-80°) | 12727.0 | 37.9 | | | G5 |
| FVH (80°-90°) | 137.1 | 0.4 | | | G2/225 |
| BL (0°-30°) | 1164.9 | 3.5 | B3/2500 | | |
| BM (30°-60°) | 1767.8 | 5.3 | B2/2500 | | |
| BH (60°-80°) | 750.7 | 2.2 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 2.6 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G5

Type III Short





REPORT NUMBER: P322314

CATALOG NUMBER: GLEON-SA0A-760-U-T3-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 57° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 3994.1 | 3994.1 | 3994.1 | 3994.1 | 3994.1 | 3994.1 | 3994.1 | 3994.1 | 3994.1 | 3994.1 | 3994.1 |
| 2.5° | 3900.3 | 3917.8 | 3930.5 | 3938.5 | 3948.0 | 3968.7 | 3975.0 | 3984.6 | 3989.3 | 3989.3 | 4000.5 |
| 5° | 3746.2 | 3765.2 | 3792.3 | 3814.5 | 3859.0 | 3916.2 | 3957.6 | 3973.4 | 4002.1 | 4027.5 | 4041.8 |
| 7.5° | 3603.1 | 3625.4 | 3657.2 | 3709.6 | 3785.9 | 3878.1 | 3963.9 | 3986.2 | 4041.8 | 4095.8 | 4122.9 |
| 10° | 3510.9 | 3528.4 | 3569.7 | 3644.4 | 3744.6 | 3873.3 | 3994.1 | 4021.1 | 4116.5 | 4207.1 | 4257.9 |
| 12.5° | 3479.2 | 3495.0 | 3538.0 | 3622.2 | 3746.2 | 3897.2 | 4064.0 | 4103.8 | 4243.6 | 4375.6 | 4447.1 |
| 15° | 3525.2 | 3528.4 | 3574.5 | 3654.0 | 3776.4 | 3956.0 | 4180.1 | 4227.7 | 4404.2 | 4575.8 | 4664.8 |
| 17.5° | 3703.3 | 3688.9 | 3712.8 | 3747.8 | 3844.7 | 4033.8 | 4302.5 | 4374.0 | 4609.2 | 4811.1 | 4895.3 |
| 20° | 4148.3 | 4148.3 | 4094.2 | 3998.9 | 4000.5 | 4154.6 | 4467.7 | 4548.8 | 4836.5 | 5070.1 | 5146.4 |
| 22.5° | 4909.6 | 4895.3 | 4787.2 | 4553.6 | 4339.0 | 4362.8 | 4669.6 | 4774.5 | 5109.9 | 5359.4 | 5384.8 |
| 25° | 5825.1 | 5807.6 | 5640.7 | 5311.7 | 4939.8 | 4699.8 | 4943.0 | 5063.8 | 5435.7 | 5656.6 | 5604.2 |
| 27.5° | 6794.6 | 6780.3 | 6615.0 | 6206.5 | 5677.3 | 5237.0 | 5268.8 | 5383.2 | 5767.9 | 5985.6 | 5818.7 |
| 30° | 7733.9 | 7738.7 | 7575.0 | 7155.4 | 6556.2 | 5922.0 | 5682.0 | 5748.8 | 6090.5 | 6311.4 | 6073.0 |
| 32.5° | 8627.2 | 8633.5 | 8492.1 | 8023.2 | 7463.7 | 6718.3 | 6254.2 | 6236.7 | 6465.6 | 6683.3 | 6410.0 |
| 35° | 9423.4 | 9439.3 | 9342.4 | 8978.4 | 8385.6 | 7605.2 | 6996.4 | 6955.1 | 6998.0 | 7244.4 | 6926.5 |
| 37.5° | 10191.1 | 10200.6 | 10127.5 | 9820.8 | 9324.9 | 8579.5 | 7934.2 | 7875.4 | 7783.2 | 7972.3 | 7608.4 |
| 40° | 11031.9 | 11008.0 | 10923.8 | 10645.7 | 10219.7 | 9655.5 | 8941.8 | 8840.1 | 8679.6 | 8848.1 | 8504.8 |
| 42.5° | 11813.9 | 11786.8 | 11801.1 | 11486.4 | 11127.2 | 10761.7 | 10116.4 | 9941.6 | 9847.8 | 10041.7 | 9604.6 |
| 45° | 12791.3 | 12777.0 | 12824.7 | 12551.3 | 12260.5 | 11995.0 | 11462.6 | 11271.9 | 11230.6 | 11457.8 | 10934.9 |
| 47.5° | 13756.1 | 13791.0 | 13938.9 | 13822.8 | 13705.2 | 13471.6 | 12888.3 | 12802.5 | 12827.9 | 13102.8 | 12338.4 |
| 50° | 14560.3 | 14601.6 | 15006.9 | 15140.4 | 15310.5 | 15173.8 | 14588.9 | 14536.5 | 14636.6 | 14884.5 | 13848.3 |
| 52.5° | 15142.0 | 15226.3 | 15730.1 | 16345.2 | 16965.0 | 17057.2 | 16473.9 | 16426.2 | 16561.3 | 16599.5 | 15014.9 |
| 55° | 15545.7 | 15620.4 | 16191.0 | 17316.3 | 18578.3 | 18975.6 | 18613.2 | 18428.9 | 18403.4 | 18026.7 | 16241.9 |
| 57.5° | 15617.2 | 15609.3 | 16429.4 | 17944.1 | 19843.4 | 20868.6 | 20639.7 | 20458.5 | 19937.2 | 19345.9 | 17648.5 |
| 60° | 15213.5 | 15259.6 | 16211.7 | 18161.8 | 20638.1 | 22300.6 | 22318.1 | 22082.8 | 21270.7 | 20628.6 | 19012.2 |
| 62.5° | 13970.6 | 14158.2 | 15119.8 | 17591.3 | 20628.6 | 22877.5 | 23548.2 | 23368.6 | 22397.5 | 21679.1 | 20394.9 |
| 65° | 11955.3 | 12022.1 | 12939.1 | 15636.3 | 19234.7 | 22635.9 | 24656.0 | 24589.3 | 23413.1 | 22699.5 | 21105.4 |
| 67.5° | 8730.5 | 8585.8 | 9549.0 | 12312.9 | 16284.8 | 21227.8 | 25450.7 | 25535.0 | 24196.7 | 22909.3 | 20348.8 |
| 68° | 7967.6 | 8010.5 | 8760.7 | 11491.2 | 15512.3 | 20730.3 | 25503.2 | 25631.9 | 24274.6 | 22772.6 | 19935.6 |
| 70° | 4749.1 | 4831.7 | 5500.8 | 7911.9 | 11801.1 | 17915.5 | 24937.4 | 25231.4 | 23810.5 | 21362.8 | 17243.2 |
| 72.5° | 1212.7 | 1311.2 | 1943.8 | 3541.1 | 6740.6 | 12622.9 | 21051.3 | 21548.8 | 20673.1 | 17330.6 | 11640.6 |
| 75° | 499.1 | 524.5 | 694.6 | 1166.6 | 2511.2 | 5686.8 | 13875.3 | 14940.2 | 14331.4 | 10375.5 | 5260.8 |
| 77.5° | 344.9 | 362.4 | 446.6 | 646.9 | 1087.1 | 1927.9 | 6802.5 | 7571.8 | 6821.6 | 3541.1 | 1147.5 |
| 80° | 247.9 | 262.2 | 319.5 | 430.7 | 624.6 | 688.2 | 2217.2 | 2563.7 | 2036.0 | 777.2 | 284.5 |
| 82.5° | 147.8 | 158.9 | 238.4 | 306.8 | 379.9 | 329.0 | 551.5 | 626.2 | 589.7 | 386.2 | 127.2 |
| 85° | 73.1 | 85.8 | 160.5 | 219.3 | 205.0 | 138.3 | 168.5 | 187.5 | 232.0 | 235.2 | 68.3 |
| 87.5° | 4.8 | 9.5 | 93.8 | 131.9 | 57.2 | 31.8 | 49.3 | 60.4 | 82.6 | 116.0 | 28.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P322314

CATALOG NUMBER: GLEON-SA0A-760-U-T3-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3994.1 | 3994.1 | 3994.1 | 3994.1 | 3994.1 | 3994.1 | 3994.1 | 3994.1 | 3994.1 | 3994.1 | 3994.1 |
| 2.5° | 4005.2 | 4006.8 | 3995.7 | 3990.9 | 3994.1 | 3975.0 | 3967.1 | 3970.3 | 3970.3 | 3975.0 | 3967.1 |
| 5° | 4045.0 | 4045.0 | 4025.9 | 4000.5 | 3986.2 | 3949.6 | 3925.8 | 3919.4 | 3914.6 | 3911.5 | 3905.1 |
| 7.5° | 4130.8 | 4121.3 | 4087.9 | 4032.3 | 3984.6 | 3905.1 | 3844.7 | 3812.9 | 3797.0 | 3790.7 | 3785.9 |
| 10° | 4269.1 | 4251.6 | 4196.0 | 4092.7 | 3983.0 | 3841.5 | 3709.6 | 3615.8 | 3538.0 | 3506.2 | 3487.1 |
| 12.5° | 4455.0 | 4429.6 | 4335.8 | 4164.2 | 3971.9 | 3711.2 | 3425.1 | 3150.2 | 2894.3 | 2789.4 | 2736.9 |
| 15° | 4669.6 | 4633.0 | 4485.2 | 4224.6 | 3906.7 | 3417.2 | 2795.7 | 2314.1 | 1959.7 | 1826.2 | 1769.0 |
| 17.5° | 4887.3 | 4839.7 | 4615.6 | 4262.7 | 3711.2 | 2808.4 | 1961.3 | 1481.3 | 1244.5 | 1180.9 | 1158.7 |
| 20° | 5106.7 | 5036.7 | 4728.4 | 4234.1 | 3269.4 | 2024.9 | 1293.8 | 1082.4 | 1014.0 | 995.0 | 988.6 |
| 22.5° | 5314.9 | 5206.8 | 4830.1 | 4122.9 | 2589.1 | 1358.9 | 1023.6 | 956.8 | 934.6 | 923.4 | 920.3 |
| 25° | 5496.1 | 5345.1 | 4919.1 | 3779.5 | 1832.6 | 1026.7 | 921.8 | 899.6 | 871.0 | 850.3 | 851.9 |
| 27.5° | 5666.1 | 5483.4 | 4973.2 | 3213.7 | 1222.2 | 877.3 | 853.5 | 823.3 | 770.8 | 740.7 | 740.7 |
| 30° | 5871.2 | 5667.7 | 5012.9 | 2473.1 | 899.6 | 775.6 | 756.5 | 710.5 | 638.9 | 599.2 | 599.2 |
| 32.5° | 6179.5 | 5947.5 | 4987.5 | 1735.6 | 745.4 | 681.8 | 637.3 | 573.8 | 495.9 | 457.7 | 456.2 |
| 35° | 6651.6 | 6379.8 | 4806.3 | 1138.0 | 658.0 | 592.8 | 521.3 | 443.4 | 375.1 | 343.3 | 341.7 |
| 37.5° | 7287.3 | 6958.3 | 4399.4 | 813.8 | 589.7 | 510.2 | 424.4 | 338.5 | 287.7 | 267.0 | 265.4 |
| 40° | 8112.2 | 7630.6 | 3817.7 | 659.6 | 526.1 | 430.7 | 327.4 | 262.2 | 227.3 | 211.4 | 213.0 |
| 42.5° | 9102.4 | 8350.6 | 3120.0 | 569.0 | 464.1 | 354.4 | 255.9 | 206.6 | 184.4 | 173.2 | 170.1 |
| 45° | 10202.2 | 9061.1 | 2388.8 | 507.0 | 402.1 | 286.1 | 200.3 | 163.7 | 146.2 | 139.9 | 139.9 |
| 47.5° | 11411.7 | 9752.4 | 1748.3 | 453.0 | 335.4 | 220.9 | 160.5 | 133.5 | 119.2 | 114.4 | 112.8 |
| 50° | 12510.0 | 10232.4 | 1260.4 | 395.8 | 275.0 | 174.8 | 130.3 | 111.3 | 101.7 | 95.4 | 95.4 |
| 52.5° | 13425.5 | 10383.4 | 928.2 | 333.8 | 222.5 | 139.9 | 108.1 | 95.4 | 85.8 | 81.1 | 81.1 |
| 55° | 14231.3 | 10321.4 | 689.8 | 275.0 | 179.6 | 114.4 | 92.2 | 81.1 | 73.1 | 68.3 | 68.3 |
| 57.5° | 15003.7 | 10121.2 | 515.0 | 224.1 | 144.6 | 92.2 | 77.9 | 68.3 | 60.4 | 57.2 | 57.2 |
| 60° | 15634.7 | 9787.4 | 383.0 | 181.2 | 116.0 | 74.7 | 65.2 | 55.6 | 49.3 | 44.5 | 44.5 |
| 62.5° | 16146.5 | 9418.7 | 281.3 | 149.4 | 92.2 | 58.8 | 50.9 | 46.1 | 36.6 | 31.8 | 31.8 |
| 65° | 16149.7 | 8806.8 | 211.4 | 124.0 | 71.5 | 46.1 | 38.1 | 36.6 | 23.8 | 19.1 | 17.5 |
| 67.5° | 14981.5 | 7592.5 | 162.1 | 106.5 | 55.6 | 35.0 | 28.6 | 30.2 | 12.7 | 7.9 | 6.4 |
| 68° | 14557.1 | 7284.1 | 152.6 | 104.9 | 52.4 | 33.4 | 27.0 | 30.2 | 11.1 | 6.4 | 4.8 |
| 70° | 12273.2 | 5794.9 | 122.4 | 101.7 | 46.1 | 25.4 | 22.3 | 30.2 | 9.5 | 4.8 | 3.2 |
| 72.5° | 7849.9 | 3363.1 | 90.6 | 81.1 | 35.0 | 19.1 | 14.3 | 27.0 | 9.5 | 3.2 | 1.6 |
| 75° | 3340.9 | 1042.6 | 62.0 | 57.2 | 20.7 | 14.3 | 9.5 | 17.5 | 6.4 | 1.6 | 0.0 |
| 77.5° | 704.1 | 235.2 | 36.6 | 35.0 | 14.3 | 9.5 | 6.4 | 4.8 | 1.6 | 0.0 | 0.0 |
| 80° | 181.2 | 68.3 | 19.1 | 17.5 | 7.9 | 4.8 | 3.2 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 57.2 | 27.0 | 11.1 | 7.9 | 3.2 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 28.6 | 15.9 | 6.4 | 3.2 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 15.9 | 4.8 | 1.6 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-9-R4

Test Date: 10/23/2019

Luminaire Tested: SA1C-760-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-9-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-760-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 5474 | CRI (Ra): | 71.7 | R9: | -27.1 |
| CIE u': | 0.2052 | R1: | 70.6 | R10: | 40.8 |
| CIE v': | 0.4804 | R2: | 74.6 | R11: | 74.6 |
| Duv: | 0.0025 | R3: | 78.3 | R12: | 50.4 |
| CIE x: | 0.3330 | R4: | 73.8 | R13: | 70.0 |
| CIE y: | 0.3466 | R5: | 72.4 | R14: | 87.8 |
| CIE z: | 0.3204 | R6: | 67.5 | | |
| Peak Wavelength (nm): | 442 | R7: | 77.5 | | |
| Dominant Wavelength (nm): | 554 | R8: | 58.9 | | |
| Purity: | 4.1 | | | | |
| Rf: | 72.1 | | | | |
| Rg: | 97.2 | | | | |



Test Conditions

Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.6/31%
 Sphere Temperature (°C): 25.9

REPORT NUMBER: SP1-1908-441-9-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-9-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-9-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13759.3 S/P: 1.85

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5527.6 M/P: 0.74

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Summary

$R_f = 72.1$
 $R_g = 97.2$
 CIE $R_a = 71.7$
 $R_g = -27.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 54 | CES51 = 88 | CES76 = 43 |
| CES02 = 59 | CES27 = 79 | CES52 = 90 | CES77 = 64 |
| CES03 = 30 | CES28 = 77 | CES53 = 77 | CES78 = 46 |
| CES04 = 69 | CES29 = 50 | CES54 = 81 | CES79 = 74 |
| CES05 = 46 | CES30 = 59 | CES55 = 80 | CES80 = 70 |
| CES06 = 50 | CES31 = 55 | CES56 = 70 | CES81 = 71 |
| CES07 = 38 | CES32 = 52 | CES57 = 68 | CES82 = 88 |
| CES08 = 38 | CES33 = 63 | CES58 = 70 | CES83 = 82 |
| CES09 = 29 | CES34 = 63 | CES59 = 88 | CES84 = 87 |
| CES10 = 72 | CES35 = 79 | CES60 = 92 | CES85 = 84 |
| CES11 = 55 | CES36 = 90 | CES61 = 88 | CES86 = 76 |
| CES12 = 61 | CES37 = 72 | CES62 = 81 | CES87 = 75 |
| CES13 = 41 | CES38 = 68 | CES63 = 75 | CES88 = 77 |
| CES14 = 74 | CES39 = 91 | CES64 = 72 | CES89 = 76 |
| CES15 = 70 | CES40 = 83 | CES65 = 65 | CES90 = 76 |
| CES16 = 46 | CES41 = 84 | CES66 = 66 | CES91 = 92 |
| CES17 = 48 | CES42 = 70 | CES67 = 64 | CES92 = 70 |
| CES18 = 55 | CES43 = 69 | CES68 = 71 | CES93 = 83 |
| CES19 = 70 | CES44 = 98 | CES69 = 80 | CES94 = 60 |
| CES20 = 64 | CES45 = 79 | CES70 = 58 | CES95 = 73 |
| CES21 = 85 | CES46 = 78 | CES71 = 55 | CES96 = 79 |
| CES22 = 77 | CES47 = 76 | CES72 = 84 | CES97 = 84 |
| CES23 = 91 | CES48 = 68 | CES73 = 47 | CES98 = 73 |
| CES24 = 90 | CES49 = 78 | CES74 = 94 | CES99 = 62 |
| CES25 = 71 | CES50 = 87 | CES75 = 51 | |



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Measure Comparisons



(END OF REPORT)