

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P318497

Luminaire Tested: **GLEON-SA3D-760-U-T3**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P318497
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-14)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GLEON-SA3D-760-U-T3
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(3) 70 CRI, 5700K, 1200mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 23693 lumens
Efficiency: N/A
Efficacy: 124.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type III - Short
BUG Rating: B3 - U0 - G4


Input Watts (W): 191
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P318497
 CATALOG NUMBER: GLEON-SA3D-760-U-T3

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5.4 fc
 Type III - Short - N/A

REPORT NUMBER: P318497
CATALOG NUMBER: GLEON-SA3D-760-U-T3

Luminous Intensity Polar Plot



— Vertical Plane Through 56-Deg Lateral - - - Horizontal Cone Through 69-Deg Vertical

REPORT NUMBER: P318497
 CATALOG NUMBER: GLEON-SA3D-760-U-T3

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 5276.4 | 0.0 | 5276.4 |
| | % Fixture | 22.3 | 0.0 | 22.3 |
| Street Side | Lumens | 18416.6 | 0.0 | 18416.6 |
| | % Fixture | 77.7 | 0.0 | 77.7 |
| Total | Lumens | 23693.0 | 0.0 | 23693.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 304.2 | 1.3 |
| 10°-20° | 978.3 | 4.1 |
| 20°-30° | 1707.7 | 7.2 |
| 30°-40° | 2453.0 | 10.4 |
| 40°-50° | 3394.8 | 14.3 |
| 50°-60° | 4973.9 | 21.0 |
| 60°-70° | 6064.1 | 25.6 |
| 70°-80° | 3352.6 | 14.2 |
| 80°-90° | 464.3 | 2.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 23693.0 | 100.0 |
| 0°-180° | 23693.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P318497
 CATALOG NUMBER: GLEON-SA3D-760-U-T3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|----------|
| | | | B | U | G |
| FL (0°-30°) | 1686.2 | 7.1 | | | |
| FM (30°-60°) | 8423.7 | 35.6 | | | |
| FH (60°-80°) | 8033.1 | 33.9 | | | G4/12000 |
| FVH (80°-90°) | 273.5 | 1.2 | | | G3/500 |
| BL (0°-30°) | 1303.9 | 5.5 | B3/2500 | | |
| BM (30°-60°) | 2398.0 | 10.1 | B2/2500 | | |
| BH (60°-80°) | 1383.6 | 5.8 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 190.8 | 0.8 | | | G2/225 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G4

Type III Short





REPORT NUMBER: P318497

CATALOG NUMBER: GLEON-SA3D-760-U-T3

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 56° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 3097.5 | 3097.5 | 3097.5 | 3097.5 | 3097.5 | 3097.5 | 3097.5 | 3097.5 | 3097.5 | 3097.5 | 3097.5 |
| 2.5° | 3117.1 | 3120.4 | 3117.9 | 3124.4 | 3117.1 | 3122.0 | 3117.9 | 3117.9 | 3115.5 | 3108.1 | 3100.0 |
| 5° | 3166.1 | 3172.6 | 3168.5 | 3175.0 | 3166.1 | 3167.7 | 3160.4 | 3160.4 | 3153.0 | 3137.5 | 3121.2 |
| 7.5° | 3242.8 | 3250.1 | 3246.9 | 3253.4 | 3241.2 | 3241.2 | 3231.4 | 3230.5 | 3215.9 | 3190.6 | 3171.8 |
| 10° | 3334.2 | 3344.0 | 3340.7 | 3350.5 | 3340.7 | 3344.0 | 3334.2 | 3334.2 | 3314.6 | 3278.7 | 3255.0 |
| 12.5° | 3467.2 | 3479.5 | 3470.5 | 3469.7 | 3465.6 | 3472.1 | 3464.0 | 3462.3 | 3444.4 | 3395.4 | 3362.8 |
| 15° | 3645.2 | 3658.2 | 3639.5 | 3637.8 | 3615.0 | 3612.5 | 3612.5 | 3610.1 | 3598.7 | 3539.9 | 3486.0 |
| 17.5° | 3850.0 | 3854.1 | 3837.8 | 3811.7 | 3782.3 | 3763.5 | 3761.1 | 3767.6 | 3767.6 | 3699.0 | 3613.3 |
| 20° | 4050.8 | 4058.2 | 4045.1 | 4015.7 | 3978.2 | 3950.4 | 3930.8 | 3943.9 | 3943.1 | 3861.5 | 3739.9 |
| 22.5° | 4269.6 | 4286.7 | 4267.1 | 4229.6 | 4185.5 | 4154.5 | 4120.2 | 4131.6 | 4132.5 | 4032.1 | 3863.9 |
| 25° | 4552.8 | 4537.3 | 4525.0 | 4472.0 | 4409.1 | 4377.3 | 4345.5 | 4356.9 | 4353.6 | 4215.7 | 3992.1 |
| 27.5° | 4803.4 | 4806.6 | 4790.3 | 4734.0 | 4661.4 | 4591.2 | 4589.5 | 4596.9 | 4584.6 | 4406.7 | 4112.9 |
| 30° | 5094.8 | 5096.4 | 5073.5 | 5022.9 | 4943.8 | 4853.2 | 4831.9 | 4844.2 | 4818.1 | 4587.9 | 4240.2 |
| 32.5° | 5384.5 | 5392.7 | 5367.4 | 5306.2 | 5242.5 | 5132.3 | 5089.9 | 5098.0 | 5032.7 | 4773.2 | 4371.6 |
| 35° | 5638.4 | 5649.8 | 5641.6 | 5600.8 | 5531.4 | 5436.8 | 5386.1 | 5381.2 | 5300.4 | 5000.1 | 4545.5 |
| 37.5° | 5897.1 | 5907.7 | 5898.7 | 5864.4 | 5836.7 | 5736.3 | 5709.4 | 5709.4 | 5569.0 | 5231.9 | 4766.6 |
| 40° | 6163.2 | 6179.5 | 6168.9 | 6121.5 | 6097.9 | 6052.2 | 5987.7 | 5972.2 | 5820.4 | 5510.2 | 5127.4 |
| 42.5° | 6410.5 | 6431.7 | 6474.1 | 6446.4 | 6398.2 | 6404.8 | 6275.0 | 6266.8 | 6155.8 | 5921.6 | 5580.4 |
| 45° | 6761.5 | 6792.5 | 6864.3 | 6843.1 | 6833.3 | 6797.4 | 6643.1 | 6635.8 | 6593.3 | 6475.0 | 6142.8 |
| 47.5° | 7144.3 | 7186.7 | 7316.5 | 7320.6 | 7425.8 | 7358.1 | 7148.3 | 7123.0 | 7132.8 | 7137.7 | 6829.2 |
| 50° | 7496.9 | 7543.4 | 7756.4 | 7856.8 | 8104.9 | 8119.6 | 7784.2 | 7761.3 | 7799.7 | 7912.3 | 7629.1 |
| 52.5° | 7778.4 | 7837.2 | 8103.3 | 8413.5 | 8838.7 | 8959.5 | 8566.9 | 8549.8 | 8578.3 | 8772.6 | 8533.4 |
| 55° | 7984.9 | 8048.6 | 8338.4 | 8903.2 | 9582.3 | 9795.3 | 9468.0 | 9451.7 | 9469.6 | 9716.9 | 9517.0 |
| 57.5° | 8033.1 | 8048.6 | 8469.0 | 9232.9 | 10209.9 | 10721.7 | 10570.7 | 10538.0 | 10449.9 | 10665.4 | 10602.5 |
| 60° | 7807.0 | 7869.0 | 8361.2 | 9348.8 | 10695.6 | 11635.0 | 11723.2 | 11682.4 | 11435.1 | 11611.4 | 11560.7 |
| 62.5° | 7348.3 | 7459.3 | 7958.8 | 9172.5 | 10885.7 | 12381.0 | 12853.6 | 12804.6 | 12378.6 | 12492.9 | 12249.6 |
| 65° | 6599.0 | 6646.4 | 7171.2 | 8564.5 | 10644.1 | 12858.5 | 13861.6 | 13837.1 | 13300.9 | 13122.1 | 12377.0 |
| 67.5° | 5258.8 | 5347.8 | 5793.4 | 7293.6 | 9655.7 | 12802.2 | 14641.1 | 14638.7 | 13903.3 | 13355.6 | 11925.6 |
| 69° | 4154.5 | 4246.7 | 4671.1 | 6008.1 | 8544.0 | 12287.2 | 14771.7 | 14800.3 | 14073.0 | 13213.6 | 11280.8 |
| 70° | 3312.2 | 3419.1 | 3710.5 | 5060.5 | 7557.3 | 11608.1 | 14663.1 | 14714.6 | 14040.4 | 12979.3 | 10685.8 |
| 72.5° | 1409.6 | 1496.1 | 1703.4 | 2608.6 | 4605.9 | 8668.1 | 13407.0 | 13601.3 | 13283.8 | 11879.1 | 8831.4 |
| 75° | 615.4 | 642.4 | 736.2 | 1063.5 | 2044.6 | 4717.7 | 10502.9 | 10862.1 | 11358.3 | 10041.0 | 6578.6 |
| 77.5° | 450.5 | 462.0 | 513.4 | 624.4 | 917.4 | 1781.8 | 6754.1 | 6963.1 | 8191.4 | 7306.7 | 4035.3 |
| 80° | 348.5 | 356.7 | 396.7 | 458.7 | 599.1 | 720.7 | 3080.4 | 3259.9 | 4605.9 | 3752.9 | 1680.6 |
| 82.5° | 277.5 | 283.2 | 311.0 | 337.9 | 413.8 | 436.7 | 1022.7 | 1134.5 | 1700.2 | 1036.6 | 444.8 |
| 85° | 257.9 | 264.5 | 274.2 | 246.5 | 265.3 | 256.3 | 442.4 | 462.8 | 513.4 | 407.3 | 186.1 |
| 87.5° | 116.7 | 137.9 | 271.8 | 191.8 | 141.2 | 112.6 | 181.2 | 189.4 | 213.0 | 213.8 | 82.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P318497
 CATALOG NUMBER: GLEON-SA3D-760-U-T3

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3097.5 | 3097.5 | 3097.5 | 3097.5 | 3097.5 | 3097.5 | 3097.5 | 3097.5 | 3097.5 | 3097.5 | 3097.5 |
| 2.5° | 3104.8 | 3102.4 | 3106.5 | 3096.7 | 3108.9 | 3108.1 | 3104.0 | 3105.7 | 3113.8 | 3113.0 | 3113.8 |
| 5° | 3123.6 | 3122.0 | 3126.9 | 3119.5 | 3134.2 | 3139.1 | 3139.9 | 3147.3 | 3156.3 | 3158.7 | 3158.7 |
| 7.5° | 3171.0 | 3171.0 | 3173.4 | 3163.6 | 3173.4 | 3172.6 | 3168.5 | 3175.9 | 3184.8 | 3185.7 | 3184.8 |
| 10° | 3252.6 | 3253.4 | 3249.3 | 3224.0 | 3215.9 | 3193.8 | 3173.4 | 3174.2 | 3185.7 | 3194.6 | 3197.1 |
| 12.5° | 3355.4 | 3352.2 | 3334.2 | 3287.7 | 3253.4 | 3208.5 | 3187.3 | 3186.5 | 3197.9 | 3205.2 | 3207.7 |
| 15° | 3473.0 | 3464.0 | 3417.5 | 3341.5 | 3281.1 | 3237.1 | 3202.8 | 3194.6 | 3188.1 | 3179.9 | 3180.8 |
| 17.5° | 3584.0 | 3563.6 | 3486.0 | 3380.7 | 3317.1 | 3258.3 | 3192.2 | 3139.1 | 3102.4 | 3081.2 | 3074.6 |
| 20° | 3696.6 | 3656.6 | 3544.8 | 3417.5 | 3336.7 | 3229.7 | 3102.4 | 2994.7 | 2927.7 | 2896.7 | 2891.0 |
| 22.5° | 3799.4 | 3735.0 | 3599.5 | 3455.8 | 3321.1 | 3133.4 | 2933.4 | 2776.7 | 2683.7 | 2642.1 | 2645.3 |
| 25° | 3899.8 | 3810.1 | 3656.6 | 3482.8 | 3242.8 | 2963.6 | 2698.4 | 2505.8 | 2398.0 | 2351.5 | 2349.9 |
| 27.5° | 3988.0 | 3886.0 | 3718.6 | 3460.7 | 3096.7 | 2722.0 | 2420.1 | 2232.3 | 2142.5 | 2102.5 | 2096.0 |
| 30° | 4089.2 | 3981.5 | 3801.1 | 3376.6 | 2882.8 | 2442.9 | 2148.3 | 2016.0 | 1952.4 | 1912.4 | 1905.0 |
| 32.5° | 4212.4 | 4111.2 | 3868.8 | 3224.0 | 2609.4 | 2151.5 | 1936.0 | 1843.8 | 1785.9 | 1741.0 | 1732.8 |
| 35° | 4392.0 | 4282.6 | 3886.0 | 3005.3 | 2309.0 | 1921.3 | 1780.1 | 1685.5 | 1607.1 | 1549.2 | 1543.4 |
| 37.5° | 4617.3 | 4497.3 | 3846.8 | 2722.0 | 2017.7 | 1772.0 | 1650.4 | 1533.7 | 1431.6 | 1350.0 | 1336.9 |
| 40° | 4942.1 | 4760.9 | 3738.2 | 2395.6 | 1803.0 | 1656.9 | 1523.9 | 1390.8 | 1264.3 | 1168.8 | 1150.0 |
| 42.5° | 5332.3 | 5070.3 | 3571.7 | 2070.7 | 1645.5 | 1540.2 | 1398.2 | 1233.3 | 1112.5 | 1044.7 | 1034.9 |
| 45° | 5828.5 | 5391.9 | 3340.7 | 1786.7 | 1490.4 | 1423.5 | 1262.7 | 1110.9 | 1035.8 | 986.0 | 977.8 |
| 47.5° | 6395.0 | 5752.6 | 3098.3 | 1555.7 | 1359.0 | 1314.1 | 1154.1 | 1056.2 | 996.6 | 957.4 | 950.1 |
| 50° | 7091.2 | 6159.9 | 2841.2 | 1366.3 | 1226.8 | 1182.7 | 1102.7 | 1026.0 | 978.6 | 948.4 | 941.1 |
| 52.5° | 7876.4 | 6619.4 | 2655.9 | 1217.0 | 1117.4 | 1085.6 | 1075.8 | 1009.6 | 971.3 | 948.4 | 941.1 |
| 55° | 8722.0 | 7087.1 | 2456.0 | 1091.3 | 1022.7 | 1031.7 | 1057.8 | 1011.3 | 985.2 | 957.4 | 946.8 |
| 57.5° | 9568.4 | 7570.3 | 2233.1 | 985.2 | 947.6 | 991.7 | 1045.6 | 1014.5 | 992.5 | 965.6 | 955.8 |
| 60° | 10237.7 | 7876.4 | 1887.9 | 896.2 | 888.0 | 947.6 | 1016.2 | 990.1 | 961.5 | 962.3 | 960.7 |
| 62.5° | 10550.3 | 7860.1 | 1506.7 | 817.0 | 828.4 | 888.0 | 968.8 | 951.7 | 928.0 | 959.9 | 962.3 |
| 65° | 10374.8 | 7468.3 | 1172.9 | 745.2 | 764.8 | 826.0 | 919.9 | 932.9 | 941.1 | 1002.3 | 1010.5 |
| 67.5° | 9638.6 | 6706.0 | 908.4 | 682.3 | 706.8 | 783.6 | 924.8 | 1016.2 | 1026.8 | 1091.3 | 1090.5 |
| 69° | 8877.1 | 5991.0 | 789.3 | 649.7 | 678.3 | 794.2 | 988.4 | 1069.2 | 1029.2 | 1097.8 | 1088.0 |
| 70° | 8238.8 | 5425.3 | 725.6 | 627.7 | 665.2 | 812.9 | 1030.9 | 1068.4 | 1017.0 | 1075.8 | 1059.4 |
| 72.5° | 6345.2 | 3903.1 | 615.4 | 586.9 | 621.1 | 777.8 | 1043.1 | 1044.7 | 988.4 | 999.9 | 972.1 |
| 75° | 4352.0 | 2466.6 | 537.1 | 531.4 | 554.2 | 701.1 | 1003.9 | 998.2 | 914.2 | 897.8 | 875.0 |
| 77.5° | 2399.6 | 1252.9 | 456.3 | 478.3 | 493.8 | 621.1 | 912.5 | 904.4 | 835.0 | 800.7 | 792.5 |
| 80° | 925.6 | 548.5 | 385.2 | 425.2 | 435.0 | 537.9 | 799.9 | 792.5 | 734.6 | 690.5 | 678.3 |
| 82.5° | 349.3 | 287.3 | 318.3 | 368.1 | 364.8 | 444.0 | 677.5 | 673.4 | 617.1 | 552.6 | 533.0 |
| 85° | 161.6 | 172.2 | 252.2 | 303.6 | 280.0 | 328.9 | 542.0 | 549.3 | 480.7 | 404.0 | 404.0 |
| 87.5° | 68.6 | 96.3 | 178.7 | 229.4 | 188.5 | 222.0 | 397.5 | 379.5 | 348.5 | 241.6 | 226.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-9-R4

Test Date: 10/23/2019

Luminaire Tested: SA1C-760-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .

Test Information


Test Method: LM-79-2008
 Report Number: SP1-1908-441-9-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-760-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 5474
 CIE u': 0.2052
 CIE v': 0.4804
 Duv: 0.0025
 CIE x: 0.3330
 CIE y: 0.3466
 CIE z: 0.3204
 Peak Wavelength (nm): 442
 Dominant Wavelength (nm): 554
 Purity: 4.1
 Rf: 72.1
 Rg: 97.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.7 | | |
| R1: | 70.6 | R9: | -27.1 |
| R2: | 74.6 | R10: | 40.8 |
| R3: | 78.3 | R11: | 74.6 |
| R4: | 73.8 | R12: | 50.4 |
| R5: | 72.4 | R13: | 70.0 |
| R6: | 67.5 | R14: | 87.8 |
| R7: | 77.5 | | |
| R8: | 58.9 | | |



Test Conditions

Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.6/31%
 Sphere Temperature (°C): 25.9

REPORT NUMBER: SP1-1908-441-9-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-9-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-9-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13759.3 S/P: 1.85

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5527.6 M/P: 0.74

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4



TM-30-18

Summary

$R_f = 72.1$
 $R_g = 97.2$
 CIE $R_a = 71.7$
 $R_g = -27.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 54 | CES51 = 88 | CES76 = 43 |
| CES02 = 59 | CES27 = 79 | CES52 = 90 | CES77 = 64 |
| CES03 = 30 | CES28 = 77 | CES53 = 77 | CES78 = 46 |
| CES04 = 69 | CES29 = 50 | CES54 = 81 | CES79 = 74 |
| CES05 = 46 | CES30 = 59 | CES55 = 80 | CES80 = 70 |
| CES06 = 50 | CES31 = 55 | CES56 = 70 | CES81 = 71 |
| CES07 = 38 | CES32 = 52 | CES57 = 68 | CES82 = 88 |
| CES08 = 38 | CES33 = 63 | CES58 = 70 | CES83 = 82 |
| CES09 = 29 | CES34 = 63 | CES59 = 88 | CES84 = 87 |
| CES10 = 72 | CES35 = 79 | CES60 = 92 | CES85 = 84 |
| CES11 = 55 | CES36 = 90 | CES61 = 88 | CES86 = 76 |
| CES12 = 61 | CES37 = 72 | CES62 = 81 | CES87 = 75 |
| CES13 = 41 | CES38 = 68 | CES63 = 75 | CES88 = 77 |
| CES14 = 74 | CES39 = 91 | CES64 = 72 | CES89 = 76 |
| CES15 = 70 | CES40 = 83 | CES65 = 65 | CES90 = 76 |
| CES16 = 46 | CES41 = 84 | CES66 = 66 | CES91 = 92 |
| CES17 = 48 | CES42 = 70 | CES67 = 64 | CES92 = 70 |
| CES18 = 55 | CES43 = 69 | CES68 = 71 | CES93 = 83 |
| CES19 = 70 | CES44 = 98 | CES69 = 80 | CES94 = 60 |
| CES20 = 64 | CES45 = 79 | CES70 = 58 | CES95 = 73 |
| CES21 = 85 | CES46 = 78 | CES71 = 55 | CES96 = 79 |
| CES22 = 77 | CES47 = 76 | CES72 = 84 | CES97 = 84 |
| CES23 = 91 | CES48 = 68 | CES73 = 47 | CES98 = 73 |
| CES24 = 90 | CES49 = 78 | CES74 = 94 | CES99 = 62 |
| CES25 = 71 | CES50 = 87 | CES75 = 51 | |



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Measure Comparisons



(END OF REPORT)