

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P316615

Luminaire Tested: **GLEON-SA1D-827-U-5MQ**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P316615  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: GLEON-SA1D-827-U-5MQ  
Description: GALLEON AREA AND ROADWAY LUMINAIRE  
(1) 80 CRI, 2700K, 1200mA LIGHTSQUARE WITH 16 LEDS AND TYPE V MEDIUM OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6274 lumens  
Efficiency: N/A  
Efficacy: 93.6 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B3 - U0 - G1


Input Watts (W): 67  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P316615  
 CATALOG NUMBER: GLEON-SA1D-827-U-5MQ

## Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.1 fc  
 Type V - Short - N/A

REPORT NUMBER: P316615  
CATALOG NUMBER: GLEON-SA1D-827-U-5MQ

## Luminous Intensity Polar Plot



REPORT NUMBER: P316615

CATALOG NUMBER: GLEON-SA1D-827-U-5MQ


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 3137.0   | 0.0    | 3137.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 3137.0   | 0.0    | 3137.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 6274.0   | 0.0    | 6274.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 64.9   | 1.0       |
| 10°-20°   | 190.5  | 3.0       |
| 20°-30°   | 324.3  | 5.2       |
| 30°-40°   | 514.4  | 8.2       |
| 40°-50°   | 837.1  | 13.3      |
| 50°-60°   | 1380.2 | 22.0      |
| 60°-70°   | 2026.1 | 32.3      |
| 70°-80°   | 895.9  | 14.3      |
| 80°-90°   | 40.6   | 0.6       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 6274.0 | 100.0     |
| 0°-180°   | 6274.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P316615


CATALOG NUMBER: GLEON-SA1D-827-U-5MQ

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 289.9  | 4.6       |                         |      |         |
| FM   | (30°-60°)   | 1365.8 | 21.8      |                         |      |         |
| FH   | (60°-80°)   | 1461.0 | 23.3      |                         |      | G1/1800 |
| FVH  | (80°-90°)   | 20.3   | 0.3       |                         |      | G1/100  |
| BL   | (0°-30°)    | 289.9  | 4.6       | B1/500                  |      |         |
| BM   | (30°-60°)   | 1365.8 | 21.8      | B2/2500                 |      |         |
| BH   | (60°-80°)   | 1461.0 | 23.3      | B3/2500                 |      | G1/1800 |
| BVH  | (80°-90°)   | 20.3   | 0.3       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G1**

Type V Short





REPORT NUMBER: P316615

CATALOG NUMBER: GLEON-SA1D-827-U-5MQ

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 685.2  | 685.2  | 685.2  | 685.2  | 685.2  | 685.2  | 685.2  | 685.2  | 685.2  | 685.2  | 685.2  |
| 2.5°  | 684.2  | 683.6  | 685.0  | 684.8  | 683.6  | 683.8  | 683.8  | 684.4  | 684.4  | 684.0  | 684.0  |
| 5°    | 681.7  | 681.3  | 682.9  | 682.9  | 681.7  | 682.1  | 682.5  | 683.1  | 682.9  | 682.5  | 682.3  |
| 7.5°  | 678.6  | 678.4  | 680.0  | 680.0  | 679.2  | 679.6  | 679.2  | 679.4  | 679.0  | 678.6  | 678.0  |
| 10°   | 673.4  | 673.8  | 675.3  | 675.7  | 675.7  | 675.9  | 675.5  | 674.4  | 673.8  | 673.2  | 672.6  |
| 12.5° | 668.6  | 668.4  | 670.5  | 671.5  | 673.2  | 675.0  | 673.8  | 670.9  | 669.6  | 668.4  | 668.0  |
| 15°   | 665.5  | 665.7  | 667.8  | 669.6  | 672.6  | 676.5  | 675.0  | 670.5  | 668.0  | 666.5  | 666.1  |
| 17.5° | 664.9  | 665.3  | 668.0  | 671.3  | 674.4  | 678.8  | 678.0  | 673.4  | 669.2  | 666.5  | 665.9  |
| 20°   | 666.3  | 666.5  | 670.7  | 675.5  | 680.9  | 685.0  | 683.1  | 678.2  | 672.6  | 668.4  | 667.4  |
| 22.5° | 669.0  | 669.9  | 675.0  | 682.5  | 690.8  | 696.4  | 694.1  | 685.6  | 676.9  | 671.7  | 670.3  |
| 25°   | 677.5  | 677.7  | 684.8  | 695.0  | 704.9  | 711.4  | 708.7  | 696.6  | 685.4  | 679.6  | 677.7  |
| 27.5° | 695.2  | 695.8  | 702.9  | 714.7  | 723.2  | 727.4  | 725.7  | 715.9  | 706.4  | 700.2  | 700.8  |
| 30°   | 720.7  | 721.6  | 729.4  | 742.5  | 747.7  | 748.8  | 748.3  | 743.8  | 735.1  | 726.7  | 727.4  |
| 32.5° | 751.9  | 752.3  | 762.9  | 774.7  | 778.9  | 779.7  | 778.9  | 774.7  | 764.3  | 753.1  | 753.7  |
| 35°   | 791.9  | 793.2  | 803.4  | 814.8  | 818.1  | 819.8  | 818.3  | 812.9  | 802.1  | 791.1  | 790.7  |
| 37.5° | 841.4  | 841.6  | 852.2  | 864.0  | 868.2  | 868.6  | 866.9  | 863.4  | 849.9  | 839.9  | 839.3  |
| 40°   | 898.7  | 899.5  | 912.0  | 924.6  | 926.3  | 924.4  | 926.7  | 924.6  | 910.7  | 899.3  | 901.2  |
| 42.5° | 968.4  | 970.3  | 985.3  | 997.7  | 992.9  | 991.9  | 993.4  | 994.0  | 982.8  | 968.9  | 967.6  |
| 45°   | 1049.6 | 1051.3 | 1070.0 | 1079.9 | 1076.8 | 1070.0 | 1072.9 | 1077.9 | 1062.3 | 1045.1 | 1046.7 |
| 47.5° | 1142.2 | 1146.4 | 1166.3 | 1175.7 | 1168.0 | 1158.6 | 1164.2 | 1171.7 | 1153.5 | 1132.1 | 1131.0 |
| 50°   | 1245.2 | 1250.4 | 1277.0 | 1290.1 | 1282.4 | 1265.2 | 1274.5 | 1279.5 | 1253.1 | 1225.5 | 1223.2 |
| 52.5° | 1355.1 | 1360.3 | 1393.7 | 1420.7 | 1415.7 | 1388.9 | 1402.0 | 1396.8 | 1366.5 | 1329.3 | 1326.4 |
| 55°   | 1479.4 | 1481.5 | 1517.7 | 1561.3 | 1566.2 | 1546.5 | 1545.7 | 1537.2 | 1492.3 | 1449.3 | 1447.3 |
| 57.5° | 1607.4 | 1608.8 | 1655.5 | 1707.0 | 1730.5 | 1730.5 | 1707.2 | 1689.2 | 1629.6 | 1579.7 | 1574.5 |
| 60°   | 1745.4 | 1750.6 | 1802.3 | 1872.3 | 1927.1 | 1943.3 | 1902.2 | 1853.0 | 1788.2 | 1727.4 | 1721.4 |
| 62.5° | 1868.4 | 1874.4 | 1953.5 | 2057.7 | 2145.8 | 2204.7 | 2104.2 | 2024.1 | 1906.2 | 1808.6 | 1797.1 |
| 65°   | 1883.9 | 1900.1 | 2015.4 | 2204.1 | 2401.2 | 2518.9 | 2326.2 | 2128.7 | 1913.8 | 1778.2 | 1766.6 |
| 67.5° | 1720.5 | 1747.9 | 1903.7 | 2197.5 | 2604.7 | 2857.4 | 2468.0 | 2068.9 | 1776.0 | 1626.0 | 1613.2 |
| 70°   | 1322.1 | 1361.9 | 1541.5 | 1922.1 | 2569.6 | 2966.4 | 2379.2 | 1811.3 | 1480.7 | 1319.4 | 1301.3 |
| 72.5° | 725.3  | 741.7  | 903.2  | 1316.2 | 2060.0 | 2520.8 | 1984.4 | 1339.3 | 981.9  | 799.0  | 768.7  |
| 75°   | 230.1  | 235.9  | 318.1  | 538.6  | 1165.3 | 1669.6 | 1260.6 | 657.4  | 361.9  | 266.8  | 263.7  |
| 77.5° | 102.2  | 102.8  | 115.0  | 157.2  | 401.4  | 845.9  | 482.1  | 179.0  | 123.3  | 107.8  | 111.3  |
| 80°   | 64.6   | 64.6   | 71.2   | 77.9   | 109.2  | 245.6  | 130.4  | 85.1   | 72.7   | 67.5   | 68.9   |
| 82.5° | 30.9   | 34.3   | 46.3   | 49.8   | 60.0   | 82.6   | 66.9   | 55.6   | 48.6   | 36.1   | 33.6   |
| 85°   | 20.3   | 17.0   | 29.3   | 33.0   | 34.9   | 39.7   | 38.8   | 36.8   | 31.8   | 18.1   | 20.1   |
| 87.5° | 9.1    | 8.7    | 15.2   | 13.9   | 13.1   | 10.0   | 15.0   | 18.5   | 17.9   | 8.9    | 8.9    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine




### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-157-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/03/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Invue  
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**  
 Description: Epic Modern Light Square 40W 5WQ Optic

### Spectral Parameters

CCT (K): 2764  
 CIE  $u'$ : 0.2591  
 CIE  $v'$ : 0.5290  
 Duv: 0.0020  
 CIE x: 0.4581  
 CIE y: 0.4156  
 CIE z: 0.1263  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 583  
 Purity: 62.2537  
 R<sub>f</sub>: 84.7  
 R<sub>g</sub>: 94.6

CRI (Ra): 80.9  
 R1: 78.8  
 R2: 89.9  
 R3: 96.2  
 R4: 79.1  
 R5: 79.1  
 R6: 88.8  
 R7: 81.3  
 R8: 54.3  
 R9: -1.5  
 R10: 77.9  
 R11: 78.9  
 R12: 71.6  
 R13: 81.2  
 R14: 98.5  
 R15: 69.9



### Test Conditions


Stabilization Time: 81M  
 Operation Time: 2H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-157-9

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



REPORT NUMBER: SP1-2407-157-9

### Photopic Flux vs. Wavelength




**Photopic Lumens: 4337.9**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 0                | 0.0              | 490       | 18018            | 2.6              | 620       | 87426            | 22.8             | 750       | 2680             | 0.0              | 880       | 58               | 0.0              |
| 365       | 0                | 0.0              | 495       | 22295            | 3.9              | 625       | 83013            | 18.2             | 755       | 2287             | 0.0              | 885       | 46               | 0.0              |
| 370       | 0                | 0.0              | 500       | 26478            | 5.8              | 630       | 78077            | 14.1             | 760       | 1944             | 0.0              | 890       | 45               | 0.0              |
| 375       | 0                | 0.0              | 505       | 30524            | 8.5              | 635       | 72080            | 10.7             | 765       | 1653             | 0.0              | 895       | 41               | 0.0              |
| 380       | 0                | 0.0              | 510       | 33611            | 11.5             | 640       | 66249            | 7.9              | 770       | 1413             | 0.0              | 900       | 38               | 0.0              |
| 385       | 0                | 0.0              | 515       | 36490            | 15.2             | 645       | 59973            | 5.7              | 775       | 1198             | 0.0              | 905       | 33               | 0.0              |
| 390       | 0                | 0.0              | 520       | 38610            | 18.7             | 650       | 53972            | 3.9              | 780       | 1025             | 0.0              | 910       | 30               | 0.0              |
| 395       | 0                | 0.0              | 525       | 40511            | 21.9             | 655       | 48369            | 2.7              | 785       | 874              | 0.0              | 915       | 23               | 0.0              |
| 400       | 48               | 0.0              | 530       | 42223            | 24.9             | 660       | 42641            | 1.8              | 790       | 747              | 0.0              | 920       | 24               | 0.0              |
| 405       | 201              | 0.0              | 535       | 44137            | 27.6             | 665       | 37602            | 1.1              | 795       | 639              | 0.0              | 925       | 22               | 0.0              |
| 410       | 457              | 0.0              | 540       | 46032            | 30.0             | 670       | 32798            | 0.7              | 800       | 547              | 0.0              | 930       | 22               | 0.0              |
| 415       | 925              | 0.0              | 545       | 48553            | 32.5             | 675       | 28558            | 0.5              | 805       | 473              | 0.0              | 935       | 17               | 0.0              |
| 420       | 1816             | 0.0              | 550       | 51408            | 34.9             | 680       | 24782            | 0.3              | 810       | 401              | 0.0              | 940       | 13               | 0.0              |
| 425       | 3217             | 0.0              | 555       | 54711            | 37.4             | 685       | 21386            | 0.2              | 815       | 351              | 0.0              | 945       | 6                | 0.0              |
| 430       | 5520             | 0.0              | 560       | 58847            | 40.0             | 690       | 18413            | 0.1              | 820       | 307              | 0.0              | 950       | 10               | 0.0              |
| 435       | 9225             | 0.1              | 565       | 63386            | 42.4             | 695       | 15721            | 0.1              | 825       | 261              | 0.0              | 955       | 11               | 0.0              |
| 440       | 15522            | 0.2              | 570       | 68196            | 44.3             | 700       | 13432            | 0.0              | 830       | 228              | 0.0              | 960       | 8                | 0.0              |
| 445       | 27642            | 0.6              | 575       | 73613            | 46.0             | 705       | 11513            | 0.0              | 835       | 193              | 0.0              | 965       | 12               | 0.0              |
| 450       | 36602            | 0.9              | 580       | 79207            | 47.1             | 710       | 9780             | 0.0              | 840       | 174              | 0.0              | 970       | 3                | 0.0              |
| 455       | 28292            | 0.9              | 585       | 84248            | 47.0             | 715       | 8356             | 0.0              | 845       | 151              | 0.0              | 975       | 8                | 0.0              |
| 460       | 21166            | 0.9              | 590       | 88397            | 45.7             | 720       | 7161             | 0.0              | 850       | 123              | 0.0              | 980       | 2                | 0.0              |
| 465       | 19092            | 1.0              | 595       | 91428            | 43.4             | 725       | 6067             | 0.0              | 855       | 106              | 0.0              | 985       | 13               | 0.0              |
| 470       | 14951            | 0.9              | 600       | 93452            | 40.3             | 730       | 5164             | 0.0              | 860       | 95               | 0.0              | 990       | 16               | 0.0              |
| 475       | 12606            | 1.0              | 605       | 93959            | 36.4             | 735       | 4393             | 0.0              | 865       | 82               | 0.0              | 995       | 20               | 0.0              |
| 480       | 13323            | 1.3              | 610       | 93079            | 32.0             | 740       | 3694             | 0.0              | 870       | 77               | 0.0              | 1000      | 0                | 0.0              |
| 485       | 15164            | 1.8              | 615       | 90707            | 27.3             | 745       | 3157             | 0.0              | 875       | 65               | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2407-157-9

### Scotopic Flux vs. Wavelength




Scotopic Lumens: 5286.7

S/P: 1.22

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 0                | 0.0              | 490       | 18018            | 75.9             | 620       | 87426            | 0.4              | 750       | 2680             | 0.0              | 880       | 58               | 0.0              |
| 365       | 0                | 0.0              | 495       | 22295            | 93.2             | 625       | 83013            | 0.2              | 755       | 2287             | 0.0              | 885       | 46               | 0.0              |
| 370       | 0                | 0.0              | 500       | 26478            | 107.8            | 630       | 78077            | 0.1              | 760       | 1944             | 0.0              | 890       | 45               | 0.0              |
| 375       | 0                | 0.0              | 505       | 30524            | 118.7            | 635       | 72080            | 0.1              | 765       | 1653             | 0.0              | 895       | 41               | 0.0              |
| 380       | 0                | 0.0              | 510       | 33611            | 122.2            | 640       | 66249            | 0.1              | 770       | 1413             | 0.0              | 900       | 38               | 0.0              |
| 385       | 0                | 0.0              | 515       | 36490            | 120.8            | 645       | 59973            | 0.0              | 775       | 1198             | 0.0              | 905       | 33               | 0.0              |
| 390       | 0                | 0.0              | 520       | 38610            | 113.9            | 650       | 53972            | 0.0              | 780       | 1025             | 0.0              | 910       | 30               | 0.0              |
| 395       | 0                | 0.0              | 525       | 40511            | 104.1            | 655       | 48369            | 0.0              | 785       | 874              | 0.0              | 915       | 23               | 0.0              |
| 400       | 48               | 0.0              | 530       | 42223            | 92.4             | 660       | 42641            | 0.0              | 790       | 747              | 0.0              | 920       | 24               | 0.0              |
| 405       | 201              | 0.0              | 535       | 44137            | 80.5             | 665       | 37602            | 0.0              | 795       | 639              | 0.0              | 925       | 22               | 0.0              |
| 410       | 457              | 0.1              | 540       | 46032            | 68.2             | 670       | 32798            | 0.0              | 800       | 547              | 0.0              | 930       | 22               | 0.0              |
| 415       | 925              | 0.3              | 545       | 48553            | 57.1             | 675       | 28558            | 0.0              | 805       | 473              | 0.0              | 935       | 17               | 0.0              |
| 420       | 1816             | 1.1              | 550       | 51408            | 46.7             | 680       | 24782            | 0.0              | 810       | 401              | 0.0              | 940       | 13               | 0.0              |
| 425       | 3217             | 2.5              | 555       | 54711            | 37.4             | 685       | 21386            | 0.0              | 815       | 351              | 0.0              | 945       | 6                | 0.0              |
| 430       | 5520             | 5.9              | 560       | 58847            | 29.4             | 690       | 18413            | 0.0              | 820       | 307              | 0.0              | 950       | 10               | 0.0              |
| 435       | 9225             | 12.5             | 565       | 63386            | 22.5             | 695       | 15721            | 0.0              | 825       | 261              | 0.0              | 955       | 11               | 0.0              |
| 440       | 15522            | 26.3             | 570       | 68196            | 16.9             | 700       | 13432            | 0.0              | 830       | 228              | 0.0              | 960       | 8                | 0.0              |
| 445       | 27642            | 55.2             | 575       | 73613            | 12.4             | 705       | 11513            | 0.0              | 835       | 193              | 0.0              | 965       | 12               | 0.0              |
| 450       | 36602            | 85.4             | 580       | 79207            | 9.0              | 710       | 9780             | 0.0              | 840       | 174              | 0.0              | 970       | 3                | 0.0              |
| 455       | 28292            | 75.1             | 585       | 84248            | 6.3              | 715       | 8356             | 0.0              | 845       | 151              | 0.0              | 975       | 8                | 0.0              |
| 460       | 21166            | 63.2             | 590       | 88397            | 4.4              | 720       | 7161             | 0.0              | 850       | 123              | 0.0              | 980       | 2                | 0.0              |
| 465       | 19092            | 63.2             | 595       | 91428            | 3.0              | 725       | 6067             | 0.0              | 855       | 106              | 0.0              | 985       | 13               | 0.0              |
| 470       | 14951            | 54.2             | 600       | 93452            | 2.0              | 730       | 5164             | 0.0              | 860       | 95               | 0.0              | 990       | 16               | 0.0              |
| 475       | 12606            | 48.8             | 605       | 93959            | 1.3              | 735       | 4393             | 0.0              | 865       | 82               | 0.0              | 995       | 20               | 0.0              |
| 480       | 13323            | 54.2             | 610       | 93079            | 0.9              | 740       | 3694             | 0.0              | 870       | 77               | 0.0              | 1000      | 0                | 0.0              |
| 485       | 15164            | 63.3             | 615       | 90707            | 0.5              | 745       | 3157             | 0.0              | 875       | 65               | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2407-157-9

### Melanopic Flux vs. Wavelength



**Melanopic Lumens: 9797**

**M/P: 2.26**


| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 0                | 0.0              | 490       | 18018            | 27.7             | 620       | 87426            | 1.1              | 750       | 2680             | 0.0              | 880       | 58               | 0.0              |
| 365       | 0                | 0.0              | 495       | 22295            | 36.0             | 625       | 83013            | 0.7              | 755       | 2287             | 0.0              | 885       | 46               | 0.0              |
| 370       | 0                | 0.0              | 500       | 26478            | 44.2             | 630       | 78077            | 0.4              | 760       | 1944             | 0.0              | 890       | 45               | 0.0              |
| 375       | 0                | 0.0              | 505       | 30524            | 51.8             | 635       | 72080            | 0.3              | 765       | 1653             | 0.0              | 895       | 41               | 0.0              |
| 380       | 0                | 0.0              | 510       | 33611            | 57.0             | 640       | 66249            | 0.2              | 770       | 1413             | 0.0              | 900       | 38               | 0.0              |
| 385       | 0                | 0.0              | 515       | 36490            | 60.5             | 645       | 59973            | 0.1              | 775       | 1198             | 0.0              | 905       | 33               | 0.0              |
| 390       | 0                | 0.0              | 520       | 38610            | 61.4             | 650       | 53972            | 0.1              | 780       | 1025             | 0.0              | 910       | 30               | 0.0              |
| 395       | 0                | 0.0              | 525       | 40511            | 60.6             | 655       | 48369            | 0.0              | 785       | 874              | 0.0              | 915       | 23               | 0.0              |
| 400       | 48               | 0.0              | 530       | 42223            | 58.2             | 660       | 42641            | 0.0              | 790       | 747              | 0.0              | 920       | 24               | 0.0              |
| 405       | 201              | 0.0              | 535       | 44137            | 55.0             | 665       | 37602            | 0.0              | 795       | 639              | 0.0              | 925       | 22               | 0.0              |
| 410       | 457              | 0.0              | 540       | 46032            | 50.9             | 670       | 32798            | 0.0              | 800       | 547              | 0.0              | 930       | 22               | 0.0              |
| 415       | 925              | 0.1              | 545       | 48553            | 46.6             | 675       | 28558            | 0.0              | 805       | 473              | 0.0              | 935       | 17               | 0.0              |
| 420       | 1816             | 0.3              | 550       | 51408            | 42.0             | 680       | 24782            | 0.0              | 810       | 401              | 0.0              | 940       | 13               | 0.0              |
| 425       | 3217             | 0.8              | 555       | 54711            | 37.4             | 685       | 21386            | 0.0              | 815       | 351              | 0.0              | 945       | 6                | 0.0              |
| 430       | 5520             | 1.9              | 560       | 58847            | 32.9             | 690       | 18413            | 0.0              | 820       | 307              | 0.0              | 950       | 10               | 0.0              |
| 435       | 9225             | 4.1              | 565       | 63386            | 28.4             | 695       | 15721            | 0.0              | 825       | 261              | 0.0              | 955       | 11               | 0.0              |
| 440       | 15522            | 8.7              | 570       | 68196            | 24.1             | 700       | 13432            | 0.0              | 830       | 228              | 0.0              | 960       | 8                | 0.0              |
| 445       | 27642            | 18.5             | 575       | 73613            | 20.0             | 705       | 11513            | 0.0              | 835       | 193              | 0.0              | 965       | 12               | 0.0              |
| 450       | 36602            | 28.3             | 580       | 79207            | 16.3             | 710       | 9780             | 0.0              | 840       | 174              | 0.0              | 970       | 3                | 0.0              |
| 455       | 28292            | 24.7             | 585       | 84248            | 12.9             | 715       | 8356             | 0.0              | 845       | 151              | 0.0              | 975       | 8                | 0.0              |
| 460       | 21166            | 20.4             | 590       | 88397            | 9.8              | 720       | 7161             | 0.0              | 850       | 123              | 0.0              | 980       | 2                | 0.0              |
| 465       | 19092            | 20.1             | 595       | 91428            | 7.3              | 725       | 6067             | 0.0              | 855       | 106              | 0.0              | 985       | 13               | 0.0              |
| 470       | 14951            | 17.2             | 600       | 93452            | 5.3              | 730       | 5164             | 0.0              | 860       | 95               | 0.0              | 990       | 16               | 0.0              |
| 475       | 12606            | 15.7             | 605       | 93959            | 3.7              | 735       | 4393             | 0.0              | 865       | 82               | 0.0              | 995       | 20               | 0.0              |
| 480       | 13323            | 18.0             | 610       | 93079            | 2.5              | 740       | 3694             | 0.0              | 870       | 77               | 0.0              | 1000      | 0                | 0.0              |
| 485       | 15164            | 21.9             | 615       | 90707            | 1.7              | 745       | 3157             | 0.0              | 875       | 65               | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2407-157-9





TM-30-18

### Summary

$R_f = 84.7$   
 $R_g = 94.6$   
 $CIE R_a = 80.9$   
 $R_g = -1.5$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 |            |







Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)